

Compact cylinders CDC, ISO 21287, Clean Design

FESTO



Compact cylinders CDC, ISO 21287, Clean Design

Key features

FESTO

Design

- With the CDC (Clean Design Compact) cylinder series, the ADN modular system has been expanded to include an easy to clean compact cylinder variant
- It is based on ISO 21287 for compact cylinders and, like the compact cylinder ADN, features short strokes and a compact design
- The compact cylinder CDC is designed as a double-acting pneumatic cylinder with piston, piston rod and profile barrel

Easy to clean

- Clean Design means smooth surfaces without slots and edges, which means fewer places where dirt can collect
- For hygiene reasons, the threads on the cylinder caps should be sealed with suitable blanking screws
- Resistant to conventional cleaning agents
- Increased corrosion protection

Easy to assemble

- Comprehensive range of mounting accessories for just about every type of installation
- Contactless position sensing via proximity sensors

Versatile

- The variants can be configured according to individual needs thanks to the modular product system
- Greater flexibility thanks to the wide range of variants

Variants

CDC-...


- Ø 20, 25 mm
- Without position sensing

CDC-...-A...-R

- Ø 32 ... 80 mm
- With position sensing integrated in the end positions




CDC-...-A-R

- Ø 32 ... 80 mm
- With sensor mounting rail for external position sensing



Note



A combination of integrated and external position sensing is possible.



Mounting options


With through screws

Direct mounting



Size


Space savings of up to 50% compared with cylinders to standard ISO 15552



Compact cylinders CDC, ISO 21287, Clean Design

Peripherals overview

FESTO



Mounting attachments and accessories		
	Description	→ Page/Internet
1	Foot mounting HNA-...-R3	For bearing and end cap 16
2	Flange mounting CRFNG	For bearing or end cap 17
3	Trunnion flange CRZNG	For bearing or end cap in combination with trunnion supports CRLNZG 18
4	Trunnion supports CRLNZG	For trunnion flange CRZNG 18
5	Swivel flange SNCB- ... -R3	For end cap 19
6	Clevis foot mounting CRLNG	For swivel flange SNCB- ... -R3 19
7	Swivel flange SNCL- ... -R3	For end cap 20
8	Clevis foot mounting CRLBN	For swivel flange SNCL- ... -R3 20
9	Rod clevis CRSG	Permits a swivelling movement of the cylinder in one plane 23
10	Rod eye CRSGS	With spherical bearing 23
11	Proximity sensor SMT-C1	For attachment to the sensor mounting rail 21
12	Cable with socket SIM-K- ... -CDN	For electrical signal transmission and power supply 21
13	One-way flow control valve CRGRLA	For regulating speed 23
14	Push-in fittings NPQH/NPQH-L/CRQS/CRQSL	For connecting compressed air tubing with standard external diameters 22
15	Blanking screws DAMD-P- ...	For covering unused mounting threads 23

Compact cylinders CDC, ISO 21287, Clean Design

FESTO

Type codes


		CDC	-	32	-	50	-	A	-	P	-	AIB	-	SME	-	R	-	K2
Type																		
Double-acting																		
CDC	Compact cylinder, Clean Design																	
Piston Ø [mm]																		
Stroke [mm]																		
Piston rod thread																		
A	Male thread																	
I	Female thread																	
Cushioning																		
P	Flexible cushioning rings/pads at both ends																	
Position sensing																		
A	For proximity sensor																	
AIB	At both ends, integrated																	
AIV	Front, integrated																	
AIH	Rear, integrated																	
Proximity sensor																		
SME	Contacting (magnetic reed)																	
Sensor mounting rail																		
R	For external position sensing (only with Ø 32 ... 80 mm)																	
Variant																		
S2	Through piston rod																	
K2	Extended male piston rod thread																	
K5	Piston rod with special thread																	
K8	Extended piston rod																	
S6	Heat-resistant seals for temperatures up to 120 °C																	

Compact cylinders CDC, ISO 21287, Clean Design

FESTO

Technical data

Function



- Ø - Diameter
20 ... 80 mm

- I - Stroke length
1 ... 500 mm

- T - www.festo.com

Variants




S2




K2



K5



K8



S6



CDC-...-A-P



CDC-...-A-P-R

General technical data							
Piston Ø	20	25	32	40	50	63	80
Pneumatic connection	M5	M5	G1/8	G1/8	G1/8	G1/8	G1/8
Piston rod thread	M8	M8	M10x1.25	M10x1.25	M12x1.25	M12x1.25	M16x1.5
Design	Piston						
	Piston rod						
	Cylinder barrel						
Cushioning	Flexible cushioning rings/pads at both ends						
Position sensing	A	For proximity sensor					
	AI B	At both ends, built-in					
	AI V	Front, built-in					
	AI H	Rear, built-in					
Type of mounting	Via through-hole						
	With female thread						
	Via accessories						
Mounting position	Any						

Operating and environmental conditions							
Piston Ø	20	25	32	40	50	63	80
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [7:4:4]					
Note on operating/pilot medium		Operation with lubricated medium possible (in which case lubricated operation will always be required)					
Operating pressure	[bar]	0.8 ... 10		0.6 ... 10			
	S2 [bar]	1.2 ... 10		1 ... 10			0.8 ... 10
	S6 [bar]	1 ... 10	0.6 ... 10				
Ambient temperature ¹⁾	[°C]	-20 ... +80					
	S6 [°C]	0 ... +120					
Food safe ²⁾		See supplementary material information					
Corrosion resistance class CRC ³⁾		3					

1) Note operating range of proximity sensors

2) Additional information www.festo.com/sp → Certificates.

3) Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional requirements for the surface and which are in direct contact with a normal industrial environment.

Compact cylinders CDC, ISO 21287, Clean Design

Technical data

FESTO

Forces [N] and impact energy [J]							
Piston Ø	20	25	32	40	50	63	80
Theoretical force at 6 bar, advancing	188	295	483	754	1178	1870	3016
S2	141	247	415	686	1057	1750	2827
Theoretical force at 6 bar, retracting	141	247	415	686	1057	1750	2827
Max. impact energy at the end positions	0.2	0.3	0.4	0.7	1	1.3	1.8
S6	0.1	0.15	0.2	0.35	0.5	0.65	0.9

Permissible impact velocity:

$$v_{perm.} = \sqrt{\frac{2 \times E_{perm.}}{m_{dead} + m_{load}}}$$

$v_{perm.}$ Permissible impact velocity
 $E_{perm.}$ Max. impact energy
 m_{dead} Moving load (drive)
 m_{load} Moving work load


Maximum permissible load:

$$m_{load} = \frac{2 \times E_{perm.}}{v^2} - m_{dead}$$

Note

These specifications represent the maximum values which can be reached. Note the maximum permitted impact energy.

Max. lateral force F_q as a function of projection x



- Ø 20
- - - - - Ø 25
- · - · - Ø 32/40
- Ø 50/63
- - - - - Ø 80

Compact cylinders CDC, ISO 21287, Clean Design


Technical data

FESTO

Weights [g]							
Piston Ø	20	25	32	40	50	63	80
Basic version							
Product weight with 0 mm stroke	133	170	277	377	567	790	1475
Additional weight per 10 mm stroke	20	23	31	35	52	59	84
Moving load with 0 mm stroke	24	33	53	82	128	177	367
Additional load per 10 mm stroke	6	6	9	9	16	16	25
S2 – Through piston rod							
Product weight with 0 mm stroke	150	183	296	386	600	827	1507
Additional weight per 10 mm stroke	26	29	40	44	67	74	109
Moving load with 0 mm stroke	34	40	64	81	144	195	367
Additional load per 10 mm stroke	12	12	18	18	32	32	49

Materials

Sectional view



Compact cylinder	Basic version	S6
1 End cap	Anodised aluminium	
2 Cylinder barrel	Anodised aluminium	
3 Piston rod	High-alloy steel	
4 Flange screws	Corrosion-resistant steel	
– Seals	TPE-U (PUR) media sealing (modified for resistance to hydrolysis and cleaning agents)	FPM
– Note on materials	Free of copper and PTFE	
	–	Contains PWIS (paint-wetting impairment substances)

Compact cylinders CDC, ISO 21287, Clean Design


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com


Basic version



1 Socket head screw with female thread for mounting attachments


+ = plus stroke length

With position sensing integrated in the end positions



1 Miniature plug connector, 3-pin, with integrated proximity sensor (order code SME) suitable for cable with socket SIM-K...-CDN

Projection of blanking screw



Compact cylinders CDC, ISO 21287, Clean Design

Technical data

FESTO

Ø	BG	D5	E	EE	G	J1	J3	L2	L3	L4
[mm]		F9				±0.1	±0.1			
20	19.5	9	36.8	M5	12	–	–	37	4.4	5
25			41.8				39			
32	26		49.8	G1/8	15	5.8	7	44		
40			57.8			8	8	45		
50	27	12	69.7			8.5		49		
63			81.3			12				
80			–		100.4			16.5	15	54

Ø	L5	L6	L7	MM Ø h8	PL	RT	TG	ZJ	≈G1
[mm]		±2			±0.1			+1	h13
20	–	–	7	10	6	M5	22	42.7	9
25							26	44.7	
32	10	35	8.7	12	8.2	M6	32.5	50.2	10
40		39					38	51.2	
50		45	10.3	16		M8	46.5	53.2	13
63		50					56.5	57.2	
80	11.5	60	11.9	20		M10	72	63	17



Note

The following maximum stroke lengths apply in combination with a swivel mounting on the end cap:

Ø [mm]	20	25	32	40	50	63	80
Max. stroke length	50		100				150

Compact cylinders CDC, ISO 21287, Clean Design


Technical data

FESTO


Dimensions – Variants

Download CAD data → www.festo.com


Basic version



S2 – Through piston rod



K2 – Extended male piston rod thread



Ø	A1	AF	AM	KF	KK	T4	WH	ZJ	ZM
[mm]		min.	−0.5				+1	+1	
20	1 ... 20	14	16	M6	M8	2.6	5.7	42.7	49.8
25								44.7	51.8
32		16	19	M8	M10x1.25	3.3	6.2	50.2	57.8
40								51.2	58.9
50		20	22	M10	M12x1.25	4.7	8.2	53.2	63.1
63								57.2	66.9
80	1 ... 30							28	M12

Compact cylinders CDC, ISO 21287, Clean Design


Technical data

FESTO


Dimensions – Variants

Download CAD data → www.festo.com

K5 – Special thread on piston rod



K8 – Extended piston rod




Ø	AF	A2	AM	K1	K2	T4	WH	ZJ
[mm]	min.		-0.5				+1	+1
20	14	1 ... 300	16	M10, M10x1.25	M5	2.6	5.7	42.7
25								44.7
32	16	1 ... 400	19	M10, M12	M6	3.3	6.2	50.2
40								51.2
50	20	1 ... 500	22	M12, M12	M8	4.7	8.2	53.2
63								57.2
80								63

Compact cylinders CDC, ISO 21287, Clean Design

Technical data

FESTO

Proximity sensor,
magnetic reed
(order code SME)



Note

The proximity sensor can only be ordered in conjunction with the order code AIB, AIV and AIH (integrated position sensing) in the modular product system.



Technical data		
General information		
Design	Integrated	
Based on standard	EN 60947-5-2	
CE mark (see declaration of conformity)	To EU EMC Directive	
Note on materials	Free of copper and PTFE	
Input signal/measuring element		
Measuring principle	Magnetic reed	
Ambient temperature	[°C]	−20 ... +60
Switching output		
Switching output	Contacting, bipolar	
Switching element function	N/O contact	
Reproducibility of switching point	[mm]	±0.1
Hysteresis	[mm]	1 ... 4, depending on the cylinder used
Switch-on time	[ms]	0.5
Switch-off time	[ms]	0.5
Max. output current	[mA]	500
Max. switching capacity AC	[W]	10 VA
Max. switching capacity DC	[W]	10 W
Inductive protective circuit	Adapted to MZ coil with LED	
Residual current	[mA]	0
Output, further data		
Protection against short circuit	No	
Protection against overloading	No	
Electronic components		
Operating voltage range	[V AC]	12 ... 30
	[V DC]	12 ... 30
Protection against polarity reversal	No	
Electromechanical components		
Electrical connection	Plug, M8x1, 3-pin	
Connection direction	Lateral	
Information on crimp connector materials	Gold-plated brass	

Compact cylinders CDC, ISO 21287, Clean Design

Technical data

FESTO

Technical data		
Mechanical components		
Tightening torque	[Nm]	0.3
Mounting position		Any
Product weight	[g]	2.7
Information on housing materials		Polyamide, epoxy resin, nickel-plated brass
Display/operation		
Switching status display		Yellow LED
Immissions/emissions		
Degree of protection		IP65, IP67 to EN 60529
		IP69K, to DIN 40050 Part 9
		Only in conjunction with plug socket with cable SIM-K-...-CDN
Corrosion resistance class CRC ¹⁾		3

1) Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional requirements for the surface and which are in direct contact with a normal industrial environment.

Compact cylinders CDC, ISO 21287, Clean Design

Ordering data – Modular products

FESTO

Ordering table											
Size	20	25	32	40	50	63	80	Condi- tions	Code	Enter code	
[M]	Module No.	543305	543306	543307	543308	543309	543310	543311			
	Function	Standard cylinder, double-acting, based on ISO 21287 (Clean Design)								CDC	CDC
	Piston Ø [mm]	20	25	32	40	50	63	80	- ...		
	Stroke [mm]	1 ... 300		1 ... 400				1 ... 500	- ...		
	Piston rod thread	Male thread								-A	
		Female thread							1	-I	
	Cushioning	Flexible cushioning rings/pads at both ends								-P	-P
	Position sensing	Without position sensing		–	–	–	–	–			
		–	–	For proximity sensor						-A	
		–	–	At both ends, integrated					2	-AIB	
–		–	Front, integrated					2	-AIV		
–		–	Rear, integrated					2	-AIH		
↓											

1 I Not with extended male thread K2

2 AIB, AIV, AIH Only with proximity sensor SME, SMT

- M** Mandatory data
- O** Options

Transfer order code

CDC - - - - **P**

Compact cylinders CDC, ISO 21287, Clean Design



Ordering data – Modular products

Ordering table										
Size	20	25	32	40	50	63	80	Condi- tions	Code	Enter code
[0]	Proximity sensor	—	—	SME (contacting)				[3]	-SME	
	Sensor mounting rail	—	—	Sensor mounting rail for external position sensing				[4]	-R	
	Type of piston rod	Through piston rod							-S2	
	Male thread extended [mm]	Extended male piston rod thread							-...K2	
	Piston rod with special thread	Male thread	M10x1.25 M10	M10 M12	M12 M16	M16 M20				
		Female thread	M5	M6	M8	M10				
	Piston rod extended [mm]	Extended piston rod							-...K8	
		1 ... 20	1 ... 30							
Temperature resistance	Heat-resistant seals for temperatures up to 120 °C						[6]	-S6		

- ☐ **SME** Only with position sensing AIB, AIV, AIH
Minimum stroke 15 mm
- ☐ **R** Must be selected with size 32, 40, 50, 63, 80

- ☐ **K8** The sum of the stroke length and piston rod extension must not exceed the maximum permissible stroke length
- ☐ **S6** Not with position sensing AIB, AIV, AIH

- ☐ **M** Mandatory data
- ☐ **O** Options

Transfer order code

– – – – – – – –

Compact cylinders CDC, ISO 21287, Clean Design

Accessories

FESTO


Foot mounting HNA-...-R3

Material:

Steel with protective coating

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data							
For Ø	AB Ø	AH	A0	AT	AU	SA	TR
[mm]	H14	JS14		±0.5	±0.2		±0.2
20	7	27	6.25	4	16	69	22
25		29				71	26
32		33.5				76	32
40	10	38	9	5	18	81	36
50		45	8		21	87	45
63		50				91	50
80	12	63	10.5	6	26	106	63

For Ø	US	XA	CRC ¹⁾	Weight	Part No.	Type
[mm]	−0.5			[g]		
20	34.5	59	3	84	537254	HNA-20-R3
25	38.5	61	3	90	537255	HNA-25-R3
32	46	66	3	123	537256	HNA-32-R3
40	54	69	3	157	537257	HNA-40-R3
50	64	74	3	278	537258	HNA-50-R3
63	75	78	3	328	537259	HNA-63-R3
80	63	89	3	634	537260	HNA-80-R3

1) Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional requirements for the surface and which are in direct contact with a normal industrial environment.

 Note
Screws with special lengths are required to fit the sizes Ø 80 mm
→ page 23

Compact cylinders CDC, ISO 21287, Clean Design

Accessories



FESTO

Flange mounting CRFNG

Material:

High-alloy steel

Free of copper and PTFE



Dimensions and ordering data						
For Ø	E	FB Ø H13	MF	R	TF	UF
[mm]						
32	45	7	10	32	64	80
40	54	9	10	36	72	90
50	65	9	12	45	90	110
63	75	9	12	50	100	120
80	93	12	16	63	126	150

Dimensions and ordering data					
For Ø	ZF	CRC ¹⁾	Weight	Part No.	Type
[mm]			[g]		
32	54	4	220	161846	CRFNG-32
40	55	4	291	161847	CRFNG-40
50	57	4	526	161848	CRFNG-50
63	61	4	680	161849	CRFNG-63
80	70	4	1508	161850	CRFNG-80

- 1) Corrosion resistance class CRC 4 to Festo standard FN 940070
Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, for instance in the chemical or food industries. These applications may need to be supported by special tests (→ also FN 940082) using appropriate media.

 Note
Screws with special lengths are required to fit the sizes Ø 80 mm
→ page 23

Compact cylinders CDC, ISO 21287, Clean Design

Accessories

FESTO

Trunnion flange CRZNG


Material:

CRZNG: Electrolytically polished

special steel casting

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data												
For Ø	C2	C3	TD Ø e9	TK	TL	TM	US	XH	XL	CRC ¹⁾	Weight	Part No. Type
[mm]												
32	71	86	12	16	12	50	45	2	52	4	150	161852 CRZNG-32
40	87	105	16	20	16	63	54	4	55	4	285	161853 CRZNG-40
50	99	117	16	24	16	75	64	4	57	4	473	161854 CRZNG-50
63	116	136	20	24	20	90	75	4	61	4	687	161855 CRZNG-63
80	136	156	20	28	20	110	93	5	81	4	1296	161856 CRZNG-80

1) Corrosion resistance class CRC 4 to Festo standard FN 940070

Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, for instance in the chemical or food industries. These applications may need to be supported by special tests (→ also FN 940082) using appropriate media.

- - Note
Screws with special lengths are required to fit the sizes Ø 80 mm
→ page 23



Trunnion supports CRLNZG

Material:

High-alloy steel

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data												
For Ø	CR Ø D11	FK Ø ±0.1	FN	FS	H1	HB Ø H13	NH	TH ±0.2	UL	CRC ¹⁾	Weight [g]	Part No. Type
[mm]												
32	12	15	30	10.5	15	6.6	18	32	46	4	205	161874 CRLNZG-32
40, 50	16	18	36	12	18	9	21	36	55	4	323	161875 CRLNZG-40/50
63, 80	20	20	40	13	20	11	23	42	65	4	435	161876 CRLNZG-63/80

1) Corrosion resistance class CRC 4 to Festo standard FN 940070

Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, for instance in the chemical or food industries. These applications may need to be supported by special tests (→ also FN 940082) using appropriate media.

Compact cylinders CDC, ISO 21287, Clean Design

FESTO

Accessories

Swivel flange SNCB-...-R3


Material:

Die-cast aluminium with protective

coating, high corrosion protection

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data											
For Ø	CB	EK Ø	FL	L	MR	UB	XC	CRC ¹⁾	Weight	Part No.	Type
[mm]	H14	e8	±0.2			h14			[g]		
32	26	10	22	13	8.5	45	72	3	100	176944	SNCB-32-R3
40	28	12	25	16	12	52	76	3	151	176945	SNCB-40-R3
50	32	12	27	16	12	60	80	3	228	176946	SNCB-50-R3
63	40	16	32	21	16	70	89	3	371	176947	SNCB-63-R3
80	50	16	36	22	16	90	99	3	632	176948	SNCB-80-R3

1) Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional requirements for the surface and which are in direct contact with a normal industrial environment.


Note
Screws with special lengths are required to fit the sizes Ø 80 mm
→ page 23

Clevis foot CRLNG

Material:

High-alloy steel

Free of copper and PTFE



Dimensions and ordering data													
For Ø	BR	BT	CK Ø	EM	GL	HB Ø	PH	RA	TE	UL	UR	CRC ¹⁾	Weight
[mm]			D11	-0.4		H13							[g]
32	10	8	10	25.8	21	6.6	32	18	38	51	31	4	120
40	11	10	12	27.8	24	6.6	36	22	41	54	35	4	161
50	12	12	12	31.8	33	9	45	30	50	65	45	4	281
63	15	12	16	39.8	37	9	50	35	52	67	50	4	370
80	15	14	16	49.8	47	11	63	40	66	86	60	4	562

1) Corrosion resistance class CRC 4 to Festo standard FN 940070

Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, for instance in the chemical or food industries. These applications may need to be supported by special tests (→ also FN 940082) using appropriate media.

Accessories



Swivel flange SNCL-...-R3


Material:

SNCL-...-R3: Die-cast aluminium with

protective coating

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data

For Ø	CD Ø	EW	FL	L	MR	XC	CRC ¹⁾	Weight	Part No.	Type
[mm]	H9	h12	±0.2					[g]		
20	8	16	20	14	8	63	3	38	537796	SNCL-20-R3
25						65	3	41	537797	SNCL-25-R3


- 1) Corrosion resistance class CRC 3 to Festo standard FN 940070
High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional requirements for the surface and which are in direct contact with a normal industrial environment.

Clevis foot CRLBN, stainless steel

Material:

High-alloy steel

Free of copper and PTFE



Dimensions and ordering data


For Ø	CM	EK Ø	FL	GL	HB	LE	MR	RG	UX	CRC ¹⁾	Weight	Part No.	Type
[mm]											[g]		
20/25	16.1	8	30 +0.4/-0.2	16	6.6	26	10	20	32	4	82	161863	CRLBN-20/25

- 1) Corrosion resistance class CRC 4 to Festo standard FN 940070
Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, for instance in the chemical or food industries. These applications may need to be supported by special tests (→ also FN 940082) using appropriate media.

Compact cylinders CDC, ISO 21287, Clean Design

Accessories

FESTO

Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switching output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Is mounted on the mounting rail	PNP	Cable, 3-wire	5.0	571339	SMT-C1-PS-24V-K-5,0-OE
			Plug M8x1, 3-pin	0.3	571342	SMT-C1-PS-24V-K-0,3-M8D
			Plug M12x1, 3-pin	0.3	571341	SMT-C1-PS-24V-K-0,3-M12

Ordering data – Connecting cables for SMT-C1-...				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541363	NEBU-M12G5-K-2.5-LE3
			5	541364	NEBU-M12G5-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541367	NEBU-M12W5-K-2.5-LE3
			5	541370	NEBU-M12W5-K-5-LE3

Ordering data – Connecting cables for integrated proximity sensor				Technical data → Internet: sim	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Angled socket, clip, 3-pin	Cable, open end, 3-wire	5	164254	SIM-K-WD-5-PU

Compact cylinders CDC, ISO 21287, Clean Design

Accessories

FESTO

Ordering data – Push-in fittings						Technical data → Internet: qs	
	Connection		Material	Weight [g]	Part No.	Type	PU ³⁾
	Thread	Tubing O.D.					
With external hex							
	M5	4	Brass, nickel-plated and chrome-plated	–	578334	NPQH-D-M5-Q4-P10	10
		6		–	578335	NPQH-D-M5-Q6-P10	
	G1/8	4		6.1	578338	NPQH-D-G18-Q4-P10	
		6		9	578339	NPQH-D-G18-Q6-P10	
		8		11.4	578340	NPQH-D-G18-Q8-P10	
	M5	4	Stainless steel	6	162860	CRQS-M5-4 ¹⁾	1
		6		8.4	162861	CRQS-M5-6 ¹⁾	
	R1/8	6		9.9	162862	CRQS-1/8-6 ²⁾	
		8		12	162863	CRQS-1/8-8 ²⁾	
With internal hex							
	M5	4	Brass, nickel-plated and chrome-plated	4.6	578370	NPQH-DK-M5-Q4-P10	10
		6		8.6	578371	NPQH-DK-M5-Q6-P10	
	G1/8	4		–	578374	NPQH-DK-G18-Q4-P10	
		6		–	578375	NPQH-DK-G18-Q6-P10	
		8		–	578376	NPQH-DK-G18-Q8-P10	

- 1) With sealing ring
 2) With PTFE coating
 3) Packaging unit quantity

Ordering data – Push-in L-fittings					Technical data ➔ Internet: qs		
	Connection		Material	Weight [g]	Part No.	Type	PU ³⁾
	Thread	Tubing O.D.					
With external hex							
	M5	4	Brass, nickel-plated and chrome-plated	8.8	578276	NPQH-L-M5-Q4-P10	10
		6		11.9	578277	NPQH-L-M5-Q6-P10	
	G1/8	4		15.7	578280	NPQH-L-G18-Q4-P10	
		6		18.5	578281	NPQH-L-G18-Q6-P10	
		8		22	578282	NPQH-L-G18-Q8-P10	
	M5	4	Stainless steel	12	162870	CRQSL-M5-4 ¹⁾	1
		6		18	162871	CRQSL-M5-6 ¹⁾	
	R1/8	6		19	162872	CRQSL-1/8-6 ²⁾	
		8		26	162873	CRQSL-1/8-8 ²⁾	

- 1) With sealing ring
 2) With PTFE coating
 3) Packaging unit quantity

Compact cylinders CDC, ISO 21287, Clean Design

Accessories

FESTO

Ordering data – Plastic tubing, standard O.D.			Technical data → Internet: tubing
		Type	
	Good resistance to chemicals and hydrolysis		PLN
	Pneumatic tubing with resistance to high temperatures and chemicals		PFAN
	Approved for use in the food industry and hydrolysis-resistant		PUN-H

Ordering data – One-way flow control valves					Technical data → Internet: crgla	
	Connection		Material	Weight [g]	Part No.	Type
	Thread	For push-in fitting				
	M5	CRQS/CRQSL/CRQST,	Electrolytically polished special steel casting	10,2	161403	CRGRLA-M5-B
	G1/8	QS		37,8	161404	CRGRLA-1/8-B

Ordering data – Blanking screws, corrosion-resistant							
	For Ø	Material	CRC ¹⁾	Weight [g]	Part No.	Type	PU ³⁾
	20, 25	High-alloy steel	3	5.5	543714	DAMD-P-M5-10-R1²⁾	4
	32, 40			9	543715	DAMD-P-M6-12-R1²⁾	
	50, 63			17.5	543716	DAMD-P-M8-16-R1²⁾	
	80			30	543717	DAMD-P-M10-16-R1²⁾	

1) Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional requirements for the surface and which are in direct contact with a normal industrial environment.

2) With sealing ring

3) Packaging unit quantity

Ordering data – Corrosion and acid-resistant piston rod attachments				Technical data → Internet: crsg			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Rod eye CRSGS				Rod clevis CRSG			
	20, 25	195581	CRSGS-M8		20, 25	13568	CRSG-M8
	32, 40	195582	CRSGS-M10x1,25		32, 40	13569	CRSG-M10x1,25
	50, 63	195583	CRSGS-M12x1,25		50, 63	13570	CRSG-M12x1,25
	80	195584	CRSGS-M16x1,5		80	13571	CRSG-M16x1,5

Ordering data – Screws					Technical data → Internet: crsg	
	For Ø	For accessories	Part No.	Type		
	80	HNA-R3, SNCB-R3	372622	DIN912-M10X30-A4-70	1	
		CRFNG	8028230	DIN912-M10X30-A4-70		
		CRZNG	744814	DIN912-M10X40-A4-70		

1) Packaging unit quantity