Valve terminal CPV, Compact Performance

FESTO











Innovative

- Cubic design for exceptional performance and low weight
- Low installation and bus connection costs
- Decentralised machines and system structures, for example
 - in handling technology
 - in conveyor technology
 - in the packaging industry
 - in sorting systems
 - in upstream machine functions
- Integrated diagnostics, condition monitoring (Fieldbus Direct)
- With Fieldbus Direct, string extension from 8 ... 32 inputs and 8 ... 32 outputs is possible without any problems (depending on version).

Versatile

- Flexible and cost-effective connection of two to eight valve slices
- Highly flexible thanks to:
 - various pneumatic functions (valve variants)
 - different pressure ranges
 - vacuum switch
 - integrated vacuum generation
- Separator plates for creating pressure zones
- Valves with integrated separation of ducts 1 and 11
- Blanking plates for later extensions

Reliable

- LED indicators
- Manual overrides for valves
- · Protection class to IP65
- Protection class IP65 also in conjunction with pneumatic multiple connector plate for control cabinet installation
- CE marking
- Certification (see technical data)

Easy to install

- Ready-to-install and tested unit
- Reduced selection, ordering, installation and commissioning costs
- Secure mounting on a wall or H-rail
- Pneumatic multiple connector plate

 quick mounting with the tubing in place
- Optimised assembly for control cabinets

CPV - The benefits at a glance

The valve assembly CPV has a unique design. It allows a flexible mix of pneumatic performance, electrical connection technologies and a variety of installation types. In particular, the pneumatic multiple connector plate enables especially space-saving installation in control cabinets. The valve terminal can often be installed directly in the previously unused wall area of the control cabinet. There is no need to connect up the valves inside the cabinet. All tubes can be connected on the outside. Instead of individual drilled holes, the pneumatic multiple connector plate needs just one rectangular through-hole.

The generously sized flow ducts and powerful flat plate silencers ensure high flow rates.

All valves are provided as valve slices. They have a compact and flow-optimised design. With two functions per valve slice (e.g. 2x 3/2-way valves), double the component density can be achieved. This saves space and reduces costs.

The cubic design permits exceptional performance with a comparatively low weight. These advantages become clear when the valve terminal is moved along on a drive.

Despite it being compact, it is also very sturdy. The connecting threads and mounting attachments are metal.

The manual override for the valves can be adapted for different operating situations. If, for example, a detenting manual override is required for set-up, this can later be easily changed again so that inadvertent actuation during operation is prevented.

The clear, large labelling systems also contribute to safe operation.

One particular advantage is the large number of electrical connection technologies. All types of valve control are possible, from individual valve connection to a flexibly expandable bus system. The integration of electric input and output modules permits low-cost solutions in a range of installation concepts.

The design principle

Each side of the cubic design has its own specific function. Thus, for example, the electrical connection is mounted on the top.


An optional inscription label holder can be placed on the front of the valve terminal

The different possible combinations allow the best possible solution for the task in hand.

- Pneumatic supply connections on the left, right or underneath
- Pneumatic working ports and function blocks (vertical stacking) underneath
- Manual operation/identification from the front
- · Electrical connection surface on top

 Mounting surface on the back, or at the front via pneumatic multiple connector plate

Main features



- [1] Inscription labels
- [2] Reduced downtimes: on-site LED diagnostics
- [3] Safe operation: manual override, non-detenting, detenting or blocked
- [4] Comprehensive range of valve functions, pressure zone formation, blanking plates
- [5] Width:
 - 10 mm,
 - 14 mm,18 mm
- [6] Robust metal thread or pre-assembled QS connectors
- 7] Quick mounting:
 - Directly using screws
 - On an H-rail
 - Via the pneumatic multiple connector plate
- [8] Operating voltage connection
- 9] Simple electrical connections:
 - Individual connection/ET200X/ ET200pro
 - Multi-pin plug
 - AS-Interface
 - I-Port interface/IO-Link®
 - Installation system CP/CPI
 - Fieldbus Direct

Equipment options

Valve functions

- 5/2-way valve, single solenoid
- 5/2-way valve (with duct separation 1, 11), single solenoid
- 5/2-way valve, single solenoid, fast-switching
- 5/2-way valve, double solenoid
- 5/2-way valve (with duct separation 1, 11), double solenoid
- 2x 3/2-way valve, normally closed
- 2x 3/2-way valve (with duct separation 1, 11), normally closed
- 2x 3/2-way valve, normally open
- 2x 3/2-way valve (with duct separation 1, 11), normally open

- 2x 3/2-way valve, 1x normally open, 1x closed
- 2x 3/2-way valve (with duct separation 1, 11), 1x normally open, 1x closed
- 2x 3/2-way valve, normally closed, integrated back pressure protection
- 5/3-way valve, mid-position closed
- 2x 2/2-way valve, normally closed
- 2x 2/2-way valve (with duct separation 1, 11), normally closed
- 2x 2/2-way valve, 1x normally open, 1x closed

- 2x 2/2-way valve (with duct separation 1, 11), 1x normally open, 1x closed
- · Vacuum generator
- Vacuum generator and 2/2-way valve with ejector pulse

Special features

Individual connection

• 2 ... 8 valve positions, max. 16 solenoid coils

AS-Interface

- 2, 4 or 8 valve positions, max. 8 solenoid coils
- 4 or 8 inputs for 4 or 8 valve positions

Multi-pin plug connection

 4, 6 or 8 valve positions, max. 16 solenoid coils

I-Port interface/IO-Link®

- 8 valve positions, max. 16 solenoid coils
- Direct connection to the CTEU/CTEL installation system from Festo (I-Port)
- Connection to an IO-Link® master

Installation system CP/CPI

- 4, 6 or 8 valve positions, max. 16 solenoid coils
- Additional valve terminals and I/O modules having CP/CPI function can be connected via CP/CPI string extension

Fieldbus Direct

- 8 valve positions, max. 16 solenoid coils
- Additional valve terminals and I/O modules having CP/CPI functions can be connected via CP/CPI string extension

System analysis with explosion protection

Valve terminals CPV

Valve terminals CPV can be used in explosion protection. Please observe permitted versions, accessories as well as the operating conditions. Corresponding information can be found in this document, marked with (x) or NEC 500.

Additional user documentation with information about function, application, commissioning, operating conditions, maintenance and care can be found on the product pages for the valve terminal under Support/Download.

ATEX II 3G

The correctness of particular features is indicated by the product configurator. If the ATEX feature (code: EX1E) is selected with a valid configuration, valve terminals will have ATEX identification to ATEX II 3G on the end plate. Accessories that have been assessed can be found in the chapter on ATEX accessories.

NEC 500, Class I, Div.2

accessories.

If a valid configuration is selected, valve terminals with electrical connection (code MP, IC) are identified with "Class I, Division 2, Groups A, B, C and D" on the end plate.

Accessories that have been assessed can be found in the chapter NEC 500

Tubing connections

Please use push-in fittings with G thread to ensure an electrically conductive connection. Suitable fittings can be found in the chapters on ATEX accessories or NEC 500 accessories.

Mechanical/pneumatic installation

When used in explosion protection areas, valve terminals CPV should be installed in suitable control cabinets or protective housing.

Please observe the additional user

Please observe the additional user documentation for potentially explosive operating conditions.

Installing a valve terminal CPV with a pneumatic multiple connector plate



Valve terminals CPV can be installed directly in the housing wall via a suitable opening using a pneumatic multiple connector plate (code GQC, GQD, GQE). This ensures tubing connections are on the outside of the control cabinet.


Wall or H-rail mounting of a valve terminal CPV inside a control cabinet



Valve terminals CPV can be positioned inside the control cabinet using wall or H-rail mounting.

Electrical connections

Individual connection (valve manifold assembly)



Connection is independent of the control technology and flexible using pre-assembled cables. This ensures that the connection is reverse polarity protected. The connector plug includes an LED for switching status indication and circuitry to protect against overvoltage. It also features a built-in cur-

rent reduction circuit. 2 to 16 solenoid coils (divided between two to eight valve slices, including odd numbers) can be selected with individual connection.

An intrinsically safe version completes the range.

More information

→ Internet: cpv10-ex-vi



For valve terminals CPV10, CPV14 or CPV18, use the configuration value "EX1E" for the "EU certification" feature and "IC" for the feature "Electrical connection".

NEC 500

For valve terminals CPV10, CPV14 or CPV18, use the configuration value "IC" for the feature "Electrical connection".



Note


For CPV10 or CPV14, use the following connecting cables:

- 8047676
 NEBV-Z3WA2L-R-E-2.5-N-LE2-S1
- 8047677 NEBV-Z3WA2L-R-E-5-N-LE2-S1
- 8047675 NEBV-Z3WA2L-R-E-10-N-LE2-S1

For CPV18, use the following connecting cables:

• KMEB-2-24-..

ET200X/ET200pro pneumatic interface for CPV10 and CPV14





Adaptation of the valve manifold assembly CPV to the input/output module ET200X/ET200pro from Siemens:
Combining the function modules of ET200X/ET200pro with the pneumatic functions of the valve manifold assembly CPV creates a highly integrative automation solution for systems for electric and pneumatic drives with:

- 8 valve slices for up to 16 CPV valves
- Faster and more reliable contacting to IP65

- Valve manifold assembly CPV10 and CPV14
- Not permitted for CPV10-EX-VI
- High degree of protection IP65/IP67
- Modular design

Multi-pin plug connection



Control signals from the controller to the valve terminal are transmitted via a pre-assembled multi-core cable, which substantially reduces installation time. The current reduction for the valves is also integrated in the multi-pin plug connection.

This valve terminal can be equipped with 4 to 16 solenoid coils (4, 6 or 8 valve slices).

(Ex) ATEX

For valve terminals CPV10, CPV14 or CPV18, use the configuration value "EX1E" for the "EU certification" feature and "MP" for the feature "Electrical connection".

NEC 500

For valve terminals CPV10, CPV14 or CPV18, use the configuration value "MP" for the feature "Electrical connection".



Note

Use the following connecting cables

- KMP3-...
- KMP4-...

AS-Interface connection





A special feature of the AS-Interface is the simultaneous transmission of data and supply power via a two-core cable. The encoded cable profile prevents connection with reverse polarity. If the valves have to be disconnected from the mains supply in an emergency situation, these can also be supplied via a separate connection. There is a choice of two versions of valve terminals for A/B mode.



For valve terminals CPV10, CPV14 or CPV18, use the configuration value "EX1E" for the "EU certification" feature and code "AS", "AZ", "AE" or "AO" for the feature "Electrical connection".

The valve terminal with AS-Interface is available in the following versions:

- Without inputs, with two or four valve slices (max. 4 solenoid coils) with additional power supply
- With four inputs and four valve slices (max. 8 solenoid coils)
- With four or eight inputs and four or eight valve slices (max. 8 solenoid coils) and additional power supply

 With four or eight inputs and four or eight valve slices incl. vacant position or vacant positions and additional power supply (max. 6 solenoid coils for A/B mode in accordance with SPEC. 2.1, max. 8 solenoid coils for A/B mode in accordance with SPEC. 3.0 with Profile 7.A.7)

More information

→ Internet: as-interface




- Note

Valve terminals to SPEC.2.1 cannot be operated on a master to SPEC.3.0 with profile 7.A.7.

Selection and development

Electrical connections

I-Port interface/IO-Link®, CTEL installation system



A CTEL system consists of the CTEL master and the devices with I-Port interface, which are connected using special connecting cables. This permits a decentralised layout of the devices. This means that the valve terminals and I/O modules with I-Port interface (devices) can be mounted very close to the cylinders to be controlled. This reduces the length of the air supply lines used, which in turn minimises flow losses as well as pressurisation and exhaust times.

The I-Port interface from Festo is based on IO-Link® and is therefore compatible with IO-Link® in certain areas. The connection type corresponds to a star topology. In other words, only one module or one valve terminal can be connected to each I-Port.



Connection via the I-Port master module of an electrical terminal CPX.

For valve terminals CPV10 or CPV14, use the configuration value "EX1E" for the "EU certification" feature and "PT" for the feature "Electrical connection".

As well as transmitting the communication data, the I-Port interfaces also handle the power supply for the connected devices.

The maximum length of a string is 20 m.

The restrictions compared to IO-Link® include:

- Permanently set baud rate of 230.4 kbps
- SIO mode is not supported
- Max. 32 bytes of input data and 32 bytes of output data
- Only one extract of the master commands is used
- Festo plug & work principle, configuration via IODD is not supported.


More information

- → Internet: cteu
- → Internet: cpx

For the electrical terminal CPX, use the configuration value "EX1E" for the feature "EU certification".

Selection and development

I-Port interface/IO-Link®, CTEU system



CTEU is a system for the compact connection of a valve terminal to different fieldbus standards such as PROFIBUS and DeviceNet $^{\circledcirc}$.

The bus node is mounted directly on the I-Port interface of the valve terminal

This makes it easier to switch between the fieldbus protocols than with Fieldbus Direct; however, there is no way of connecting I/O modules to the bus node (as with the CPI string extension). The following fieldbus protocols are supported:

- CANopen
- DeviceNet[®]
- CC-LINK[®]
- PROFIBUS
- EtherCAT®
- AS-Interface
- PROFINET
- EtherNet/IP
- VARAN

More information

→ Internet: cteu



Connection via I-Port (code: PT).

For valve terminals CPV10 or CPV14, use the configuration value "EX1E" for the "EU certification" feature and "PT" for the feature "Electrical connection".




Note

Please note that the directly mounted bus node CTEU must be ordered separately and only the following versions are permitted:

- 8107588 CTEU-PB-EX1C
- 8107589 CTEU-PN-EX1C
- 8107591 CTEU-EP-EX1C

Electrical connections

Installation system CP/CPI



The installation system CP/CPI comprises an interface for connecting valve terminals and I/O modules with CP connection to the modular electrical terminal CPX.

All CP valve terminals and CP modules are connected using a ready-to-install CP cable, and are attached to the CP interface. In each case 4 modules, for example one valve terminal CPV and one to three CP input modules, make up an installation string that ends at the CP interface.

Scope of services:

- Max. 4 installation strings per CP interface
- · Max. 10 metre line length per string (radius)
- Max. 4 CP modules per string
- · Max. 32 inputs and max. 32 outputs per string

The following bus protocols are sup-

- PROFIBUS DP
- DeviceNet®
- CANopen
- CC-LINK®
- EtherNet/IP
- PROFINET
- POWERLINK
- EtherCAT®
- · Sercos III

In the installation system CP/CPI, the valve terminal CPV is treated as an output module having up to 8 outputs (4, 6 or 8 valve slices or 4 to 16 solenoid coils per terminal). The connecting cables transfer all the required electrical signals (control signals, operating voltage for the internal electronics of the modules, load voltage supply for connected valves).

More information

→ Internet: cpi



For valve terminals CPV10 or CPV14, use the configuration value "EX1E" for the "EU certification" feature and "FB" for the feature "Electrical connection".

Fieldbus Direct

Fieldbus Direct is a system for the compact connection of a CPV Profibus DP valve terminal to different fieldbus standards.

The bus node is directly integrated in the electrical control of the valve termi-

nal and therefore takes up only a minimal amount of space. The CPI string extension option enables the functions and components of the system CPI to be used.

The new high-performance CPI string extension offers up to 4 supplementary CPI modules in a mix with CP- or CPI-compatible valve terminals for extension. It is possible to extend the Fieldbus Direct system from 8 ... 32 inputs and 8 ... 32 outputs without any problems.




For valve terminals CPV10 or CPV14. use the configuration value "EX1E" for the "EU certification" feature and "D1" or "D2" for the feature "Electrical con-

Selection and development

| Valve terminal configurator | | | • | → Internet: www.festo.com |
|---|--|---|-------------------------------------|--|
| General | CPV10-VI | CPV14-VI | CPV18-VI | |
| A valve terminal configurator is available to help you select a suitable valve terminal, making it much easier to order the right product. | Order a valve terminal CPV10-VI using the order code: | Order a valve terminal CPV14-VI using the order code: | Order a value the order co | ve terminal CPV18-VI using ode: |
| | Ordering system CPV10 | Ordering system CPV14 | Ordering sy | stem CPV18 |
| The valve terminals are assembled according to your order specification and are individually checked. This reduces assembly and installation time to a minimum. | → Internet: cpv10 | → Internet: cpv14 | → Internet | t: cpv18 |
| Ordering data – Product options | | | | |
| | Configurable product This product and all its product options can be ordered using the configurator. | The configurator can be found at → www.festo.com/catalogue/cpv Enter the part number or the type. | Part no. 18200 18210 18220 | Type CPV10-VI CPV14-VI CPV18-VI |

Peripherals overview

Overview - CPV valve terminal



- Basic electrical unit (Fieldbus Direct, installation system CP/CPI, I-Port interface/IO-Link[®], AS-Interface, multi-pin, individual connection)
- [2] Right end plate with flat plate silencer
- [3] Comprehensive range of valve
- [4] Right end plate (threaded connections not in combination with pneumatic multiple connector plate)
- [5] Inscription label holder
- [6] QS push-in fittings

- [7] Functional module (vertical stacking)
- [8] Pneumatic multiple connector plate
- [9] Left end plate (threaded connections not in combination with pneumatic multiple connector plate)
- [10] Left end plate with flat plate silencer
- [11] H-rail mounting
- [12] Wall mounting
- [13] Connecting cable for individual connection

Valves

Valves CPV are valves with an integrated sub-base, i.e. in addition to the valve function they also include all pneumatic ducts for supply, exhaust and for the working ports. The supply ducts are the central component of the valve slices and enable a direct flow through the valve slices so that maxi-

mum flow rates can be achieved. All valves have a pneumatic pilot control for optimising performance. The valve function is based on a piston spool system with patented sealing principle, ensuring a broad range of applications and long service life.

The components for the pneumatics and the pneumatic functions are always the same for all types of control. Most functions are also available in the different valve sizes (grid dimension). Restrictions are pointed out where applicable.


| Valve fur | nction | | | | |
|-----------|--|------|----|----|---|
| Code | Circuit symbol | Size | | | Description |
| | | 10 | 14 | 18 | |
| M, MK | 14 4 2 14 84 5 1 3 12 | • | • | • | 5/2-way valve, single solenoid Pneumatic spring return Piston spool valve With duct separation 1, 11 for valve MK Size 18 only available for valve M |
| | 14 4 2 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 | • | - | - | 5/2-way valve, single solenoid Pneumatic spring return Piston spool valve Fast switching |
| J, JK | 14 4 2 12 14 84 5 1 3 12 | • | • | • | 5/2-way valve, double solenoid Piston spool valve With duct separation 1, 11 for valve JK Size 18 only available for valve J |
| c,cK | 14 112 112 11 14 82/84 1 3/5 12 11 | • | • | • | 2x 3/2-way valve, single solenoid Normally closed Pneumatic spring return Piston spool valve With duct separation 1, 11 for valve CK Size 18 only available for valve C |
| СУ | 14 2 112 112 11 14 82/84 1 3/5 12 11 | • | - | - | 2x 3/2-way valve, single solenoid Normally closed Pneumatic spring return Integrated back pressure protection Piston spool valve Not suitable for vacuum - Note If it is necessary to ensure that the back pressure flaps are securely closed in the event of a sudden loss or shutdown of the operating pressure, the valve terminal must be operated with external pilot air supply. |

| Valve fur | | | | | |
|-----------|--|------------|----|----|--|
| Code | Circuit symbol | Size 10 | 14 | 18 | Description |
| N, NK | 14 82/84 1 12 11 3/5 | • | • | • | 2x 3/2-way valve, single solenoid Normally open Pneumatic spring return Piston spool valve With duct separation 1, 11 for valve NK Size 18 only available for valve N By using these valves in the open initial position, the function of a 5/3-way valve with mid-position pressurised can be achieved |
| Н, НК | 14 2 110 110 110 110 110 110 110 110 110 1 | • | • | • | 2x 3/2-way valve, single solenoid Normal position 1x open (pilot control 12) 1x closed (pilot control 14) Pneumatic spring return Piston spool valve With duct separation 1, 11 for valve HK Size 18 only available for valve H For optimised cylinder movement. With simultaneous actuation of both solenoid coils, corresponds to valve function M (5/2-way, single solenoid). As each side of the piston surface can be pressurised or exhausted independently from each other, the cylinder can execute faster movements. |
| G | 14 W 4 2 W 12 14 84 5 1 3 | - | - | • | 5/3-way valve, mid-position closed • Mechanical spring return • Piston spool valve |
| - | | • | • | _ | 5/3G ¹⁾ function, mid-position closed for size 10 and 14. The valve function "mid-position closed" is created using a 2x 3/2-way valve, normally closed (code C). The valve kit CPV10-BS-5/3G-M7 or CPV14-BS-5/3G-1/8 (incorporating a double piloted check valve function) is used for this. The valve kit is intended for use with one working pressure for each valve slice, i.e. it must not be used in dual-pressure operation (different pressure at port 1 and 11). If other valve slices are used in dual-pressure operation, a separator plate must be used to separate the valve slice equipped with the 5/3G valve kit from the compressed air duct 1 and 11 (code T). With pneumatic multiple connector plate P and M, not in the first or last valve position. Cannot be used with pneumatic multiple connector plate GQC and GQD. • Piston spool valve |

¹⁾ Cannot be installed in combination with the pneumatic multiple connector plate for control cabinets CPV10-VI-P...-C or CPV10-VI-P...-D



A filter must be installed upstream of valves operated in vacuum mode. This prevents any foreign matter in the intake air getting into the valve (e.g. when operating a suction cup).



| Code | nal pneumatic functions Circuit symbol | Size | | | Description | | | |
|------|---|------|----|----|--|--|--|--|
| | | 10 | 14 | 18 | | | | |
| A | Vacuum generator 4 2 14 84 1 3/5 111 | • | • | • | Vacuum generation according to the ejector principle. Vacuum slices of different widths for different suction capacities. Combinations with a number of vacuum and/or directional control discs are possible on the same valve terminal. The principle consists of an open connection between the exhaust duct 3/5 and the work ing port 4. If a nozzle is not connected, any back pressure that occurs in the exhaust duct flows back into the working port. If a nozzle is connected, the vacuum can be reduced using the back pressure. This effect is improved by optimising the exhaust. With just one vacuum generator per | | | |
| E | Vacuum generator with ejector pulse 4 2 12/14 1 3/5 82/84 11 | • | • | • | valve terminal and separation using the separator plate (code S), the effect does not occur. Vacuum generator on pilot side 14 Reset via mechanical spring and pneumatic spring Ejector pulse on pilot side 12 (code E) With more than two vacuum generators, pay attention to the air supply and exhaust | | | |
| P | Input (valve side) 2 4 2 4 Output (cylinder side) | • | • | - | 2x one-way flow control valve, supply air flow control Module (attachment) for direct flange connection to the valves CPV. Also suitable for pneumatic multiple connector plate. It is not possible to combine different valve attachments. Not with valve function G Not in the first or last valve position with accessories M, P, V (pneumatic multiple connector plate) Cannot be used with accessories GQC or GQD (pneumatic multiple connector plate) | | | |
| Q | Input (valve side) 2 4 2 4 Output (cylinder side) | • | • | - | 2x one-way flow control valve, exhaust air flow control Module (attachment) for direct flange connection to the valves CPV. Also suitable for pneumatic multiple connector plate. It is not possible to combine different valve attachments. Not with valve function G Not in the first or last valve position with accessories M, P, V (pneumatic multiple connector plate) Cannot be used with accessories GQC or GQD (pneumatic multiple connector plate) | | | |
| V | Input (valve side) 2 1 Output (cylinder side) | • | • | _ | One-way flow control valve for vacuum The module CPVBS-GRZ-V has a built-in check valve as well as a throttle function for adjusting the ejector pulse. The check valve temporarily maintains the vacuum, even if the vacuum generator is switched off. The module is suitable for vacuum generators (code A, E). Not in the first or last valve position with accessories M, P, V (pneumatic multiple connector plate) Cannot be used with accessories GQC or GQD (pneumatic multiple connector plate) | | | |

Creating pressure zones

Two pressure levels per valve are created using different pressure at port 1 and 11. Thus, for example, a cylinder drive can be advanced with high pressure and retracted with low pressure to save energy.

The maximum possible number of pressure zones is determined by the combination of the following components:

- Use of a separator plate
- Type of end plate pair
- Valve slice type
- Number of valve slices

arator plates or valves with integrated duct separation.

The valve terminal CPV can be divided into 2 to 4 pressure zones using sep-

| Code | or plates/valves with integrated duct separation Illustration | Size | | Note | |
|---------------------------------------|--|------|----|------|---|
| | | 10 | 14 | 18 | |
| T | Separator plate for creating pressure zones, supply duct 1 and 11 are separate 82/84 12/14 3/5 11 | • | • | • | Using one separator plate (code T), only the air supply duct (port 1 and 11) is interrupted to allow two pressure levels. Not in the first or last valve position Not with compressed air supply A, B, C, D, U, V, W, X |
| S | Separator plate for creating pressure zones, supply duct 1, 11 and exhaust 3, 5 are separate 82/84 12/14 3/5 1 11 | • | • | • | The separator plate (code S) divides the exhaust duct 3/5 as well as the supply duct 1 and 11. This plate should be used if one of the pressure zones is a vacuum, to prevent any effect on the vacuum or to prevent back pressures on adjacent valve functions. Not in the first or last valve position Not with compressed air supply A, B, C, D, U, V, W, X (compressed air supply on one side) |
| L | Blanking plate (vacant position) 82/84 12/14 3/5 1 11 | • | • | • | A blanking plate (code L) is used to provide a vacant position at which a valve can be inserted later. |
| MK, JK, CK, NK, DK, IK | Valve with integrated separation of ducts 1 and 11 82/84 12/14 3/5 11 | • | - | _ | With these valves, the air supply ducts (port 1 and 11) are sealed by a casting skin to the right of the valve. Compared with using a separator plate, this has the advantage that none of the valve positions is occupied by a separator plate. - Note Where internal pilot air via the right end plate is used as the compressed air supply, at least one further valve with the code M, F, J, C, CY, N, H, G, D, I, A or E must be used directly to the right of this valve. |

Examples: Pneumatic supply


External pilot air supply, flat plate silencer at both ends

Compressed air supply via pneumatic multiple connector plate:

Code H

The diagram on the right shows an example of the configuration and connection of the compressed air supply with external pilot air supply. Port 12/14 on the pneumatic multiple connector plate is equipped with a fitting for this. Exhaust ports 3/5 and 82/84 are exhausted via the flat plate silencers.

A separating seal each can be optionally used to create pressure zones.



Internal pilot air supply, ducted exhaust air or threaded silencer

Compressed air supply via end plates: Code Z

The diagram on the right shows an example of the configuration and connection of the compressed air supply with internal pilot air supply.


The pilot air is branched at the right end plate of port 1 or 11. The exhaust 3/5 and 82/84 is expelled via the threaded silencer.

A separating seal each can be optionally used to create pressure zones.

Examples: Creating pressure zones

CPV with separator plate T


Up to 4 pressure zones can be created on the valve terminals CPV. The diagram shows an example of the configuration and connection of four pressure zones using separator plate code T – with external pilot air supply.



- [1] Vacuum -0.9 bar
- [2] Air pulse 2 bar
- [3] Forward stroke 6 bar
- [4] Return stroke 4 bar

CPV with integrated separation of duct 1 and 11 in valves ...K

Up to 4 pressure zones can be created on the valve terminals CPV. The diagram shows an example of the configuration and connection of four pressure zones with external pilot air supply and the use of a valve ...K with integrated separation of ducts 1 and 11.



- [1] Vacuum -0.9 bar
- [2] Air pulse 2 bar
- [3] Forward stroke 6 bar
- [4] Return stroke 4 bar

Compressed air supply and exhaust

A characteristic feature of a valve terminal CPV is the two end plates which supply the valve slices with pressure and exhaust them.

- Large duct cross sections enable very high flow rate performance, even with several valves switching simultaneously
- Large flat plate silencers in the end plates
- Internal/external pilot air supply

Each individual valve is supplied with compressed air from two individual ducts (supply ports 1/11) and exhausted via a large integrated exhaust duct (exhaust 3/5). This design allows

unique functionality and flexibility, making it very easy to have multiple pressure zones per terminal or combinations of vacuum applications.

The valve terminal is supplied via end plates, either on the left, on the right or on both sides. End plate combinations other than those listed are possible (on request).

Pilot air supply

Internal pilot air supply

This can be selected if the supply pressure at pneumatic port 1 is 0.3 ... 0.8 MPa. With internal pilot air supply, the branch is located in the left or right end plate. There is no port 12/14.


External pilot air supply

External pilot air supply is required if the supply pressure at pneumatic port 1 is lower than 0.3 MPa or higher than 0.8 MPa. In this case, a pressure of 0.3 ... 0.8 MPa is applied at port 12/14.

If a gradual pressure build-up in the system using a soft-start valve is required, an external pilot air supply should be selected. In this case, the control pressure applied during switch-on is already very high.

External pilot air supply is also required if it is necessary to ensure that the back pressure valves (valve order code CY) are securely closed in the event of a sudden loss or shutdown of the operating pressure.

End plates



Example of an end plate:

The diagram shows a left end plate with external pilot air supply. The exhaust ports 3/5 and 82/84 can be equipped with fittings or silencers. An end plate for internal pilot air supply does not have ports 12/14 and 11. Port 82/84 is always present and should be fitted with a silencer. With an end plate for internal pilot air sup-

ply, port 12/14 is connected internally to port 1.


| | 1 | sed air supply via end plate | | | | | 1 |
|------|---|---|--|------------|---|----|--|
| Code | Illustration Type of pilot air supply (inte | ernal/external) | | Size 10 | | 18 | Note |
| U | Internal pilot air supply | 82/84 82/84 3/5 3/5 12/14 12/14 1 1 1 | No. | • | • | • | Ports in right end plate only No pressure zone separation permissible Not suitable for vacuum |
| V | Internal pilot air supply | 82/84 82/84 3/5 3/5 J5 12/14 12/14 11 11 J | | • | • | • | Ports in left end plate only No pressure zone separation permissible Not suitable for vacuum |
| W | External pilot air supply | 82/84 82/84 | Vision of the second of the se | • | • | • | Ports in right end plate only No pressure zone separation permissible Suitable for vacuum |
| X | External pilot air supply | 82/84 82/84 | | • | • | • | Ports in left end plate only No pressure zone separation permissible Suitable for vacuum |
| Υ | Internal pilot air supply | 82/84 82/84 3/5 3/5 3/5 12/14 12/14 11 11 | | • | • | • | Ports in left and right end plate Maximum three pressure zones Valves on the left of the separator plate suitable for vacuum |
| Z | External pilot air supply | 82/84 82/84 S2/84 | | | • | • | Ports in left and right end plate Maximum four pressure zones Suitable for vacuum |

| End pl | ate combination for compressed air supply via pneumatic multiple connector plate | | | | | |
|--------|--|----|------|----|----|---|
| Code | Illustration | | Size | | | Note |
| | Type of pilot air supply (internal/external) | | 10 | 14 | 18 | |
| Y | Internal pilot air supply 82/84 82/84 11 11 11 11 11 11 11 11 11 11 11 11 11 | | • | • | • | Ports on pneumatic multiple connector plate Pressure zone separation only permissible with separator plate (code T) Maximum two pressure zones Valves on the left of the separator plate suitable for vacuum Only for accessories M, P, V, GQC, GQE, GQD (pneumatic multiple connector plate) |
| Z | External pilot air supply 82/84 11/11 11 11 11 | 50 | • | • | • | Ports on pneumatic multiple connector plate Pressure zone separation only permissible with separator plate (code T) Maximum three pressure zones Suitable for vacuum Only for accessories M, P, V, GQC, GQE, GQD (pneumatic multiple connector plate) |

| zn u pr a Code | Illustration | sed air supply via end plate with flat plate silencer | Size | | | Note |
|--------------------------|--------------------------------|---|------|---|----|--|
| Juc | Type of pilot air supply (inte | ernal/external) | 10 | | 18 | , note |
| | Internal pilot air supply | 82/84 82/84 3/5 3/5 12/14 11 | • | • | • | Ports in right end plate No pressure zone separation permissible Not suitable for vacuum |
| | Internal pilot air supply | 82/84 82/84 3/5 3/5 12/14 11 | • | • | • | Ports in left end plate No pressure zone separation permissible Not suitable for vacuum |
| | External pilot air supply | 82/84 82/84 D D D D D D D D D D D D D D D D D D D | • | • | • | Ports in right end plate No pressure zone separation permissible Suitable for vacuum |
| | External pilot air supply | 82/84 82/84 3/5 3/5 12/14 11 1 | • | • | • | Ports in left end plate No pressure zone separation permissible Suitable for vacuum |

| End pla Code | te combination for compressed air supply via pneumatic multiple connector plate with flat plate silence Illustration | er Size | | | Note |
|-----------------|---|--------------|----|----|---|
| | Type of pilot air supply (internal/external) | | 14 | 18 | |
| E | External pilot air supply 82/84 11/11 11 11 11 | • | • | • | Ports on pneumatic multiple connector plate Exhaust air vented via flat plate silencer on the right Pressure zone separation only permissible with separator plate (code T) Maximum four pressure zones Suitable for vacuum Only for accessories M, P, V, GQC, GQE, GQD (pneumatic multiple connector plate) |
| F | External pilot air supply 82/84 82/84 12/14 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 | - | • | • | Ports on pneumatic multiple connector plate Exhaust air vented via flat plate silencer on the left Pressure zone separation only permissible with separator plate (code T) Maximum four pressure zones Suitable for vacuum Only for accessories M, P, V, GQC, GQE, GQD (pneumatic multiple connector plate) |
| G | Internal pilot air supply 82/84 82/84 12/14 11 11 11 11 | • | • | • | Ports on pneumatic multiple connector plate Exhaust air vented via flat plate silencer on the left Pressure zone separation only permissible with separator plate (code T) Maximum three pressure zones Not suitable for vacuum Only for accessories M, P, V, GQC, GQE, GQD (pneumatic multiple connector plate) |
| Н | External pilot air supply 82/84 82/84 112/14 1 1 1 | • | • | • | Ports on pneumatic multiple connector plate Exhaust air vented via flat plate silencers at both ends Pressure zone separation permissible Suitable for vacuum Only for accessories M, P, V, GQC, GQE, GQD (pneumatic multiple connector plate) |
| J | Internal pilot air supply 82/84 82/84 12/14 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 | • | • | • | Ports on pneumatic multiple connector plate Exhaust air vented via flat plate silencers at both ends Pressure zone separation permissible Maximum three pressure zones Valves on the left of the separator plate suitable for vacuum Only for accessories M, P, V, GQC, GQE, GQD (pneumatic multiple connector plate) |
| K | Internal pilot air supply 82/84 11/11 1 1 1 1 | • | • | • | Ports on pneumatic multiple connector plate Exhaust air vented via flat plate silencer on the right Pressure zone separation permissible Maximum three pressure zones Suitable for vacuum in combination with separator plate Only for accessories M, P, V, GQC, GQE, GQD (pneumatic multiple connector plate) |

Pneumatic connection



The working lines are located directly in the valve slices.

Threaded connections and Quick Star push-in fittings (QS) are available for different tubing sizes.

The supply ports are located in the end plates or in the pneumatic multiple connector plate.

Push-in fittings are available fully assembled.

The following working lines can be selected:

- Push-in fittings, large: code A
- Push-in fittings, small: code B
- · Threaded connections: code C

Connection sizes for threads and QS push-in fittings can be found in the table below.

Pneumatic multiple connector plate


One-piece sub-bases are available for use with a pneumatic multiple connector plate; these contain both the working ports and also the supply ports. This allows the valve terminal as a pneumatic "function" to be separated from the ports.

The pneumatic multiple connector plate enables different types of mounting, from wall mounting to direct attachment through a housing wall.


Easy-to-service and flexible connection technology thanks to:

- Common connection via the pneumatic multiple connector plate with all connections on one side
- For mounting/dismounting, the valve terminal is secured/released using just four screws while the pneumatic tubing remains connected
- Minimal time required for mounting/dismounting
- No faults during recommissioning caused by incorrectly connected tubing

CPV valve terminal



Pneumatic multiple connector plate



| Connect | ion sizes | | | | |
|---------------------------|------------------------|-----------------------|-------------------|--|--|
| Connect | ion to ISO 5599 | CPV10 | CPV14 | CPV18 | Comment |
| 1/11 Supply air G1/8 G1/4 | | G1/4 | G3/8 | Fitting in end plate or pneumatic multiple connector plate | |
| 2/4 | Working port | M7 (QS6/QS4) | G1/8 (QS8/QS6) | G1/4 (QS10/QS8) | Port in valve slice, push-in fitting via clips |
| 3/5 | Exhaust air port | G3/8 | G1/2 | G1/2 | Via right/left end plate |
| | | G1/4 | G3/8 | G1/2 | Pneumatic multiple connector plate |
| 12/14 | Pilot air supply port | M5 | G1/8 | G1/4 | Fitting in end plate or pneumatic multiple connector plate |
| 82/84 | Pilot exhaust air port | M5 | G1/8 | G1/4 | Via right/left end plate |
| | | M7 (M5) ¹⁾ | G1/8 | G1/4 | Pneumatic multiple connector plate |

¹⁾ With pneumatic multiple connector plate with flange

25

| | Code | Connection | Designation | Size 10 | Size 14 | Size 18 |
|---------------|------------------|-----------------------|-----------------|---------------|---------------|---------------|
| | Compressed air | | | QS6 | QS8 | QS10 |
| | supply | | | Туре | Туре | Туре |
| ♠ | Without pneumat | c multiple connector | plate | | | <u>:</u> |
| | U, V | 82/84 | Silencer | AMTE-M-LH-M5 | AMTE-M-LH-G18 | AMTE-M-LH-G14 |
| | | 3/5 | Silencer | AMTE-M-LH-G38 | AMTE-M-LH-G12 | AMTE-M-LH-G12 |
| | | 1 | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| | W, X | 82/84 | Silencer | AMTE-M-LH-M5 | AMTE-M-LH-G18 | AMTE-M-LH-G14 |
| | | 3/5 | Silencer | AMTE-M-LH-G38 | AMTE-M-LH-G12 | AMTE-M-LH-G12 |
| ~ | | 1 | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| | | 12/14 | Push-in fitting | QSM-M5-6-I | QS-G1/8-8-I | QS-G1/4-10-I |
| | Υ | 82/84 on right | Silencer | AMTE-M-LH-M5 | AMTE-M-LH-G18 | AMTE-M-LH-G12 |
| | | 82/84 on left | Blanking plug | B-M5 | B-1/8 | B-1/4 |
| | | 3/5 on right | Silencer | AMTE-M-LH-G38 | AMTE-M-LH-G12 | AMTE-M-LH-G12 |
| | | 3/5 on left | Blanking plug | B-3/8 | B-1/2 | B-1/2 |
| | | 1/11 on left | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| ~~ | Z | 82/84 on right | Silencer | AMTE-M-LH-M5 | AMTE-M-LH-G18 | AMTE-M-LH-G12 |
| | - | 82/84 on left | Blanking plug | B-M5 | B-1/8 | B-1/4 |
| | | 3/5 on right | Silencer | AMTE-M-LH-G38 | AMTE-M-LH-G12 | AMTE-M-LH-G12 |
| | | 3/5 on left | Blanking plug | B-3/8 | B-1/2 | B-1/2 |
| | | 12/14 on right | Push-in fitting | QSM-M5-6-I | QS-G1/8-8-I | QS-G1/4-10-I |
| | | 12/14 on left | Blanking plug | B-M5 | B-1/8 | B-1/4 |
| | | 1/11 | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| | With pneumatic m | ultiple connector pla | te; code M | | | |
| ~~ | Υ | 82/84 | Silencer | UC-M7 | AMTE-M-LH-G18 | AMTE-M-LH-G12 |
| | | 12/14 | Blanking plug | B-M7 | B-1/8 | B-1/4 |
| €⋒ . | | 3/5 | Silencer | AMTE-M-LH-G12 | AMTE-M-LH-G38 | AMTE-M-LH-G12 |
| | | 1/11 on left | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| | | 11 on right | Blanking plug | B-1/8 | B-1/4 | B-3/8 |
| | Z | 82/84 | Silencer | UC-M7 | AMTE-M-LH-G18 | AMTE-M-LH-G12 |
| | | 3/5 | Silencer | AMTE-M-LH-G12 | AMTE-M-LH-G38 | AMTE-M-LH-G12 |
| | | 12/14 | Push-in fitting | QSM-M7-6-I | QS-G1/8-8-I | QS-G1/4-10-I |
| | | 1/11 on left | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| | With pneumatic m | ultiple connector pla | te; code P, GQC | | | |
| | Υ | 82/84 | Silencer | AMTE-M-LH-M5 | AMTE-M-LH-G18 | AMTE-M-LH-G12 |
| | | 12/14 | Blanking plug | B-M5 | B-1/8 | B-1/4 |
| | | 3/5 | Silencer | AMTE-M-LH-G12 | U-3/8-B | AMTE-M-LH-G12 |
| 1 9932 | | 1/11 on left | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| • | | 11 on right | Blanking plug | B-1/8 | B-1/4 | B-3/8 |
| | Z | 82/84 | Silencer | AMTE-M-LH-M5 | AMTE-M-LH-G18 | AMTE-M-LH-G12 |
| | | 3/5 | Silencer | AMTE-M-LH-G12 | AMTE-M-LH-G38 | AMTE-M-LH-G12 |
| | | 12/14 | Push-in fitting | QSM-M5-6-I | QS-G1/8-8-I | QS-G1/4-10-I |
| | | 1/11 on left | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| | | | | | | |
| | | | | | | |

Valve terminal CPV, Compact Performance

| | Code | Connection | Designation | Size 10 | Size 14 | Size 18 |
|-------------|------------------|------------------------------|-----------------|-------------|--------------|--------------|
| | Compressed air | | | QS6 | QS8 | QS10 |
| | supply | | | Туре | Type | Туре |
| A. | Without pneumati | ic multiple connector p | late | | | |
| | A, B | 82/84 | Blanking plug | B-M5 | B-1/8 | B-1/4 |
| | | 3/5 | Blanking plug | B-3/8 | B-1/2 | B-1/2 |
| | | 1 | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| | C, D | 82/84 | Blanking plug | B-M5 | B-1/8 | B-1/4 |
| * *• | | 3/5 | Blanking plug | B-3/8 | B-1/2 | B-1/2 |
| | | 1 | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-l | QS-G3/8-12-I |
| | | 12/14 | Push-in fitting | QSM-M5-6-I | QS-G1/8-8-I | QS-G1/4-10-l |
| | With pneumatic m | ultiple connector plate | e; code M | | , | |
| | E, F, H | 82/84 | Blanking plug | B-M7 | B-1/8 | B-1/4 |
| | | 3/5 | Blanking plug | B-1/4 | B-3/8 | B-1/2 |
| | | 1/11 | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| | | 12/14 | Push-in fitting | QSM-M7-6-I | QS-G1/8-8-I | QS-G1/4-10-l |
| | G, J, K | 82/84 | Blanking plug | B-M7 | B-1/8 | B-1/4 |
| - | | 3/5 | Blanking plug | B-1/4 | B-3/8 | B-1/2 |
| | | On right in 1, left | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-l | QS-G3/8-12-I |
| | | On right in 11 | Blanking plug | B-1/8 | B-1/4 | B-3/8 |
| <u></u> | | 12/14 | Blanking plug | B-M7 | B-1/8 | B-1/4 |
| A . | With pneumatic m | ultiple connector plate | e; code P, GQC | | | |
| | E, F, H | 82/84 | Blanking plug | B-M5 | B-1/8 | B-1/4 |
| | | 3/5 | Blanking plug | B-1/4 | B-3/8 | B-1/2 |
| | | 1/11 | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-l | QS-G3/8-12-I |
| | | 12/14 | Push-in fitting | QSM-M5-6-I | QS-1/8-8-I | QS-1/4-10-l |
| | G, J, K | 82/84 | Blanking plug | B-M5 | B-1/8 | B-1/4 |
| | | 3/5 | Blanking plug | B-1/4 | B-3/8 | B-1/2 |
| | | On right in 1, left | Push-in fitting | QS-G1/8-8-I | QS-G1/4-10-I | QS-G3/8-12-I |
| | | On right in 11 | Blanking plug | B-1/8 | B-1/4 | B-3/8 |
| | | 12/14 | Blanking plug | B-M5 | B-1/8 | B-1/4 |

CPV valve terminal size 10 and 14 with valve extensions

Function blocks




CPV10-BS-5/3G-M7 CPV14-BS-5/3G-1/8 Valve kit 5/3G for creating a 5/3-way function, mid-position closed, for size 10 and 14:

The valve function "mid-position closed" is created using a valve slice with 2x 3/2-way valve, normally closed (code C).

The valve kit CPV10-BS-5/3G-M7 or CPV14-BS-5/3G-1/8 (incorporating a double piloted check valve function) is used for this.

The valve kit is intended for use with one working pressure for each valve slice, i.e. it must not be used in dual-pressure operation (different pressure at port 1 and 11).

Additional functions for valve positions




The valve terminal CPV in size 10 and 14 can be enhanced with further pneumatic functions with the aid of these valve extensions (vertical stacking):

- One-way flow control valves x2 for flow control directly at the valve terminal for
 - Supply air flow control
 - Exhaust air flow control
- The vacuum flow control module must be used with the vacuum generator with or without ejector pulse and offers a one-way function and an adjustable ejector pulse.
- 2x one-way flow control valve for supply air flow control
- Additional function code P



Note

The additional functions cannot be used on the first or last valve position in combination with a pneumatic multiple connector plate M, P, and cannot be used at all in combination with a pneumatic multiple connector plate GQC, GQE, GQD.




CPV10-BS-2xGRAZ-M7 CPV14-BS-2xGRAZ-1/8

CPV10-BS-2xGRZZ-M7

CPV14-BS-2xGRZZ-1/8

- 2x one-way flow control valve for exhaust air flow control
- Additional function code O



CPV10-BS-GRZ-V-M7 CPV14-BS-GRZ-V-1/8

- Vacuum flow control module
- Additional function code V



Key features - Mounting

Mounting options


The valve terminals have holes for four retaining screws, with the side for the pneumatic fittings being the screw-on surface. These drilled holes are also used to mount the valve terminal on the pneumatic multiple connector plate.

In addition to this type of mounting, there are other mounting options:

- H-rail mounting
- Wall mounting
- Wall mounting via pneumatic multiple connector plate with flange
- On rear side via wall mounting
- On the front (CPV10/14 with IC connection only)
- Mounting via through-hole in wall

The mountings are attached to the left and right end plates using a screw and a fixing bolt.

Mounting for H-rail



For valve terminal CPV10/14: CPV10/14-VI-BG-NRH-35 (Mounting code H)




For valve terminal CPV18: CPV18-VI-BG-NRH-35 (Mounting code H)




H-rail to EN 60715 not for accessories M, P, V (pneumatic multiple connector plate)




Attachment for wall mounting




For valve terminal CPV10/14: CPV10/14-VI-BG-RWL-B (Mounting code U)




For valve terminal CPV18: CPV18-VI-BG-RW (mounting code W)




Attachment for individual connection and ET200X/ET200pro (included in the scope of delivery)




For valve terminal CPV10/14: CPV...-VI-BG-ET200X (mounting code X)



Through-hole in wall, e.g. on the machine




Wall mounting via pneumatic multiple connector plate



Key features - Mounting


Pneumatic multiple connector plate for wall/machine mounting

With flange, with all pneumatic connections, code P



- For 10 mm, 14 mm and 18 mm
- Multiple connector plate protrudes at the end plates
- Through-holes for mounting (no thread) in the flange
- Two additional holes running crossways through this pneumatic multiple connector plate also allow rear mounting of valve terminal CPV.

Without flange, with all pneumatic connections, code M




- For 10 mm, 14 mm and 18 mm
- Multiple connector plate ends flush with the end plates
- Mounting holes (with thread) for wall or base mounting in the connection side of the pneumatic multiple connector plate

[1] Mounting holes

Pneumatic multiple connector plate for control cabinet installation


With all pneumatic connections, code GQC



- For 10 mm and 14 mm
- Multiple connector plate protrudes at the end plates
- Mounting holes (with thread) in the flange
- Multiple connector plate with seal

[1] Mounting holes






- For 10 mm and 14 mm
- Multiple connector plate ends flush with the end plates
- The mounting holes (with thread) are in the connection side of the pneumatic multiple connector plate
- Multiple connector plate with seal

[1] Mounting holes

With all pneumatic connections, code GQE



- For 10 mm
- Multiple connector plate protrudes at the end plates
- Mounting holes (with thread) in the flange
- Multiple connector plate with seal

[1] Mounting holes

[1] Mounting holes



When using the pneumatic multiple connector plate M or P, the outermost valve slices cannot be fitted with valve extensions (e.g. one-way flow control valve).

Valve terminals CPV with flat plate silencer can only be mounted on a wall. When using the pneumatic multiple connector plate GQC, GQD and GQE, the following restrictions apply:

- In general, no valve extensions can be fitted
- Cannot be combined with H-rail mounting
- Cannot be combined with wall mounting
- Only with 10 mm and 14 mm

Key features – Display and operation

Manual override

Three types of manual override are available:

- Non-detenting via slide
- Detenting
- Blocked

A subsequent conversion of the manual override (MO) from non-detenting to detenting or blocked is possible at any time

To do this, the valve locking mechanism must first be removed. This is only possible when the individual valve is not installed or by removing the tie rod on the valve terminal.



Note

Follow the instructions in the user documentation when doing this.

| Diocke | te to to on the valve terminat. | | | | | |
|--------|---------------------------------|---|---------------|---|---|--|
| Code | Illustration | | Size 10 14 18 | | Note | |
| N | Manual override, non-detenting | • | • | • | In the "non-detenting" version, a locking mechanism prevents the blue slider from moving. The manual override is activated using a pointed object (ballpoint pen or similar) through the opening. | |
| R | Manual override, detenting | • | • | • | In the "detenting" version, the manual override is activated by sliding the slider. A locking mechanism can be used to provide the non-detenting function. | |
| V | Manual override, blocked | • | • | • | In the "blocked" version, the detenting and non-detenting activation is prevented by a cover. As with the non-detenting locking mechanism, this cover can be added subsequently, but cannot then be removed from the valve. | |

Key features – Display and operation

Display and operation

LEDs for indicating the switching status are located on the electrical connection for the valve terminal CPV:


- Indicating the switching status of the pilot solenoid coil 12 for output 2
- Indicating the switching status of the pilot solenoid coil 14 for output 4
- Can be read from "above" as well as from the "front"

With individual connection, an LED for indicating the switching status is located in the connector plug.


Inscription labels

- Clip with inscription field on the connector plug (for individual connection)
- Labelling clips on the connection node (multi-pin, AS-Interface, installation system CP, Fieldbus Direct)

Valve manifold assembly CPV with individual connection




CPV valve terminal with multi-pin plug connection



- [1] Pre-assembled connecting cable for each pilot solenoid coil
- [2] Slot for inscription label
- [3] Yellow LED, signal status indication of the pilot solenoid coils (for each connecting cable)
- [4] Earth connection
- [5] Terminal lug for solenoid coil 14
- [6] Terminal lug for solenoid coil 12
- [7] Sub-D multi-pin plug (9-pin for valve terminals with 4 valves, 25pin for valve terminals with 6 or 8 valves)

Inscription system



- [1] Inscription labels
 Type IBS-6x10 for CPV10/14
 Type IBS 9x20 for CPV18
- [2] Transparent inscription label holder for large paper labels (can be read from both sides)
- [3] Inscription label holder
- [4] Inscription labels type IBS 6x10

Inscription labels can be affixed as follows:

- On the top of the basic electrical unit
- On the inscription label holder
 The inscription label holder enables additional inscription labels to be attached while covering the manual override, protecting it from unintentional activation. The inscription labels are used to record additional information regarding the valves.

They can be ordered together with the valve terminal using the code. The relevant inscription labels are supplied in a frame and are ordered separately.

Transparent inscription label holder

The transparent inscription label holder CPV...-VI-ST-... offers an additional option for labelling, e.g. for large paper labels that can be read from both sides.

Key features - Electrical components

Electrical connection

The valve slice contacts that are directed upwards form the interface to different types of electrical connection. The electrical connection is secured from above using 4 screws.

With the same pneumatic part, the valve terminal can thus be adapted to the different electrical requirements or fieldbus protocols.


Electrical power

Valves CPV10/14 are controlled via a current reduction which reduces the power consumption and prevents the generation of heat.

This current reduction is already integrated into the respective basic electrical unit (multi-pin connection or field-bus interface) or into the connecting


When switching off, voltage peaks are limited to 38 V DC.

Individual connection



With individual connections, integration is on the pneumatic part only; the solenoid valves are connected with individual cables.

Key features – Electrical components



Key features - Electrical components

ET200X/ET200pro pneumatic interface for CPV10 and CPV14


Adaptation of the valve manifold assembly CPV to the input/output module ET200X/ET200pro from Siemens.
Combining the function modules of ET200X/ET200pro with the pneumatic functions of the valve manifold assembly CPV creates a highly integrative automation solution for systems for electric and pneumatic drives with:

• 8 valve slices for up to 16 CPV valves


- · Faster and more reliable contacting
- Valve manifold assembly CPV10 and CPV14
- High degree of protection IP65/IP67
- Modular design
- Large number of I/O modules
 - Digital I/O
- Analogue I/O
- Branching used to control threephase motors

· PROFIBUS DP interface


Mounting set for ET200X CPV-...-VI-BG-ET200X (included in the scope of delivery)



Specific data for the ET200X/ET200pro pneumatic interface can be found in the Siemens product catalogues.










With valve manifold assembly CPV10-ET200pro, a moulded seal is required to achieve the IP degree of protection.

The moulded seal CPV10-GE-8 or CPV14-GE-8 must be ordered separately.

- 🏺 - Note

Not permitted in combination with CPV10-EX-VI.

Multi-pin plug connection



The multi-pin plug connection provides electrical integration in addition to pneumatic integration, and enables the control cabinet and the valve terminal to be connected using a single cable.

IP65 protection is guaranteed even with the Sub-D push-in connectors thanks to the plug housing of the cable KMP-...

The following plug sizes are used:

- Valve terminal with 4 valves: 9-pin
- Valve terminal with 6 valves: 25-pin
- Valve terminal with 8 valves: 25-pin

Pre-assembled connecting cables are supplied for ease of connection.

Lengths of 5 m and 10 m can be supplied as standard. The pre-assembled connecting cables are also available in a version suitable for energy chains. The cable KMP6-... can be used instead for applications with IP40 protection.

Key features – Electrical components

| Pin allocation – Pre-assembled mul | lti-pin cable (view from plug-in directio | on) | | | |
|------------------------------------|---|--------------------|-------------------------|---------------------|-----|
| | View of plug | Pin | Wire colour | Valve 24 V DC | |
| Cable KMP3-25P-16 or KMP4-25P | with 25-pin Sub-D plug for valve ter | minals with 6 or 8 | 3 valves | | |
| | | 1 | White | 1 | 14 |
| | 01 | 2 | Green | | 12 |
| | 140 02 | 3 | Yellow | 2 | 14 |
| | 15 O | 4 | Grey | | 12 |
| | 160 | 5 | Pink | 3 | 14 |
| | 0.411 | 6 | Blue | | 12 |
| // | 17 0 5 | 7 | Red | 4 | 14 |
| 6/ | 18 0 | 8 | Violet | | 12 |
| | 190 0 6 | 9 | Grey-pink | 5 | 14 |
| | 200 07 | 10 | Red-blue | | 12 |
| | 08 | 11 | White-green | 6 | 14 |
| | 210 | 12 | Brown-green | | 12 |
| | 220 010 | 13 | White-yellow | 7 | 14 |
| | 230 | 14 | Yellow-brown | | 12 |
| | 240 | 15 | White-grey | 8 | 14 |
| | 012 | 16 | Grey-brown | | 12 |
| | 250 | 17 | White-pink (KMP4 only) | | |
| | | 18 | Pink-brown (KMP4 only) | | |
| | | 19 | White-blue (KMP4 only) | | |
| | | 20 | Brown-blue (KMP4 only) | | |
| | | 21 | White-red (KMP4 only) | | |
| | | 22 | Brown-red (KMP4 only) | | |
| | | 23 | White-black (KMP4 only) | | |
| | | 24 | Brown | (0 V) ¹⁾ | |
| | | 25 | Black | (0 V) ¹⁾ | |
| | | | | | |
| | | | | | |
| C.I.I. WARDS OR WARDS OR THE | | *** * * | | | |
| Capie KMP3-9P or KMP4-9P With | h 9-pin Sub-D plug for valve terminals | | White | 1 | 1.6 |
| | | 1 | | 1 | 14 |
| | $\begin{pmatrix} 6 & 0 & 1 \end{pmatrix}$ | 2 | Green | 2 | |
| | 0 2 1 | 3 | Yellow | 2 | 14 |
| | 7 0 0 3 | 4 | Grey Pink | 2 | |
| | 8004 | 5 | | 3 | 14 |
| / / ** | 90 | 6 | Blue | | 12 |
| // | (> 5)) | 7 | Red | 4 | 14 |
| 6/ | | 8 | Violet | Com | 12 |
| 7 | | 9 | Black | Common | |

 $^{1) \\ 0 \} V \ for positive \ switching \ control \ signals; \ connect \ 24 \ V \ for \ negative \ switching \ control \ signals; \ mixed \ operation \ is \ not \ permitted.$

Key features – Electrical components

| Pin allocation – Pre-assembled mult | i-pin cable (view from plug-in direc | | | | |
|-------------------------------------|--|-------------|---------------------------|---------------------|----|
| | View of plug | Pin | Wire colour | Valve 24 V DC | |
| Cable KMP6-25P-20 with 25-pin Su | ub-D plug for valve terminals with 6 | or 8 valves | | | |
| ^ | | 1 | White | 1 | 14 |
| | (01) | 2 | Brown | | 12 |
| | 14 0 | 3 | Green | 2 | 14 |
| | 150 | 4 | Yellow | | 12 |
| | 160 | 5 | Grey | 3 | 14 |
| | 04 | 6 | Pink | | 12 |
| - | 17 0 5 | 7 | Blue | 4 | 14 |
| | 18 0 | 8 | Red | | 12 |
| | 190 06 | 9 | Black | 5 | 14 |
| | 20 O 7 O 8 21 O 9 | | Violet | | 12 |
| | | 11 | Grey-pink | 6 | 14 |
| | | | Red-blue | | 12 |
| | 220 010 | | White-green | 7 | 14 |
| | 230 | | Brown-green | | 12 |
| | 240 | | White-yellow | 8 | 14 |
| | 012 | | Yellow-brown | | 12 |
| | 250 013 | | White-grey | | |
| | | | Grey-brown | | |
| | | | White-pink | | |
| | | | Pink-brown | | |
| | | | White-blue ¹⁾ | | |
| | | | Brown-blue ¹⁾ | | |
| | | | White-red ¹⁾ | | |
| | | | Brown-red ¹⁾ | (0 V) ²⁾ | |
| | | 25 | White-black ¹⁾ | (0 V) ²⁾ | |
| | | | | | |
| | | | | | |
| | D 1 (1 (1 (1 (1 (1 (1 (1 (1 (1 | | | | |
| Cable KMP6-9P-20 with 9-pin Sub- | υ plug for valve terminals with 4 va | | White | 1 | 14 |
| | | | Brown | 1 | 12 |
| | $ \begin{pmatrix} 6 & 0 & 1 \\ 6 & 0 & 0 & 2 \\ 7 & 0 & 0 & 3 \\ 8 & 0 & 0 & 3 \end{pmatrix} $ | | Green | 2 | 14 |
| | | | Yellow | | 12 |
| V 1111 | | | Grey | 3 | 14 |
| | 9 0 4 | | Pink | | 12 |
| | (0 5) | | Blue | 4 | 14 |
| | | | Red | 4 | 12 |
| | | <u> </u> | Black | Common | 12 |
| | | الا | טומנו | Collillion | |

- 1) Wire cross section $0.34\ mm^2$
- $2) \\ 0 \ V \ for positive \ switching \ control \ signals; \ connect \ 24 \ V \ for \ negative \ switching \ control \ signals; \ mixed \ operation \ is \ not \ permitted.$



Two

threaded sleeves (NEAU-TA-M35-U4, $\rightarrow p.$ 69) are required to secure the multi-pin cable KMP6.

Key features - Electrical components

Valve terminal CPV - AS-Interface valve terminal

The AS-Interface allows individual components or small component groups to be widely distributed in terms of space.

The AS-Interface connection of valve terminal CPV can be used to control 2, 4 or 8 solenoid coils.

The valve terminal cover contains LEDs that indicate the operating status and the protective circuit for the valves.

The standard AS-Interface protocol permits a maximum of 4 inputs and 4 outputs in one unit. By using 2 AS-Interface slaves in one valve terminal, it is possible to control 8 inputs and 8 out-

puts in a valve terminal with 8 valves (8 solenoid coils).

All valve terminals CPV can be operated with other functions such as vacuum generators.

Valve terminals CPV with inputs are also available for A/B mode to SPEC 2.1 and 3.0.


AS-Interface control

- For 2, 4 or 8 valves
- Wide range of variants from the broad modular offering


AS-Interface with A/B operation


- For 3 or 4 or for 6 or 8 valves, depending on the specification
- It still provides all the benefits of the straightforward installation system
- 100% more inputs/master
- 50% more outputs/master
- Improved diagnostics of faults in the peripherals
- More functions on the AS-Interface within Spec 2.1 and 3.0.
- → Internet: as-interface

AS-Interface valve terminal with auxiliary power supply



AS-Interface valve terminal with auxiliary power supply and inputs





Key features - Electrical components

I-Port interface/IO-Link®

The I-Port interface/IO-Link® enables the valve terminal CPV to be connected to the following systems:


- I-Port master from Festo (CPX terminal, CECC)
- · Bus node CTEU from Festo
- IO-Link® master

A maximum of 16 solenoid coils can be actuated, distributed over a maximum of 8 valve positions. The maximum distance between the I-Port/IO-Link® master and valve terminal with I-Port interface/IO-Link is 20 m.


The 5-pin connecting cables contain the power supply for the valves; the power supply for the internal valve terminal electronics and the control signals are separate from this. The valve terminal cover contains LEDs that indicate the operating status and the protective circuit for the valves.
All valve terminals CPV can be operated with other functions such as vacuum generators.

- → Internet: cteu
- → Internet: cpx


CPV valve terminal with I-Port interface/IO-Link®



CPV valve terminal with I-Port interface with bus node



Installation system CP/CPI, valve terminal



The valve terminals CPV are integrated into fieldbus systems or stand-alone control systems by connecting the terminals using single, pre-assembled terminal connections to the corresponding bus node or control block.

The system integrates the valve terminal CPV and various I/O modules, etc. into a single installation concept.

The 5-pin connecting cables carry the supply power and control signals. The valve terminal cover contains LEDs that indicate the operating status and the protective circuits for the valves.


Max. 8 valve slices for up to 16 CPV valves

The input and output statuses of the connected module are exchanged with the CP bus node via the CP string.

→ Internet: cpi

Instructions for use

Fieldbus Direct valve terminal



Fieldbus Direct is a system for connecting a valve terminal, like Profibus for example.

The CP string extension option enables the functions and components of the CPI installation system to be used.

The optional string extension allows additional valve terminals and I/O modules with CP/CPI function to be

connected to the Fieldbus Direct bus

Depending on the version, the valve terminals are available in all three sizes, 10, 14 and 18 mm, each having 8 valve slices.

Operating materials

Operate your system with unlubricated compressed air, if possible. Festo valves and cylinders are designed so that, if used as intended, they will not require additional lubrication and will still achieve a long service life.

The quality of compressed air downstream of the compressor must correspond to that of unlubricated compressed air. If possible, do not operate the entire system with lubricated compressed air. The lubricators should, where possible, always be installed directly upstream of the actuator requiring them.

Incorrect additional oil and too high an oil content in the compressed air reduce the service life of the valve terminal

Use Festo special oil OFSW-32 or the alternatives listed in the Festo catalogue (as specified in DIN 51524 HLP32; basic oil viscosity 32 CST at 40°C).

Bio-oils

When using bio-oils (oils which are based on synthetic or native esters, e.g. rapeseed oil methyl ester), the maximum residual oil content of 0.1 mg/m³ must not be exceeded (see ISO 8573-1 Class 2).

Mineral oils

When using mineral oils (e.g. HLP oils to DIN 51524, parts 1 to 3) or similar oils based on poly-alpha-olefins (PAO), the maximum residual oil content of 5 mg/m^3 must not be exceeded (see ISO 8573-1 Class 4).

A higher residual oil content is not permitted, regardless of the compressor oil, because the permanent lubrication would otherwise be flushed out over a period of time.

Datasheet

- N - Flow rate up to CPV10: 400 l/min CPV14: 800 l/min CPV18: 1600 l/min

- **[]** - Valve width CPV10: 10 mm CPV14: 14 mm CPV18: 18 mm

Voltage 24 V DC



| General technical data | | | | |
|-------------------------------------|----------|----------------------------------|---------------------------------------|-------------------------------|
| | | CPV10 | CPV14 | CPV18 |
| Design | | Electromagnetically actuated p | iston spool valve | |
| Lubrication | | Life-time lubrication, PWIS-free | (free of paint-wetting impairment sub | ostances) |
| Type of mounting | | Via pneumatic multiple connec | tor plate | |
| | | Via backwall | | |
| | | On H-rail | | |
| Mounting position | | Any | | |
| Overlap | | Positive overlap | | |
| Manual override | | Non-detenting/detenting/block | red | |
| Width | [mm] | 10 | 14 | 18 |
| Nominal size | [mm] | 4 | 6 | 8 |
| Nominal flow rate without fitting | [l/min] | 400 | 800 | 1600 1400 ³⁾ |
| b value | | 0.4 | 0.42 | 0.38 |
| Dvalue | | 0.4 | 0.42 | 0.38 0.41^{2} |
| | | | 0.37 | 0.41° 0.40° |
| c value | [l/sbar] | 1.6 | 3.2 | 6.3 |
| Cvalue | [i/sbai] | 1.0 | 5.2 | 5.66 ³⁾ |
| Pneumatic connections ¹⁾ | | | | |
| Pneumatic connection | | Via end plate or pneumatic mu | ltiple connector plate | |
| Supply port | 1/11 | G1/8 | G1/4 | G3/8 |
| Exhaust port | 3/5 | G3/8 (G1/4) | G1/2 (G3/8) | G1/2 |
| Working ports | 2/4 | M7 | G1/8 | G1/4 |
| Pilot air port | 12/14 | M5 (M7) | G1/8 | G1/4 |
| Pilot exhaust air port | 82/84 | M5 (M7) | G1/8 | G1/4 |

 $^{1) \}quad \hbox{Connection dimensions in brackets for pneumatic multiple connector plate} \\$

³⁾ Values for 5/3-way valve with mechanical spring return

| Safety characteristics | | | | |
|---------------------------------------|------|---|------------------------|-------|
| | | CPV10 | CPV14 | CPV18 |
| Tried-and-tested component | | Yes | | |
| Max. positive test pulse with logic 0 | [µs] | 1400 | 1400 | 1900 |
| Max. negative test pulse with logic 1 | [µs] | 700 | 400 | 1700 |
| Shock resistance | | Shock test with severity level 2, to EN 600 | 068-2-27 | |
| Vibration resistant | • | Transport application test with severity le | vel 2, to EN 60068-2-6 | |

²⁾ Values for 2x 2/2-way valve

| Operating and environmental conditions | – Valves | of width 10 mm | | | | | | | | | | |
|--|----------|-----------------|---|-----------|-------------|----------|-------|-------|----------|-----------------|-------|-------|
| Valve function order code | | M, MK F | I, JK | N, NK | C, CK | H, HK | D, DK | I, IK | CY | G ²⁾ | А | E |
| Operating medium | | Compressed air | compressed air to ISO 8573-1:2010 [7:4:4] → 36 | | | | | | | | | |
| Note on the operating/pilot medium | | Lubricated oper | Lubricated operation possible (in which case lubrication will always be required) | | | | | | | | | |
| Operating pressure | [MPa] | -0.09 +1 | | | | | | | +0.01 +1 | - | - | - |
| | [bar] | -0.9 +10 | | | | | | | +0.1 +10 | 2.5 +10 | 3 +8 | 2 +10 |
| Operating pressure for valve terminal with | [MPa] | 0.3 0.8 | | | | | | | • | - | - | - |
| internal pilot air supply | [bar] | 38 | | | | | | | | • | • | |
| Pilot pressure | [MPa] | 0.3 0.8 | | | | | | | | - | - | - |
| | [bar] | 38 | | - | | | | | | - | - | - |
| Ambient temperature | [°C] | −5 +50 | | | | | | | | | 0 +50 | |
| Temperature of medium | [°C] | −5 +50 | | | | | | | | | 0 +50 | |
| Storage temperature | [°C] | -20 +40 | | | | | | | | | | |
| Duty cycle | [%] | 100 (in conjunc | tion with | holding o | current rec | luction) | | | | | | |
| Relative air humidity at 25°C | [%] | 95 with no cond | ensation | | | | | | | | | |
| Corrosion resistance class CRC ¹⁾ | | 2 | | | | | | | | | 1 | |
| Note on materials | | RoHS-compliant | | | | | | | | | | |

More information www.festo.com/x/topic/crc
 5/3G function possible as kit for width 10 mm and 14 mm

| Valve function order code | _ | M, MK | J, JK | N, NK | C, CK | H, HK | D, DK | I, IK | G ²⁾ | А | E | | |
|--|-------|------------|---|-----------------|----------------|-------|-------|-------|-----------------|-------|-------|--|--|
| Operating medium | | Compresse | Compressed air to ISO 8573-1:2010 [7:4:4] → 36 | | | | | | | | | | |
| Note on the operating/pilot medium | | Lubricated | Lubricated operation possible (in which case lubrication will always be required) | | | | | | | | | | |
| Operating pressure | [MPa] | -0.09 + | 1 | | | | | | - | - | - | | |
| | [bar] | -0.9 +1 | 0 | | | | | | 2.5 +10 | 3 +8 | 2 +10 | | |
| Operating pressure for valve terminal with | [MPa] | 0.3 0.8 | | | | | | | - | - | - | | |
| internal pilot air supply | [bar] | 3 8 | , | - | | | | | | | • | | |
| Pilot pressure | [MPa] | 0.3 0.8 | , | | | | | | - | - | - | | |
| | [bar] | 38 | , | | | | | | - | - | - | | |
| Ambient temperature | [°C] | -5 +50 | , | | | | | | | 0 +50 | • | | |
| Temperature of medium | [°C] | -5 +50 | | | | | | | | 0 +50 | | | |
| Storage temperature | [°C] | -20 +40 |) | | | | | | | | | | |
| Duty cycle | [%] | 100 (in co | njunction v | vith holding cu | ırrent reducti | on) | | | | | | | |
| Relative air humidity at 25°C | [%] | 95 with no | condensa | tion | | | | | | | | | |
| Corrosion resistance class CRC ¹⁾ | | 2 1 | | | | | | | | | | | |
| Note on materials | | RoHS-com | oliant | | | | | | | | | | |

More information www.festo.com/x/topic/crc
 5/3G function possible as kit for width 10 mm and 14 mm

Datasheet

| Operating and environmental conditions | – Valves | of width 18 n | nm | | | | | | | | | | |
|--|----------|---------------|---|---------|---|---|---|---|----------|-------|-------|--|--|
| Valve function order code | | М | J | N | С | Н | D | I | G | А | E | | |
| Operating medium | | Compressed | Compressed air to ISO 8573-1:2010 [7:4:4] → 36 | | | | | | | | | | |
| Note on the operating/pilot medium | | Lubricated o | Lubricated operation possible (in which case lubrication will always be required) | | | | | | | | | | |
| Operating pressure | [MPa] | -0.09 +1 | | | | | | | | - | - | | |
| | [bar] | -0.9 +10 | | | | | | | | 3 +8 | 2 +10 | | |
| Operating pressure for valve terminal with | [MPa] | 0.3 0.8 | | | | | | | | - | - | | |
| internal pilot air supply | [bar] | 38 | | | | | | | | | · | | |
| Pilot pressure | [MPa] | 0.3 0.8 | 0.2 0.8 | 0.3 0.8 | | | | | 0.35 0.8 | - | - | | |
| | [bar] | 38 | 2 8 | 3 8 | | | | | 3.5 8 | - | | | |
| Ambient temperature | [°C] | -5 +50 | | | | | | | | 0 +50 | | | |
| Temperature of medium | [°C] | −5 +50 | | | | | | | | 0 +50 | | | |
| Storage temperature | [°C] | -20 +40 | | | | | | | | | | | |
| Duty cycle | [%] | 100 | | | | | | | | | | | |
| Relative air humidity at 25°C | [%] | 95 with no c | ondensation | | | | | | | | | | |
| Corrosion resistance class CRC ¹⁾ | | 2 1 | | | | | | | | | | | |
| Note on materials | | RoHS-compl | iant | | | | | | | | | | |

¹⁾ More information www.festo.com/x/topic/crc

| ATEX | |
|--|---|
| ATEX category for gas | II 3G |
| Type of (ignition) protection for gas | Ex nA IIC T4 X Gc |
| Valve terminal certifications | |
| UL certified | c UL us Recognized (OL) |
| Explosion protection certification outside the EU | EPL Gc (GB) |
| | NEC 500 Class I, Div. 2 |
| CE marking (see declaration of conformity) ¹⁾ | To EU RoHS Directive |
| | To EU Explosion Protection Directive (ATEX) |
| | To EU EMC Directive |
| UKCA marking (see declaration of conformity) ¹⁾ | To UK RoHS instructions |
| | To UK EX instructions |
| | To UK instructions for EMC |
| KC marking | KC EMC |
| Certification | RCM |
| | C-Tick |

¹⁾ More information: www.festo.com/catalogue/... → Support/Downloads.



The approvals and certificates apply only to fully assembled valve terminals that have been fully configured using the configurator and have the associated identification on the product.

Please observe the associated user documentation (e.g. ATEX operating conditions or UL operating conditions).

Valve terminals CPV with explosion protection certification according to NEC 500 Class I, Div. 2 are approved for types MP and IC.



Please use push-in fittings and silencers with electrically conductive straight thread.

| ATEX | | | | |
|--|-------------------------|-------------------------------|--------------|-------------|
| Certifications for pneumatic multiple connector plates for | the valve terminal CPV | | | |
| Pneumatic multiple connector plate | CPV10-VI-PC | CPV10-VI-PD | CPV14-VI-PC. | CPV14-VI-PD |
| ATEX category for gas | II 2G | | | |
| Type of (ignition) protection for gas | Ex ec IIC Gb | | | |
| ATEX category for dust | II 2D | | | |
| Type of (ignition) protection for dust | Ex tc IIIC Db | | | |
| ATEX ambient temperature [°C] | -10°C <= Ta <= +60°C | | | |
| Certificate-issuing authority | IECEx TUR 12.0002X | | | |
| | TÜV 06 ATEX 7334 X | | | |
| | German Technical Conti | ol Board (TÜV) 21 UKEX 7013 X | | |
| Explosion protection certification outside the EU | EPL Dc (IECEx) | | | |
| | EPL Db (IEC Ex) | | | |
| | EPL Db (GB) | | | |
| | EPL Gc (IECEx) | | | |
| | EPL Gb (IECEx) | | | |
| | EPL Gb (GB) | | | |
| CE marking (see declaration of conformity) ¹⁾ | To EU Explosion Protect | ion Directive (ATEX) | | |
| UKCA marking (see declaration of conformity) ¹⁾ | To UK explosion regulat | ions | | |
| | To UK RoHS regulations | | | |

 $^{1) \}quad \text{More information: www.festo.com/catalogue/...} \rightarrow \text{Support/Downloads}.$

Datasheet

| Electrical data | | | | |
|--|--------|---|------------------------|--------------------|
| | | CPV10 | CPV14 | CPV18 |
| Operating voltage | [V DC] | 24 (+10/-15%) | | |
| Ramp steepness (IC and MP only) | [V/ms] | > 0.4 minimum voltage rise time to reach | the high-current phase | |
| Limitation of the voltage peaks when switching off | [V DC] | 38 | | |
| Residual ripple | [Vss] | 4 | | |
| Electrical power consumption | [W] | 0.6 (0.45 at 21 V); (with CPV10-M11H 0.65) | 0.9 (0.65 at 21 V) | 1.5 (0.95 at 21 V) |
| Protection against electric shock (protection against direct and indirect contact to EN 60204-1/IEC 204) | | Through PELV power supply unit | | |
| Protection rating to EN 60529 | [IP] | 65 (for all types of signal transmission in | mounted state) | |

| Valve switching times [ms] | | | | | | | | | | | | | | | | | | | | |
|----------------------------|---------|----|----|----|----|----|----|----|----|----|-----|----|----|----|----|----|----|----|----------|----|
| Valve function order code | | М | MK | F | J | JK | N | NK | C | CK | CY | Н | HK | G | D | DK | 1 | IK | Α | E |
| CPV10 | | | | | | | | | | | | | | | | | | | | |
| Switching times | On | 17 | 17 | 12 | - | - | 17 | 17 | 17 | 17 | 17 | 17 | 17 | 20 | 15 | 15 | 15 | 15 | - | 15 |
| | Off | 27 | 27 | 17 | - | - | 25 | 25 | 25 | 25 | 25 | 25 | 25 | 30 | 17 | 17 | 17 | 17 | - | 17 |
| | Change- | - | - | - | 10 | 10 | - | - | - | - | - | - | - | - | - | - | - | - | - | - |
| | over | | | | | | | | | | | | | | | | | | | |
| CPV14 | | | | | | | | | | | | | | | | | | | | |
| Switching times | On | 25 | 25 | - | - | - | 24 | 24 | 24 | 24 | - | 24 | 24 | 22 | 13 | 13 | 13 | 13 | - | 13 |
| | Off | 35 | 35 | - | - | - | 30 | 30 | 30 | 30 | ĺ – | 30 | 30 | 30 | 16 | 16 | 16 | 16 | - | 16 |
| | Change- | - | - | - | 12 | 12 | - | - | - | - | ĺ – | 1- | - | - | - | - | - | - | - | - |
| | over | | | | | | | | | | | | | | | | | | | |
| CPV18 | | | | | | | | | | | | | | | | | | | | - |
| Switching times | On | 18 | - | - | - | - | 18 | - | 18 | - | - | - | - | 14 | 14 | - | 14 | - | - | 14 |
| | Off | 26 | - | - | - | İ- | 24 | - | 24 | - | - | - | - | 32 | 20 | - | 20 | - | 1- | 20 |
| | Change- | - | - | - | 12 | İ- | ļ- | - | - | - | - | - | - | - | 1- | - | - | - | 1- | - |
| | over | | | | | | | | | | | | | | | | | | | |


| Materials | | | | |
|------------------------------------|----------------------------|-------|-------|--|
| | CPV10 | CPV14 | CPV18 | |
| Basic electrical unit | Die-cast aluminium, PA, NB | R | | |
| Valve slices | Die-cast aluminium | | | |
| Valve module 5/3G | Die-cast aluminium, POM | | | |
| Blanking plate/separator plate | PA | | | |
| End plates | Die-cast aluminium | | | |
| Flat plate silencer | Die-cast aluminium, PE | | | |
| Pneumatic multiple connector plate | Wrought aluminium alloy | | | |
| Inscription label holder | POM, PVC | | | |
| Seal | NBR, HNBR | | | |


| Product weight | | | |
|--|-------|-------|-------|
| Approx. weights [g] | CPV10 | CPV14 | CPV18 |
| Electrical connection plate with AS-Interface connection | | | |
| on CP valve terminals with 2 valve positions | 85 | 130 | 275 |
| on CP valve terminals with 4 valve positions | 110 | 175 | 355 |
| on CP valve terminals with 8 valve positions | 400 | 460 | - |
| Electrical connection plates with CP connection | | | |
| on CP valve terminals with 4 valve positions | 145 | 230 | - |
| on CP valve terminals with 6 valve positions | 180 | 250 | - |
| on CP valve terminals with 8 valve positions | 200 | 300 | - |
| Electrical connection plates with MP connection | | | |
| on CP valve terminals with 4 valve positions | 110 | 170 | 400 |
| on CP valve terminals with 6 valve positions | 140 | 230 | 425 |
| on CP valve terminals with 8 valve positions | 165 | 275 | 515 |
| End plates (2 pieces) | 160 | 280 | 740 |
| Pneumatic multiple connector plate | | | |
| on CP valve terminals with 2 valve positions | 120 | 270 | 520 |
| on CP valve terminals with 4 valve positions | 165 | 390 | 750 |
| on CP valve terminals with 6 valve positions | 225 | 510 | 870 |
| on CP valve terminals with 8 valve positions | 270 | 630 | 1300 |
| Flat plate silencer | 147 | 234 | - |
| Blanking plate | 25 | 45 | 90 |
| Separator plate | 25 | 45 | 90 |
| Valve sub-bases, vacuum generators | 70 | 110 | 260 |
| Function element: 5/3G function | 46 | 105 | - |
| Function element: one-way flow control valve | 25 | 54 | 125 |

Datasheet


Vacuum generators

Vacuum as a function of operating pressure





- [1] Vacuum [bar]
- [2] Operating pressure [bar]




- [1] Vacuum [bar]
- [2] Operating pressure [bar]

- [1] Vacuum [bar]
- [2] Operating pressure [bar]


Vacuum generators

Air consumption as a function of operating pressure




- [1] Air consumption [l/min]
- [2] Operating pressure [bar]

Suction capacity as a function of negative pressure at P_{nom}



Evacuation time for a volume of 1 litre at P_{nom}




- [1] Evacuation time [s]
- [2] Vacuum [bar]


Dimensions Download CAD data → www.festo.com Valve manifold assembly with individual connection - CPV10/14/18 7 D4 D4_ 8 [1] Slots for inscription labels ⊕ Pneumatic multiple connector 4 5 82/84 12/14 [3] Holder for inscription labels (CPV10/14/18-VI-BZ-T-... or 9 CPV10/14/18-VI-ST-T-...) [4] Left end plate (threaded connec-2 D₃ D'3 tions not in combination with pneumatic multiple connector plate) [5] Right end plate (threaded connections not in combination with pneumatic multiple conη nector plate) [6] Connecting cable NEBV-... for CPV10/14 KMEB-2-... for CPV18 [7] Individual threaded connection 3 (without pneumatic multiple L1 connector plate) L1 12 L3 14 15 L6 17 18 D1 D2 D3 D4 CPV10 2 valves 50 41.8 71 52.8 9.5 11.8 M7 G1/8 G3/8 M5 62 15 3 valves 51.8 60 4 valves 70 61.8 5 valves 80 71.8 90 81.8 6 valves 7 valves 100 91.8 8 valves 110 101.8 CPV14 G1/8 G1/4 G1/2 G1/8 2 valves 68 58 78 89 58.8 20 9.5 11.8 72 3 valves 82 4 valves 96 86 5 valves 110 100 6 valves 124 114 7 valves 138 128 8 valves 152 142 CPV18 106.5 118 73 20 9.5 21.6 G1/4 G3/8 G1/2 G1/4 2 valves 96 85.5 3 valves 103.5 114 4 valves 121.5 132 5 valves 150 139.5 6 valves 168 157.5 186 7 valves 175.5 8 valves 204 193.5


Dimensions

Download CAD data → www.festo.com

Valve manifold assembly with individual connection and flat plate silencer – CPV10/14/18








- [1] Slots for inscription labels
- [2] Pneumatic multiple connector plate
- [3] Holder for inscription labels (CPV10/14/18-VI-BZ-T-... or CPV10/14/18-VI-ST-T-...)
- [4] Left flat plate silencer
- [5] Right flat plate silencer
- [6] Connecting cable
 NEBV-... for CPV10/14
 KMBE-2-... for CPV18
- [7] Individual threaded connection (without pneumatic multiple connector plate)

| | | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L8 | L28 | L29 | L30 | D1 |
|-------|----------|-----|-------|-------|-----|------|----|-----|------|-----|-----|------|------|
| CPV10 | 2 valves | 50 | 41.8 | 62 | 71 | 52.8 | 15 | 9.5 | 11.8 | 67 | 84 | 2.5 | M7 |
| | 3 valves | 60 | 51.8 | | | | | | | 77 | 94 | | |
| | 4 valves | 70 | 61.8 | | | | | | | 87 | 104 | | |
| | 5 valves | 80 | 71.8 | | | | | | | 97 | 114 | | |
| | 6 valves | 90 | 81.8 | | | | | | | 107 | 124 | | |
| | 7 valves | 100 | 91.8 | | | | | | | 117 | 134 | | |
| | 8 valves | 110 | 101.8 | | | | | | | 127 | 144 | | |
| CPV14 | 2 valves | 68 | 58 | 78 | 89 | 58.8 | 20 | 9.5 | 11.8 | 85 | 102 | 3 | G1/8 |
| | 3 valves | 82 | 72 | | | | | | | 99 | 116 | | |
| | 4 valves | 96 | 86 | | | | | | | 113 | 130 | | |
| | 5 valves | 110 | 100 | | | | | | | 127 | 144 | | |
| | 6 valves | 124 | 114 | | | | | | | 141 | 158 | | |
| | 7 valves | 138 | 128 | | | | | | | 155 | 172 | | |
| | 8 valves | 152 | 142 | | | | | | | 169 | 186 | | |
| CPV18 | 2 valves | 96 | 85.5 | 106.5 | 118 | 73 | 20 | 9.5 | 21.6 | 127 | 158 | 4.55 | G1/4 |
| | 3 valves | 114 | 105.5 | | | | | | | 145 | 176 | | |
| | 4 valves | 132 | 121.5 | | | | | | | 163 | 194 | | |
| | 5 valves | 150 | 139.5 | | | | | | | 181 | 212 | | |
| | 6 valves | 168 | 157.5 | | | | | | | 199 | 230 | | |
| | 7 valves | 186 | 175.5 | | | | | | | 217 | 248 | | |
| | 8 valves | 204 | 193.5 | | | | | | | 235 | 266 | | |

Dimensions


Valve terminal with multi-pin plug connection - CPV10/14/18



- [1] Slots for inscription labels
- [2] Pneumatic multiple connector plate
- [3] Holder for inscription labels (CPV10/14/18-VI-BZ-T-... or CPV10/14/18-VI-ST-T-...)

Download CAD data → www.festo.com

Valve terminal with AS-Interface connection – CPV10/14/18




- [1] Slots for inscription labels
- [2] Pneumatic multiple connector plate
- [3] Holder for inscription labels (CPV10/14/18-VI-BZ-T-... or CPV10/14/18-VI-ST-T-...)

| Multi-pin | olug connectio | on | | | | | | | | | | | | |
|-----------|----------------|-----|-------|-------|-----|------|----|-----|------|-----|-----|------|------|-----|
| | | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L9 | L10 | L11 | L12 | L13 | L14 |
| CPV10 | 4 valves | 70 | 61.8 | 62 | 71 | 52.8 | 15 | 9.5 | 39.5 | 10 | 50 | 23.5 | 58.8 | 30 |
| | 6 valves | 90 | 81.8 | | | | | | | 10 | 70 | | | |
| | 8 valves | 110 | 101.8 | | | | | | | 20 | 70 | | | |
| CPV14 | 4 valves | 96 | 86 | 78 | 89 | 58.8 | 20 | 9.5 | 61.8 | 23 | 50 | 23.5 | 58.8 | 30 |
| | 6 valves | 124 | 114 | | | | | | | 27 | 70 | | | |
| | 8 valves | 152 | 142 | | | | | | | 41 | 70 | | | |
| CPV18 | 4 valves | 132 | 121.5 | 106.5 | 118 | 73 | 20 | 9.5 | 88.4 | 41 | 50 | 28 | 63 | 30 |
| | 6 valves | 168 | 157.5 | | | | | | | 49 | 70 | | | |
| | 8 valves | 204 | 193.5 | | | | | | | 67 | 70 | | | |

| AS-Interfa | ce connection | I | | | | | | | | | | | | | |
|------------|---------------|-----|-------|-------|-----|------|----|-----|------|------|------|------|------|-----|-----|
| | | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L12 | L15 | L16 | L17 | L18 | L19 | L20 |
| CPV10 | 2 valves | 50 | 41.8 | 62 | 71 | 52.8 | 15 | 9.5 | - | 10.9 | 38.1 | 2.5 | 35.5 | 21 | 10 |
| | 4 valves | 70 | 61.8 | | | | | | 23.5 | | | | | | |
| | 8 valves | 110 | 101.8 | | | | | | | - | - | - | - | | |
| CPV14 | 2 valves | 68 | 58 | 78 | 89 | 58.8 | 20 | 9.5 | - | 14 | 52 | 5 | 35.5 | 21 | 10 |
| | 4 valves | 96 | 86 | | | | | | 23.5 | | | | | | |
| | 8 valves | 152 | 142 | | | | | | | - | - | - | - | | |
| CPV18 | 2 valves | 96 | 85.5 | 106.5 | 118 | 73 | 20 | 9.5 | - | 27.4 | 68.2 | 10.4 | 40 | 21 | 10 |
| | 4 valves | 132 | 121.5 | | | | | | 28 |] | | | | | |
| | 8 valves | 204 | 193.5 | | | | | | | - | - | - | - | | |


Dimensions

Valve terminal with AS-Interface connection and additional inputs – CPV10/14



- [1] Slots for inscription labels
- [2] Pneumatic multiple connector plate
- [3] Holder for inscription labels (CPV10/14/18-VI-BZ-T-... or CPV10/14/18-VI-ST-T-...)

Download CAD data → <u>www.festo.com</u> Valve terminal with AS-Interface connection and additional



- [1] Slots for inscription labels
- [2] Pneumatic multiple connector plate
- [3] Holder for inscription labels (CPV10/14/18-VI-BZ-T-... or CPV10/14/18-VI-ST-T-...)


| | | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L12 | L13 | L15 | L16 | L17 |
|-------|----------|-----|-------|----|----|------|----|-----|------|------|------|------|-----|
| CPV10 | 4 valves | 70 | 61.8 | 62 | 71 | 52.8 | 15 | 9.5 | 35.1 | 47.1 | 10.9 | 38.1 | 3 |
| | 8 valves | 110 | 101.8 | | | | | | | | 10.4 | 38.6 | 3 |
| CPV14 | 4 valves | 96 | 86 | 78 | 89 | 58.8 | 20 |] | | | 18.8 | 46.8 | 5 |

| | | L18 | L19 | L20 | L21 | L22 | L23 | L24 | L25 |
|-------|----------|-----|-----|------|-----|------|------|------|-----|
| CPV10 | 4 valves | 21 | 10 | 35 | - | - | - | - | - |
| | 8 valves | | | 31.9 | 88 | 53.3 | 20.3 | 11.5 | 6.2 |
| CPV14 | 4 valves | | | 43.3 | - | ı | 1 | - | - |

Dimensions Download CAD data → www.festo.com Valve terminal with AS-Interface connection and additional inputs - CPV14 L 13 L12 L21 \oplus • O [1] Slots for inscription labels [2] Pneumatic multiple connector 1 plate L23 L24 L26 L24 3 [3] Holder for inscription labels (CPV10/14/18-VI-BZ-T-... or L1 CPV10/14/18-VI-ST-T-...) L2 L1 L3 L4 L5 L6 L7 L12 L13 L15 CPV14 8 valves 152 142 78 89 58.8 20 9.5 35.1 47.1 18.8 L16 L19 L20 L22 L23 L24 L26 L17 L18 L21 CPV14 8 valves 46.8 5 21 10 46.3 122 66 25 14 18

Dimensions


Valve terminal with installation system CPI - CPV10/14



- [1] Slots for inscription labels
- [2] Pneumatic multiple connector plate
- [3] Holder for inscription labels (CPV10/14-VI-BZ-T-... or CPV10/14-VI-ST-T-...)

Download CAD data → www.festo.com

Valve terminal with I-Port interface/IO-Link® - CPV10/14



- [1] Slots for inscription labels
- [2] Pneumatic multiple connector plate
- [3] Holder for inscription labels


| Valve term | ninal with inst | allation syste | em CPI | | | | | | | | | | | |
|------------|-----------------|----------------|--------|----|----|------|----|-----|------|------|-----|------|-----|-----|
| | | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L9 | L10 | L11 | L12 | L13 | L14 |
| CPV10 | 4 valves | 70 | 61.8 | 62 | 71 | 52.8 | 15 | 9.5 | 39.5 | 13.5 | 43 | 23.5 | 46 | 30 |
| | 6 valves | 90 | 81.8 | 1 | | | | | | 17 | 56 | | | |
| | 8 valves | 110 | 101.8 | 1 | | | | | | 27 | 56 | | | |
| CPV14 | 4 valves | 96 | 86 | 78 | 89 | 58.8 | 20 | 9.5 | 61.8 | 20 | 56 | 23.5 | 46 | 30 |
| | 6 valves | 124 | 114 |] | | | | | | 34 | | | | |
| | 8 valves | 152 | 142 |] | | | | | | 48 | | | | |

| Valve term | ninal with I-Po | ort interface/IO-I | _ink [®] | | | | | | | | | |
|------------|-----------------|--------------------|-------------------|----|----|------|----|-----|------|------|------|------|
| | | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L27 | L28 | L29 | L30 |
| CPV10 | 8 valves | 110 | 101.8 | 62 | 71 | 52.8 | 15 | 9.5 | 26.2 | 38.3 | 32 | 30.2 |
| CPV14 | 8 valves | 152 | 142 | 78 | 89 | 58.8 | 20 | 9.5 | 26.2 | 38.3 | 32.4 | 56.5 |

Dimensions

Valve terminal with Fieldbus Direct – CPV10/14/18

Download CAD data → www.festo.com




- [1] Slots for inscription labels
- [2] Pneumatic multiple connector plate
- [3] Holder for inscription labels (CPV10/14/18-VI-BZ-T-... or CPV10/14/18-VI-ST-T-...)

| | | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L9 |
|-------|----------|-----|-------|-------|-----|------|----|-----|------|
| CPV10 | 8 valves | 110 | 101.8 | 62 | 71 | 52.8 | 15 | 9.5 | 35.8 |
| CPV14 | 8 valves | 152 | 142 | 78 | 89 | 58.8 | 20 | | 52.8 |
| CPV18 | 8 valves | 204 | 193.5 | 106.5 | 118 | 73 | 20 | | 79.8 |

| | | L10 | L11 | L12 | L13 | L14 | L27 | L31 | L32 | L33 |
|-------|----------|-----|-----|------|------|-----|------|------|-----|------|
| CPV10 | 8 valves | 25 | 64 | 26.2 | 36.7 | 45 | 30.9 | 55.1 | 60 | 34.6 |
| CPV14 | 8 valves | 46 | | 26.2 | 36.7 | | 30.9 | 55.1 | | 34.6 |
| CPV18 | 8 valves | 72 |] | 31.2 | 41.7 |] | 35.9 | 59.6 | | 36.6 |

Dimensions

Valve terminal with Fieldbus Direct – CPV10/14/18 PROFIBUS DP




Download CAD data → www.festo.com


- [1] Slots for inscription labels
- [2] Pneumatic multiple connector plate
- [3] Holder for inscription labels (CPV10/14/18-VI-BZ-T-... or CPV10/14/18-VI-ST-T-...)

| | | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L9 | L10 | L12 | L13 | L32 | L33 |
|-------|----------|-----|-------|-------|-----|------|----|-----|------|-----|------|------|-----|------|
| CPV10 | 8 valves | 110 | 101.8 | 62 | 71 | 52.8 | 15 | 9.5 | 35.5 | 25 | 26.2 | 36.7 | 60 | 34.6 |
| CPV14 | 8 valves | 152 | 142 | 78 | 89 | 58.8 | 20 | | 52.8 | 46 | 26.2 | 36.7 |] | 34.6 |
| CPV18 | 8 valves | 204 | 193.5 | 106.5 | 118 | 73 | 20 | | 79.8 | 72 | 31.2 | 41.7 | | 36.6 |

Dimensions

Wall mounting CPV10/14-VI-BG-RWL-B for CPV10/14







Download CAD data → www.festo.com

[1] Valve terminal CPV-...

| | | | | CPV10 | | | | | | | CPV14 | | | |
|----|----------|----------|----------|----------|----------|----------|----------|----------|----------|----------|----------|----------|----------|----------|
| | 2 valves | 3 valves | 4 valves | 5 valves | 6 valves | 7 valves | 8 valves | 2 valves | 3 valves | 4 valves | 5 valves | 6 valves | 7 valves | 8 valves |
| L1 | 74 | 84 | 94 | 104 | 114 | 124 | 134 | 90 | 104 | 118 | 132 | 146 | 160 | 174 |
| L2 | 48 | 58 | 68 | 78 | 88 | 98 | 108 | 64 | 78 | 92 | 106 | 120 | 134 | 148 |
| L3 | 58 | 68 | 78 | 88 | 98 | 108 | 118 | 74 | 88 | 102 | 116 | 130 | 144 | 158 |

| | B1 | B2 | В3 | B4 | B5 | B6 | B7 | B8 | D1 | H1 | L4 | L5 | L6 |
|-------|-----|----|----|----|------|----|----|-----|-----|----|----|----|----|
| CPV10 | 109 | 92 | 80 | 69 | 29.6 | 40 | 20 | 4.6 | 4.5 | 8 | 26 | 14 | 10 |
| CPV14 | 1 | | | | | | | | | | | | |






[1] Valve terminal CPV-...

| | | | | CPV18 | | | |
|----|----------|----------|----------|----------|----------|----------|----------|
| | 2 valves | 3 valves | 4 valves | 5 valves | 6 valves | 7 valves | 8 valves |
| L1 | 96 | 114 | 132 | 150 | 168 | 186 | 204 |
| L2 | 66 | 84 | 102 | 120 | 138 | 156 | 174 |


| | B1 | B2 | D1 | D2 | H1 | H2 | L4 | L5 |
|-------|-------|-----|-----|-----|----|----|----|------|
| CPV18 | 136.5 | 120 | 6.4 | 6.2 | 11 | 3 | 30 | 12.8 |

Dimensions Download CAD data → www.festo.com Mounting CPV10-VI-BG-ET200X for individual connection and ET200X L1 L2 L3 L4 <u>H1</u> D2 **B**3 B4 **B** L5 В1 B2 В3 В4 D1 D2 D3 Н1 L1 L2 L3 L4 L5 132 101.8 CPV10 119.5 109.5 54.8 38.7 6.6 5.4 4 6 152 122 30



Dimensions


Attachment for H-rail mounting CPV10/14-VI-BG-NRH-35



Download CAD data $\rightarrow \underline{\text{www.festo.com}}$


- [1] Valve terminal CPV10/14
- [2] H-rail to EN 60715

| | | B1 ±0.1 | B2 | D1 | H1 | H2 | H3 -0.1 | H4 ±0.1 | L1 | L2 ±0.1 | L3 ±0.1 | L4 |
|----|--------|------------|----|----|----|-----|------------|------------|------|------------|------------|------|
| CP | V10/14 | 13 | 8 | M4 | 10 | 7.5 | 7.5 | 1 | 49.1 | 35 | 27 | 11.2 |




DataSireet

Pneumatic multiple connector plate - CPV10/14/18



$\label{eq:Download CAD data \to $\underline{\mbox{www.festo.com}}$ Pneumatic multiple connector plate with flange - CPV10/14/18$




| Multi-pin į | plug | | | | | | | | | | | |
|-------------|----------|-------|-------|-------|------|----|----|------|------|------|------|----|
| | | L1 | L2 | L3 | L4 | L5 | L6 | D1 | D2 | D3 | D4 | D5 |
| CPV10 | 2 valves | 49.5 | 42.5 | 70 | 63 | 15 | 10 | M7 | G1/8 | G1/4 | M7 | M4 |
| | 4 valves | 69.5 | 62.5 | | | | | | | | | |
| | 6 valves | 89.5 | ,82.5 |] | | | | | | | | |
| | 8 valves | 109.5 | 102.5 |] | | | | | | | | |
| CPV14 | 2 valves | 67.5 | 53.5 | 86.6 | 76.6 | 20 | 14 | G1/8 | G1/4 | G3/8 | G1/8 | M4 |
| | 4 valves | 95.5 | 81.5 |] | | | | | | | | |
| | 6 valves | 123.5 | 109.5 |] | | | | | | | | |
| | 8 valves | 151.5 | 137.5 | | | | | | | | | |
| CPV18 | 2 valves | 95.5 | 87.5 | 119.6 | 108 | 20 | 18 | G1/4 | G3/8 | G1/2 | G1/4 | M5 |
| | 4 valves | 131 | 123 | | | | | | | | | |
| | 6 valves | 167 | 159 |] | | | | | | | | |
| | 8 valves | 203 | 195 | | | | | | | | | |

| | | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L8 | D1 | D2 | D3 | D4 | D5 |
|-------|----------|-----|-----|-----|----|----|----|----|----|------|------|------|------|-----|
| CPV10 | 2 valves | 74 | 62 | 73 | 40 | 15 | 10 | 18 | 6 | M7 | G1/8 | G1/4 | M5 | 6.5 |
| | 4 valves | 94 | 82 | | | | | | | | | | | |
| | 6 valves | 114 | 102 | | | | | | | | | | | |
| | 8 valves | 134 | 122 | | | | | | | | | | | |
| CPV14 | 2 valves | 92 | 80 | 89 | 59 | 20 | 14 | 18 | 6 | G1/8 | G1/4 | G3/8 | G1/8 | 6.5 |
| | 4 valves | 120 | 108 | | | | | | | | | | | |
| | 6 valves | 148 | 136 | | | | | | | | | | | |
| | 8 valves | 176 | 164 | | | | | | | | | | | |
| CPV18 | 2 valves | 119 | 107 | 118 | 88 | 20 | 18 | 18 | 6 | G1/4 | G3/8 | G1/2 | G1/4 | 6.5 |
| | 4 valves | 155 | 143 | | | | | | | | | | | |
| | 6 valves | 191 | 179 | | | | | | | | | | | |
| | 8 valves | 227 | 215 | | | | | | | | | | | |

Dimensions


Pneumatic multiple connector plate for control cabinet installation, without supply ports – CPV10/14


Download CAD data → www.festo.com



[1] Seal


| | | L1 | L2 | L3 | B1 | B2 | В3 | D1 | D2 | H1 |
|-------|----------|-------|----|----|------|------|------|------|----|----|
| CPV10 | 2 valves | 49.5 | - | 10 | 70 | 40 | 15 | M7 | M5 | 15 |
| | 4 valves | 69.5 | 28 | | | | | | | |
| | 6 valves | 89.5 | 49 | | | | | | | |
| | 8 valves | 109.5 | 68 | | | | | | | |
| CPV14 | 2 valves | 67.5 | 13 | 14 | 86.6 | 55.6 | 15.5 | G1/8 | M5 | 20 |
| | 4 valves | 95.5 | 40 | | | | | | | |
| | 6 valves | 123.5 | 68 | | | | | | | |
| | 8 valves | 151.5 | 96 | | | | | | | |






[1] Seal

| | | L1 | L2 | L3 | B1 | B2 | В3 | D1 | D2 | D3 | D4 | H1 |
|-------|----------|-----|-----|----|----|----|----|------|----|------|------|----|
| CPV10 | 2 valves | 82 | 62 | 10 | 84 | 64 | 10 | M7 | M5 | G1/4 | G1/8 | 15 |
| | 4 valves | 102 | 82 | | | | | | | | | |
| | 6 valves | 122 | 102 | | | | | | | | | |
| | 8 valves | 142 | 122 | | | | | | | | | |
| CPV14 | 2 valves | 102 | 82 | 14 | 99 | 79 | 10 | G1/8 | M5 | G3/8 | G1/4 | 20 |
| | 4 valves | 130 | 110 | | | | | | | | | |
| | 6 valves | 158 | 138 | | | | | | | | | |
| | 8 valves | 186 | 166 | | | | | | | | | |



Dimensions


Valve kit for 5/3 function - CPV10/14




[1] Retaining screw enclosed separately

| Туре | B1 | D1 | D2 | H1 | L1 | L2 |
|-------------------|------|------|------|----|------|----|
| CPV10-BS-5/3G-M7 | 9.9 | M7 | M2.5 | 22 | 55.8 | 23 |
| CPV14-BS-5/3G-1/8 | 13.8 | G1/8 | M3 | 28 | 72.8 | 30 |

Additional one-way flow control valve function - CPV10/14






[1] Retaining screw enclosed separately

Additional one-way flow control valve function for vacuum – CPV10/14

Download CAD data → www.festo.com

CPV-...-BS-2xGRZ-V-...




| Туре | B1 | D1 | D2 | H1 | H2 | L1 | L2 | L3 |
|---------------------|------|------|------|----|----|------|-------|-------|
| CPV10-BS-2xGRM7 | 9.9 | M7 | M2.5 | 26 | 6 | 55.8 | 41.4 | 22.9 |
| CPV10-BS-2xGRZ-VM7 | | | | | | | - | |
| CPV14-BS-2xGR1/8 | 13.8 | G1/8 | M3 | 32 | 8 | 72.8 | 53.15 | 28.65 |
| CPV14-BS-2xGRZ-V1/8 | | | | | | | - | |


Download CAD data → www.festo.com


Datasheet

Dimensions

Fieldbus interface FBS-SUB-9-GS-DP-B







[1] Valve terminal with Fieldbus Direct CPV10/14/18 and bus node [2] Sub-D socket, 9-pin



| FBS | CPV10 | CPV14 | CPV18 |
|-----|----------|----------|----------|
| | 8 valves | 8 valves | 8 valves |
| B1 | 20 | 20 | 20 |
| H1 | 64 | 64 | 64 |
| H2 | - | _ | - |
| L1 | 24.5 | 45.5 | 71.5 |
| L2 | 61 | 61 | 61 |

| Ordering data | | | | | |
|-------------------|---------------|--|----------------|----------|-----------------------------|
| | Code | Valve function | Product weight | Part no. | Туре |
| | | | [g] | | |
| dividual sub-base | valve, size 1 | 0/14/18 | | | |
| 26m. | M | 5/2-way valve, single solenoid, piston spool valve | 70 | 161414 | CPV10-M1H-5LS-M7 |
| A. | | | 120 | 161360 | CPV14-M1H-5LS-1/8 |
| | | | 260 | 163190 | CPV18-M1H-5LS-1/4 |
| | F | 5/2-way valve, single solenoid, fast switching, piston spool valve | 70 | 187439 | CPV10-M11H-5LS-M7 |
| | J | 5/2-way valve, double solenoid, piston spool valve | 70 | 161415 | CPV10-M1H-5JS-M7 |
| | | | 120 | 161361 | CPV14-M1H-5JS-1/8 |
| _ | | | 260 | 163191 | CPV18-M1H-5JS-1/4 |
| | N | 2x 3/2-way valve, normally open, piston spool valve | 70 | 161417 | CPV10-M1H-2x3-OLS-M7 |
| | | | 120 | 161363 | CPV14-M1H-2x3-OLS-1/8 |
| | | | 260 | 163188 | CPV18-M1H-2x3-OLS-1/4 |
| | С | 2x 3/2-way valve, normally closed, piston spool valve | 70 | 161416 | CPV10-M1H-2x3-GLS-M7 |
| | | | 120 | 161362 | CPV14-M1H-2x3-GLS-1/8 |
| | | | 260 | 163189 | CPV18-M1H-2x3-GLS-1/4 |
| | CY | 2x 3/2-way valve, normally closed, | 70 | 553260 | CPV10-M1H-2x3-GLS-Y-M7 |
| | | integrated back pressure protection, piston spool valve | | 333200 | 0.120 2.3 020 1 |
| | Н | 2x 3/2-way valve, 1x normally open, 1x normally closed, piston spool | 70 | 176064 | CPV10-M1H-30LS-3GLS-M7 |
| | | valve | 120 | 176067 | CPV14-M1H-30LS-3GLS-1/8 |
| | | | 260 | 176070 | CPV18-M1H-30LS-3GLS-1/4 |
| | G | 5/3-way valve, mid-position closed, piston spool valve | 260 | 176061 | CPV18-M1H-5/3GS-1/4 |
| | D | 2x 2/2-way valve, normally closed, piston spool valve | 70 | 185880 | CPV10-M1H-2x2-GLS-M7 |
| | | 2x 2/2 may raise, normally closed, piston spect talle | 120 | 185883 | CPV14-M1H-2x2-GLS-1/8 |
| | | | 260 | 185886 | CPV18-M1H-2x2-GLS-1/4 |
| | 1 | 2x 2/2-way valve, 1x normally open, 1x normally closed, piston spool | 70 | 187843 | CPV10-M1H-20LS-2GLS-M7 |
| | ' | valve | 120 | 187846 | CPV14-M1H-20LS-2GLS-1/8 |
| | | valve . | 260 | 187849 | CPV18-M1H-20LS-2GLS-1/6 |
| | | | 200 | 10/049 | CF V 10-M111-20L3-20L3-1/4 |
| dividual sub-base | valve with d | uct separation 1, 11 sizes 10/14 | | | |
| ₹ | MK | 5/2-way valve (with duct separation 1, 11), single solenoid, piston | 70 | 553256 | CPV10-M1H-5LS-K-M7 |
| De Abe | | spool valve | 120 | 553258 | CPV14-M1H-5LS-K-1/8 |
| | JK | 5/2-way valve (with duct separation 1, 11), double solenoid, piston | 70 | 559644 | CPV10-M1H-5JS-K-M7 |
| | | spool valve | 120 | 559651 | CPV14-M1H-5JS-K-1/8 |
| | NK | 2x 3/2-way valve (with duct separation 1, 11), normally open, piston | 70 | 559641 | CPV10-M1H-2x3-OLS-K-M7 |
| | | spool valve | 120 | 559648 | CPV14-M1H-2x3-OLS-K-1/8 |
| | CK | 2x 3/2-way valve (with duct separation 1, 11) normally closed, piston | 70 | 553257 | CPV10-M1H-2x3-GLS-K-M7 |
| | | spool valve | 120 | 553259 | CPV14-M1H-2x3-GLS-K-1/8 |
| | HK | 2x 3/2-way valve (with duct separation 1, 11), 1x normally open, 1x | 70 | 559642 | CPV10-M1H-30LS-3GLS-K-M7 |
| | | normally closed, piston spool valve | 120 | 559649 | CPV14-M1H-30LS-3GLS-K-1/8 |
| | DK | 2x 2/2-way valve (with duct separation 1, 11), normally closed, piston | 70 | 559645 | CPV10-M1H-2x2-GLS-K-M7 |
| | | spool valve | 120 | 559652 | CPV14-M1H-2x2-GLS-K-1/8 |
| | IK | 2x 2/2-way valve (with duct separation 1, 11), 1x normally open, 1x | 70 | 559646 | CPV10-M1H-20LS-2GLS-K-M7 |
| | " | normally closed, piston spool valve | 120 | 559653 | CPV14-M1H-20LS-2GLS-K-1/8 |
| | | ווסיוווענוץ בנספבע, פופנטוו פרסטני יענייב | 120 | 223023 | CF V 14-W1H-20L3-20L3-R-1/8 |

| Vacuum generator A Vacuum generator E Vacuum generator with ejector pulse Function block G Valve kit for 5/3-way valve function, closed (in combination with valve slice C) for size 10 and 14 | Product weight [g] | 185862 185868 185874 185865 185871 185877 | CPV10-M1H-V70-M7 CPV14-M1H-V95-1/8 CPV18-M1H-V140-1/4 CPV10-M1H-V170-2GLS-M7 CPV14-M1H-V195-2GLS-1/8 CPV18-M1H-V1140-2GLS-1/4 CPV10-BS-5/3G-M7 CPV14-BS-5/3G-1/8 |
|--|-------------------------------------|--|---|
| A Vacuum generator E Vacuum generator with ejector pulse Function block G Valve kit for 5/3-way valve function, closed (in combination with valve | 25 98 227 25 114 264 | 185868 185874 185865 185871 185877 | CPV14-M1H-V95-1/8 CPV18-M1H-V140-1/4 CPV10-M1H-V170-2GLS-M7 CPV14-M1H-V195-2GLS-1/8 CPV18-M1H-V1140-2GLS-1/4 CPV10-BS-5/3G-M7 |
| A Vacuum generator E Vacuum generator with ejector pulse Function block G Valve kit for 5/3-way valve function, closed (in combination with valve | 98 227 25 114 264 | 185868 185874 185865 185871 185877 | CPV14-M1H-V95-1/8 CPV18-M1H-V140-1/4 CPV10-M1H-V170-2GLS-M7 CPV14-M1H-V195-2GLS-1/8 CPV18-M1H-V1140-2GLS-1/4 CPV10-BS-5/3G-M7 |
| A Vacuum generator E Vacuum generator with ejector pulse Function block G Valve kit for 5/3-way valve function, closed (in combination with valve | 98 227 25 114 264 | 185868 185874 185865 185871 185877 | CPV14-M1H-V95-1/8 CPV18-M1H-V140-1/4 CPV10-M1H-V170-2GLS-M7 CPV14-M1H-V195-2GLS-1/8 CPV18-M1H-V1140-2GLS-1/4 CPV10-BS-5/3G-M7 |
| Function block G Valve kit for 5/3-way valve function, closed (in combination with valve | 98 227 25 114 264 | 185874 185865 185871 185877 176055 | CPV18-M1H-V140-1/4 CPV10-M1H-V170-2GLS-M7 CPV14-M1H-V195-2GLS-1/8 CPV18-M1H-V1140-2GLS-1/4 CPV10-BS-5/3G-M7 |
| Function block G Valve kit for 5/3-way valve function, closed (in combination with valve | 25 114 264 | 185865 185871 185877 176055 | CPV18-M1H-V140-1/4 CPV10-M1H-V170-2GLS-M7 CPV14-M1H-V195-2GLS-1/8 CPV18-M1H-V1140-2GLS-1/4 CPV10-BS-5/3G-M7 |
| Function block G Valve kit for 5/3-way valve function, closed (in combination with valve | 114 264 | 185871 185877 176055 | CPV14-M1H-VI95-2GLS-1/8 CPV18-M1H-VI140-2GLS-1/4 CPV10-BS-5/3G-M7 |
| Function block G Valve kit for 5/3-way valve function, closed (in combination with valve | 264 | 185877 | CPV18-M1H-VI140-2GLS-1/4 CPV10-BS-5/3G-M7 |
| G Valve kit for 5/3-way valve function, closed (in combination with valve | 23 | 176055 | CPV10-BS-5/3G-M7 |
| G Valve kit for 5/3-way valve function, closed (in combination with valve | | | |
| G Valve kit for 5/3-way valve function, closed (in combination with valve | | | |
| | | | |
| Since C) for size 10 and 14 | 190 | 1/605/ | |
| | | | G(414-03-7) 20-1/0 |
| Separator plates | | | |
| T Separator plate, duct 1/11 closed | 25 | 161369 | CPV10-DZP |
| | - | 162551 | CPV14-DZP |
| | 25 | 163282 | CPV18-DZP |
| S Separator plate, duct 1/11, 3/5 closed | 25 | 178678 | CPV10-DZPR |
| | | 178680 | CPV14-DZPR |
| | | 184543 | CPV18-DZPR |
| Blanking plate | | | |
| L Blanking plate | 25 | 161368 | CPV10-RZP |
| | | 162550 | CPV14-RZP |
| | | 163283 | CPV18-RZP |
| Additional functions for valve positions | | | |
| P One-way flow control valve, 2x supply air | 30 | 184140 | CPV10-BS-2XGRZZ-M7 |
| | 54 | 184142 | CPV14-BS-2XGRZZ-1/8 |
| P One-way flow control valve, 2x supply air Q One-way flow control valve, 2x exhaust air | 30 | 184141 | CPV10-BS-2XGRAZ-M7 |
| | 54 | 184143 | CPV14-BS-2XGRAZ-1/8 |
| V One-way flow control valve for vacuum | 30 | 185889 | CPV10-BS-GRZ-V-M7 |
| | - | 185891 | CPV14-BS-GRZ-V-1/8 |

| ordering data | Code | Designation | | Product weight | Part no. | Туре |
|------------------|---------------|---|----------|----------------|----------|-------------------|
| | | | | [g] | | ' |
| eumatic multiple | connector nla | ate | | 101 | | |
| | M | Pneumatic multiple connector plate, | 2 valves | 135 | 161969 | CPV10-VI-P2-M7 |
| | | for wall/machine mounting, | 4 valves | 164 | 161970 | CPV10-VI-P4-M7 |
| → | | without side flange | 6 valves | 219 | 161971 | CPV10-VI-P6-M7 |
| | | | 8 valves | 272 | 163893 | CPV10-VI-P8-M7 |
| |] | | 2 valves | 261 | 163894 | CPV14-VI-P2-1/8 |
| \^•• // | | | 4 valves | 379 | 163895 | CPV14-VI-P4-1/8 |
| \checkmark | | | 6 valves | 505 | 163896 | CPV14-VI-P6-1/8 |
| | | | 8 valves | 627 | 163897 | CPV14-VI-P8-1/8 |
| | | | 2 valves | 519 | 165292 | CPV18-VI-P2-1/4 |
| | | | 4 valves | 695 | 165293 | CPV18-VI-P4-1/4 |
| | | | 6 valves | 907 | 165294 | CPV18-VI-P6-1/4 |
| | | | 8 valves | 1116 | 165295 | CPV18-VI-P8-1/4 |
| | Р | Pneumatic multiple connector plate, | 2 valves | 182 | 152420 | CPV10-VI-P2-M7-B |
| | | for wall/machine mounting, | 4 valves | 228 | 152421 | CPV10-VI-P4-M7-B |
| | | with side flange | 6 valves | 283 | 152422 | CPV10-VI-P6-M7-B |
| | | | 8 valves | 336 | 152423 | CPV10-VI-P8-M7-B |
| | | | 2 valves | 365 | 152424 | CPV14-VI-P2-1/8-B |
| | | | 4 valves | 483 | 152425 | CPV14-VI-P4-1/8-B |
| | | | 6 valves | 609 | 152426 | CPV14-VI-P6-1/8-B |
| | | | 8 valves | 731 | 152427 | CPV14-VI-P8-1/8-B |
| | | | 2 valves | 659 | 175632 | CPV18-VI-P2-1/4-B |
| | | | 4 valves | 832 | 175634 | CPV18-VI-P4-1/4-B |
| | | | 6 valves | 1047 | 175636 | CPV18-VI-P6-1/4-B |
| | | | 8 valves | 1256 | 175638 | CPV18-VI-P8-1/4-B |
| | GQC | Pneumatic multiple connector plate with sealing | 2 valves | 250 | 538807 | CPV10-VI-P2-M7-C |
| | ` | ring, | 4 valves | 320 | 538808 | CPV10-VI-P4-M7-C |
| | | for control cabinet assembly, | 6 valves | 390 | 538809 | CPV10-VI-P6-M7-C |
| | | with supply ports | 8 valves | 460 | 538810 | CPV10-VI-P8-M7-C |
| | | | 2 valves | 500 | 539498 | CPV14-VI-P2-1/8-C |
| | | | 4 valves | 650 | 539499 | CPV14-VI-P4-1/8-C |
| | | | 6 valves | 800 | 539500 | CPV14-VI-P6-1/8-C |
| | | | 8 valves | 920 | 539501 | CPV14-VI-P8-1/8-C |
| | GQD | Pneumatic multiple connector plate with sealing | 2 valves | 80 | 538811 | CPV10-VI-P2-M7-D |
| | , | ring, | 4 valves | 150 | 538812 | CPV10-VI-P4-M7-D |
| | | for control cabinet assembly, | 6 valves | 220 | 538813 | CPV10-VI-P6-M7-D |
| | | without supply ports | 8 valves | 290 | 538814 | CPV10-VI-P8-M7-D |
| | | | 2 valves | 350 | 539502 | CPV14-VI-P2-1/8-D |
| | | | 4 valves | 550 | 539503 | CPV14-VI-P4-1/8-D |
| | | | 6 valves | 400 | 539504 | CPV14-VI-P6-1/8-D |
| | | | 8 valves | 650 | 539505 | CPV14-VI-P8-1/8-D |
| | GQE | Pneumatic multiple connector plate with sealing | 2 valves | 300 | 566709 | CPV10-VI-P2-1/8-C |
| | - | ring, | 4 valves | 370 | 566710 | CPV10-VI-P4-1/8-C |
| | | for control cabinet assembly, | 6 valves | 440 | 566711 | CPV10-VI-P6-1/8-C |
| | | with all ports | 8 valves | 510 | 566712 | CPV10-VI-P8-1/8-C |

| Ordering data | | | | | | | | |
|-------------------------|--------------------|--|----------------|----------|------------------------------------|--|--|--|
| | Code | Designation | Product weight | Part no. | Туре | | | |
| | | | [g] | | / | | | |
| Inscription label holde | rc | | 101 | | | | | |
| niscription tabet notue | Z | Holder for inscription labels | 32 | 162560 | CPV10-VI-BZ-T-2 | | | |
| | | Trotter for inscription tabets | 33 | 162561 | CPV10-VI-BZ-T-3 | | | |
| | | | 34 | 162562 | CPV10-VI-BZ-T-4 | | | |
| | | L | 35 | 162563 | CPV10-VI-BZ-T-5 | | | |
| | | | 36 | 162564 | CPV10-VI-BZ-T-6 | | | |
| | | | 37 | 162565 | CPV10-VI-BZ-T-7 | | | |
| | | | 38 | 162566 | CPV10-VI-BZ-T-8 | | | |
| | | | 8 | 162567 | CPV14-VI-BZ-T-2 | | | |
| | | | 9.5 | 162568 | CPV14-VI-BZ-T-3 | | | |
| | | | 11 | 162569 | CPV14-VI-BZ-T-4 | | | |
| | | | 12.5 | 162570 | CPV14-VI-BZ-T-5 | | | |
| | | | 14 | 162571 | CPV14-VI-BZ-T-6 | | | |
| | | | 15.5 | 162571 | CPV14-VI-BZ-T-7 | | | |
| | | | 17 | | | | | |
| | | | 9 | 162573 | CPV14-VI-BZ-T-8 CPV18-VI-BZ-T-2 | | | |
| | | | | 163293 | | | | |
| | | | 10.5 | 163294 | CPV18-VI-BZ-T-3 | | | |
| | | | 12 | 163295 | CPV18-VI-BZ-T-4 CPV18-VI-BZ-T-5 | | | |
| | | | 13.5 | 163296 | | | | |
| | | | 16 | 163297 | CPV18-VI-BZ-T-6 | | | |
| | | | 17.5 | 163298 | CPV18-VI-BZ-T-7 | | | |
| | _ | | 29 | 163299 | CPV18-VI-BZ-T-8 | | | |
| | T | Holder for inscription labels, transparent | 11 | 194066 | CPV10-VI-ST-T-2 | | | |
| | | | 14 | 194067 | CPV10-VI-ST-T-3 | | | |
| | | | 17 | 194068 | CPV10-VI-ST-T-4 | | | |
| | | | 20 | 194069 | CPV10-VI-ST-T-5 | | | |
| | | | 23 | 194070 | CPV10-VI-ST-T-6 | | | |
| | | | 24 | 194071 | CPV10-VI-ST-T-7 | | | |
| | | | 29 | 194072 | CPV10-VI-ST-T-8 | | | |
| | | | _ | 194073 | CPV14-VI-ST-T-2 | | | |
| | | | 18 | 194074 | CPV14-VI-ST-T-3 | | | |
| | | | 22 | 194075 | CPV14-VI-ST-T-4 | | | |
| | | | 25 | 194076 | CPV14-VI-ST-T-5 | | | |
| | | | 53 | 194077 | CPV14-VI-ST-T-6 | | | |
| | | | 59 | 194078 | CPV14-VI-ST-T-7 | | | |
| | | | 63 | 194079 | CPV14-VI-ST-T-8 | | | |
| | | | 17 | 194080 | CPV18-VI-ST-T-2 | | | |
| | | | 23 | 194081 | CPV18-VI-ST-T-3 | | | |
| | | | 29 | 194082 | CPV18-VI-ST-T-4 | | | |
| | | | 35 | 194083 | CPV18-VI-ST-T-5 | | | |
| | | | 41 | 194084 | CPV18-VI-ST-T-6 | | | |
| | | | 47 | 194085 | CPV18-VI-ST-T-7 | | | |
| | | | 53 | 194086 | CPV18-VI-ST-T-8 | | | |
| Inscription labels | Inscription labels | | | | | | | |
| seription tubets | I - | 6x10 mm in frame, 64 pieces | - | 18576 | IBS 6x10 | | | |
| | | 9x20 mm in frames, 20 pieces (CPV18 only) | _ | 18182 | IBS 9x20 | | | |
| | | 27.20 mm m manies, 20 proces (ci v10 onty) | | 10102 | IDD JAZO | | | |
| | | | | | | | | |

Accessories

| Ordering data | | | | | | |
|----------------------|-----------------|--|-----------------------------|--------------------|--------------------|------------------------------|
| - | Code | Designation | | Product weight [g] | Part no. | Туре |
| Mounting | | | | | | |
| 6 3 | Н | Mounting for H-rail | | 15.8 | 162556 | CPV10/14-VI-BG-NRH-35 |
| | | | | 50 | 163291 | CPV18-VI-BG-NRH-35 |
| | W | Attachment for wall mounting | For CPV18 | 200 | 163292 | CPV18-VI-BG-RW |
| | U | | For CPV10/14 | 118 | 189541 | CPV10/14-VI-BG-RWL-B |
| | X | Mounting for individual connection and ET2 | 200X (included in the scope | 216 | 165801 | CPV10-VI-BG-ET200X |
| 69/10 | | of delivery) | 326 | 165803 | CPV14-VI-BG-ET200X | |
| Manual override | | | | | | |
| | - | Locking clip (for manual override), non-deta | achable | 1.5 | 526203 | CPV10/14-HS |
| | | | 3 | 526204 | CPV18-HS | |
| | V | Locking clip (cover for manual override), no | n-detachable | 0.15 | 530055 | CPV10/14-HV |
| | | | 0.53 | 530056 | CPV18-HV | |
| Connecting cable for | r individual co | onnection, electrical | | | | |
| | D | Angled socket, plug pattern ZC, self-tap- | 2.5 m | 50 | 8047676 | NEBV-Z3WA2L-R-E-2.5-N-LE2-S1 |
| £7K | E | ping screw, for CPV10/14 | 5 m | 90 | 8047677 | NEBV-Z3WA2L-R-E-5-N-LE2-S1 |
| | F | | 10 m | 170 | 8047675 | NEBV-Z3WA2L-R-E-10-N-LE2-S1 |
| Plug socket with cal | ole for individ | ual connection, electrical | | | | |
| <i>M</i> | D | For CPV18 | 2.5 m | 200 | 174844 | KMEB-2-24-2.5-LED |
| | E | | 5 m | 400 | 174845 | KMEB-2-24-5-LED |



Connecting cables are pre-assembled. They include a protective circuit and an LED for indicating the operating status.

| rdering data | Code | Designation | | | Product weight | Part no. | Туре |
|------------------|----------------|---|----------|--------|----------------|----------|-------------------|
| ulti-pin cable | ` | | | | • | ï | |
| ~ % | Υ | Plug socket (Sub-D plug can be crimped), for | 9-pin | | 73 | 18708 | SD-SUB-D-BU9 |
| | | assembly by the user | 25-pin | | 75 | 18709 | SD-SUB-D-BU25 |
| <u></u> | R | Connecting cable, IP65, polyvinyl chloride | 9-pin | 5 m | 425 | 18698 | KMP3-9P-08-5 |
| ~// | " | commenting subset, in est, portrum, comente | 25-pin | ┤ ```` | 672 | 18624 | KMP3-25P-16-5 |
| | S | \dashv | 9-pin | 10 m | 814 | 18579 | KMP3-9P-08-10 |
| | | | 25-pin | - 10 | 1303 | 18625 | KMP3-25P-16-10 |
| | _ | Connecting cable, IP65, polyurethane (suita- | 9-pin | 5 m | 378 | 193014 | KMP4-9P-5-PUR |
| ® | | ble for energy chains) | <u> </u> | | 702 | 193014 | KMP4-25P-5-PUR |
| \checkmark | | ble for energy chains) | 25-pin | 10 | 1 | | |
| | - | | 9-pin | 10 m | 723 1617 | 193015 | KMP4-9P-10-PUR |
| | | C. C. III IDGs at the little | 25-pin | - | 1 1 | 193019 | KMP4-25P-10-PUR |
| | - | Connecting cable, IP65, polyvinyl chloride | 9-pin | 5 m | 413 | 193012 | KMP4-9P-5-PVC |
| | | (suitable for energy chains) | 25-pin | 1 | 854 | 193016 | KMP4-25P-5-PVC |
| | | | 9-pin | 10 m | 791 | 193013 | KMP4-9P-10-PVC |
| | | | 25-pin | | 1657 | 193017 | KMP4-25P-10-PVC |
| / | | Connecting cable, IP40, polyvinyl chloride | 9-pin | 2.5 m | 248 | 531184 | KMP6-09P-8-2.5 |
| | | For CPV10/14/18 only | 25-pin | | 432 | 530046 | KMP6-25P-20-2.5 |
| | | | 9-pin | 5 m | 454 | 531185 | KMP6-09P-8-5 |
| | | | 25-pin | | 814 | 530047 | KMP6-25P-20-5 |
| | | | 9-pin | 10 m | 864 | 531186 | KMP6-09P-8-10 |
| | | | 25-pin | | 1600 | 530048 | KMP6-25P-20-10 |
| } | - | Threaded sleeve for multi-pin cable KMP6, IP40 | _ | - | - | 572608 | NEAU-TA-M35-U4 |
| ering data | Code | Designation | | | Product weight | Part no. | Туре |
| | | | | | [g] | | |
| dbus interface f | or Fieldbus Di | rect | | | · | · | |
| | GE | Sub-D plug, IP65, 9-pin for PROFIBUS DP | | | 60 | 532216 | FBS-SUB-9-GS-DP-B |
| | GF | Bus connection 2x M12 adapter (B-coded, ReverseKey) for PROFIBUS DP | | | 80 | 533118 | FBA-2-M12-5POL-RK |

| Ordering data | | | | | | |
|-----------------------|-----------------|-------------------------|--|----------------|--------------|----------------------|
| | Code | de Designation | | Product weight | Part no. | Туре |
| | | | | [g] | | |
| Fieldbus interface fo | r Fieldbus Dire | ect | | | | |
| | | | straight, for assembly by the user of a connect- | _ | 1067905 | NECU-M-B12G5-C2-PB |
| | | ing cable for FBA-2-M1 | 2-5POL-RK | | | |
| | | | | | | |
| | _ | Dlug M1 2v1 E nin etre | aight, for assembly by the user of a connecting | _ | 1066354 | NECU-M-S-B12G5-C2-PB |
| | - | cable for FBA-2-M12-5 | | _ | 1000554 | NECU-M-3-B12G3-C2-FB |
| | | cubic for FB/Y 2 Wi12 3 | | | | |
| | | | | | | |
| Operating voltage co | nnection for F | ieldbus Direct | | | | |
| | Straight so | cket | M12, 4-pin, PG7, IP67 | 13 | 18494 | SIE-GD |
| | | | M12, 4-pin, PG9, IP67 | 29 | 18495 | FBSD-GD-9 |
| | | | | | | |
| | Angled plu | g socket | M12, 4-pin, IP67 | 13 | 12956 | SIE-WD-TR |
| | | | M12, 4-pin, PG9, IP67 | 30 | 18525 | FBSD-WD-9 |
| | | | | | | |
| | | | | | | |
| | | | | | | |
| Blanking plug | 1-, ,, | | | Ι. | 1 | |
| | Blanking p | lug | | 1 | 3843 | B-M5 |
| | | | | 2 | 174309 | B-M7 |
| - | | | | 7 | 3568 | B-1/8 |
| | | | | 15 | 3569 | B-1/4 |
| | | | | 43 | 3570 3571 | B-3/8 B-1/2 |
| | | | | 40 | 33/1 | B-1/2 |
| Push-in fitting | | | | | | |
| | Push-in fitt | ting | | 12 | 186109 | QS-G1/8-8-I |
| | | | | 20 | 186112 | QS-G1/4-10-I |
| | | | | 34 | 186114 | QS-G3/8-12-I |
| | | | | 4.4 | 153317 | QSM-M5-6-I |
| | | | | 6.4 | 153321 | QSM-M7-6-I |
| Silencer | | | | | | |
| | Silencer | | | 1.5 | 1205858 | AMTE-M-LH-M5 |
| | | | | 43 | 1205863 | AMTE-M-LH-G12 |
| | | | | 13 | 1205861 | AMTE-M-LH-G14 |
| | | | | 7.5 | 1205860 | AMTE-M-LH-G18 |
| | | | | 26 | 1205862 | AMTE-M-LH-G38 |
| | | | | 1.2 | 161418 | UC-M7 |
| User documentation | | | | | | |
| | | n CPV pneumatics | German | _ | 165100 | P.BE-CPV-DE |
| | | - p | English | 1 | 165200 | P.BE-CPV-EN |
| | | | French | 1 | 165130 | P.BE-CPV-FR |
| | | | Italian | 1 | 165160 | P.BE-CPV-IT |
| - | | | Spanish | 1 | 165230 | P.BE-CPV-ES |
| | | : | | | | |

ATEX accessories

| Ordering data | | | | | |
|-----------------------|---------------|--|----------------|------------------|---|
| | Code | Valve function | Product weight | Part no. | Туре |
| | | | [g] | | |
| Individual sub-base v | alve, size 10 | 0/14/18 | | | |
| - Cha | M | 5/2-way valve, single solenoid, piston spool valve | 70 | 161414 | CPV10-M1H-5LS-M7 |
| | | | 120 | 161360 | CPV14-M1H-5LS-1/8 |
| | | | 260 | 163190 | CPV18-M1H-5LS-1/4 |
| | F | 5/2-way valve, single solenoid, fast switching, piston spool valve | 70 | 187439 | CPV10-M11H-5LS-M7 |
| | J | 5/2-way valve, double solenoid, piston spool valve | 70 | 161415 | CPV10-M1H-5JS-M7 |
| | | | 120 | 161361 | CPV14-M1H-5JS-1/8 |
| | | | 260 | 163191 | CPV18-M1H-5JS-1/4 |
| | N | 2x 3/2-way valve, normally open, piston spool valve | 70 | 161417 | CPV10-M1H-2x3-OLS-M7 |
| | | | 120 | 161363 | CPV14-M1H-2x3-OLS-1/8 |
| | | | 260 | 163188 | CPV18-M1H-2x3-OLS-1/4 |
| | С | 2x 3/2-way valve, normally closed, piston spool valve | 70 | 161416 | CPV10-M1H-2x3-GLS-M7 |
| | | | 120 | 161362 | CPV14-M1H-2x3-GLS-1/8 |
| | | | 260 | 163189 | CPV18-M1H-2x3-GLS-1/4 |
| | CY | 2x 3/2-way valve, normally closed, | 70 | 553260 | CPV10-M1H-2x3-GLS-Y-M7 |
| | | integrated back pressure protection, piston spool valve | | | |
| | Н | 2x 3/2-way valve, 1x normally open, 1x normally closed, piston spool valve | 70 | 176064 | CPV10-M1H-30LS-3GLS-M7 |
| | | | 120 | 176067 | CPV14-M1H-30LS-3GLS-1/8 |
| | | | 260 | 176070 | CPV18-M1H-30LS-3GLS-1/4 |
| | G | 5/3-way valve, mid-position closed, piston spool valve | 260 | 176061 | CPV18-M1H-5/3GS-1/4 |
| | D | | 70 | 185880 | CPV10-M1H-2x2-GLS-M7 |
| | | | 120 | 185883 | CPV14-M1H-2x2-GLS-1/8 |
| | | | 260 | 185886 | CPV18-M1H-2x2-GLS-1/4 |
| | I | 2x 2/2-way valve, 1x normally open, 1x normally closed, piston spool valve | 70 | 187843 | CPV10-M1H-2OLS-2GLS-M7 |
| | | | 120 | 187846 | CPV14-M1H-20LS-2GLS-1/8 |
| | | | 260 | 187849 | CPV18-M1H-20LS-2GLS-1/4 |
| | 1 11 1 | | - | | |
| individual sub-base v | | ict separation 1, 11 sizes 10/14 | 70 | EE33E4 | CDV10 M1H FIG V M7 |
| | MK | 5/2-way valve (with duct separation 1, 11), single solenoid, piston spool valve | 70 120 | 553256 553258 | CPV10-M1H-5LS-K-M7 CPV14-M1H-5LS-K-1/8 |
| | JK | 5/2-way valve (with duct separation 1, 11), double solenoid, piston | 70 | | · · · · · · · · · · · · · · · · · · · |
| | JK | spool valve | 120 | 559644 | CPV10-M1H-5JS-K-M7 |
| | NIZ | | | 559651 | CPV14-M1H-5JS-K-1/8 |
| | NK | 2x 3/2-way valve (with duct separation 1, 11), normally open, piston spool valve | 70 120 | 559641 | CPV10-M1H-2x3-OLS-K-M7 |
| | CV | ' | 70 | 559648 | CPV14-M1H-2x3-OLS-K-1/8 CPV10-M1H-2x3-GLS-K-M7 |
| | CK | 2x 3/2-way valve (with duct separation 1, 11) normally closed, piston | | 553257 | |
| | 111/ | spool valve | 120 70 | 553259 | CPV14-M1H-2x3-GLS-K-1/8 |
| | HK | 2x 3/2-way valve (with duct separation 1, 11), 1x normally open, | | 559642 | CPV10-M1H-30LS-3GLS-K-M7 |
| | DV | 1x normally closed, piston spool valve | 120 | 559649 | CPV14-M1H-30LS-3GLS-K-1/8 |
| | DK | 2x 2/2-way valve (with duct separation 1, 11), normally closed, piston | 70 | 559645 | CPV10-M1H-2x2-GLS-K-M7 |
| | | spool valve | 120 | 559652 | CPV14-M1H-2x2-GLS-K-1/8 |
| | IK | 2x 2/2-way valve (with duct separation 1, 11), 1x normally open, | 70 | 559646 | CPV10-M1H-20LS-2GLS-K-M7 |
| | | 1x normally closed, piston spool valve | 120 | 559653 | CPV14-M1H-2OLS-2GLS-K-1/8 |

ATEX accessories

| Ordering data | | | | | |
|----------------------|----------------|---|--------------------|----------|--------------------------|
| - | Code | Designation | Product weight [g] | Part no. | Туре |
| Vacuum generator | | | | | |
| | Α | Vacuum generator | 25 | 185862 | CPV10-M1H-V70-M7 |
| Marcha. | | | 98 | 185868 | CPV14-M1H-V95-1/8 |
| | | | 227 | 185874 | CPV18-M1H-V140-1/4 |
| | E | Vacuum generator with ejector pulse | 25 | 185865 | CPV10-M1H-VI70-2GLS-M7 |
| | | | 114 | 185871 | CPV14-M1H-VI95-2GLS-1/8 |
| | | | 264 | 185877 | CPV18-M1H-VI140-2GLS-1/4 |
| Function block | | | | | |
| | G | Valve kit for 5/3-way valve function, closed (in combination with valve | 23 | 176055 | CPV10-BS-5/3G-M7 |
| | | slice C) for size 10 and 14 | 190 | 176057 | CPV14-BS-5/3G-1/8 |
| Separator plates | | | | , | |
| $\overline{\wedge}$ | T | Separator plate, duct 1/11 closed | 25 | 161369 | CPV10-DZP |
| | | | - | 162551 | CPV14-DZP |
| | | | 25 | 163282 | CPV18-DZP |
| | S | Separator plate, duct 1/11, 3/5 closed | 25 | 178678 | CPV10-DZPR |
| | | | | 178680 | CPV14-DZPR |
| | | | | 184543 | CPV18-DZPR |
| Blanking plate | | 1 | | | |
| Stanting place | L | Blanking plate | 25 | 161368 | CPV10-RZP |
| | | | | 162550 | CPV14-RZP |
| | | | | 163283 | CPV18-RZP |
| Additional functions | for valve posi | itions | | | |
| | Р | One-way flow control valve, 2x supply air | 30 | 184140 | CPV10-BS-2XGRZZ-M7 |
| | | | 54 | 184142 | CPV14-BS-2XGRZZ-1/8 |
| | Q | One-way flow control valve, 2x exhaust air | 30 | 184141 | CPV10-BS-2XGRAZ-M7 |
| | | | 54 | 184143 | CPV14-BS-2XGRAZ-1/8 |
| | V | One-way flow control valve for vacuum | 30 | 185889 | CPV10-BS-GRZ-V-M7 |
| | | | - | 185891 | CPV14-BS-GRZ-V-1/8 |

| | Code | Designation | | Product weight P | Part no. | Type | |
|--------------------|-------------|---|----------|------------------|----------|-------------------|--|
| | | | [g] | | | | |
| umatic multiple co | nnector pla | ate | | | | | |
| | M | Pneumatic multiple connector plate, | 2 valves | 135 | 161969 | CPV10-VI-P2-M7 | |
| 9 | | for wall/machine mounting, | 4 valves | 164 | 161970 | CPV10-VI-P4-M7 | |
| | | without side flange | 6 valves | 219 | 161971 | CPV10-VI-P6-M7 | |
| | | | 8 valves | 272 | 163893 | CPV10-VI-P8-M7 | |
| | | | 2 valves | 261 | 163894 | CPV14-VI-P2-1/8 | |
| | | | 4 valves | 379 | 163895 | CPV14-VI-P4-1/8 | |
| V | | | 6 valves | 505 | 163896 | CPV14-VI-P6-1/8 | |
| | | | 8 valves | 627 | 163897 | CPV14-VI-P8-1/8 | |
| | | | 2 valves | 519 | 165292 | CPV18-VI-P2-1/4 | |
| | | | 4 valves | 695 | 165293 | CPV18-VI-P4-1/4 | |
| | | | 6 valves | 907 | 165294 | CPV18-VI-P6-1/4 | |
| | | | 8 valves | 1116 | 165295 | CPV18-VI-P8-1/4 | |
| | Р | Pneumatic multiple connector plate, | 2 valves | 182 | 152420 | CPV10-VI-P2-M7-B | |
| | | for wall/machine mounting, | 4 valves | 228 | 152421 | CPV10-VI-P4-M7-B | |
| | | with side flange | 6 valves | 283 | 152422 | CPV10-VI-P6-M7-B | |
| | | | 8 valves | 336 | 152423 | CPV10-VI-P8-M7-B | |
| | | | 2 valves | 365 | 152424 | CPV14-VI-P2-1/8-B | |
| | | | 4 valves | 483 | 152425 | CPV14-VI-P4-1/8-B | |
| | | | 6 valves | 609 | 152426 | CPV14-VI-P6-1/8-B | |
| | | | 8 valves | 731 | 152427 | CPV14-VI-P8-1/8-B | |
| | | | 2 valves | 659 | 175632 | CPV18-VI-P2-1/4-B | |
| | İ | | 4 valves | 832 | 175634 | CPV18-VI-P4-1/4-B | |
| | İ | | 6 valves | 1047 | 175636 | CPV18-VI-P6-1/4-B | |
| | | | 8 valves | 1256 | 175638 | CPV18-VI-P8-1/4-B | |
| | GQC | Pneumatic multiple connector plate with sealing | 2 valves | 250 | 538807 | CPV10-VI-P2-M7-C | |
| | | ring, | 4 valves | 320 | 538808 | CPV10-VI-P4-M7-C | |
| | | for control cabinet assembly, | 6 valves | 390 | 538809 | CPV10-VI-P6-M7-C | |
| | İ | with supply ports | 8 valves | 460 | 538810 | CPV10-VI-P8-M7-C | |
| | | | 2 valves | 500 | 539498 | CPV14-VI-P2-1/8-C | |
| | | | 4 valves | 650 | 539499 | CPV14-VI-P4-1/8-C | |
| | | | 6 valves | 800 | 539500 | CPV14-VI-P6-1/8-C | |
| | | | 8 valves | 920 | 539501 | CPV14-VI-P8-1/8-C | |
| | GQD | Pneumatic multiple connector plate with sealing | 2 valves | 80 | 538811 | CPV10-VI-P2-M7-D | |
| | | ring, | 4 valves | 150 | 538812 | CPV10-VI-P4-M7-D | |
| | | for control cabinet assembly, | 6 valves | 220 | 538813 | CPV10-VI-P6-M7-D | |
| | | without supply ports | 8 valves | 290 | 538814 | CPV10-VI-P8-M7-D | |
| | | | 2 valves | 350 | 539502 | CPV14-VI-P2-1/8-D | |
| | | | 4 valves | 550 | 539503 | CPV14-VI-P4-1/8-D | |
| | | | 6 valves | 400 | 539504 | CPV14-VI-P6-1/8-D | |
| | | | 8 valves | 650 | 539505 | CPV14-VI-P8-1/8-D | |
| | GQE | Pneumatic multiple connector plate with sealing | 2 valves | 300 | 566709 | CPV10-VI-P2-1/8-C | |
| | | ring, | 4 valves | 370 | 566710 | CPV10-VI-P4-1/8-C | |
| | | for control cabinet assembly, | 6 valves | 440 | 566711 | CPV10-VI-P6-1/8-C | |
| | | with all ports | 8 valves | 510 | 566712 | CPV10-VI-P8-1/8-C | |

| Ordering data | | | | | |
|---------------------------|------|--|----------------|----------|------------------------------------|
| | Code | Designation | Product weight | Part no. | Туре |
| | | | [g] | | 7. |
| Inscription label holde | rc | | 107 | | |
| niiscription tabet notice | Z | Holder for inscription labels | 32 | 162560 | CPV10-VI-BZ-T-2 |
| | | Thotaer for inscription tabets | 33 | 162561 | CPV10-VI-BZ-T-3 |
| | | | 34 | 162562 | CPV10-VI-BZ-T-4 |
| | | | 35 | 162563 | CPV10-VI-BZ-T-5 |
| | | | 36 | 162564 | CPV10-VI-BZ-T-6 |
| | | | 37 | 162565 | CPV10-VI-BZ-T-7 |
| | | | 38 | 162566 | CPV10-VI-BZ-T-8 |
| | | | 8 | 162567 | CPV14-VI-BZ-T-2 |
| | | | 9.5 | 162568 | CPV14-VI-BZ-T-3 |
| | | | 11 | 162569 | CPV14-VI-BZ-T-4 |
| | | | 12.5 | 162570 | CPV14-VI-BZ-T-5 |
| | | | 14 | 162571 | CPV14-VI-BZ-T-6 |
| | | | 15.5 | 162572 | CPV14-VI-BZ-T-7 |
| | | | 17 | - | |
| | | | 9 | 162573 | CPV14-VI-BZ-T-8 CPV18-VI-BZ-T-2 |
| | | | 10.5 | 163293 | |
| | | | | 163294 | CPV18-VI-BZ-T-3 |
| | | | 12 | 163295 | CPV18-VI-BZ-T-4 |
| | | | 13.5 | 163296 | CPV18-VI-BZ-T-5 |
| | | | 16 | 163297 | CPV18-VI-BZ-T-6 |
| | | | 17.5 | 163298 | CPV18-VI-BZ-T-7 |
| | - | | 29 | 163299 | CPV18-VI-BZ-T-8 |
| | T | Holder for inscription labels, transparent | 11 | 194066 | CPV10-VI-ST-T-2 |
| | | | 14 | 194067 | CPV10-VI-ST-T-3 |
| | | | 17 | 194068 | CPV10-VI-ST-T-4 |
| | | | 20 | 194069 | CPV10-VI-ST-T-5 |
| | | | 23 | 194070 | CPV10-VI-ST-T-6 |
| | | | 24 | 194071 | CPV10-VI-ST-T-7 |
| | | | 29 | 194072 | CPV10-VI-ST-T-8 |
| | | | - | 194073 | CPV14-VI-ST-T-2 |
| | | | 18 | 194074 | CPV14-VI-ST-T-3 |
| | | | 22 | 194075 | CPV14-VI-ST-T-4 |
| | | | 25 | 194076 | CPV14-VI-ST-T-5 |
| | | | 53 | 194077 | CPV14-VI-ST-T-6 |
| | | | 59 | 194078 | CPV14-VI-ST-T-7 |
| | | | 63 | 194079 | CPV14-VI-ST-T-8 |
| | | | 17 | 194080 | CPV18-VI-ST-T-2 |
| | | | 23 | 194081 | CPV18-VI-ST-T-3 |
| | | | 29 | 194082 | CPV18-VI-ST-T-4 |
| | | | 35 | 194083 | CPV18-VI-ST-T-5 |
| | | | 41 | 194084 | CPV18-VI-ST-T-6 |
| | | | 47 | 194085 | CPV18-VI-ST-T-7 |
| | | | 53 | 194086 | CPV18-VI-ST-T-8 |
| Inscription labels | | | | | |
| | - | 6x10 mm in frame, 64 pieces | I - | 18576 | IBS 6x10 |
| | | 9x20 mm in frames, 20 pieces (CPV18 only) | - | 18182 | IBS 9x20 |
| | | , | | 23102 | |
| · | | | | | |

ATEX accessories

| Ordering data | | | | | | |
|------------------------|----------------|--|--------------------|--------------------|--------------------|------------------------------|
| | Code | Designation | | Product weight [g] | Part no. | Туре |
| Mounting | _ | | | | | |
| | Н | Mounting for H-rail | | 15.8 | 162556 | CPV10/14-VI-BG-NRH-35 |
| | | | | | 163291 | CPV18-VI-BG-NRH-35 |
| | W | Attachment for wall mounting | nounting For CPV18 | | 163292 | CPV18-VI-BG-RW |
| | U | | For CPV10/14 | 118 | 189541 | CPV10/14-VI-BG-RWL-B |
| <u>^</u> | Х | Mounting for individual connection and ET2 | 216 | 165801 | CPV10-VI-BG-ET200X | |
| 69 | | of delivery) | , | 326 | 165803 | CPV14-VI-BG-ET200X |
| Manual override | | | | | | |
| | - | Locking clip (for manual override), non-deta | 1.5 | 526203 | CPV10/14-HS | |
| | | | | 3 | 526204 | CPV18-HS |
| | V | Locking clip (cover for manual override), no | n-detachable | 0.15 | 530055 | CPV10/14-HV |
| | | | | 0.53 | 530056 | CPV18-HV |
| Connecting cable for i | ndividual co | nnection, electrical | | | | |
| 1 | D | Angled socket, plug pattern ZC, self-tap- | 2.5 m | 50 | 8047676 | NEBV-Z3WA2L-R-E-2.5-N-LE2-S1 |
| £ | E | ping screw, for CPV10/14 | 5 m | 90 | 8047677 | NEBV-Z3WA2L-R-E-5-N-LE2-S1 |
| | F | | 10 m | | 8047675 | NEBV-Z3WA2L-R-E-10-N-LE2-S1 |
| Plug socket with cahl | e for individu | ial connection, electrical | - | | | |
| A A | D | For CPV18 | 2.5 m | 200 | 174844 | KMEB-2-24-2.5-LED |
| | E | | 5 m | 400 | 174845 | KMEB-2-24-5-LED |



Connecting cables are pre-assembled. They include a protective circuit and an LED for indicating the operating status.

| Ordering data | | | | | | | |
|----------------------|----------------|--|-----------------|----------------------|----------------|----------|-------------------------------|
| Ordering data | Code | Designation | | | Product weight | Part no. | Туре |
| | | | | | [g] | | , |
| Multi-pin cable | | | | | | <u>'</u> | ' |
| | Υ | Plug socket (Sub-D plug can be crimped), for | 9-pin | | 73 | 18708 | SD-SUB-D-BU9 |
| | | assembly by the user | 25-pin | | 75 | 18709 | SD-SUB-D-BU25 |
| | | | ' | | | | |
| | | | | | | | |
| • | R | Connecting cable, IP65, polyvinyl chloride | 0 =:= | 5 m | /25 | 18698 | KWD2 OD OO F |
| //ੈ | K | Connecting capie, 1765, polyvinyi chioride | 9-pin 25-pin | - ³ | 425 672 | 18624 | KMP3-9P-08-5 KMP3-25P-16-5 |
| | S | | 9-pin | 10 m | 814 | 18579 | KMP3-9P-08-10 |
| | | | 25-pin | - 10 | 1303 | 18625 | KMP3-25P-16-10 |
| | _ | Connecting cable, IP65, polyurethane (suita- | 9-pin | 5 m | 378 | 193014 | KMP4-9P-5-PUR |
| | | ble for energy chains) | 25-pin | | 702 | 193018 | KMP4-25P-5-PUR |
| _ | - | | 9-pin | 10 m | 723 | 193015 | KMP4-9P-10-PUR |
| | | | 25-pin | | 1617 | 193019 | KMP4-25P-10-PUR |
| | - | Connecting cable, IP65, polyvinyl chloride | 9-pin | 5 m | 413 | 193012 | KMP4-9P-5-PVC |
| | | (suitable for energy chains) | 25-pin | 7 | 854 | 193016 | KMP4-25P-5-PVC |
| | | | 9-pin | 10 m | 791 | 193013 | KMP4-9P-10-PVC |
| | | | 25-pin | | 1657 | 193017 | KMP4-25P-10-PVC |
| | | | | | | | |
| Ordering data | | | | | | | |
| | Code | Designation | | | Product weight | Part no. | Туре |
| | | | | | [g] | | |
| Fieldbus interface f | or Fieldbus Di | | | | | | |
| | GE | Sub-D plug, IP65, 9-pin for PROFIBUS DP | | | 60 | 532216 | FBS-SUB-9-GS-DP-B |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| 4 | | | | | | | |
| | GF | Bus connection 2x M12 adapter (B-coded, Rev | erseKey) for | PROFIBUS | 80 | 533118 | FBA-2-M12-5POL-RK |
| | | DP | | | | | |
| | | | | | | | |
| | i i | · · | | | • | | |
| Ordering data | | | | | | | |
| | Designati | on | Certification | on | | Part no. | Туре |
| Bus node | | | | | | | |
| ••> | EP bus no | ode | RCM | | | 8107591 | CTEU-EP-EX1C |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| • | PN bus no | ode | 1 | | | 8107589 | CTEU-PN-EX1C |
| 1 | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| ~ | PB bus no | ode | 1 | | | 8107588 | CTEU-PB-EX1C |
| 1 | 1 5 503 110 | | | | | 0107,508 | |
| | | | | | | | |
| | | | | | | | |
| الغطيلال ا | | | | | | | |
| → | | | | | | | |

| Ordering data | | | | | | |
|----------------------|------------------|------------------------|--|----------------|----------|----------------------|
| | Code | Designation | | Product weight | Part no. | Туре |
| | | | | [g] | | |
| Fieldbus interface f | or Fieldbus Dire | ect | | | | |
| | - | Socket M12x1, 5-pin, | straight, for assembly by the user of a connect- | | 1067905 | NECU-M-B12G5-C2-PB |
| | | ing cable for FBA-2-M1 | 2-5POL-RK | | | |
| | | | | | | |
| | | Dlug M1 2v1 E pin et | raight, for assembly by the user of a connecting | _ | 1066354 | NECU-M-S-B12G5-C2-PB |
| | - | cable for FBA-2-M12-5 | | _ | 1000554 | NECU-W-3-B12G3-C2-FB |
| | | custo for fish 2 miles | 1 OLIN | | | |
| | | | | | | |
| Operating voltage of | onnection for F | ieldbus Direct | | | | |
| | Straight so | cket | M12, 4-pin, PG7, IP67 | 13 | 18494 | SIE-GD |
| | | | M12, 4-pin, PG9, IP67 | 29 | 18495 | FBSD-GD-9 |
| | | | | | | |
| (| Angled plu | g socket | M12, 4-pin, IP67 | 13 | 12956 | SIE-WD-TR |
| | | • | M12, 4-pin, PG9, IP67 | 30 | 18525 | FBSD-WD-9 |
| | | | | | | |
| | | | | | | |
| | | | | | | |
| Blanking plug | | | | | | |
| | Blanking p | lug | | 1 | 3843 | B-M5 |
| | | | | 2 | 174309 | B-M7 |
| | | | | 7 | 3568 | B-1/8 |
| | | | | 15 | 3569 | B-1/4 |
| | | | | 23 | 3570 | B-3/8 |
| | | | | 43 | 3571 | B-1/2 |
| Push-in fitting | | | | | | |
| | Push-in fitt | ting | | 12 | 186109 | QS-G1/8-8-I |
| | | | | 20 | 186112 | QS-G1/4-10-I |
| | | | | 34 | 186114 | QS-G3/8-12-I |
| | | | | 4.4 | 153317 | QSM-M5-6-I |
| | | | | 6.4 | 153321 | QSM-M7-6-I |
| Silencer | | | | | | |
| | Silencer | | | 1.5 | 1205858 | AMTE-M-LH-M5 |
| | | | | 43 | 1205863 | AMTE-M-LH-G12 |
| | | | | 13 | 1205861 | AMTE-M-LH-G14 |
| | | | | 7.5 | 1205860 | AMTE-M-LH-G18 |
| | | | | 26 | 1205862 | AMTE-M-LH-G38 |
| | | | | 1.2 | 161418 | UC-M7 |
| Hear dearments ** | | | | | , | |
| User documentatio | | n CPV pneumatics | German | T_ | 165100 | P.BE-CPV-DE |
| | Description | rer v pneumatics | English | - | 165100 | P.BE-CPV-EN |
| | → | | French | - | 165200 | P.BE-CPV-FR |
| | | | Italian | - | 165160 | P.BE-CPV-IT |
| ~ | | | Spanish | - | 165230 | P.BE-CPV-ES |
| | | | Shamon | | 10,2,0 | 1.52 61 7 25 |

| Ordering data | | | | | |
|-------------------|---------------|---|----------------|----------|---------------------------|
| | Code | Valve function | Product weight | Part no. | Туре |
| | | | [g] | | |
| dividual sub-base | valve, size 1 | 0/14/18 | | | |
| Share. | М | 5/2-way valve, single solenoid, piston spool valve | 70 | 161414 | CPV10-M1H-5LS-M7 |
| No. | | | 120 | 161360 | CPV14-M1H-5LS-1/8 |
| | | | 260 | 163190 | CPV18-M1H-5LS-1/4 |
| | F | 5/2-way valve, single solenoid, fast switching, piston spool valve | 70 | 187439 | CPV10-M11H-5LS-M7 |
| | J | 5/2-way valve, double solenoid, piston spool valve | 70 | 161415 | CPV10-M1H-5JS-M7 |
| | | | 120 | 161361 | CPV14-M1H-5JS-1/8 |
| | | | 260 | 163191 | CPV18-M1H-5JS-1/4 |
| | N | 2x 3/2-way valve, normally open, piston spool valve | 70 | 161417 | CPV10-M1H-2x3-OLS-M7 |
| | | | 120 | 161363 | CPV14-M1H-2x3-OLS-1/8 |
| | | | 260 | 163188 | CPV18-M1H-2x3-OLS-1/4 |
| | C | 2x 3/2-way valve, normally closed, piston spool valve | 70 | 161416 | CPV10-M1H-2x3-GLS-M7 |
| | | | 120 | 161362 | CPV14-M1H-2x3-GLS-1/8 |
| | | | 260 | 163189 | CPV18-M1H-2x3-GLS-1/4 |
| | CY | 2x 3/2-way valve, normally closed, integrated back pressure protection, piston spool valve | 70 | 553260 | CPV10-M1H-2x3-GLS-Y-M7 |
| | Н | 2x 3/2-way valve, 1x normally open, 1x normally closed, piston spool | 70 | 176064 | CPV10-M1H-30LS-3GLS-M7 |
| | | valve | 120 | 176067 | CPV14-M1H-30LS-3GLS-1/8 |
| | | | 260 | 176070 | CPV18-M1H-30LS-3GLS-1/4 |
| | G | 5/3-way valve, mid-position closed, piston spool valve | 260 | 176061 | CPV18-M1H-5/3GS-1/4 |
| | D | 2x 2/2-way valve, normally closed, piston spool valve | 70 | 185880 | CPV10-M1H-2x2-GLS-M7 |
| | - | | 120 | 185883 | CPV14-M1H-2x2-GLS-1/8 |
| | | | 260 | 185886 | CPV18-M1H-2x2-GLS-1/4 |
| | I | 2x 2/2-way valve, 1x normally open, 1x normally closed, piston spool valve | 70 | 187843 | CPV10-M1H-20LS-2GLS-M7 |
| | | | 120 | 187846 | CPV14-M1H-20LS-2GLS-1/8 |
| | | | 260 | 187849 | CPV18-M1H-20LS-2GLS-1/4 |
| | | | 1200 | 10/01/ | c. 110 min 2013 2013 1/4 |
| lividual sub-base | | uct separation 1, 11 sizes 10/14 | | | |
| 1 91. | MK | 5/2-way valve (with duct separation 1, 11), single solenoid, piston | 70 | 553256 | CPV10-M1H-5LS-K-M7 |
| No. No. | | spool valve | 120 | 553258 | CPV14-M1H-5LS-K-1/8 |
| | JK | 5/2-way valve (with duct separation 1, 11), double solenoid, piston | 70 | 559644 | CPV10-M1H-5JS-K-M7 |
| | | spool valve | 120 | 559651 | CPV14-M1H-5JS-K-1/8 |
| | NK | 2x 3/2-way valve (with duct separation 1, 11), normally open, piston | 70 | 559641 | CPV10-M1H-2x3-OLS-K-M7 |
| | | spool valve | 120 | 559648 | CPV14-M1H-2x3-OLS-K-1/8 |
| | CK | 2x 3/2-way valve (with duct separation 1, 11) normally closed, piston | 70 | 553257 | CPV10-M1H-2x3-GLS-K-M7 |
| | | spool valve | 120 | 553259 | CPV14-M1H-2x3-GLS-K-1/8 |
| | НК | 2x 3/2-way valve (with duct separation 1, 11), 1x normally open, 1x | 70 | 559642 | CPV10-M1H-30LS-3GLS-K-M7 |
| | | normally closed, piston spool valve | 120 | 559649 | CPV14-M1H-30LS-3GLS-K-1/8 |
| | DK | 2x 2/2-way valve (with duct separation 1, 11), normally closed, piston | 70 | 559645 | CPV10-M1H-2x2-GLS-K-M7 |
| | | spool valve | 120 | 559652 | CPV14-M1H-2x2-GLS-K-1/8 |
| | IK | 2x 2/2-way valve (with duct separation 1, 11), 1x normally open, 1x | 70 | 559646 | CPV10-M1H-2OLS-2GLS-K-M7 |
| | | normally closed, piston spool valve | 120 | 559653 | CPV14-M1H-20LS-2GLS-K-1/8 |

| Ordering data | | | | | |
|----------------------|---------------|---|----------------|------------------|--------------------------|
| | Code | Designation | Product weight | Part no. | Туре |
| | | | [g] | | |
| Vacuum generator | | | | | |
| \sim | Α | Vacuum generator | 25 | 185862 | CPV10-M1H-V70-M7 |
| La Company | | | 98 | 185868 | CPV14-M1H-V95-1/8 |
| | | | 227 | 185874 | CPV18-M1H-V140-1/4 |
| | E | Vacuum generator with ejector pulse | 25 | 185865 | CPV10-M1H-VI70-2GLS-M7 |
| | | | 114 | 185871 | CPV14-M1H-VI95-2GLS-1/8 |
| | | | 264 | 185877 | CPV18-M1H-VI140-2GLS-1/4 |
| Function block | | | | | • |
| runction block | G | Valve kit for 5/3-way valve function, closed (in combination with valve | 23 | 176055 | CPV10-BS-5/3G-M7 |
| | G | slice C) for size 10 and 14 | 190 | | CPV14-BS-5/3G-1/8 |
| | | Since Cy for Size 10 driu 14 | 190 | 176057 | CPV14-BS-5/3G-1/8 |
| | | | | | |
| | | | | | |
| | | | | | |
| Separator plates | - | | T | | L |
| | Т | Separator plate, duct 1/11 closed | 25 | 161369 | CPV10-DZP |
| No. 18 Person | | | | 162551 | CPV14-DZP |
| | | C | 25 | 163282 | CPV18-DZP |
| | S | Separator plate, duct 1/11, 3/5 closed | 25 | 178678 | CPV10-DZPR |
| | | | | 178680 184543 | CPV14-DZPR CPV18-DZPR |
| | | | | 164545 | CPV16-DZPR |
| Blanking plate | | | | | · |
| Colored Plate | L | Blanking plate | 25 | 161368 | CPV10-RZP |
| | | blanking plate | 23 | 162550 | CPV14-RZP |
| | | | | 163283 | CPV14-RZP |
| | | | | 103203 | CI VIO-REI |
| | | | | | |
| | | | | | |
| | | | <u> </u> | | |
| Additional functions | for valve pos | | | | |
| | P | One-way flow control valve, 2x supply air | 30 | 184140 | CPV10-BS-2XGRZZ-M7 |
| | | | 54 | 184142 | CPV14-BS-2XGRZZ-1/8 |
| | Q | One-way flow control valve, 2x exhaust air | 30 | 184141 | CPV10-BS-2XGRAZ-M7 |
| | | | 54 | 184143 | CPV14-BS-2XGRAZ-1/8 |
| | | | | | |
| | V | One-way flow control valve for vacuum | 30 | 185889 | CPV10-BS-GRZ-V-M7 |
| | | ,, | - | 185891 | CPV14-BS-GRZ-V-1/8 |
| | | | | | , |
| | | | | | |
| | | | | | |
| | | | | | |

| | Code | Designation | | Product weight | Part no. | Туре | |
|-------------------|--------------|---|----------|----------------|----------|-------------------|--|
| | | | [g] | | | | |
| umatic multiple c | onnector pla | ate | | | | | |
| 4 ⁸ -0 | M | Pneumatic multiple connector plate, | 2 valves | 135 | 161969 | CPV10-VI-P2-M7 | |
| 6.6 | | for wall/machine mounting, | 4 valves | 164 | 161970 | CPV10-VI-P4-M7 | |
| ? •• | | without side flange | 6 valves | 219 | 161971 | CPV10-VI-P6-M7 | |
| | , | | 8 valves | 272 | 163893 | CPV10-VI-P8-M7 | |
| | J | | 2 valves | 261 | 163894 | CPV14-VI-P2-1/8 | |
| Y | | | 4 valves | 379 | 163895 | CPV14-VI-P4-1/8 | |
| * | | | 6 valves | 505 | 163896 | CPV14-VI-P6-1/8 | |
| | | | 8 valves | 627 | 163897 | CPV14-VI-P8-1/8 | |
| | | | 2 valves | 519 | 165292 | CPV18-VI-P2-1/4 | |
| | | | 4 valves | 695 | 165293 | CPV18-VI-P4-1/4 | |
| | | | 6 valves | 907 | 165294 | CPV18-VI-P6-1/4 | |
| | | | 8 valves | 1116 | 165295 | CPV18-VI-P8-1/4 | |
| | Р | Pneumatic multiple connector plate, | 2 valves | 182 | 152420 | CPV10-VI-P2-M7-B | |
| | | for wall/machine mounting, | 4 valves | 228 | 152421 | CPV10-VI-P4-M7-B | |
| | | with side flange | 6 valves | 283 | 152422 | CPV10-VI-P6-M7-B | |
| | | | 8 valves | 336 | 152423 | CPV10-VI-P8-M7-B | |
| | | | 2 valves | 365 | 152424 | CPV14-VI-P2-1/8-B | |
| | | | 4 valves | 483 | 152425 | CPV14-VI-P4-1/8-B | |
| | | | 6 valves | 609 | 152426 | CPV14-VI-P6-1/8-B | |
| | | | 8 valves | 731 | 152427 | CPV14-VI-P8-1/8-B | |
| | | | 2 valves | 659 | 175632 | CPV18-VI-P2-1/4-B | |
| | | | 4 valves | 832 | 175634 | CPV18-VI-P4-1/4-B | |
| | | | 6 valves | 1047 | 175636 | CPV18-VI-P6-1/4-B | |
| | | | 8 valves | 1256 | 175638 | CPV18-VI-P8-1/4-B | |
| | GQC | Pneumatic multiple connector plate with sealing | 2 valves | 250 | 538807 | CPV10-VI-P2-M7-C | |
| | | ring, | 4 valves | 320 | 538808 | CPV10-VI-P4-M7-C | |
| | | for control cabinet assembly, | 6 valves | 390 | 538809 | CPV10-VI-P6-M7-C | |
| | | with supply ports | 8 valves | 460 | 538810 | CPV10-VI-P8-M7-C | |
| | | | 2 valves | 500 | 539498 | CPV14-VI-P2-1/8-C | |
| | | | 4 valves | 650 | 539499 | CPV14-VI-P4-1/8-C | |
| | | | 6 valves | 800 | 539500 | CPV14-VI-P6-1/8-C | |
| | | | 8 valves | 920 | 539501 | CPV14-VI-P8-1/8-C | |
| | GQD | Pneumatic multiple connector plate with sealing | 2 valves | 80 | 538811 | CPV10-VI-P2-M7-D | |
| | | ring, | 4 valves | 150 | 538812 | CPV10-VI-P4-M7-D | |
| | | for control cabinet assembly, | 6 valves | 220 | 538813 | CPV10-VI-P6-M7-D | |
| | | without supply ports | 8 valves | 290 | 538814 | CPV10-VI-P8-M7-D | |
| | | | 2 valves | 350 | 539502 | CPV14-VI-P2-1/8-D | |
| | | | 4 valves | 550 | 539503 | CPV14-VI-P4-1/8-D | |
| | | | 6 valves | 400 | 539504 | CPV14-VI-P6-1/8-D | |
| | | | 8 valves | 650 | 539505 | CPV14-VI-P8-1/8-D | |
| | GQE | Pneumatic multiple connector plate with sealing | 2 valves | 300 | 566709 | CPV10-VI-P2-1/8-C | |
| | | ring, | 4 valves | 370 | 566710 | CPV10-VI-P4-1/8-C | |
| | | for control cabinet assembly, | 6 valves | 440 | 566711 | CPV10-VI-P6-1/8-C | |
| | | with all ports | 8 valves | 510 | 566712 | CPV10-VI-P8-1/8-C | |

| Ordering data | | | | | |
|------------------------|------|--|----------------|----------|-----------------|
| | Code | Designation | Product weight | Part no. | Туре |
| | | | [g] | | |
| Inscription label hold | ers | | | 1 | |
| | Z | Holder for inscription labels | 32 | 162560 | CPV10-VI-BZ-T-2 |
| | | | 33 | 162561 | CPV10-VI-BZ-T-3 |
| | | | 34 | 162562 | CPV10-VI-BZ-T-4 |
| | | | 35 | 162563 | CPV10-VI-BZ-T-5 |
| | | | 36 | 162564 | CPV10-VI-BZ-T-6 |
| | | | 37 | 162565 | CPV10-VI-BZ-T-7 |
| | | | 38 | 162566 | CPV10-VI-BZ-T-8 |
| | | | 8 | 162567 | CPV14-VI-BZ-T-2 |
| | | | 9.5 | 162568 | CPV14-VI-BZ-T-3 |
| | | | 11 | 162569 | CPV14-VI-BZ-T-4 |
| | | | 12.5 | 162570 | CPV14-VI-BZ-T-5 |
| | | | 14 | 162571 | CPV14-VI-BZ-T-6 |
| | | | 15.5 | 162572 | CPV14-VI-BZ-T-7 |
| | | | 17 | 162573 | CPV14-VI-BZ-T-8 |
| | | | 9 | 163293 | CPV18-VI-BZ-T-2 |
| | | | 10.5 | 163294 | CPV18-VI-BZ-T-3 |
| | | | 12 | 163295 | CPV18-VI-BZ-T-4 |
| | | | 13.5 | 163296 | CPV18-VI-BZ-T-5 |
| | | | 16 | 163297 | CPV18-VI-BZ-T-6 |
| | | | 17.5 | 163298 | CPV18-VI-BZ-T-7 |
| | | | 29 | 163299 | CPV18-VI-BZ-T-8 |
| | T | Holder for inscription labels, transparent | 11 | 194066 | CPV10-VI-ST-T-2 |
| | | | 14 | 194067 | CPV10-VI-ST-T-3 |
| | | | 17 | 194068 | CPV10-VI-ST-T-4 |
| | | | 20 | 194069 | CPV10-VI-ST-T-5 |
| | | | 23 | 194070 | CPV10-VI-ST-T-6 |
| | | | 24 | 194071 | CPV10-VI-ST-T-7 |
| | | | 29 | 194072 | CPV10-VI-ST-T-8 |
| | | | - | 194073 | CPV14-VI-ST-T-2 |
| | | | 18 | 194074 | CPV14-VI-ST-T-3 |
| | | | 22 | 194075 | CPV14-VI-ST-T-4 |
| | | | 25 | 194076 | CPV14-VI-ST-T-5 |
| | | | 53 | 194077 | CPV14-VI-ST-T-6 |
| | | | 59 | 194078 | CPV14-VI-ST-T-7 |
| | | | 63 | 194079 | CPV14-VI-ST-T-8 |
| | | | 17 | 194080 | CPV18-VI-ST-T-2 |
| | | | 23 | 194081 | CPV18-VI-ST-T-3 |
| | | | 29 | 194082 | CPV18-VI-ST-T-4 |
| | | | 35 | 194083 | CPV18-VI-ST-T-5 |
| | | | 41 | 194084 | CPV18-VI-ST-T-6 |
| | | | 47 | 194085 | CPV18-VI-ST-T-7 |
| | | | 53 | 194086 | CPV18-VI-ST-T-8 |
| Inscription labels | | | <u> </u> | | |
| macription tabets | Τ_ | 6x10 mm in frame, 64 pieces | 1_ | 18576 | IBS 6x10 |
| | | 9x20 mm in frames, 20 pieces (CPV18 only) | | 18182 | IBS 9x20 |
| | | 20 mini in manies, 20 pieces (CFV10 unity) | - | 10102 | 103 7820 |
| * | | | | | |

Accessories NEC500

| Ordering data | | | | | | |
|----------------------|-----------------|--|-----------------------------|-----------------------|--------------------|------------------------------|
| - | Code | Designation | | Product weight [g] | Part no. | Туре |
| Mounting | | | | | | |
| 6 3 | Н | Mounting for H-rail | | 15.8 | 162556 | CPV10/14-VI-BG-NRH-35 |
| | | | 5 | | 163291 | CPV18-VI-BG-NRH-35 |
| | W | Attachment for wall mounting | For CPV18 | 200 | 163292 | CPV18-VI-BG-RW |
| | U | | For CPV10/14 | 118 | 189541 | CPV10/14-VI-BG-RWL-B |
| | X | Mounting for individual connection and ET2 | 200X (included in the scope | 216 | 165801 | CPV10-VI-BG-ET200X |
| 69/10 | | of delivery) | 326 | 165803 | CPV14-VI-BG-ET200X | |
| Manual override | | | | | | |
| | - | Locking clip (for manual override), non-deta | 1.5 | 526203 | CPV10/14-HS | |
| | | | | 3 | 526204 | CPV18-HS |
| | V | Locking clip (cover for manual override), no | 0.15 | 530055 | CPV10/14-HV | |
| | | | | 0.53 | 530056 | CPV18-HV |
| Connecting cable for | r individual co | onnection, electrical | | | | |
| | D | Angled socket, plug pattern ZC, self-tap- | 2.5 m | 50 | 8047676 | NEBV-Z3WA2L-R-E-2.5-N-LE2-S1 |
| <i>5</i> 74 | E | ping screw, for CPV10/14 | 5 m | 90 | 8047677 | NEBV-Z3WA2L-R-E-5-N-LE2-S1 |
| | F | | 10 m | 170 | 8047675 | NEBV-Z3WA2L-R-E-10-N-LE2-S1 |
| Plug socket with cal | ole for individ | ual connection, electrical | | | | |
| <i>M</i> | D | For CPV18 | 2.5 m | 200 | 174844 | KMEB-2-24-2.5-LED |
| | E | | 5 m | 400 | 174845 | KMEB-2-24-5-LED |



Connecting cables are pre-assembled. They include a protective circuit and an LED for indicating the operating status.

| Ordering data | | | | | | | |
|---|------|--|-------------|------|------|----------|-----------------|
| | Code | Designation | Designation | | | Part no. | Туре |
| Multi-pin cable | | | | | | | |
| ~~ | Υ | Plug socket (Sub-D plug can be crimped), for | 9-pin | | 73 | 18708 | SD-SUB-D-BU9 |
| | | assembly by the user | 25-pin | | 75 | 18709 | SD-SUB-D-BU25 |
| /9 | R | Connecting cable, IP65, polyvinyl chloride | 9-pin | 5 m | 425 | 18698 | KMP3-9P-08-5 |
| | | | 25-pin | 1 | 672 | 18624 | KMP3-25P-16-5 |
| - E - E - E - E - E - E - E - E - E - E | S | S | 9-pin | 10 m | 814 | 18579 | KMP3-9P-08-10 |
| | | | 25-pin | | 1303 | 18625 | KMP3-25P-16-10 |
| | = | Connecting cable, IP65, polyurethane (suita- | 9-pin | 5 m | 378 | 193014 | KMP4-9P-5-PUR |
| | | ble for energy chains) | 25-pin | 1 | 702 | 193018 | KMP4-25P-5-PUR |
| | - | | 9-pin | 10 m | 723 | 193015 | KMP4-9P-10-PUR |
| | | | 25-pin | | 1617 | 193019 | KMP4-25P-10-PUR |
| | - | Connecting cable, IP65, polyvinyl chloride | 9-pin | 5 m | 413 | 193012 | KMP4-9P-5-PVC |
| | | (suitable for energy chains) | 25-pin | 1 | 854 | 193016 | KMP4-25P-5-PVC |
| | | | 9-pin | 10 m | 791 | 193013 | KMP4-9P-10-PVC |
| | | | 25-pin | | 1657 | 193017 | KMP4-25P-10-PVC |

| Ordering data | | | | | | |
|-------------------|---------------|----------------|---------|----------------|----------|---------------|
| | Code | Designation | | Product weight | Part no. | Туре |
| | | | | [g] | | |
| Blanking plug | _ | • | | | • | |
| | Blanking plu | ıg | | 1 | 3843 | B-M5 |
| | | | | 2 | 174309 | B-M7 |
| | | | | 7 | 3568 | B-1/8 |
| | | | | 15 | 3569 | B-1/4 |
| | | | | | 3570 | B-3/8 |
| | | | | 43 | 3571 | B-1/2 |
| Push-in fitting | | | | | | |
| | Push-in fitti | ng | | 12 | 186109 | QS-G1/8-8-I |
| | | | | 20 | 186112 | QS-G1/4-10-I |
| | | | | | 186114 | QS-G3/8-12-I |
| | | | | | 153317 | QSM-M5-6-I |
| | | | | 6.4 | 153321 | QSM-M7-6-I |
| Silencer | | | | | | |
| | Silencer | , | | 1.5 | 1205858 | AMTE-M-LH-M5 |
| | | | | 43 | 1205863 | AMTE-M-LH-G12 |
| | | | | 13 | 1205861 | AMTE-M-LH-G14 |
| | | | | 7.5 | 1205860 | AMTE-M-LH-G18 |
| | | | | 26 | 1205862 | AMTE-M-LH-G38 |
| | | | | 1.2 | 161418 | UC-M7 |
| User documentatio | n — | | | | | |
| | | CPV pneumatics | German | - | 165100 | P.BE-CPV-DE |
| | > | | English | | 165200 | P.BE-CPV-EN |
| | | | French | | 165130 | P.BE-CPV-FR |
| | | | Italian | | 165160 | P.BE-CPV-IT |
| | | | Spanish | | 165230 | P.BE-CPV-ES |