

Proportional-pressure regulator VPPM

FESTO



Characteristics

At a glance

Innovative:

- Multi-sensor control (cascade control)
- Diagnostics
- Choice of control characteristics
- Temperature-compensated
- High dynamic response
- High repetition accuracy
- Modular system processing
- IO-Link® for direct connection to a higher-order IO-Link®/I-Port master

Flexible:

- Individual valves (inline valve)
- Sub-base valves (manifold/flanged valve)
- Various user interfaces: LED displays, LCD display, setting/selection buttons
- Choice of valves with different pressure ranges
- Pressure range can be modified at the valve
- Choice of different setpoint specifications: current input; voltage input

Operationally safe:

- Integrated pressure sensor with separate output
- Cable break monitoring
- Pressure is maintained if the controller fails

Easy to assemble:

- Manifold block (manifold)
- H-rail mounting
- Individually with mounting bracket
- QS fittings

Layout of a control loop (layout):

- The reference variable w (setpoint value e.g. 5 volts or 8 milliamperes) first acts on a comparator. The measuring equipment sends the value of the controlled variable x (actual value e.g. 3 bar) to the comparator as feedback variable r. The control element detects the control difference e and controls the final control element. The output of the final control element acts on the system. The control element thus attempts to compensate for the difference between the reference variable w and the controlled variable x by using the final control element.

Operating principle:

- This process runs continuously so changes in the reference variable are always detected. However, a system deviation will also occur if the reference variable is constant and the controlled variable changes. This happens when there is a change in the flow rate through the valve, caused by a switching operation, a cylinder movement or a load change. The disturbance variable z also causes a control difference, such as, for example, a pressure drop in the air supply. The disturbance variable z has an unintended effect on the controlled variable x. The controller always tries to re-adjust the controlled variable x to the reference variable w.


Multi-sensor control (cascade control) of the VPPM:

- Unlike conventional direct-acting control systems, in multi-sensor control several control loops are nested inside one another. The overall controlled system is thus divided into smaller sections that are easier to control for specific tasks.

Valve function


[3]

3-way proportional-pressure regulator, closed



Characteristics

Ordering data - modular system



Configurable product

This product and all its product options can be ordered online via the configurator.

Diagrams

Further information → vppm



The diagrams shown in this document are also available online. These can be used to display precise values.

Proportional-pressure regulator VPPM

Type code

001	Series	009	Upper pressure value of control range
VPPM	Proportional pressure regulator, modular	2H	2 bar
002	Nominal width [mm]	6H	6 bar
6	6	10H	10 bar
8	8		
12	12		
003	Directional control valve type	010	Alternative lower pressure regulation range
L	In-line valve	...L	0 ... 9 bar
F	Flanged valve		
T	Flanged valve for valve terminal		
004	Mounting method	011	Alternative upper pressure regulation range
	Standard	...H	0.2 ... 10 bar
A	Valve terminal MPA	012	Setpoint input for individual valves
			For valve terminals/servo-pneumatics
005	Dynamic response	A4	4 ... 20 mA
L	Low	LK	IO-Link®
006	Valve function	V1	0 ... 10 V
1	3/2-way valve, normally closed		
007	Pneumatic connection	013	Switching input/output
F	Flange/sub-base		None
G18	G1/8	N	NPN
G14	G1/4	P	PNP
G12	G1/2		
008	Lower pressure value of control range	014	Overall accuracy
OL	0 bar		2%
		S1	1 %
		015	Operator unit/interface
			None
		C1	With LCD, variable pressure unit

Datasheet

Analogue interface, general technical data														
Pneumatic connection, port 1	Sub-base					G1/8		G1/4		G1/2				
Nominal size, supply	6 mm			8 mm			6 mm		8 mm		12 mm			
Nominal size, exhaust	4.5 mm			7 mm			4.5 mm		7 mm		12 mm			
Standard nominal flow rate (standardised to DIN 1343)	380 l/ min	900 l/ min	1,400 l/ min	450 l/ min	1,050 l/ min	1,650 l/ min	1,750 l/ min	380 l/ min	900 l/ min	1,400 l/ min	1,750 l/ min	2,750 l/ min	4,500 l/ min	7,000 l/ min
Valve function	3-way proportional pressure regulator													
Design	Piloted diaphragm regulator													
Sealing principle	Soft													
Type of actuation	Electric													
Type of piloting	Pilot actuated													
Type of reset	Mechanical spring													
Type of mounting	Either:, With through-hole, With accessories													
Mounting position	optional													
Product weight	400 g	560 g					400 g	560 g	560 g	2,050 g				

Analogue interface, electrical data				
Pneumatic connection, port 1	Sub-base	G1/8	G1/4	G1/2
Electrical connection	8-pin, M12, Plugs	Via sub-base	8-pin, M12, Plugs	
Operational voltage range DC	21.6 ... 26.4 V			
Residual ripple	10%			
Duty cycle	100%			
Max. electrical power consumption	7 W			12 W
Setpoint value input	–			
Short circuit current rating	For all electrical connections			
Reverse polarity protection	For all electrical connections			
Degree of protection	IP65			
Signal range analogue input	0 - 10 V 4 - 20 mA	–	0 - 10 V 4 - 20 mA	
Signal range analogue output	0 - 10 V 4 - 20 mA	–	0 - 10 V 4 - 20 mA	

Proportional-pressure regulator VPPM

Datasheet

Analogue interface, operating and environmental conditions			
Pressure regulation range	0.01 ... 1 MPa	0.002 ... 0.2 MPa	0.006 ... 0.6 MPa
Pressure regulation range	0.1 ... 10 bar	0.02 ... 2 bar	0.06 ... 6 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases		
Note on operating and pilot medium	Lubricated operation not possible		
Inlet pressure 1 ¹⁾	0 ... 1.1 MPa	0 ... 0.4 MPa	0 ... 0.8 MPa
Inlet pressure 1 ²⁾	0 ... 11 bar	0 ... 4 bar	0 ... 8 bar
Max. pressure hysteresis	0.05 bar	0.01 bar	0.03 bar
Hysteresis	0.5 %FS		
Linearity	1 %FS		
Linearity error in ± %FS	–		
Reproducibility	0.5 %FS		
Total accuracy	1.25%FS		
Repetition accuracy FS	0.5%		
Temperature coefficient	0.04 %/K		
Ambient temperature	0 ... 60°C		
Media temperature	10 ... 50°C		
Note on materials	RoHS-compliant		
LABS (PWIS) conformity	VDMA24364-B1/B2-L		
Corrosion resistance class CRC ³⁾	2 - Moderate corrosion stress		
CE mark (see declaration of conformity) ⁴⁾	To EU EMC Directive In accordance with EU RoHS Directive		
CE marking (see declaration of conformity) ⁵⁾	To UK instructions for EMC To UK RoHS instructions		
Approval	RCM trademark c UL us listed (OL)		
Certificate issuing authority	UL E322346		

1) The input pressure 1 should always be 1 bar greater than the maximum regulated outlet pressure.

2) The input pressure 1 should always be 1 bar greater than the maximum regulated outlet pressure.

3) More information www.festo.com/x/topic/crc

4) For information about the area of use, see the declaration of conformity at: www.festo.com/catalogue/.../d/Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

5) For information about the area of use, see the declaration of conformity at: www.festo.com/catalogue/.../d/Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Analogue interface, materials

Material housing	Wrought aluminium alloy, Anodised		
Material membrane	–		

IO-Link® interface, general technical data

Pneumatic connection, port 1	Sub-base						G1/8	G1/4			G1/2		
Nominal size, supply	6 mm						6 mm	8 mm			12 mm		
Nominal size, exhaust	4.5 mm						7 mm	4.5 mm			7 mm		
Standard nominal flow rate (standardised to DIN 1343)	380 l/min	900 l/min	1,400 l/min	450 l/min	1,050 l/min	1,650 l/min	380 l/min	900 l/min	1,400 l/min	650 l/min	1,750 l/min	2,750 l/min	1,900 l/min
Valve function	3-way proportional pressure regulator												
Design	Piloted diaphragm regulator												
Sealing principle	Soft												
Type of actuation	Electric												
Type of piloting	Pilot actuated												
Type of reset	Mechanical spring												
Type of mounting	Either., With through-hole, With accessories												
Mounting position	optional												
Product weight	400 g	560 g	400 g	560 g	560 g	2,050 g							
IO-Link, Protocol version	Device V 1.1												
IO-Link, Process data length OUT	2 bytes												
IO-Link, Process data length IN	2 bytes												
IO-Link, communication mode	COM1 (4.8 kB), COM2 (38.4 kB), COM3 (230.4 kB)												
IO-Link, Min. cycle time	0.5 ms												

Datasheet

IO-Link® interface, operating and environmental conditions			
Pressure regulation range	0.01 ... 1 MPa	0.002 ... 0.2 MPa	0.006 ... 0.6 MPa
Pressure regulation range	0.1 ... 10 bar	0.02 ... 2 bar	0.06 ... 6 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases		
Note on operating and pilot medium	Lubricated operation not possible		
Inlet pressure 1	0 ... 1.1 MPa	0 ... 0.4 MPa	0 ... 0.8 MPa
Inlet pressure 1	0 ... 11 bar	0 ... 4 bar	0 ... 8 bar
Max. pressure hysteresis	0.05 bar	0.01 bar	0.03 bar
Hysteresis	0.5 %FS		
Linearity	1 %FS		
Linearity error in \pm %FS	–		
Reproducibility	0.5 %FS		
Total accuracy	1.25%FS		
Repetition accuracy FS	0.5%		
Temperature coefficient	0.04 %/K		
Ambient temperature	0 ... 60°C		
Media temperature	10 ... 50°C		
Note on materials	RoHS-compliant		
LABS (PWIS) conformity	VDMA24364-B1/B2-L		
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress		
CE mark (see declaration of conformity) ²⁾	To EU EMC Directive In accordance with EU RoHS Directive		
CE marking (see declaration of conformity) ³⁾	To UK instructions for EMC To UK RoHS instructions		
Approval	RCM trademark c UL us listed (OL)		
Certificate issuing authority	UL E322346		

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the declaration of conformity at: www.festo.com/catalogue/... d Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.


3) For information about the area of use, see the declaration of conformity at: www.festo.com/catalogue/... d Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

IO-Link® interface, materials

Material housing	Wrought aluminium alloy, Anodised
------------------	-----------------------------------


Flow rate qn from 1 → 2 as a function of excess output pressure p2, VPPM-6L/F-...-OL2H-... (2 bar)




Proportional-pressure regulator VPPM

Datasheet


Flow rate q_n from 1 \rightarrow 2 as a function of excess output pressure p_2 , VPPM-6L/F-...-0L6H-... (6 bar)





Flow rate q_n from 1 \rightarrow 2 as a function of excess output pressure p_2 , VPPM-6L/F-...-0L10H-... (10 bar)



Flow rate q_n from 2 \rightarrow 3 as a function of excess output pressure p_2 , VPPM-6L/F-...-0L2H-... (2 bar)




Datasheet

Flow rate q_n from 2 \rightarrow 3 as a function of excess output pressure p_2 , VPPM-6L/F-...-0L6H-... (6 bar)Flow rate q_n from 2 \rightarrow 3 as a function of excess output pressure p_2 , VPPM-6L/F-...-0L10H-... (10 bar)Flow rate q_n from 1 \rightarrow 2 as a function of excess output pressure p_2 , VPPM-8L/F-...-0L2H-... (2 bar)


Proportional-pressure regulator VPPM

Datasheet


Flow rate q_n from 1 → 2 as a function of excess output pressure p_2 , VPPM-8L/F-...-0L6H-... (6 bar)






Flow rate q_n from 1 → 2 as a function of excess output pressure p_2 , VPPM-8L/F-...-0L10H-... (10 bar)



Flow rate q_n from 2 → 3 as a function of excess output pressure p_2 , VPPM-8L/F-...-0L2H-... (2 bar)




Datasheet

Flow rate q_n from 2 → 3 as a function of excess output pressure p_2 , VPPM-8L/F-...-0L6H-... (6 bar)Flow rate q_n from 2 → 3 as a function of excess output pressure p_2 , VPPM-8L/F-...-0L10H-... (10 bar)Flow rate q_n from 1 → 2 as a function of excess output pressure p_2 , VPPM-8F/8TA-...-0L2H-... (2 bar)


Proportional-pressure regulator VPPM

Datasheet


Flow rate q_n from 1 → 2 as a function of excess output pressure p_2 , VPPM-8F/8TA-...-0L6H-... (6 bar)






Flow rate q_n from 1 → 2 as a function of excess output pressure p_2 , VPPM-8F/8TA-...-0L10H-... (10 bar)



Flow rate q_n from 2 → 3 as a function of excess output pressure p_2 , VPPM-8F/8TA-...-0L2H-... (2 bar)




Datasheet

Flow rate q_n from 2 \rightarrow 3 as a function of excess output pressure p_2 , VPPM-8F/8TA-...-OL6H-.... (6 bar)Flow rate q_n from 2 \rightarrow 3 as a function of excess output pressure p_2 , VPPM-8F/8TA-...-OL10H-... (10 bar)Flow rate q_n from 1 \rightarrow 2 as a function of excess output pressure p_2 , VPPM-12L-...-OL2H-... (4 bar)


Proportional-pressure regulator VPPM

Datasheet


Flow rate q_n from 1 \rightarrow 2 as a function of excess output pressure p_2 , VPPM-12L-...-0L6H-... (8 bar)




Flow rate q_n from 1 \rightarrow 2 as a function of excess output pressure p_2 , VPPM-12L-...-0L10H-... (11 bar)



Flow rate q_n from 2 \rightarrow 3 as a function of excess output pressure p_2 , VPPM-12L-...-0L2H-... (4 bar)




Datasheet

Flow rate q_n from 2 → 3 as a function of excess output pressure p_2 , VPPM-12L-...-0L6H-... (8 bar)Flow rate q_n from 2 → 3 as a function of excess output pressure p_2 , VPPM-12L-...-0L10H-... (11 bar)

Dimensions

Dimensions – Analogue interface, VPPM-6F, sub-base valve

Download CAD data → www.festo.com




	B1	B2	D2 Ø	D4 Ø	D5 Ø	H1	H2	H3	H4	H5	H8	H9	H10	H11
VPPM-6F	65,4	47,5	M12x1	4,4	6	126,9	110,4	80,1	52,8	41,3	28,3	26,3	23	12,2

	L1	L2	L3	L4	L5	L6
VPPM-6F	41,5	31,5	30,3	28,4	12,3	25

Dimensions

Dimensions – Analogue interface, VPPM-6L- pneumatic connection G1/8

Download CAD data → www.festo.com


	B1	B2	B3	D1	D2	D4 ∅	H1	H2	H3	H4	H6	H7	H9	H10	H12
VPPM-6L	65,5	47,5	16	G1/8	M12x1	4,4	126,9	110,4	80,1	52,8	42	27	26,3	23	12
	L1					L2					L6				
VPPM-6L	41,5					31,5					25				

Proportional-pressure regulator VPPM

Dimensions

Dimensions – Analogue interface, VPPM-8F, sub-base valve

Download CAD data → www.festo.com




	B1	B2	D2	D5 ∅	H1	H2	H3	H4	H5	H8	H9	H10	H11
VPPM-8F	77,4	59,5	M12x1	8	126,9	110,4	80	52,8	41,3	28,3	26,3	23	12,2

	L1	L2	L3	L4	L5	L6
VPPM-8F	41,5	31,5	29,3	28,4	12,3	25

Dimensions

Dimensions – Analogue interface, VPPM-8L, pneumatic connection G1/4

Download CAD data → www.festo.com


	B1	B2	B3	D1	D2	H1	H2	H3	H4	H6	H7	H9	H10	H12
VPPM-8L	77,4	59,5	22	G1/4	M12x1	126,9	110,4	80	52,8	42	27	26,3	23	12

	L1	L2	L6
VPPM-8L	47	31,5	25

Dimensions

Dimensions – Analogue interface, VPPM-6TA, sub-base valve


Download CAD data → www.festo.com



	B1	D5 Ø	H2	H3	H4	H5	H8	H9	H11
VPPM-6TA	55,1	6	110,4	95,5	52,8	41,3	28,3	26,3	12,2
	L1	L2	L3	L4	L5	L6			
VPPM-6TA	41,5	31,5	30,3	28,4	12,3	9,9			

Dimensions

Dimensions – Analogue interface, VPPM-8TA, sub-base valve with LCD

Download CAD data → www.festo.com


	B1	D5 ∅	H2	H3	H4	H5	H8	H9	H10	H11	H13
VPPM-8TA	77,4	8	110,4	80	52,8	41,3	28,3	26,3	23	12,2	95,5
	L1	L2	L3	L4	L5	L6	L7				
VPPM-8TA	41,5	31,5	29,3	28,4	12,3	25	9,9				

Proportional-pressure regulator VPPM

Dimensions

Dimensions – Analogue interface, VPPM-12L, pneumatic connection G1/2

Download CAD data → www.festo.com




[1] With LCD

	B1	B2	B3	B4	D1	D2	D4 ∅	H1	H2	H3	H4	H6	H7	H9	H10	H12	H13
VPPM-12L	107,4	89,5	36	74	G1/2	M12x1	5,5	162,8	146,3	116	78,2	63	38,5	33,2	23	16,5	35,9

	L1	L2	L6	L7
VPPM-12L	72	53	25	9,5

Dimensions

Dimensions – IO-Link® interface, VPPM-6F, sub-base valve

Download CAD data → www.festo.com

	B1	B2	D2 ∅	D5 ∅	H1	H2	H4	H5	H8	H9	H11
VPPM-6F	65,5	47,5	M12x1	6	126,9	110,4	52,8	41,3	28,3	26,3	12,2


	L1	L2	L3	L4	L5	W1 ± 5°
VPPM-6F	41,5	31,5	30,3	28,4	12,3	45°

Proportional-pressure regulator VPPM

Dimensions

Dimensions – IO-Link® interface, VPPM-6L- pneumatic connection G1/8

Download CAD data → www.festo.com




	B1	B2	B3	D1 Ø	D2 Ø	D4 Ø	H1	H2	H4	H6	H7	H9	H12
VPPM-6L	65,5	47,5	16	G1/8	M12x1	4,4	126,9	110,4	52,8	42	27	26,3	12

	L1	L2	W1 ± 5°
VPPM-6L	41,5	31,5	45°

Dimensions


Dimensions – IO-Link® interface, VPPM-8F, sub-base valve

Download CAD data → www.festo.com

	B1	B2	D2	D5 Ø	H1	H2	H4	H5	H8	H9	H11
VPPM-8L	77,4	59,5	M12x1	8	126,9	110,4	52,8	41,3	28,3	26,3	12,2
	L1		L2		L3		L4		L5		W1 ± 5°
VPPM-8L	41,5		31,5		29,3		28,4		12,3		45°

Proportional-pressure regulator VPPM

Dimensions




	B1	B2	B3	D1	D2	H1	H2	H4	H6	H7	H9	H12
VPPM-8L	77,4	59,5	22	G1/4	M12x1	126,9	110,4	52,8	42	27	26,3	12

	L1	L2	W1 ± 5°
VPPM-8L	47	31,5	45°

Dimensions

Dimensions – IO-Link® interface, VPPM-12L, pneumatic connection G1/2


Download CAD data → www.festo.com

	B1	B2	B3	B4	D1	D2	D4 Ø	H1	H2	H4	H6	H7	H9	H12	H13
VPPM-12L	107,4	89,5	36	74	G1/2	M12x1	5,5	162,8	146,3	78,2	63	38,5	33,2	16,5	35,9
<hr/>															
	L1				L2			L7						W1 ±5°	
VPPM-12L	72				53			9,5						45°	

Dimensions

Dimensions – Manifold block VABM-P1

Download CAD data → www.festo.com




	B1	D1	D2	D3 ∅	D4 ∅	D5 ∅	H1	H2	H3	H4	H5
VABM-P1-SF-G14-2-P3											
VABM-P1-SF-G14-3-P3	30,2	G1/2	G1/4	17,8	11	6,2	~116	50	34,5	15,5	7,5
VABM-P1-SF-G14-4-P3											

	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VABM-P1-SF-G14-2-P3	113	96	42							
VABM-P1-SF-G14-3-P3	155	138	84	110,4	42	27	14	31,7	14,4	8,5
VABM-P1-SF-G14-4-P3	197	180	126							

Dimensions

Dimensions – Cover plate VABB-P1

Download CAD data → www.festo.com


	B1	H1	H2	H3	L1	L2
VABB-P1	5	56	26,5	5,2	41,5	31,5

Proportional-pressure regulator VPPM

Dimensions

Dimensions – Bracket VAME-P1-A


Download CAD data → www.festo.com



	B1	B2	B3	B4	D1 ∅	H1	H2	H3	H4	H5	H6	L1	L2	L3
VAME-P1-A	41	22	8	3	4,5	70	88,6	70	66,4	38,3	9,5	55	45	5


Dimensions

Dimensions – H-rail mounting VAME-P1-T

Download CAD data → www.festo.com

	B1	B2	B3	H1	H2	H3	H4	H5	H6	H7	L1	L2	L3	L4	L5	L6
VAME-P1-T	20,7	20	10	71,2	60	90,3	66,9	49,1	33,7	7,2	55	34	31,5	15,75	13	8

Dimensions




	B1	B2	B3	D1	D2	H1	H2	H2	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
NEBV-M12G8	38,8	20,5	13,8	6,3	3,2	18,8	16,3	9,4	2500	500	44,9	41,7	17,5	15	15	13,3	7,1	3,6

Dimensions

Dimensions – Connecting cable NEBV-M12G8-K-5-M12G4

Download CAD data → www.festo.com



	L1	L2	L3
NEBV-M12G8-K-2-M12G4	2000	44,9	41,7
NEBV-M12G8-K-5-M12G4	5000	44,9	41,7

Proportional-pressure regulator VPPM

Ordering data

VPPM with analogue interface							
Signal range ana- logue input	Signal range ana- logue output	Total accuracy	Pneumatic connec- tion, port 1	Pressure regulation range	Part no.	Type	
0 - 10 V	0 - 10 V	1.25%FS	Sub-base	0.002 ... 0.2 MPa	542239	VPPM-6F-L-1-F-0L2H-V1N-S1	
					542245	VPPM-6F-L-1-F-0L2H-V1N	
					558339	VPPM-6F-L-1-F-0L6H-V1P-C1	
					571286	VPPM-8F-L-1-F-0L6H-V1P-S1	
					542246	VPPM-6F-L-1-F-0L6H-V1N	
					571285	VPPM-8F-L-1-F-0L6H-V1P	
					558347	VPPM-6F-L-1-F-0L6H-V1N-C1	
					571287	VPPM-8F-L-1-F-0L6H-V1P-S1C1	
					542240	VPPM-6F-L-1-F-0L6H-V1N-S1	
				0.01 ... 1 MPa	542241	VPPM-6F-L-1-F-0L10H-V1N-S1	
					542247	VPPM-6F-L-1-F-0L10H-V1N	
			G1/8		542233	VPPM-6L-L-1-G18-0L2H-V1N	
					542227	VPPM-6L-L-1-G18-0L2H-V1N-S1	
					542228	VPPM-6L-L-1-G18-0L6H-V1N-S1	
					554043	VPPM-6L-L-1-G18-0L6H-V1P	
					575121	VPPM-6L-L-1-G18-0L6H-V1P-S1C1	
					554039	VPPM-6L-L-1-G18-0L6H-V1P-S1	
					558337	VPPM-6L-L-1-G18-0L6H-V1P-C1	
					542234	VPPM-6L-L-1-G18-0L6H-V1N	
					558346	VPPM-6L-L-1-G18-0L6H-V1N-C1	
					571448	VPPM-6L-L-1-G18-0L6H-V1N-S1C1	
			0.01 ... 1 MPa	558345	VPPM-6L-L-1-G18-0L10H-V1N-S1C1		
				554044	VPPM-6L-L-1-G18-0L10H-V1P		
				558335	VPPM-6L-L-1-G18-0L10H-V1P-S1C1		
				542229	VPPM-6L-L-1-G18-0L10H-V1N-S1		
				542235	VPPM-6L-L-1-G18-0L10H-V1N		
				554040	VPPM-6L-L-1-G18-0L10H-V1P-S1		
				575125	VPPM-6L-L-1-G18-0L10H-V1P-C1		
			G1/4	0.006 ... 0.6 MPa	571296	VPPM-8L-L-1-G14-0L6H-V1P	
					571294	VPPM-8L-L-1-G14-0L6H-V1N-S1	
					571295	VPPM-8L-L-1-G14-0L6H-V1N-S1C1	
					571297	VPPM-8L-L-1-G14-0L6H-V1P-S1	
					571298	VPPM-8L-L-1-G14-0L6H-V1P-S1C1	
				0.01 ... 1 MPa	571293	VPPM-8L-L-1-G14-0L10H-V1P-S1C1	
					571291	VPPM-8L-L-1-G14-0L10H-V1N-S1	
					571292	VPPM-8L-L-1-G14-0L10H-V1P-S1	
			G1/2	0.006 ... 0.6 MPa	575240	VPPM-12L-L-1-G12-0L6H-V1P-S1	
					575238	VPPM-12L-L-1-G12-0L6H-V1N-S1	
					575241	VPPM-12L-L-1-G12-0L6H-V1P-S1C1	
					575239	VPPM-12L-L-1-G12-0L6H-V1N-S1C1	
				0.01 ... 1 MPa	575236	VPPM-12L-L-1-G12-0L10H-V1P-S1	
					575235	VPPM-12L-L-1-G12-0L10H-V1N-S1	
					575237	VPPM-12L-L-1-G12-0L10H-V1P-S1C1	
					542248	VPPM-6F-L-1-F-0L2H-A4N	
					542242	VPPM-6F-L-1-F-0L2H-A4N-S1	
			Sub-base	0.006 ... 0.6 MPa	558340	VPPM-6F-L-1-F-0L6H-A4P-C1	
					571282	VPPM-8F-L-1-F-0L6H-A4P	
					542243	VPPM-6F-L-1-F-0L6H-A4N-S1	
					571284	VPPM-8F-L-1-F-0L6H-A4P-S1C1	
					571283	VPPM-8F-L-1-F-0L6H-A4P-S1	
				0.01 ... 1 MPa	542249	VPPM-6F-L-1-F-0L6H-A4N	
					542244	VPPM-6F-L-1-F-0L10H-A4N-S1	
					542250	VPPM-6F-L-1-F-0L10H-A4N	
					542230	VPPM-6L-L-1-G18-0L2H-A4N-S1	
					542236	VPPM-6L-L-1-G18-0L2H-A4N	
4 - 20 mA	4 - 20 mA		G1/8	0.002 ... 0.2 MPa	542231	VPPM-6L-L-1-G18-0L6H-A4N-S1	
					554045	VPPM-6L-L-1-G18-0L6H-A4P	
					542237	VPPM-6L-L-1-G18-0L6H-A4N	
					575128	VPPM-6L-L-1-G18-0L6H-A4P-S1C1	
				0.006 ... 0.6 MPa	558338	VPPM-6L-L-1-G18-0L6H-A4P-C1	

Ordering data

VPPM with analogue interface						
Signal range analogue input	Signal range analogue output	Total accuracy	Pneumatic connection, port 1	Pressure regulation range	Part no.	Type
4 - 20 mA	4 - 20 mA	1.25%FS	G1/8	0.006 ... 0.6 MPa	554041	VPPM-6L-L-1-G18-0L6H-A4P-S1
				0.01 ... 1 MPa	554042	VPPM-6L-L-1-G18-0L10H-A4P-S1
					542232	VPPM-6L-L-1-G18-0L10H-A4N-S1
					542238	VPPM-6L-L-1-G18-0L10H-A4N
					554046	VPPM-6L-L-1-G18-0L10H-A4P
					558336	VPPM-6L-L-1-G18-0L10H-A4P-S1C1
			G1/4	0.006 ... 0.6 MPa	571302	VPPM-8L-L-1-G14-0L6H-A4N-S1
					571299	VPPM-8L-L-1-G14-0L6H-A4P
					571303	VPPM-8L-L-1-G14-0L6H-A4N-S1C1
					571300	VPPM-8L-L-1-G14-0L6H-A4P-S1
					571301	VPPM-8L-L-1-G14-0L6H-A4P-S1C1
				0.01 ... 1 MPa	571288	VPPM-8L-L-1-G14-0L10H-A4N-S1
			G1/2		571289	VPPM-8L-L-1-G14-0L10H-A4P-S1
					571290	VPPM-8L-L-1-G14-0L10H-A4P-S1C1
				0.006 ... 0.6 MPa	575243	VPPM-12L-L-1-G12-0L6H-A4P-S1C1
					575242	VPPM-12L-L-1-G12-0L6H-A4P-S1
					575244	VPPM-12L-L-1-G12-0L6H-A4N-S1
					575245	VPPM-12L-L-1-G12-0L6H-A4N-S1C1
			0.01 ... 1 MPa		575232	VPPM-12L-L-1-G12-0L10H-A4N-S1
					575234	VPPM-12L-L-1-G12-0L10H-A4P-S1C1
					575233	VPPM-12L-L-1-G12-0L10H-A4P-S1

VPPM with analogue interface, for valve manifold				
Total accuracy	Pneumatic connection, port 1	Pressure regulation range	Part no.	Type
1.25%FS	Sub-base	0.002 ... 0.2 MPa	572407	VPPM-8TA-L-1-F-0L2H-S1C1
			542217	VPPM-6TA-L-1-F-0L2H-S1
			542220	VPPM-6TA-L-1-F-0L2H
			572410	VPPM-8TA-L-1-F-0L2H-C1
		0.006 ... 0.6 MPa	542218	VPPM-6TA-L-1-F-0L6H-S1
			572408	VPPM-8TA-L-1-F-0L6H-S1C1
			572411	VPPM-8TA-L-1-F-0L6H-C1
			542221	VPPM-6TA-L-1-F-0L6H
		0.01 ... 1 MPa	572412	VPPM-8TA-L-1-F-0L10H-C1
			542219	VPPM-6TA-L-1-F-0L10H-S1
			542222	VPPM-6TA-L-1-F-0L10H
			572409	VPPM-8TA-L-1-F-0L10H-S1C1

VPPM with IO-Link® interface				
Total accuracy	Pneumatic connection, port 1	Pressure regulation range	Part no.	Type
1.25%FS	Sub-base	0.002 ... 0.2 MPa	8031107	VPPM-6F-L-1-F-0L2H-LK-S1
			8031110	VPPM-8F-L-1-F-0L2H-LK-S1
			8031111	VPPM-8F-L-1-F-0L6H-LK-S1
		0.01 ... 1 MPa	8031108	VPPM-6F-L-1-F-0L6H-LK-S1
			8031112	VPPM-8F-L-1-F-0L10H-LK-S1
			8031109	VPPM-6F-L-1-F-0L10H-LK-S1
		G1/8	8024258	VPPM-6L-L-1-G18-0L2H-LK-S1
			8024259	VPPM-6L-L-1-G18-0L6H-LK-S1
			8024260	VPPM-6L-L-1-G18-0L10H-LK-S1
		G1/4	8024261	VPPM-8L-L-1-G14-0L2H-LK-S1
			8024262	VPPM-8L-L-1-G14-0L6H-LK-S1
			8024263	VPPM-8L-L-1-G14-0L10H-LK-S1
		G1/2	8024264	VPPM-12L-L-1-G12-0L2H-LK-S1
			8024265	VPPM-12L-L-1-G12-0L6H-LK-S1
			8024266	VPPM-12L-L-1-G12-0L10H-LK-S1


Proportional-pressure regulator VPPM

Ordering data

Modular product system			
	Nominal size, supply	Part no.	Type
	6 mm	543432	VPPM-6...
	8 mm	543433	VPPM-8
	12 mm	543435	VPPM-12

Peripherals

Individual valve VPPM-6L..., VPPM-8L...




Accessories		→ Page/Internet
Type/order code	Description	
[1]	Proportional-pressure regulator with LCD	-
[2]	Proportional-pressure regulator with LED	-
[3]	Proportional-pressure regulator with LED, with IO-Link®	-
[4]	Connecting cable	44
[5]	Angled plug socket with cable	44
[6]	Plug socket with cable, straight	43
[7]	Push-in fitting	qs
[8]	Silencer	u
[9]	Bracket	43

Peripherals

Accessories		→ Page/Internet
Type/order code	Description	
[10] H-rail mounting	For mounting on an H-rail	43

Peripherals


Individual valve VPPM-12L...



Accessories		→ Page/Internet
Type/order code	Description	
[1]	Proportional-pressure regulator with LED or LCD	Operator unit with LED or LCD
[2]	Proportional-pressure regulator with LED, with IO-Link®	Operator unit with LED, IO-Link®
[3]	Push-in fitting	For connecting tubing with standard O.D.
[4]	Connecting cable	—
[5]	Angled plug socket with cable	—
[6]	Plug socket with cable, straight	—
[7]	Retaining screws	—
[8]	Silencer	For mounting in exhaust ports

Peripherals

Valve manifold assembly with VPPM-6F..., VPPM-8F...



Accessories	Type/order code	Description	→ Page/Internet
[1]	Manifold block VABM	-	43
[2]	Proportional-pressure regulator with LCD	Operator unit with LCD	-
[3]	Proportional-pressure regulator with LED	Operator unit with LED	-
[4]	Proportional-pressure regulator with LED, with IO-Link®	Operator unit with LED, IO-Link®	-
[5]	Connecting cable	-	44
[6]	Angled plug socket with cable	-	44


Peripherals

Accessories		→ Page/Internet
Type/order code	Description	
[7] Plug socket with cable, straight	–	43
[8] Blanking plug	–	b
[9] Push-in fitting	For connecting tubing with standard O.D.	qs
[10] Silencer	For mounting in exhaust ports	u
[11] Cover plate	For vacant position, seal and countersunk screws are included in the scope of delivery	43

Proportional-pressure regulator VPPM

Peripherals


VPPM-6TA..., VPPM-8TA... for valve terminal MPA-S



Accessories	Type/order code	Description	→ Page/Internet
[1]	Valve terminal MPA-S	With fieldbus connection and VPPM	mpas
[2]	Proportional pressure regulator	For valve terminal MPA-S	mpas
[3]	Electrical interlinking module	For the sub-base of the proportional-pressure regulator	mpas
[4]	Push-in fitting	–	qs
[5]	Sub-base	Without electrical linking module or electrical module	mpas
[6]	Mounting	–	mpas


Accessories

Manifold block

	Product weight	Corrosion resistance class CRC ¹⁾	Part no.	Type
	900 g	2 - Moderate corrosion stress	542252	VABM-P1-SF-G14-2-P3
	1,230 g		542253	VABM-P1-SF-G14-3-P3
	1,565 g		542254	VABM-P1-SF-G14-4-P3

1) More information www.festo.com/x/topic/crc

Cover plate

	Product weight	Corrosion resistance class CRC ¹⁾	Part no.	Type
	35 g	1 - Low corrosion stress	558350	VABB-P1


1) More information www.festo.com/x/topic/crc

Bracket

	Product weight	Corrosion resistance class CRC ¹⁾	Part no.	Type
	71 g	1 - Low corrosion stress	542251	VAME-P1-A

1) More information www.festo.com/x/topic/crc

H-rail mounting

	Product weight	Corrosion resistance class CRC ¹⁾	Part no.	Type
	150 g	1 - Low corrosion stress	542255	VAME-P1-T

1) More information www.festo.com/x/topic/crc

Connecting cable, straight socket

	Electrical connection 1, connection type	Electrical connection 1, cable outlet	Electrical connection 1, number of connections/cores	Electrical connection 1, connector system	Cable length	Part no.	Type
	Socket	Straight	8	M12x1, A-coded to EN 61076-2- 101	2 m	525616	SIM-M12-8GD-2-PU
					5 m	525618	SIM-M12-8GD-5-PU
					10 m	570008	SIM-M12-8GD-10-PU

Connecting cable, angled socket

	Electrical connection 1, connection type	Electrical connection 1, cable outlet	Electrical connection 1, number of connections/cores	Electrical connection 1, connector system	Cable length	Part no.	Type
	Socket	Angled	8	M12x1, A-coded to EN 61076-2- 101	2 m	542256	NEBU-M12W8-K-2-N-LE8

Proportional-pressure regulator VPPM

Accessories

Connecting cable, angled socket							
	Electrical connection 1, connection type	Electrical connection 1, cable outlet	Electrical connection 1, number of connections/cores	Electrical connection 1, connector system	Cable length	Part no.	Type
	Socket	Angled	8	M12x1, A-coded to EN 61076-2- 101	5 m	542257	NEBU-M12W8-K-5-N-LE8
					10 m	570007	NEBU-M12W8-K-10-N-LE8

Connecting cable, one straight socket and one straight plug							
	Electrical connection 1, connection type	Electrical connection 1, cable outlet	Electrical connection 1, number of connections/cores	Electrical connection 1, connector system	Cable length	Part no.	Type
	Socket	Straight	8	M12x1, A-coded to EN 61076-2- 101	2 m	553575	NEBV-M12G8-K-2-M12G4
					5 m	553576	NEBV-M12G8-K-5-M12G4

Connecting cable, one straight socket and two straight plugs							
	Electrical connection 1, connection type	Electrical connection 1, cable outlet	Electrical connection 1, number of connections/cores	Electrical connection 1, connector system	Cable length	Part no.	Type
	Socket	Straight	8	M12x1, A-coded to EN 61076-2-101	547888	NEBV-M12G8-KD-3-M12G4	

Connecting cable for IO-Link® interface								
	Electrical connection 1, connection type	Electrical connection 1, cable outlet	Electrical connection 1, number of connections/cores	Electrical connection 1, connector system	Degree of protection	Cable length	Part no.	Type
	Socket	Straight	5	M12x1, A-coded to EN 61076- 2-101	IP65,	5 m	574321	NEBU-M12G5-E-5-Q8N-M12G5
					IP68,	7.5 m	574322	NEBU-M12G5-E-7.5-Q8N-M12G5
					IP69K	10 m	574323	NEBU-M12G5-E-10-Q8N-M12G5