


Solenoid valves VMPA


FESTO



Solenoid valves VMPA

Key features

FESTO



Innovative

- Slim high-performance valves in a sturdy metal housing
- MPA1 (width 10 mm):
flow rate up to 360 l/min
- MPA14 (width 14 mm):
flow rate up to 670 l/min
- MPA2 (width 20 mm):
flow rate up to 870 l/min

The valves are identical with the valves from the valve terminals MPA-S, MPA-F and MPA-L. This simplifies planning, ordering and warehousing.

Versatile

- High pressure range
–0.9 ... 10 bar
- Wide range of valve functions

Reliable

- Fast troubleshooting thanks to LEDs on the valves and diagnostics via fieldbus
- Extensive operating voltage range $\pm 25\%$
- Easy to service thanks to replaceable valves and electronic modules
- Manual override either non-detenting, detenting or secured against unauthorised activation (covered)


Easy to mount

- Secure wall mounting

Solenoid valves VMPA

Key features

FESTO



Equipment options

Valve functions

- 5/2-way valve, single solenoid
- 5/2-way valve, double solenoid
- 2x 3/2-way valve, normally open
- 2x 3/2-way valve, normally closed
- 2x 3/2-way valve, 1x normally open, 1x normally closed
- 5/3-way valve, mid-position pressurised

- 5/3-way valve, mid-position closed
- 5/3-way valve, mid-position exhausted
- 2x 2/2-way valve, normally closed

Special features

- Electrical M8 connection, 4-pin with screw connection
- Detachable electronics module with integrated holding current reduction

Solenoid valves VMPA

Peripherals overview

FESTO


Individual sub-base for solenoid valve width 10 mm

Ordering:

- Using individual part numbers

Individual sub-bases of the type VMPA1-IC-... can be equipped with any 10 mm solenoid valve VMPA1.

The electrical connection is established using a standardised 4-pin M8 plug (EN 60947-5-2).



Description	Brief description	→ Page/Internet
1 Solenoid valve	VMPA1...	24
2 Manual override (MO)	Non-detenting/turning with detent, per solenoid coil	–
3 Cover cap, coded	After fitting the cover cap, manual override operation is non-detenting only	26
4 Cover cap, covered	After fitting the cover cap, manual override is blocked	26
5 Cover cap, manual override detenting	After fitting the cover cap, manual override is detenting and can be operated without tools	26
6 Inscription label holder	Can be pushed onto manual override	26
7 Sub-base	For solenoid valve VMPA1...	26
8 Fittings and/or silencers	M7 for working ports (2, 4) and air/exhaust ports (1, 3, 5)	26
9 Fittings, silencers or blanking plugs	M5 for pilot air supply/pilot exhaust air (12/14, 82/84) and pressure compensation	26
10 Electrical port M8	4-pin	–

Solenoid valves VMPA

Peripherals overview

FESTO


Individual sub-base for solenoid valve width 14 mm

Ordering:

- Using individual part numbers

Individual sub-bases of the type VMPA14-IC-... can be equipped with any 14 mm solenoid valve VMPA14.

The electrical connection is established using a standardised 4-pin M8 plug (EN 60947-5-2).



Designation	Brief description	→ Page/Internet
1 Solenoid valve	VMPA14...	24
2 Manual override (MO)	Non-detenting/turning with detent, per solenoid coil	–
3 Cover cap, coded	After fitting the cover cap, manual override operation is non-detenting only	26
4 Cover cap, covered	After fitting the cover cap, manual override is blocked	26
5 Cover cap, manual override detenting	After fitting the cover cap, manual override is detenting and can be operated without tools	26
6 Inscription label holder	Can be pushed onto manual override	26
7 Sub-base	For solenoid valve VMPA14...	26
8 Fittings and/or silencers	G $\frac{1}{8}$ for working ports (2, 4) and air/exhaust ports (1, 3, 5)	26
9 Fittings, silencers or blanking plugs	M5 for pilot air supply/pilot exhaust air (12/14, 82/84) and pressure compensation	26
10 Electrical port M8	4-pin	–

Solenoid valves VMPA

Peripherals overview

FESTO


Individual sub-base for solenoid valve width 20 mm

Ordering:

- Using individual part numbers

Individual sub-bases of the type VMPA2-IC-... can be equipped with any 20 mm solenoid valve VMPA2.

The electrical connection is established using a standardised 4-pin M8 plug (EN 60947-5-2).




Designation	Brief description	→ Page/Internet
1 Solenoid valve	VMPA2...	24
2 Manual override (MO)	Non-detenting/turning with detent, per solenoid coil	–
3 Cover cap, coded	After fitting the cover cap, manual override operation is non-detenting only	26
4 Cover cap, covered	After fitting the cover cap, manual override is blocked	26
5 Cover cap, manual override detenting	After fitting the cover cap, manual override is detenting and can be operated without tools	26
6 Inscription label holder	Can be pushed onto manual override	26
7 Sub-base	For solenoid valve VMPA2...	26
8 Fittings and/or silencers	G $\frac{1}{8}$ for working ports (2, 4) and air/exhaust ports (1, 3, 5)	26
9 Fittings, silencers or blanking plugs	M5 for pilot air supply/pilot exhaust air (12/14, 82/84) and pressure compensation	26
10 Electrical port M8	4-pin	–

Solenoid valves VMPA

Key features – Pneumatic components

FESTO

Sub-base valve



The VMPA offers a comprehensive range of valve functions. All valves are equipped with a patented sealing system that facilitates efficient sealing, a broad pressure range and long service life. They have a pneumatic pilot control for optimising performance. Air is supplied by means of pilot air supply.

Solenoid valves can be quickly replaced since the tubing connectors remain on the sub-base. This design is also particularly slim.

Irrespective of the valve function there are solenoid valves with one solenoid coil (single solenoid) or with two solenoid coils (double solenoid or two single solenoid valves in one housing).

Design

Valve replacement

The valves are attached to the metal manifold block using two screws, which means that they can be easily

replaced. The mechanical sturdiness of the sub-base guarantees good long-term sealing.

Valve code

The valve code (M, MS, MU, J, N, NS, NU, K, KS, KU, H, HS, HU, B, G, E, X, W,

D, DS, I) is located on the front of the valve beneath the manual override.

5/2-way valve

Type	Circuit symbol	Width [mm]	Description
M		10, 14, 20	• Single solenoid • Pneumatic spring return • Reverse operation • Operating pressure –0.9 ... +10 bar
MS		10, 14, 20	• Single solenoid • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +8 bar
MU		10	• Single solenoid • Polymer poppet valve • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +10 bar
J		10, 14, 20	• Double solenoid • Reverse operation • Operating pressure –0.9 ... +10 bar

Solenoid valves VMPA




Key features – Pneumatic components

FESTO



2x 3/2-way valve			
Type	Circuit symbol	Width [mm]	Description
N		10, 14, 20	• Single solenoid • Normally open • Pneumatic spring return • Operating pressure 3 ... 10 bar
NS		10, 14, 20	• Single solenoid • Normally open • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +8 bar
NU		10	• Single solenoid • Polymer poppet valve • Normally open • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +10 bar
K		10, 14, 20	• Single solenoid • Normally closed • Pneumatic spring return • Operating pressure 3 ... 10 bar
KS		10, 14, 20	• Single solenoid • Normally closed • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +8 bar
KU		10	• Single solenoid • Polymer poppet valve • Normally closed • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +10 bar
H		10, 14, 20	• Single solenoid • Normal position – 1x closed – 1x open • Pneumatic spring return • Operating pressure 3 ... 10 bar
HS		10, 14, 20	• Single solenoid • Normal position – 1x closed – 1x open • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +8 bar
HU		10	• Single solenoid • Polymer poppet valve • Normal position – 1x closed – 1x open • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +10 bar

Solenoid valves VMPA

Key features – Pneumatic components

5/3-way valve			
Type	Circuit symbol	Width [mm]	Description
B		10, 14, 20	• Mid-position pressurised¹⁾ • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +10 bar
G		10, 14, 20	• Mid-position closed¹⁾ • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +10 bar
E		10, 14, 20	• Mid-position exhausted¹⁾ • Mechanical spring return • Reverse operation • Operating pressure –0.9 ... +10 bar

- 1) If neither solenoid coil is energised, the valve moves to its mid-position by means of spring force.
If both coils are energised at the same time, the valve remains in the previously assumed switching position.

3/2-way valve			
Type	Circuit symbol	Width [mm]	Description
W		10, 14, 20	• Single solenoid • Normally open • External compressed air supply • Pneumatic spring return • Reverse operation • Operating pressure –0.9 ... +10 bar Compressed air (–0.9 ... +10 bar) supplied at working port 2 can be switched with both internal and external pilot air supply.
X		10, 14, 20	• Single solenoid • Normally closed • External compressed air supply • Pneumatic spring return • Reverse operation • Operating pressure –0.9 ... +10 bar Compressed air (–0.9 ... +10 bar) supplied at working port 4 can be switched with both internal and external pilot air supply.

Solenoid valves VMPA

Key features – Pneumatic components

FESTO

2x 2/2-way valve			
Type	Circuit symbol	Width [mm]	Description
D		10, 14, 20	• Single solenoid • Normally closed • Pneumatic spring return • Operating pressure 3 ... 10 bar
DS		10, 14, 20	• Single solenoid • Normally closed • Mechanical spring return • Reverse operation • Operating pressure -0.9 ... +8 bar
I		10, 14, 20	• Single solenoid • 1x normally closed • 1x normally closed, reverse operation only • Pneumatic spring return • Operating pressure 3 ... 10 bar • Vacuum at port 3/5 only

-  - Note

A filter must be installed upstream of valves operated in vacuum mode. This prevents any foreign matter in the intake air getting into the valve (e.g. when operating a suction cup).

Pilot air supply

The pneumatic connection is located on the individual sub-base.
The ports differ for the following types of pilot air supply:

- internal pilot air and
- external pilot air.

Internal pilot air supply

Internal pilot air supply can be selected if the required working pressure is between 3 and 8 bar. The pilot air in the sub-base is branched from the compressed air supply 1 using an internal connection. Port 12/14 is sealed with a blanking plug at the factory.

External pilot air supply

If the supply pressure is less than 3 bar or greater than 8 bar, you must operate your valve VMPA using external pilot air. The pilot air is supplied via port 12/14 of the sub-base in this case.

-  - Note


If a slow pressure rise by means of a soft-start valve is required in the system, external pilot air should be selected whereby the pilot pressure applied during switch-on is already very high.

Solenoid valves VMPA

Key features – Assembly and operation

FESTO

Assembling the solenoid valve on an individual sub-base



- 1 Horizontal mounting holes
- 2 Vertical mounting holes

The individual sub-base for wall mounting is designed for integration into a system or machine. It can be mounted horizontally or vertically.

Display and operation

Each valve solenoid coil is allocated an LED which indicates its operating status.

- Indicator 12 shows the switching status of the coil for output 2
- Indicator 14 shows the switching status of the coil for output 4

Manual override


The manual override (MO) enables the valve to be actuated when not electrically activated or energised. The pilot valve is switched by pushing the manual override. The set switching status can also be locked by turning

the manual override.

Alternatives:

- A cover (VMPA-HBT-B) can be fitted over the manual override to prevent it from being locked. The manual override can then only be activated by pushing it.

- A cover (VMPA-HBV-B) can be fitted over the manual override to prevent it from being accidentally actuated.
- The cover cap (VAMC-L1-CD) can be used to operate the manual override in detenting mode without additional tools.



Note

A manually actuated valve (manual override) cannot be reset electrically. Conversely, an electrically actuated valve cannot be reset using the mechanical manual override.


Solenoid valves VMPA

Key features – Assembly and operation

FESTO


Manual override (MO)

MO with automatic return (non-detenting)




- 1 Press in the stem of the MO with a pin or screwdriver. Pilot valve switches and actuates the main valve.
- 2 Remove the pin or screwdriver. Spring force pushes the stem of the MO back. Pilot valve returns to its initial position and so too the single solenoid main valve (not with double solenoid valve code J).

MO with locking (detenting)




- 1 Press in the stem of the MO with a pin or screwdriver until the valve switches and then turn the stem clockwise by 90° until the stop is reached. Valve remains switched.
- 2 Turn the stem anti-clockwise by 90° until the stop is reached and then remove the pin or screwdriver. Spring force pushes the stem of the MO back. The valve returns to its initial position (not with double solenoid valve code J).

MO with automatic return (non-detenting)




MO is operated by pressing it with a pointed object or screwdriver and reset by spring force (detenting position prevented due to coded cover cap).

MO with locking turning – assembly



Turn MO to clip it onto the pilot valve.
The MO cap can then be operated (detenting) without tools.


MO with locking turning – actuation



Sliding the cap for the MO in the direction of the arrow causes the following to happen:

- Cap locks into the stop position.
- Pilot valve switches and actuates the main valve.

MO with locking turning – actuation



Sliding the cap for the MO in the direction of the arrow causes the following to happen:


- Cap locks into the stop position.
- Spring force pushes the stem of the MO back.
- Pilot valve returns to its initial position and so too the single solenoid main valve (not with double solenoid valve code J).

Solenoid valves VMPA

Key features – Electrical components

FESTO


Electrical power as a result of current reduction



Each solenoid coil MPA is protected with a spark arresting protective circuit as well as against polarity reversal. All valve types are additionally equipped with integrated current reduction.

Valves MPA are supplied with operating voltage in the range 18 ... 30 V (24 V +/-25%). This high tolerance is made possible through integrated control electronics and offers additional security, e.g. if the operating voltage drops.

Electrical connection



1 Electrical connection, plug 4-pin, M8, to EN 60947-5-2

Tightening torque for M8 plug: 0.25 ... 0.5 Nm (manual torque)

Pin allocation to ISO 20401

	Pin	With positive logic	With positive logic
	1	Unused	Unused
	2	U _B for coil 12	0 V for coil 12
	3	0 V for coil 12 and 14	U _B for coil 12 and 14
	4	U _B for coil 14	0 V for coil 14

Instructions for use

Equipment

Operate system equipment with unlubricated compressed air if possible. Festo valves and cylinders are designed so that, if used as designated, they will not require additional lubrication and will still achieve a long service life. The quality of compressed air downstream of the compressor must correspond to that of unlubricated compressed air. If possible, do not operate all of your system equipment with lubricated compressed air. The lubricators should, where possible, always be installed directly upstream of the actuator used.

Unsuitable additional oil and too high an oil content in the compressed air reduce the service life of the valve terminal. Use Festo special oil OFSW-32 or the alternatives listed in the Festo catalogue (as specified in DIN 51524 HLP32; basic oil viscosity 32 CST at 40 °C).

Bio-oils

When using bio-oils (oils which are based on synthetic or native ester, e.g. rapeseed oil methyl ester), the maximum residual oil content of 0.1 mg/m³ must not be exceeded (see ISO 8573-1 Class 2).

Mineral oils

When using mineral oils (e.g. HLP oils to DIN 51524, parts 1 to 3) or similar oils based on poly-alpha-olefins (PAO), the maximum residual oil content of 5 mg/m³ must not be exceeded (see ISO 8573-1 Class 4). A higher residual oil content irrespective of the compressor oil cannot be permitted, as the basic lubricant would be flushed out over time.

Solenoid valves VMPA

FESTO

Technical data – solenoid valve mounting on sub-base

-  - Flow rate
 VMPA1: Up to 360 l/min
 VMPA14: Up to 670 l/min
 VMPA2: Up to 870 l/min

-  - Voltage
 24 V DC

-  - Valve width
 VMPA1: 10 mm
 VMPA14: 14 mm
 VMPA2: 20 mm



General technical data			
Width	10 mm	14 mm	20 mm
Lubrication	Life-time lubrication, PWIS-free (free of paint-wetting impairment substances)		
Type of mounting	Via through-hole		
Mounting position	Any		
Manual override	Non-detenting, detenting		
Valve weight [g]	➔ Page 15		
Sub-base weight [g]	92	184	233
Pneumatic connections			
Pneumatic connection	Via sub-base		

Solenoid valves VMPA

Technical data – solenoid valve

FESTO

Technical data – Valve width 10 mm															
Code			M	J	N	K	H	B	G	E	X	W	D	I	
Switching times	On	[ms]	10	10	10	10	10	10	10	10	10	10	10	8	
	Off	[ms]	20	–	20	20	20	35	35	35	20	20	20	20	
	Changeover	[ms]	–	15	–	–	–	15	15	15	–	–	–	–	
Operating pressure		[bar]	–0.9 ... +10		3 ... 10			–0.9 ... +10						3 ... 10	
Pilot pressure		[bar]	3 ... 8												
Standard nominal flow rate		[l/min]	360	360	300	230	300	300	320	240	255	255	230	260	
Design			Piston spool valve												
Max. tightening torque of valve mounting		[Nm]	0.25												
Materials			Die-cast aluminium												
Product weight		[g]	49	56	56	56	56	56	56	56	49	49	56	–	

Technical data – Valve width 10 mm											
Code			MS	NS	KS	HS	DS	MU	NU	KU	HU
Switching times	On	[ms]	10	14	14	14	14	10	8	8	8
	Off	[ms]	27	16	16	16	16	12	8	10	10
	Changeover	[ms]	–	–	–	–	–	–	–	–	–
Operating pressure		[bar]	–0.9 ... +8					–0.9 ... +10			
Pilot pressure		[bar]	3 ... 8								
Standard nominal flow rate		[l/min]	360	300	230	300	230	190	190	160	190
Design			Piston spool valve					Poppet valve with spring return			
Max. tightening torque of valve mounting		[Nm]	0.25								
Materials			Die-cast aluminium					PPA reinforced			
Product weight		[g]	56	56	56	56	56	35	42	42	42

Technical data – Valve width 14 mm																			
Code			M	J	N	K	H	B	G	E	X	W	D	I	MS	NS	KS	HS	DS
Switching times	On	[ms]	13	9	12	12	12	16	13	13	12	12	12	9	13	12	12	12	10
	Off	[ms]	30	–	38	38	38	50	52	50	20	20	30	25	30	23	23	23	25
	Changeover	[ms]	–	24	–	–	–	26	26	26	–	–	–	–	–	–	–	–	–
Operating pressure		[bar]	–0.9 ... +10												–0.9 ... +8				
Pilot pressure		[bar]	3 ... 8																
Standard nominal flow rate		[l/min]	670	670	650	600	650	630	610	480	400	400	650	570	670	520	560	520	570
Design			Piston spool valve																
Max. tightening torque of valve mounting		[Nm]	0.65																
Materials			Die-cast aluminium																
Product weight		[g]	77																

Technical data – Valve width 20 mm																				
Code			M	J	N	K	H	B	G	E	X	W	D	I	MS	NS	KS	HS	DS	
Switching times	On	[ms]	15	9	8	8	8	11	10	11	13	13	7	7	8	12	12	12	12	
	Off	[ms]	28	–	28	28	28	46	40	47	22	22	25	23	36	25	25	25	25	
	Changeover	[ms]	–	22	–	–	–	23	21	23	–	–	–	–	–	–	–	–	–	
Operating pressure		[bar]	–0.9 ... +10				3 ... 10				–0.9 ... +10				3 ... 10		–0.9 ... +8			
Pilot pressure		[bar]	3 ... 8																	
Standard nominal flow rate		[l/min]	700	700	560	500	560	520	630	610	590	500	680	680	700	560	500	560	680	
Design			Piston spool valve																	
Max. tightening torque of valve mounting		[Nm]	0.65																	
Materials			Die-cast aluminium																	
Product weight		[g]	100											–		100				

Solenoid valves VMPA

Technical data – solenoid valve



Current consumption per solenoid coil at nominal voltage			
Width	10 mm	14 mm	20 mm
Nominal pick-up current [mA]	50	50	110
Nominal current with current reduction [mA]	10	10	23
Time until current reduction [ms]	20	20	20

Electrical data		
Nominal voltage [V DC]	24	
Operating voltage range [V DC]	18 ... 30	
Residual ripple [Vss]	4	
Protection class to EN 60529	IP65 (for all types of signal transmission in assembled state)	

Operating and environmental conditions	
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)
Ambient temperature [°C]	–5 ... +50
Temperature of medium [°C]	–5 ... +50
Storage temperature [°C]	–20 ... +40
Relative air humidity	Max. 90% at 40 °C
Corrosion resistance class CRC ¹⁾	1
CE marking (see declaration of conformity)	To EU EMC Directive ²⁾
Certification	cULus recognized (OL)

- 1) Corrosion resistance class 1 according to Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → Certificates.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Materials	
Sub-base	Die-cast aluminium
Seals	Nitrile rubber
Note on materials	RoHS-compliant


Solenoid valves VMPA

Technical data – solenoid valve

FESTO


Pilot pressure p2 as a function of working pressure p1 with external pilot air supply

For valves with code: M, J, B, G, E, W, X



1 Operating range for valves with external pilot air supply


For valves with code: N, K, H, D, I




1 Operating range for valves with external pilot air supply

Pilot pressure p2 as a function of working pressure p1 for valves with mechanical spring return


For valves in width 10 mm with code: MS, NS, KS, HS, DS




For valves in width 20 mm with code: MS, NS, KS, HS, DS



For valves in width 14 mm with code: NS, KS, HS, DS



For polymer poppet valve in width 10 mm with code: MU, NU, KU, HU



Solenoid valves VMPA

Technical data – sub-base

FESTO

-  - Flow rate
VMPA1: Up to 360 l/min
VMPA14: Up to 670 l/min
VMPA2: Up to 870 l/min
-  - Voltage
24 V DC
-  - Valve width
VMPA1: 10 mm
VMPA14: 14 mm
VMPA2: 20 mm



General technical data				
Width		10 mm	14 mm	20 mm
Electrical connection		Plug, M8x1, 4-pin, to EN 60947-5-2		
Type of mounting		Via through-hole		
Mounting position		Any		
Pneumatic connections				
Supply port	1	M7	G1/8	G1/8
Exhaust port	3	M7	G1/8	G1/8
	5	M7	G1/8	G1/8
Working ports	2	M7	G1/8	G1/8
	4	M7	G1/8	G1/8
Pilot air port	12/14	M5	M5	M5
Pilot exhaust air port	82/84	M5	M5	M5

Operating and environmental conditions				
Type			VMPA...-1	VMPA...-EX1E
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[bar]	3 ... 8	
	External pilot air supply	[bar]	−0.9 ... 10	
Pilot pressure		[bar]	3 ... 8	
Ambient temperature		[°C]	−5 ... +50	
CE marking (see declaration of conformity)			To EU EMC Directive ¹⁾	To EU EMC Directive ¹⁾
			–	To EU Explosion Protection Directive (ATEX)

- 1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → Certificates.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

ATEX ¹⁾		
Type	VMPA...-EX1E	
ATEX category gas	II 3G	 - Note Also applies to the sub-base for individual connection type VMPA...-EX1E with retrofitted valve (see declaration of conformity).
Explosion ignition protection type for gas	Ex nA IIC T4 X Gc	
Explosion-proof temperature	[°C]	
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)	

- 1) For special ATEX applications please speak to your technical consultant

Materials	
Sub-base	Die-cast aluminium
Note on materials	RoHS-compliant

Solenoid valves VMPA


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Solenoid valve width 10 mm on individual sub-base



Type	B1	B2	B3	D1	D2	D3	D4 Ø	D5 Ø	H1	H2	H3	H6	H7	H8
VMPA1-...	28.8	20.2	3.2	M8x1	M7	M5	3.4	3.4	52.2	21	12.9	11.6	6.8	5.7

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16
VMPA1-...	107.3	66.6	64.2	56.7	49.8	44.1	35	25.9	20.3	13.3	47.4	16.4	11.3	5.6	1.2	3.2

Solenoid valves VMPA


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Solenoid valve width 14 mm on individual sub-base



Type	B1	B2	B3	D1	D2	D3	D4 Ø	D5 Ø	H1	H2	H3	H4	H5	H6	H7	H8
VMPA14-...	35.1	24.4	3.2	M8x1	G1/8	M5	5.5	3.4	59	29.4	27.4	19.8	17.9	17	8.7	7.7

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16
VMPA14-...	107.3	67	62.2	58	48.2	46.2	35.9	25	22.8	12.5	50.9	16.3	10.1	3.9	1.2	2.9

Solenoid valves VMPA


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Solenoid valve width 20 mm on individual sub-base




Type	B1	B2	B3	D1	D2	D3	D4 Ø	D5 Ø	H1	H2	H3	H4	H5	H6	H7	H8
VMPA2-...	37.2	30.5	3.2	M8x1	G1/8	M5	5.5	3.4	60.5	29.4	27.4	10.7	17.9	17	8.7	7.7

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16
VMPA2-...	107.3	66.6	64.2	60.3	49.4	47.6	37	26.4	24.6	13.7	50.9	16.3	11.2	4.4	1.2	3.2

Solenoid valves VMPA

FESTO


Ordering data

Ordering data				
	Valve function	Width [mm]	Part No.	Type
Internal pilot air supply – Solenoid valve on individual sub-base				
	5/2-way valve			
	Single solenoid	10	533376	VMPA1-M1H-M-M7-PI
		14	8023543	VMPA14-M1H-M-PI
		20	537963	VMPA2-M1H-M-G1/8-PI
	Single solenoid, mechanical spring return	14	8023554	VMPA14-M1H-MS-G1/8-PI
	Double solenoid	10	533377	VMPA1-M1H-J-M7-PI
		14	8023542	VMPA14-M1H-J-G1/8-PI
		20	537964	VMPA2-M1H-J-G1/8-PI
	2x 3/2-way valve			
	Normally open	10	533382	VMPA1-M1H-N-M7-PI
		14	8023550	VMPA14-M1H-N-G1/8-PI
		20	537969	VMPA2-M1H-N-G1/8-PI
	Normally open, mechanical spring return	14	8023556	VMPA14-M1H-NS-G1/8-PI
	Normally closed	10	533381	VMPA1-M1H-K-M7-PI
		14	8023549	VMPA14-M1H-K-G1/8-PI
		20	537968	VMPA2-M1H-K-G1/8-PI
	Normally closed, mechanical spring return	14	8023555	VMPA14-M1H-KS-G1/8-PI
	1x normally open, 1x normally closed	10	533383	VMPA1-M1H-H-M7-PI
		14	8023551	VMPA14-M1H-H-G1/8-PI
		20	537970	VMPA2-M1H-H-G1/8-PI
	1x normally open, 1x normally closed, mechanical spring return	14	8023558	VMPA14-M1H-HS-G1/8-PI
	5/3-way valve			
	Mid-position pressurised	10	533378	VMPA1-M1H-B-M7-PI
		14	8023544	VMPA14-M1H-B-G1/8-PI
		20	537965	VMPA2-M1H-B-G1/8-PI
	Mid-position closed	10	533379	VMPA1-M1H-G-M7-PI
		14	8023546	VMPA14-M1H-G-G1/8-PI
		20	537966	VMPA2-M1H-G-G1/8-PI
	Mid-position exhausted	10	533380	VMPA1-M1H-E-M7-PI
		14	8023545	VMPA14-M1H-E-G1/8-PI
		20	537967	VMPA2-M1H-E-G1/8-PI
	2x 2/2-way valve			
	Normally closed	10	533384	VMPA1-M1H-D-M7-PI
		14	8023552	VMPA14-M1H-D-G1/8-PI
		20	537971	VMPA2-M1H-D-G1/8-PI
	Normally closed, mechanical spring return	14	8023557	VMPA14-M1H-DS-G1/8-PI
	1x normally closed	10	545230	VMPA1-M1H-I-M7-PI
	1x normally closed, reverse operation	14	8023553	VMPA14-M1H-I-G1/8-PI
		20	545232	VMPA2-M1H-I-G1/8-PI

Solenoid valves VMPA

FESTO


Ordering data

Ordering data				
	Valve function	Width [mm]	Part No.	Type
External pilot air supply – Solenoid valve on individual sub-base				
	5/2-way valve			
	Single solenoid	10	533385	VMPA1-M1H-M-S-M7-PI
		14	8023560	VMPA14-M1H-M-S-G1/8-PI
		20	537972	VMPA2-M1H-M-S-G1/8-PI
	Single solenoid, mechanical spring return	14	8023571	VMPA14-M1H-MS-S-G1/8-PI
	Double solenoid	10	533386	VMPA1-M1H-J-S-M7-PI
		14	8023559	VMPA14-M1H-J-S-G1/8-PI
		20	537973	VMPA2-M1H-J-S-G1/8-PI
	2x 3/2-way valve			
	Normally open	10	533391	VMPA1-M1H-N-S-M7-PI
		14	8023567	VMPA14-M1H-N-S-G1/8-PI
		20	537978	VMPA2-M1H-N-S-G1/8-PI
	Normally open, mechanical spring return	14	8023573	VMPA14-M1H-NS-S-G1/8-PI
	Normally closed	10	533390	VMPA1-M1H-K-S-M7-PI
		14	8023566	VMPA14-M1H-K-S-G1/8-PI
		20	537977	VMPA2-M1H-K-S-G1/8-PI
	Normally closed, mechanical spring return	14	8023572	VMPA14-M1H-KS-S-G1/8-PI
	1x normally open, 1x normally closed	10	533392	VMPA1-M1H-H-S-M7-PI
		14	8023568	VMPA14-M1H-H-S-G1/8-PI
		20	537979	VMPA2-M1H-H-S-G1/8-PI
	1x normally open, 1x normally closed, mechanical spring return	14	8023575	VMPA14-M1H-HS-S-G1/8-PI
	5/3-way valve			
	Mid-position pressurised	10	533387	VMPA1-M1H-B-S-M7-PI
		14	8023561	VMPA14-M1H-B-S-G1/8-PI
		20	537974	VMPA2-M1H-B-S-G1/8-PI
	Mid-position closed	10	533388	VMPA1-M1H-G-S-M7-PI
		14	8023563	VMPA14-M1H-G-S-G1/8-PI
		20	537975	VMPA2-M1H-G-S-G1/8-PI
	Mid-position exhausted	10	533389	VMPA1-M1H-E-S-M7-PI
		14	8023562	VMPA14-M1H-E-S-G1/8-PI
		20	537976	VMPA2-M1H-E-S-G1/8-PI
	2x 2/2-way valve			
	Normally closed	10	533393	VMPA1-M1H-D-S-M7-PI
		14	8023569	VMPA14-M1H-D-S-G1/8-PI
		20	537980	VMPA2-M1H-D-S-G1/8-PI
	Normally closed, mechanical spring return	14	8023574	VMPA14-M1H-DS-S-G1/8-PI
	1x normally closed	10	545231	VMPA1-M1H-I-S-M7-PI
	1x normally closed, reverse operation	14	8023570	VMPA14-M1H-I-S-G1/8-PI
		20	545233	VMPA2-M1H-I-S-G1/8-PI

Solenoid valves VMPA



FESTO

Ordering data

Ordering data		Valve function	Width [mm]	Part No.	Type
Individual solenoid valve, piston spool valve					
	5/2-way valve				
	Single solenoid		10	533342	VMPA1-M1H-M-PI
			14	573718	VMPA14-M1H-M-PI
			20	537952	VMPA2-M1H-M-PI
	Single solenoid, mechanical spring return		10	571334	VMPA1-M1H-MS-PI
			14	573974	VMPA14-M1H-MS-PI
			20	571333	VMPA2-M1H-MS-PI
	Double solenoid		10	533343	VMPA1-M1H-J-PI
			14	573717	VMPA14-M1H-J-PI
			20	537953	VMPA2-M1H-J-PI
	2x 3/2-way valve				
	Normally open		10	533348	VMPA1-M1H-N-PI
			14	573725	VMPA14-M1H-N-PI
			20	537958	VMPA2-M1H-N-PI
	Normally open, mechanical spring return		10	556839	VMPA1-M1H-NS-PI
			14	575977	VMPA14-M1H-NS-PI
			20	568655	VMPA2-M1H-NS-PI
	Normally closed		10	533347	VMPA1-M1H-K-PI
			14	573724	VMPA14-M1H-K-PI
			20	537957	VMPA2-M1H-K-PI
	Normally closed, mechanical spring return		10	556838	VMPA1-M1H-KS-PI
			14	575976	VMPA14-M1H-KS-PI
			20	568656	VMPA2-M1H-KS-PI
	1x normally open, 1x normally closed		10	533349	VMPA1-M1H-H-PI
			14	573726	VMPA14-M1H-H-PI
			20	537959	VMPA2-M1H-H-PI
	1x normally open, 1x normally closed, mechanical spring return		10	556840	VMPA1-M1H-HS-PI
			14	575979	VMPA14-M1H-HS-PI
			20	568658	VMPA2-M1H-HS-PI
	5/3-way valve				
	Mid-position pressurised		10	533344	VMPA1-M1H-B-PI
			14	573719	VMPA14-M1H-B-PI
			20	537954	VMPA2-M1H-B-PI
	Mid-position closed		10	533345	VMPA1-M1H-G-PI
			14	573721	VMPA14-M1H-G-PI
			20	537955	VMPA2-M1H-G-PI
	Mid-position exhausted		10	533346	VMPA1-M1H-E-PI
			14	573720	VMPA14-M1H-E-PI
			20	537956	VMPA2-M1H-E-PI

Solenoid valves VMPA


Ordering data





Ordering data				
	Valve function	Width [mm]	Part No.	Type
Individual solenoid valve, piston spool valve				
	3/2-way valve			
	Normally open, external compressed air supply	10	540050	VMPA1-M1H-W-PI
		14	573723	VMPA14-M1H-W-PI
		20	540051	VMPA2-M1H-W-PI
	Normally closed, external compressed air supply	10	534415	VMPA1-M1H-X-PI
		14	573722	VMPA14-M1H-X-PI
		20	537961	VMPA2-M1H-X-PI
	2x 2/2-way valve			
	Normally closed	10	533350	VMPA1-M1H-D-PI
		14	573727	VMPA14-M1H-D-PI
		20	537960	VMPA2-M1H-D-PI
	Normally closed, mechanical spring return	10	556841	VMPA1-M1H-DS-PI
		14	575978	VMPA14-M1H-DS-PI
		20	568657	VMPA2-M1H-DS-PI
	1x normally closed 1x normally closed, reverse operation only	10	543605	VMPA1-M1H-I-PI
		14	573728	VMPA14-M1H-I-PI
		20	543703	VMPA2-M1H-I-PI
Individual solenoid valve, polymer poppet valve				
	5/2-way valve			
	Single solenoid, mechanical spring return	10	553113	VMPA1-M1H-MU-PI
	2x 3/2-way valve			
	normally open, mechanical spring return	10	553111	VMPA1-M1H-NU-PI
	Normally closed, mechanical spring return	10	553110	VMPA1-M1H-KU-PI
	1x normally open, 1x normally closed, mechanical spring return	10	553112	VMPA1-M1H-HU-PI

Solenoid valves VMPA

FESTO

Ordering data



Ordering data					
Designation			Width [mm]	Part No.	Type
Sub-base for individual valve					
	Without ATEX specification	Internal pilot air	10	533394	VMPA1-IC-AP-1
			14	8023666	VMPA14-IC-AP-1
			20	537981	VMPA2-IC-AP-1
		External pilot air	10	533395	VMPA1-IC-AP-S-1
			14	8023667	VMPA14-IC-AP-S-1
			20	537982	VMPA2-IC-AP-S-1
	With ATEX specification → 18	Internal pilot air	10	8005149	VMPA1-IC-AP-1-EX1E
			14	8023668	VMPA14-IC-AP-1-EX1E
			20	8005151	VMPA2-IC-AP-1-EX1E
		External pilot air	10	8005150	VMPA1-IC-AP-S-1-EX1E
			14	8023669	VMPA14-IC-AP-S-1-EX1E
			20	8005152	VMPA2-IC-AP-S-1-EX1E

Ordering data				
Designation			Part No.	Type
Cover				
	Cover cap for manual override with coded cover cap, manual override non-detenting (x10)		540897	VMPA-HBT-B
	Cover cap for manual override, covered, manual override blocked (x10)		540898	VMPA-HBV-B
	Cover cap for manual override, manual override detenting, can be operated manually without accessories (x10)		8002234	VAMC-L1-CD
	Inscription label holder for an inscription label and cover for the switching status indication and the manual override (blocked) (x10)		570818	ASLR-D-L1
Connecting cable, individual connection				
	• Straight socket, M8x1, 4-pin • Open end, 4-wire	2.5 m	158960	SIM-M8-4GD-2,5-PU
		5 m	158961	SIM-M8-4GD-5-PU
	• Angled socket, M8x1, 4-pin • Open end, 4-wire	2.5 m	158962	SIM-M8-4WD-2,5-PU
		5 m	158963	SIM-M8-4WD-5-PU
	• Straight socket, M8x1, 4-pin • Open end, 4-wire	2.5 m	541342	NEBU-M8G4-K-2.5-LE4
		5 m	541343	NEBU-M8G4-K-5-LE4
	• Angled socket, M8x1, 4-pin • Open end, 4-wire	2.5 m	541344	NEBU-M8W4-K-2.5-LE4
		5 m	541345	NEBU-M8W4-K-5-LE4
	Modular system for connecting cables		–	➔ Internet: nebu
Push-in fitting				
	Connecting thread M5 for tubing O.D. (10 pieces)	3 mm	153313	QSM-M5-3-I
		4 mm	153315	QSM-M5-4-I
		6 mm	153317	QSM-M5-6-I
	Connecting thread M7 for tubing O.D. (10 pieces)	4 mm	153319	QSM-M7-4-I
		6 mm	153321	QSM-M7-6-I
	Connecting thread G1/8 for tubing O.D. (10 pieces)	6 mm	186107	QS-G1/8-6-I
		8 mm	186109	QS-G1/8-8-I

Solenoid valves VMPA

Accessories

FESTO

Ordering data				
Designation			Part No.	Type
Silencer				
	Connecting thread	M5	165003	UC-M5
		M7	161418	UC-M7
		G1/8	161419	UC-1/8
	Push-in sleeve connection	3 mm	165005	UC-QS-3H
		4 mm	165006	UC-QS-4H
		6 mm	165007	UC-QS-6H
		8 mm	175611	UC-QS-8H
Blanking plug				
	Thread M5 (10 pieces)		3843	B-M5
	Thread M7 (10 pieces)		174309	B-M7
	Thread G1/8 (10 pieces)		3568	B-1/8
Plug				
	Blanking plug for tubing O.D. (10 pieces)	4 mm	153267	QSC-4H
		6 mm	153268	QSC-6H
		8 mm	153269	QSC-8H