

Valve terminals VTSA







Innovative

- High-performance valves in a sturdy metal housing
- Five valve sizes on one valve terminal
- Standardised from the multi-pin plug to the fieldbus connection and control block
- Dream team: fieldbus valve terminal suitable for electrical peripherals CPX. This means:
 - Forward-looking internal communication system for actuating the valves and CPX modules
 - Four valve sizes on one valve terminal without adapters
 - Integration of smart valve functions with VTSA-F-CB
- Valve functions for integration in control architectures of higher categories to EN ISO 13849-1

Versatile

- Modular system offering a range of configuration options
- Up to 32 solenoid coils
- Conversions and extensions are possible at any time
- Possible to integrate innovative function modules
- Flexible air supply and variable pressure zones
- Reverse operation
- High pressure range
- -0.9 ... 10 bar, flow rate range
- 550 ... 4000 l/min
- Wide range of valve functions
- Valves: 24 V DC

Valve terminal VTSA-F-CB


- Serial communication in the pneumatic part
- A maximum of 7 voltage zones (6 of which via PROFIsafe shut-off module and one additional voltage zone via Uval)
- Up to 24 solenoid coils per voltage zone
- Up to 96 valve positions and up to 64 interlinking blocks per valve terminal

Reliable

- Sturdy and durable metal components
 - Valves
 - Manifold sub-bases
 - Seals
- Fast troubleshooting with LEDs on the valves and diagnostics via fieldbus
- Reliable servicing thanks to valves that can be replaced quickly and easily
- Manual override, either non-detenting, non-detenting/detenting or concealed
- Durable thanks to tried-and-tested piston spool valves
- Large and durable labelling system
- 100% duty cycle

Easy to install

- Ready-to-install and tested unit
- Reduced selection, ordering, installation and commissioning costs
- Solid wall mounting or DIN rail mounting
- Manifold sub-bases can be extended using four screws, sturdy duct separation on metal support



- [1] Quick to mount: directly using screws or DIN rail
- [2] CPX diagnostic interface for handheld devices (channel-oriented diagnostics down to the individual valve)
- [3] Pneumatic interface to CPX
- [4] Width18 mm, 26 mm, 42 mm and 52 mm can be combined on a single valve terminal without adapter
- [5] Reduced downtimes: on-site LED diagnostics
- [6] Safe operation: manual override non-detenting, non-detenting/ detenting or concealed
- [7] Versatile: 32 valve positions/ 32 solenoid coilsOne valve series for a wide range
- of flow rates [8] Comprehensive range of valve functions
- [9] Modular: air supply plate facilitates the creation of multiple pressure zones as well as numerous additional exhaust and supply ports
- [10] Practical: large connections, flow-optimised ducts, sturdy metal threads or pre-assembled push-in connections for compressed air tubing with standardised O.D.
- [11] Convenient: large inscription labels
- [12] Reliable: valves, outputs and logic voltage can be switched off separately

- [13] Simple electrical connections
 - Fieldbus interface via CPX
 - Multi-pin plug connection with pre-assembled cable or terminal strip (Cage Clamp[®])
 - Control block via CPX
 - AS-Interface
 - Individual connection
 - IO-Link®
 - I-Port
 - AP interface

Equipment options

Valve functions

- 2x 2/2-way valve, single solenoid, pneumatic spring, normally closed
- 2x 3/2-way valve, single solenoid
 Normally open
- Normally open, reversible
- Normally closed
- Normally closed, reversible
- 2x 3/2-way valve, single solenoid
 1x normally open, 1x normally closed
 - 1x normally open, 1x normally closed, reversible

- 5/2-way solenoid valve
 - Single solenoid, pneumatic spring/mechanical spring
 - Double solenoid
 - Double solenoid with dominant signal
- 5/2-way valves for special functions, single solenoid
 - Mechanical spring
 - Switching position sensing via inductive sensors with PNP or NPN output
 - Protection against unexpected start-up to EN 1037
 - Reversing
- 5/3-way solenoid valve
 - Mid-position pressurised
 - Mid-position closed
 - Mid-position exhausted

- 5/3-way solenoid valve for special functions
 - Switching position 14 is retained (switching position 14 is retained in the event of an emergency off application/power failure), there is no spring return to switching position 12.
 - Only for valve terminal (plug-in)Mid-position exhausted or
 - mid-position $1 \rightarrow 2, 4 \rightarrow 5$
 - Switching position 14 is retained
 - Pneumatic spring return

- 5/3-way solenoid valve for special functions
 - Switching position 12 is retained (switching position 12 is retained in the event of an emergency off application/power failure), there is no spring return to switching position 14.
 - Only for valve terminal (plug-in)
 - Mid-position exhausted or mid-position 1→4, 2→3
- Switching position 12 is retained
- Pneumatic spring return
- Soft-start valve for slow and safe pressure build-up
 - High degree of safety
 - Sensing function provides feedback on switching operation

Connection variants				
Individual valve on individual sub-base, plug-in		Individual valve on individual sub-base, square plug or plug-in		
 Electrical connection via standardised 4-pin M12 plug or via 4-pin spring-loaded terminal for configuration by the user 	• Available with internal/external pilot air supply	 With integrated switching position sensing Electrical connection to EN 175301- 803 type C (square plug) or 	 For configuration by the user via 4-pin spring-loaded terminal or Cable with open end 	
Fieldbus interface CPX terminal	Fieldbus interface CPX terminal with VT	SA-F-CB		
 Max. 32 valve positions/ max. 32 solenoid coils Any compressed air supply Any number of pressure zones 	 Serial communication in the pneumatic part Up to 6 voltage zones for load voltage of the valves in the pneumatic part Flexible shutdown of up to 3 voltage zones in the CPX interfaces, either internally with PROFIsafe or externally by 3x M12 	 Pilot air switching valve or interme- diate plate for switchable pilot air with integrated pressure sensor and connection via internal bus Soft-start valve with integrated pres- sure sensor and connection via in- ternal bus 	• Vacuum generator with 3 perfor- mance settings, air-saving circuit, optional increased ejection rate (power ejector pulse) and connec- tion via internal bus, parameters can be configured via the CPX sys- tem	
Valve terminal with individual con- nection	Valve terminal with multi-pin plug conn	ection:	AS-Interface	
 Max. 20 valve positions/ max. 20 solenoid coils Any compressed air supply Any number of pressure zones 	 Max. 32 valve positions/ max. 32 solenoid coils Parallel, modular valve linking 	Any compressed air supplyAny number of pressure zones	 1 to 8 valve positions/ max. 8 solenoid coils Soft-start valve for slow and safe pressure build-up 	
I-Port	IO-Link [®]		AP interface	
 Max. 16 valve positions/ max. 32 solenoid coils Connection to an I-Port master Direct mounting of a bus node 	 Max. 16 valve positions/ max. 32 solenoid coils Connection to an IO-Link master 		 Max. 12 valve positions/ max. 24 solenoid coils Connection to an AP bus master 	
Combinable				
 Width 18 mm: flow rate of VTSA up to 550 l/min, VTSA-F up to 700 l/min Width 26 mm: flow rate of VTSA up to 1100 l/min, VTSA-F up to 1350 l/min 	 Width 42 mm: flow rate of VTSA up to 1300 l/min, VTSA-F up to 1860 l/min Width 52 mm: valve flow rate up to 2900 l/min 	• Width 18 mm, 26 mm, 42 mm, 52 mm can be combined on a single valve terminal (not for VTSA-F-CB)	 Valve terminal VTSA complies with ISO 15407-2 for width 18 and 26 mm ISO 5599-2 for width 42 and 52 mm 	

Valve terminal configurator			→ Internet: www.festo.com
General	VTSA	VTSA-F	VTSA-F-CB
A valve terminal configurator is availa- ble to help you select a suitable VTSA valve terminal, making it much easier to order the right product. The valve terminals are assembled ac- cording to your order specification and are individually checked. This reduces	 Valve terminal to ISO 15407-2 and ISO 5599-2 (flow rate: standard). Parallel communication between CPX module and switching valves VTSA 	 Valve terminal, flow rate-optimised (interlinking blocks) (flow rate: increased). Parallel communication between CPX module and switching valves VTSA 	 Valve terminal: optimised in terms of flow rate and communication (flow rate: increased). Serial communication between the CPX module and selected VTSA modules
assembly and installation time to a minimum.	Order a valve terminal VTSA using the order code:	Order a valve terminal VTSA-F using the order code:	Order a valve terminal VTSA-F-CB usin the order code:
	Ordering system for VTSA → Internet: vtsa	Ordering system for VTSA-F → Internet: vtsa-f	Ordering system for VTSA-F-CB → Internet: vtsa-f-cb
	Ordering system for CPX → Internet: cpx	Ordering system for CPX → Internet: cpx	Ordering system for CPX → Internet: cpx
Ordering data – Product options			
	Configurable product This product and all its product op- tions can be ordered using the config- urator.	The configurator can be found at → www.festo.com/catalogue/ Enter the part number or the type.	Part no. Type 539215 VTSA-MP 547963 VTSA-F-MP 539217 VTSA-FB 547965 VTSA-F-FB 8130719 VTSA-F-FB-AP 555564 VTSA-F-ASI 555566 VTSA-F-ASI 8073100 VTSA-F-CB

Valve terminals VTSA

Key features

Individual pneumatic connection



Valve terminal with individual electrical connection

width 52 mm can be used with actuators that are further away from the valve terminal.

Valves on individual sub-bases up to

The electrical connection is established either via a standardised 4-pin M12 plug 24 V DC (EN 61076-2-101), 4-pin spring-loaded terminal or a cable with open end 24 V DC, which are configured by the user.

Control signals from the controller to the valve terminal are transmitted via an individual connecting cable.

Control signals from the controller to

the valve terminal are transmitted via

a pre-assembled multi-core cable or a

multi-pin plug connection assembled

by the user (spring-loaded terminal).

This substantially reduces installation

time.

The valve terminal can be equipped with a maximum of 20 valves and a maximum 20 solenoid coils.


The valve terminal can be equipped


with a maximum of 32 valves and a

maximum 32 solenoid coils.

The electrical connection is established via a 5-pin M12 plug, 24 V DC

Valve terminal with multi-pin plug connection:





- A special feature of the AS-Interface is the simultaneous transmission of data and supply power via a two-core cable. The encoded cable profile prevents connection with reverse polarity. The valve terminal with AS-Interface is available in the following versions:
- With one to eight modular valve positions (max. 8 solenoid coils). This corresponds to one to eight valves VSVA.
- With all available valve functions.

Variants

- Multi-pin plug connection with terminal strip (spring-loaded terminal), 24 V DC
- Pre-assembled connecting cable, 24 V DC
- Sub-D plug connector for assembly by the user, 37-pin, 24 V DC
- Round plug connector M23, 19-pin, 24 V DC

The connection technology used for the inputs can be selected as with CPX: M8, M12, Sub-D, spring-loaded terminal (terminals to IP20).

More information → Internet: as-interface


· 🏺 - Note

The valve terminal VTSA/VTSA-F with AS-Interface connection is based on the same electrical links as the valve terminal with multi-pin plug connection. This means a valve terminal with multi-pin plug connection can be converted using an AS-Interface module (\rightarrow page 152). The technical specifications of the AS-Interface system must be observed in this case.


→ Page 73

→ Internet: as-interface

Valve terminal with I-Port/IO-Link® connection



Valve terminal with AP interface




- The connection to a higher-order controller can be achieved by:
- Connection to an I-Port master from Festo (e.g. CPX-CTEL)
- Direct mounting of a bus node on the I-Port interface
- Connection to an IO-Link master (in IO-Link[®] mode)

The valve terminal can comprise a maximum of 32 solenoid coils or 16 valve positions.

Control signals from the controller to the valve terminal are transmitted via the AP bus protocol from Festo.

The valve terminal can comprise a maximum of 24 solenoid coils or 12 valve positions.

Valve terminal with fieldbus interface from the CPX system



An integrated fieldbus node manages the communication connection with a higher-order PLC. This enables a space-saving pneumatic and electrical solution to be implemented. Valve terminals with fieldbus interfaces from the CPX system can be configured with up to 16 manifold sub-bases. With 2 solenoid coils per connection, up to 32 solenoid coils can thus be actuated. There is an extended range of functions in combination with the CPX system and the smart valve terminal VTSA-F-CB:


- Serial communication in the pneumatic part
- Several voltage zones for load voltage of the valves in the pneumatic part
- Flexible shutdown of up to 3 voltage zones in the CPX interface, either internally with PROFIsafe or externally by 3x M12
- Flexible zoning for electrical and pneumatic sections, for decentralised control of various system/machine areas

- VTSA/VTSA-F versions
- PROFIBUS
- DeviceNet[®]
- CANopen
- CC-LINK[®]
- EtherNet/IP
- EtherCAT[®]
- Modbus TCP
- PROFINET
- POWERLINK
- Sercos III


VTSA-F-CB versions

- PROFIBUS
- EtherNet/IP
- EtherCAT[®]
- PROFINET
- → Internet: cpx

Valve terminal with control block connection from the CPX system



CP string extension from the CPX system



A controller integrated in the Festo valve terminal enables the construction of stand-alone control units with protection to IP65 without a control cabinet thanks to two different operating modes.

The optional CP string extension ena-

bles additional valve terminals and I/O

modules to be connected to the field-

bus node of the CPX terminal on up to

modules as well as valve terminals

MPA-S and CPV can be connected.

4 CP strings. Different input and output

In the slave operating mode, these valve terminals can be used for intelligent preprocessing and are therefore ideal modules for designs using decentralised intelligence.

The maximum length of the CP string

extension is 10 metres, which means

that the extension modules can be

mounted directly on-site. All the re-

ted via the CP cable, which in turn

needed on the extension module.

means that no further installation is

quired electrical signals are transmit-

In the master operating mode, terminal groups can be designed with many options and functions that can autonomously control a medium-sized machine/system.

→ Internet: cpx

One CP string offers:

- 32 input signals
- 32 output signals for output stages 24 V DC or solenoid coils
- Logic and sensor supply for the input modules
- Load voltage supply for the valve terminals
- Logic supply for the output module
- → Internet: cpi

Key features – Valves

Solenoid valve with switching position sensing for VTSA/VTSA-F/VTSA-F-CB, width 18 mm, 26 mm



The 5/2-way single solenoid valve with spring return features switching position sensing. The normal position of the piston spool is monitored. It is available as a valve with plug-in or individual connection with pilot valves to ISO 15218 and square plug type C. This valve is not a safety device in accordance with the Machinery Directive 2006/42/EC. It is suitable for use in safety-related parts of control systems to EN ISO 13849-1.

→ Page 157

ontiot block with salety fund	ction for VTSA/VTSA-F, width 26 mm		
	5/2-way solenoid valve These valves are used for special ap- plications, for example for: • Protection against unexpected	This control block is suitable for use as a press safety valve to EN 962.	This valve is a safety device in accord ance with the Machinery Directive 2006/42/EC.
	start-up Safe reversing Drives in manually loaded machin- ing jigs 		→ Page 167

Intermediate plate for switchable pilot air for VTSA/VTSA-F, width 18 mm, 26 mm



The intermediate plate for switchable pilot air is a combination of a 5/2-way solenoid valve with switching position sensing and the intermediate plate VABF-S4-...-S. It enables the pilot air supply to be verifiably switched on and off (sensing function) from duct 1 to 14 for the entire pressure zone or valve terminal. Switching position sensing is carried out using an inductive PNP proximity switch with cable and M12x1 push-in connector to EN 61076-2-104. This valve is not a safety device in accordance with the Machinery Directive 2006/42/EC. It is suitable for use in safety-related parts of control systems to EN ISO 13849-1.


→ Page 174

- 🕴 - Note

The intermediate plate for switchable pilot air and pilot air can only be operated on the valve terminal VTSA/VTSA-F in combination with a right end plate for external pilot air type VABE-S6-1RZ- Port 14 on the right end plate must then be sealed.

Key features – Valves

Pilot air switching valve for VTSA-F-CB with serial communication



The pilot air switching valve is used for pressurising and exhausting duct 14 for one pressure zone or the entire valve terminal VTSA-F-CB. In combination with the CPX system, the pilot air switching valve enables additional functions:

- Comprehensive diagnostics
- Transmission of analogue signals
 The elimination of cable connections between the pneumatic and electrical sections

In combination with the CPX system, an integrated pressure sensor and integrated feedback enable wireless detection of the status of the pilot air switching valve.


The pilot air switching valve can be used to implement the safety function "Protection against unexpected startup".

The pilot air switching valve can be supplied with compressed air internally via the valve terminal or externally via duct 2. The hybrid manifold sub-base can be equipped both with an 18 mm and a 26 mm solenoid valve.

This valve is not a safety device to the Machinery Directive 2006/42/EC. It is suitable for use in safety-related parts of control systems to EN ISO 13849-1.

→ Page 184

Soft-start valve for VTSA/VTSA-F, module width 43 mm




The soft-start valve is separately electrically actuated, independently of the multi-pin plug connection, AS-Interface or fieldbus interface, via a square plug of type C to EN 175301-803 or optionally via an M12 adapter. The valve can optionally be ordered with a sensor that monitors switching of the soft-start valve. The soft-start valve can supply the valve terminal or one or more pressure zones with compressed air. The pressure build-up for each pressure zone is optimised for the application directly at the valve terminal by setting the switch-over pressure and the filling time.

A maximum of 5 soft-start valves can thus be integrated on one valve terminal.

→ Page 190

Soft-start valve for VTSA-F-CB with serial communication



The soft-start valve pressurises/exhausts duct 1 (supply air) of the valve terminal, or one or more pressure zones.

The soft-start valve enables additional functions in combination with the CPX system:

- Comprehensive diagnostics
- Transmission of analogue signals
- The elimination of cable connections between the pneumatic and electrical sections of the CPX/VTSA-F-CB


In combination with the CPX system, an integrated pressure sensor and integrated feedback enable wireless detection of the status of the soft-start valve.

The filling time can be adjusted; the switch-over pressure is set to half the operating pressure. The pressure build-up for each pressure zone can thus be optimised for the application directly at the valve terminal. This valve is not a safety device to the Machinery Directive 2006/42/EC. It is suitable for use in safety-related parts of control systems to EN ISO 13849-1.

→ Page 200

Key features – Valves

Vacuum block for VTSA-VTSA-F, module width 53 mm



5/3-way solenoid valve, with switching position 12 retained. The vacuum block is screwed to a manifold sub-base for 2 valve positions,

width 26 mm, and thus integrated into the valve terminal VTSA/VTSA-F.

The vacuum block is supplied with power and the vacuum is sensed via a standardised 4-pin M12 plug. The vacuum block is used in conjunction with a suction gripper to pick up, hold and place components. An adjustable ejector pulse is used for setting the components down.

5/3-way solenoid valve for special

functions (3 phases). Mid-position is

exhausted. Switching position 14 is

retained (code SA) or switching posi-

tion 12 is retained (code SE).

For pressureless switching, self-holding, pneumatic operation

The vacuum block is equipped with an air saving function. If the electrical or pneumatic supply fails, the valve moves to switching position 12 "generate vacuum".

→ Page 211


Possible applications:

es (inserting stations)

5/3-way solenoid valve for special functions For holding, blocking a movement (mechanically)

5/3-way solenoid valve for special functions; port 2 is pressurised, port 4 exhausted. Switching position 14 is retained (code SA) or switching position 12 is retained (code SE).

- Possible applications:
- Using lifting cylinders • Using rotary cylinders
- Integrated vacuum generator for VTSA-F-CB with serial communication



The vacuum generator in combination with the CPX/VTSA-F-CB and FMT (Festo Maintenance Tool) offers additional smart functions:

- Opening and saving of up to four records (on a local computer)
- Teach-in functionality: recording homing runs, gripping and holding the workpiece, and setting it down
- Preventive maintenance: measurement of all vacuum times, comparison with the homing run, warning message if a definable level of deviation is reached
- Locking the ejector pulse: either when a safety function (voltage zone with safe shut-off within the valve terminal) is requested or when there is a fault with the valve load voltage (e.g. undervoltage)

• Pneumatic manual clamps for devic-

- Switching air-saving function on/off
- Changing the vacuum limits per data record

The vacuum generator is used in conjunction with a suction gripper to pick up, hold and place components. An adjustable ejector pulse is used for setting the components down. → Page 216

Peripherals

Modular pneumatic peripherals

The modular design of the valve terminal VTSA/VTSA-F/VTSA-F-CB enables great flexibility right from the planning stage and offers maximum ease of service in operation.


The system consists of manifold sub-bases and valves.

The manifold sub-bases are screwed together, thus forming the support system for the valves. Inside the manifold sub-bases are the connection ducts for supplying compressed air to and exhausting the valve terminal as well as the working ports for the pneumatic cylinders for each valve.


Valve modularity


Each manifold sub-base is connected to the next using four screws. Individual valve terminal sections can be isolated and further blocks easily inserted by loosening these screws. This ensures that the valve terminal can be rapidly and reliably extended.

Basic system modularity



Vertical stacking modularity





Peripherals


Modular electrical peripherals

How the valves are actuated depends on whether a multi-pin terminal or fieldbus terminal is used. The VTSA/VTSA-F with CPX interface is based on the internal bus system of the CPX and uses this communication system for all solenoid coils and a range of electrical input and output functions. Parallel links enable the following:Transmission of switching informa-

- tion
- Compact design
- Position-based diagnostics
- Separate power supply for valves
- Flexible conversion without address shifting
- Option of CP interface
- CPX-CEC as stand-alone controller with access via Ethernet and web server
- Transmission of status, parameter and diagnostic data
- \rightarrow Internet: cpx


VTSA/VTSA-F with electrical peripherals CPX

CPX terminal in metal design



(QQQQQQ

Modularity with electrical peripherals CPX



The metal CPX modules are mechanically connected using an angled fitting.

The CPX terminal can thus be expanded at any time.

- Note


The CPX connection blocks are also available in metal. This means a complete solution in a sturdy metal design can be selected for applications of the valve terminal VTSA/VTSA-F/VTSA-F-CB in welding environments.

Valve terminal widths

Regardless of the type of control (e.g. multi-pin plug, fieldbus, etc.), valve terminals VTSA/VTSA-F of widths:

- 18 mm
- 26 mm
- 42 mm
- 52 mm

can be combined without adapters. These four widths can also be used without an adapter for the valve terminal VTSA-F-CB controlled via CPX. This enables a flow range for the VTSA of: 400 l/min to 2900 l/min For the VTSA-F of: 700 l/min to 2900 l/min and for the VTSA-F-CB of: 700 l/min to 2900 l/min to be covered on one valve terminal. A wide range of valve functions and vertical stacking components are available for all widths. The valve terminal VTSA-F-CB is controlled via the CPX pneumatic interface with serial communication. The valve terminal VTSA-F-CB cannot be installed in combination with a valve terminal VTSA/VTSA-F.



		Description	→ Page/Internet
[1]	Valve	Width 18 mm	112
[2]	Valve	Width 26 mm	120
[3]	Valve	Width 42 mm	128
[4]	Valve	Width 52 mm	135
[5]	Multi-pin plug connection	With 24 V DC multi-pin cable (VTSA/VTSA-F only)	151
[6]	Inscription labels	For manifold sub-base, connecting plate, angled connection plate	156


Individual sub-base, width 18 mm, ISO 15407-2


Order code:

• Using individual part numbers


Individual sub-bases can be equipped with any valve.

Width 18 mm with spring-loaded terminal or cable (open end)





Width 18 mm with M12 plug





		Description	→ Page/Internet
[1]	Fitting	G1/8 for supply air/exhaust ports (1, 3, 5) and working ports (2, 4)	242
[2]	Silencer	U-1/8-B for exhaust ports (3, 5)	243
[3]	Electrical connection	Spring-loaded terminal, cable (open end) or M12 plug ¹), 4-pin	-
[4]	Valve VSVA	Width 18 mm	112
[5]	Manual override	Non-detenting/detenting, per solenoid coil	-
[6]	Cover cap, heavy duty	For manual override, non-detenting heavy duty, detenting via accessory	155
[7]	Cover cap, coded	For non-detenting manual override (limited function)	155
[8]	Cover cap, concealed	MO concealed by cover cap – operation of MO prevented	155
[9]	Inscription label holder	For valves	156
[10]	Individual sub-base	For valve VSVA	240
[11]	Inscription label holder	For manifold block	156

1) Only for 24 V DC

Individual sub-base, width 26 mm, ISO 15407-2

With spring-loaded terminal or cable (open end)






		Description	→ Page/Internet
[1]	Fitting	G1/4 for supply air/exhaust ports (1, 3, 5) and working ports (2, 4)	242
[2]	Silencer	U-1/4-B for exhaust ports (3, 5)	243
[3]	Electrical connection	Spring-loaded terminal, cable (open end) or M12 plug ¹), 4-pin	-
[4]	Valve VSVA	Width 26 mm	120
[5]	Manual override	Non-detenting/detenting, per solenoid coil	-
[6]	Cover cap, heavy duty	For manual override, non-detenting heavy duty, detenting via accessory	155
[7]	Cover cap, coded	For non-detenting manual override (limited function)	155
[8]	Cover cap, concealed	MO concealed by cover cap – operation of MO prevented	155
[9]	Inscription label holder	For valves	156
[10]	Individual sub-base	For valve VSVA	240
[11]	Inscription label holder	For manifold block	156


1) Only for 24 V DC

With M12 push-in connector

Individual sub-base, width 42 mm, ISO 5599-2

With spring-loaded terminal or cable (open end)






		Description	→ Page/Internet
[1]	Fitting	G3/8 for supply air/exhaust ports (1, 3, 5) and working ports (2, 4)	242
[2]	Silencer	U-3/8-B for exhaust ports (3, 5)	243
[3]	Electrical connection	Spring-loaded terminal, cable (open end) or M12 plug ¹), 4-pin	-
[4]	Valve VSVA	Width 42 mm	128
[5]	Manual override	Non-detenting/detenting, per solenoid coil	-
[6]	Cover cap, heavy duty	For manual override, non-detenting heavy duty, detenting via accessory	155
[7]	Cover cap, coded	For non-detenting manual override (limited function)	155
[8]	Cover cap, concealed	MO concealed by cover cap – operation of MO prevented	155
[9]	Inscription label holder	For valves	156
[10]	Individual sub-base	For valve VSVA	240
[11]	Inscription label holder	For manifold block	156

With M12 plug

1) Only for 24 V DC

Individual sub-base, width 52 mm, ISO 5599-2

With spring-loaded terminal or cable (open end)



 7
 8

 6
 9

 4
 9

 4
 9

 3
 9

 1
 10

		Description	→ Page/Internet
[1]	Fitting	G1/2 for supply air/exhaust ports (1, 3, 5) and working ports (2, 4)	242
[2]	Silencer	U-1/2-B for exhaust ports (3, 5)	243
[3]	Electrical connection	Spring-loaded terminal, cable (open end) or M12 plug ¹), 4-pin	-
[4]	Valve VSVA	Width 52 mm	135
[5]	Manual override	Non-detenting/detenting, per solenoid coil	-
[6]	Cover cap, heavy duty	For manual override, non-detenting heavy duty, detenting via accessory	155
[7]	Cover cap, coded	For non-detenting manual override (limited function)	155
[8]	Cover cap, concealed	MO concealed by cover cap – operation of MO prevented	155
[9]	Inscription label holder	For valves	156
[10]	Individual sub-base	For valve VSVA	240
[11]	Inscription label holder	For manifold block	156

1) Only for 24 V DC

With M12 plug

Pneumatic components of valve terminal VTSA/VTSA-F

The conventional manifold sub-bases for valves with a width of 18 or 26 mm are either suitable for

- 2 single solenoid valves or
- 2 double solenoid valves

depending on the size.


The hybrid manifold sub-base makes it possible to use

1 double solenoid valve (18 mm) and

1 double solenoid valve (26 mm)

together on the same manifold subbase. The manifold sub-bases for valves with a width of 42 or 52 mm are suitable for:

- 1 single solenoid valve or
- 1 double solenoid valve
- Double solenoid valve positions can be equipped with any valve or a cover plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a cover plate.



Pneumatic components of valve terminal VTSA/VTSA-F

Pneumatic components of valve terminal VTSA/VTSA-F				
Description -> Page/Internet				
1] Exhaust port cover	For ducted exhaust air (ports 3 and 5 combined)	143		
[2] Duct separation/seal	-	155		
3] Manifold sub-base	For soft-start valve	198		
4] Soft-start valve	For slow and safe pressure build-up	190		
5] Plug socket	-	199		
5] Throttle plate	-	149		
7] Pressure regulator plate	-	144		
3] Valve	Width 18 mm or 26 mm	112, 120		
9] Cover cap, heavy duty	For manual override, non-detenting heavy duty, detenting via accessory	155		
10] Cover cap, coded	For non-detenting manual override (limited function)	155		
11] Cover cap, concealed	MO concealed by cover cap – operation of MO prevented	155		
12] Inscription label holder	For valve	156		
13] Cover plate	For unused valve position (vacant position)	149		
14] Valve	Width 42 mm or 52 mm	128, 135		
15] End plate with pilot air selector	-	154		
16] Blanking plug	-	243		
17] Manifold sub-base VTSA	For valves with a width of 42 mm or 52 mm	142		
17] Manifold sub-base VTSA-F	For valves with a width of 42 mm or 52 mm	142		
18] Manifold sub-base VTSA	For valves with a width of 18 mm or 26 mm	142		
18] Manifold sub-base VTSA-F	For valves with a width of 18 mm or 26 mm	142		
19] Fittings	-	242		
20] Silencer	-	243		
21] Inscription label holder	For manifold sub-base, connecting plate, angled connection plate	156		
22] Supply plate	-	143		
23] Control element	Regulator knobs in different versions	40		

-- Note

Special applications for the valve terminal, such as:

- Solenoid valve with switching position sensing
- Control block with safety function
- Pilot air switching valve
- Soft-start valve
- Vacuum block

are listed after \rightarrow Accessories – General

Pneumatic components of valve terminal VTSA-F-CB

The conventional manifold sub-bases for valves with a width of 18 or 26 mm are either suitable for

- 2 single solenoid valves or
- 2 double solenoid valves

depending on the size.


The hybrid manifold sub-base (with CBUS loop-through) makes it possible to use

• 1 double solenoid valve (18 mm) and

• 1 double solenoid valve (26 mm) together on the same manifold subbase.

The manifold sub-bases for valves with a width of 42 or 52 mm are suitable for:

- 1 single solenoid valve or1 double solenoid valve
- Double solenoid valve positions can be equipped with any valve or a cover plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a cover plate.



Pneumatic components of valve terminal VTSA-F-CB

Pneumatic components of valve terminal VTSA-F-CB			
	Description	→ Page/Internet	
[1] Duct separation/seal	-	155	
[2] Exhaust port cover	For ducted exhaust air (ports 3 and 5 combined)	143	
[3] Manifold sub-base	For soft-start valve	205	
[4] Soft-start valve for VTSA-F-CB	For slow and safe pressure build-up	200	
[5] Pilot air switching valve for VTSA-F-CB	-	184	
[6] Vacuum generator for VTSA-F-CB	For vacuum generation	216	
[7] Manifold sub-base VTSA-F-CB	For valves with a width of 18 mm or 26 mm with CBUS loop-through	142	
[8] Throttle plate	-	149	
[9] Pressure regulator plate	-	144	
[10] Valve	Width 18 mm or 26 mm	112, 120	
[11] Cover cap, heavy duty	For manual override, non-detenting heavy duty, detenting via accessory	155	
[12] Cover cap, coded	For non-detenting manual override (limited function)	155	
[13] Cover cap, concealed	MO concealed by cover cap – operation of MO prevented	155	
[14] Inscription label holder	For valve	156	
[15] Control element	Regulator knobs in different versions	40	
[16] Cover plate	For unused valve position (vacant position)	149	
[17] Valve	Width 42 mm or 52 mm	128, 135	
[18] End plate with pilot air selector	-	154	
[19] Blanking plug	-	243	
[20] Manifold sub-base VTSA-F-CB	For valves with a width of 18 mm or 26 mm with CBUS loop-through	142	
[21] Fittings	-	242	
[22] Silencer	-	243	
[23] Manifold sub-base VTSA-F-CB	For pilot air switching valve (hybrid manifold sub-base)	142	
[24] Inscription label holder	For manifold sub-base, connecting plate, angled connection plate	156	
[25] Supply plate/air supply plate	-	143	

-- Note

Special applications for the valve terminal, such as:

- Solenoid valve with switching position sensing
- Control block with safety function
- Pilot air switching valve
- Soft-start valve
- Vacuum generator

are listed after \rightarrow Accessories – General

Valve terminal with individual electrical connection

Order code for VTSA:

44E-... for the electric components 44P-... for the pneumatic components

Order code for VTSA-F:

- 45E-... for the electric components
- 45P-... for the pneumatic components

Valve terminals VTSA/VTSA-F with individual electrical connection can be expanded with up to 20 valves with max. 20 solenoid coils.


The manifold sub-bases for valves with a width of 18 or 26 mm are suitable for either

• 2 single solenoid valves or

• 2 double solenoid valves and the manifold sub-bases for valves with a width of 42 or 52 mm are suitable for

- 1 single solenoid valve or
- 1 double solenoid valve depending on the size.

- Double solenoid valve positions can be equipped with any valve or a cover plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a cover plate.
- The electrical connection is established via a 5-pin M12 plug (24 V DC).



		Description	→ Page/Internet
[1]	Cover	For individual connection	151
[2]	Multi-pin plug connection	Individual connection with M12, 10-way or 6-way (including cover)	151

Valve terminal with electrical multi-pin plug connection

Order code for VTSA:

44E-... for the electric components 44P-... for the pneumatic components

Order code for VTSA-F:

- 45E-... for the electric components
- 45P-... for the pneumatic components


Valve terminals VTSA/VTSA-F with multipin plug connection can be expanded with up to 32 valves with max. 32 solenoid coils. The manifold sub-bases for valves with a width of 18 or 26 mm are suitable for

2 single solenoid valves or 2 double solenoid valves

and the manifold sub-bases for valves with a width of 42 or 52 mm are suitable for

- 1 single solenoid valve or
- 1 double solenoid valve

- Double solenoid valve positions can be equipped with any valve or a cover plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a cover plate.
- The following multi-pin plug connections to IP65 are available:
- 37-pin Sub-D connection (24 V DC): the connecting cable can be ordered in lengths of 2.5 m, 5 m and 10 m for max. 8, 22 or 32 solenoid coils respectively.
- Terminal strip (24 V DC), 19-pin round plug (24 V DC)



		Description	→ Page/Internet
[1]	Inscription labels	Large, for multi-pin plug connection	-
[2]	Multi-pin cable	Connecting cable	154
[3]	Multi-pin plug connection	Via M23 round plug connection, 24 V DC	151
[4]	Multi-pin plug connection	Via terminal strip (CageClamp) 24 V DC	151
[5]	Multi-pin plug connection	Via multi-pin cable, 24 V DC	151

Valve terminal with AS-Interface connection

- Order code for VTSA:
- 52E-... for the electric components44P-... for the pneumatic components
- Order code for VTSA-F:
- 52E-... for the electric components
- 45P-... for the pneumatic components

Valve terminals VTSA/VTSA-F with AS-Interface connection can be expanded with up to 8 valves with max. 8 solenoid coils.


The manifold sub-bases for valves with a width of 18 or 26 mm are suitable for either

- 2 single solenoid valves or
- 2 double solenoid valves

and the manifold sub-bases for valves with a width of 42 or 52 mm are suitable for

- 1 single solenoid valve or
- 1 double solenoid valve
- depending on the size.

- Double solenoid valve positions can be equipped with any valve or a cover plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a blanking plate.



		Description	→ Page/Internet
[1]	Multi-pin plug connection	Can be ordered together with the AS-Interface module as an electrical connection for AS-Interface	152
[2]	Manifold block for AS-Interface	-	152
[3]	AS-Interface module	-	152

Valve terminal with I-Port/IO-Link® connection

- Order code for VTSA:
- 44E-... for the electric components 44P-... for the pneumatic components
- Order code for VTSA-F: • 45E-... for the electric components
- 45P-... for the pneumatic components

Valve terminals VTSA/VTSA-F with I-Port/IO-Link[®] connection can be expanded with up to 16 valves with max. 32 solenoid coils. The manifold sub-bases for valves with a width of 18 or 26 mm are suitable for either


- 2 single solenoid valves or
- 2 double solenoid valves

and the manifold sub-bases for valves with a width of 42 or 52 mm are suitable for

- 1 single solenoid valve or
- 1 double solenoid valve

depending on the size.

- Double solenoid valve positions can be equipped with any valve or a cover plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a blanking plate.



Valve terminal with AP interface

- Order code for VTSA:
- 44E-... for the electric components 44P-... for the pneumatic components
- Order code for VTSA-F:
- 45E-... for the electric components
- 45P-... for the pneumatic components


VTSA/VTSA-F valve terminals with AP interface can be expanded with up to 12 valves with a maximum of 24 solenoid coils. The manifold sub-bases for valves with a width of 18 or 26 mm are suitable for either

• 2 single solenoid valves or

• 2 double solenoid valves and the manifold sub-bases for valves with a width of 42 or 52 mm are suitable for

- 1 single solenoid valve or
- 1 double solenoid valve
- depending on the size.

- Double solenoid valve positions can be equipped with any valve or a cover plate.
- Single solenoid valve positions can only be equipped with single solenoid valves or a blanking plate.



Valve terminal with fieldbus interface, control block (electrical peripherals CPX)

Order code:

- 50E-... for the electrical peripherals, polymer variant
- 51E-... for the electrical peripherals, metal variant
- 53E-... for the electrical peripherals, for control cabinet installation
- For VTSA:
- 44P-... for the pneumatic components For VTSA-F:
- 45P-... for the pneumatic components For VTSA-F-CB:
- 46P-... for the pneumatic components

Valve terminals VTSA/VTSA-F with parallel communication and fieldbus interface can be expanded with up to 32 valves with max. 32 solenoid coils.

The manifold sub-bases for valves with a width of 18 or 26 mm are suitable for either

• 2 single solenoid valves or

• 2 double solenoid valves and the manifold sub-bases for valves

with a width of 42 or 52 mm are suitable for

- 1 single solenoid valve or
- 1 double solenoid valve
- depending on the size.
- Double solenoid valve positions can be equipped with any valve or a cover plate.


• Single solenoid valve positions can only be equipped with single solenoid valves or a blanking plate.

The valve terminal VTSA-F-CB with serial communication can be expanded with up to 96 valves with max. 96 solenoid coils. 4 zones can be equipped with max. 24 valves/solenoid coils.

Each valve position can be equipped with any valve or a blanking plate. The rules for CPX apply to the equipment that can be used with the electrical peripherals CPX.

In general:


- Max. 10 electrical modules
- Digital inputs/outputs
- Analogue inputs/outputs
- Parameterisation of inputs and outputs
- Integrated, convenient diagnostics
- Preventive maintenance concepts



		Description	→ Page/Internet
[1]	Inscription labels	Large, for pneumatic interface CPX	-
[2]	Pneumatic interface	-	151
[3]	Fieldbus interface		срх

Valve terminal with fieldbus/multi-pin plug connection and individually electrically actuated valve

In applications with specific emergency off conditions, it may be necessary to switch one or more valves separately from the valve terminal controller. Standard valves (VSVA) with individual electrical connection (round or square plug) are therefore mounted on the valve terminal. In order for degree of protection IP65 to be achieved, the functionless opening in the sub-base for the electrical connection must be sealed. A sealing cap is available for width 18 mm and 26 mm. With manifold or individual sub-bases, valves with width 42 mm and 52 mm must be used with a seal to comply with the IP degree of protection (see \rightarrow page 149). For centrally controlling the valve terminal via a multi-pin plug connection or fieldbus interface, the occupied valve position acts like a vacant position, i.e. the assigned address in the fieldbus node or the corresponding connection in the multi-pin plug connection is occupied.




		Description	→ Page/Internet
[1]	Sealing cap	For sealing the electrical connection on the sub-base	149
[2]	Valve	Width 18 mm or width 26 mm	valves vsva
[3]	Connecting cable	-	valves vsva
[4]	Seal	For ensuring the IP degree of protection (with width 42 mm and 52 mm)	150
[5]	Valve	Width 42 mm or width 52 mm	valves vsva

- 🏺 - Note

Standards-based valves VSVA can be used on the valve terminal. A vacant position must be provided for this in the valve terminal configurator. The appropriate standards-based valve VSVA can be ordered on the Internet at:

→ vsva


Manifold sub-base



VTSA/VTSA-F with parallel communication is based on a modular system which consists of manifold sub-bases and valves.

The VTSA-F manifold sub-bases are designed to optimise the flow rate.

Hybrid manifold sub-base



Port patterns to ISO 154072 Width 18 mm (size 02)



Manifold sub-bases are available for valve widths 18 mm and 26 mm in a double grid, i.e. two valves per manifold sub-base.

For VTSA-F-CB with serial communication, there are manifold sub-bases available for valve widths 18 mm and 26 mm in a double grid. For valves with a width of 42 mm or 52 mm, there are manifold sub-bases with one valve per sub-base. The manifold sub-base contains a duct seal and an electric interlinking module. They can be freely mixed within a valve terminal.

The manifold sub-bases are screwed together, thus forming the support system for the valves. Inside the manifold sub-bases are the connection ducts for supplying compressed air to and exhausting the valve terminal as well as the working ports for the pneumatic cylinders for each valve. Each manifold sub-base is connected to the next using four screws. Individual valve terminal sections can be isolated and further manifold sub-bases can be inserted by loosening these screws. This ensures that the valve terminal can be rapidly and reliably extended.

With hybrid manifold sub-bases, a valve with a width of 18 mm can be combined with a valve with a width of 26 mm on one manifold sub-base.

Width 26 mm (size 01)

О

 \square


 \bigcap

 \square

 \bigcirc


 \square

Width 42 mm (size 1)




Port patterns to ISO 55992


Width 52 mm (size 2)



Port patterns – High-flow sub-bases with optimised flow rate (no standard) Width 18 mm Width 26 mm








Hybrid manifold sub-base

Width 18 mm + 26 mm



- 🏺 - Note

The illustrations shown represent the pneumatic port patterns. The port patterns on the valve terminal VTSA-F/VTSA-F-CB and the hybrid manifold sub-base do not correspond to the ISO standards.

Valve terminals VTSA

Key features – Pneumatic components

Code		Туре	Width				No. of valve positions	Working ports (2, 4)		
			18 mm	26 mm	42 mm	52 mm	(solenoid coils) ¹⁾	Code M Large	Code N Small	
Nanifolo	l sub-base for double solenoid v	alves								
Ą		VABV-S4-2S-G18-2T2					2 (4)	QS-G1/8-8	-	
λK			-	_	_	_		-	QS-G1/8-6	
5		VABV-S4-1S-G14-2T2					2 (4)	QS-G1/4-10	-	
ΒK								-	QS-G1/4-8	
		VABV-S2-1S-G38-T2			_		1 (2)	QS-G3/8-12	-	
ΪK			-	_		_		-	QS-G3/8-10	
		VABV-S2-2S-G12-T2	1 (2)	QS-G1/2-16	-					
ЭК					-			-	QS-G1/2-12	
Aanifolo	I sub-base for single solenoid va	lves		1	1	1				
		VABV-S4-2S-G18-2T1		_	_	_	2 (2)	QS-G1/8-8	-	
К								-	QS-G1/8-6	
:		VABV-S4-1S-G14-2T1					2 (2)	QS-G1/4-10	-	
K			-		-	-		-	QS-G1/4-8	
i		VABV-S2-1S-G38-T1					1 (1)	QS-G3/8-12	-	
К			-	-	-	-		-	QS-G3/8-10	
		VABV-S2-2S-G12-T1					1 (1)	QS-G1/2-16	-	
K			-	-	-				QS-G1/2-12	

1) The value in brackets is the max. number of solenoid coils that can be actuated

Code	I sub-base variants with QS fitting	Type	Width				No. of valve posi-	Working ports (2, 4)		
			18 mm	26 mm	42 mm	52 mm	tions (solenoid coils) ¹⁾	Code M Large	Code N Small	
Manifolo	l sub-base for double solenoid valv	ves								
A		VABV-S4-2HS-G18-2T2					2 (4)	QS-G1/8-8	-	
AK			-	-	-	-		-	QS-G1/8-6	
В		VABV-S4-1HS-G14-2T2					2 (4)	QS-G1/4-10	-	
BK	030		_		_	_		-	QS-G1/4-8	
С		VABV-S2-1HS-G38-T2	_	_		_	1 (2)	QS-G3/8-12	-	
СК								-	QS-G3/8-10	
D		VABV-S2-2S-G12-T2	_	_	_		1 (2)	QS-G1/2-16	-	
DK								-	QS-G1/2-12	
Manifold	l sub-base for double solenoid val	ves, hybrid sub-base								
ХА		VABV-S4-12HS-G-2T2	1st valve 18	mm			2 (4)	Left valve position: QS-G1/8-8 QS-G1/8-10	-	
			2nd valve	⊧ e position mm	_	_		Right valve position: QS-G1/4-8 QS-G1/4-10		
XAK		 VABV-S4-12HS-G-2T2 1x double solenoid, width 18 mm 		position mm			2 (4)	-	Left valve position: QS-G1/8-6 QS-G1/8-8	
		 1x double solenoid, width 26 mm with small fittings 	2nd valve	e position mm	_	_			Right valve position: QS-G1/4-6 QS-G1/4-8	
Manifold	l sub-base for single solenoid valv	es								
E		VABV-S4-2HS-G18-2T1					2 (2)	QS-G1/8-8	-	
EK			-	-	-	-		-	QS-G1/8-6	
F		VABV-S4-1HS-G14-2T1					2 (2)	QS-G1/4-10	-	
FK	030		_	•	_	_		-	QS-G1/4-8	
G		VABV-S2-1HS-G38-T1	_	_		_	1 (1)	QS-G3/8-12	-	
GK							1 (1)	-	QS-G3/8-10	
H		VABV-S2-2S-G12-T1	_	_	_	•	1 (1)	QS-G1/2-16		
HK								-	QS-G1/2-12	

1) The value in brackets is the max. number of solenoid coils that can be actuated

Code		Туре	Width	Width					
			18 mm	26 mm	42 mm	52 mm	(solenoid coils) ¹⁾		
Nanifol	d sub-base for double solenoid val	ves							
Ą		VABV-S4-2HS-G18-CB-2T2		-	-	-	2 (4)		
3		VABV-S4-1HS-G14-CB-2T2					2 (4)		
			-	•	-	-			
2	*	VABV-S2-1HS-G38-CB-T2					1 (2)		
)		VABV-S2-2S-G12-CB-T2					1 (2)		
Manifol	d sub-base for double solenoid val	ves hybrid manifold sub-base							
Ä		VABV-S4-12HS-G-CB-2T2			1	1	2 (4)		
		 (external sensor evaluation) 1x double solenoid, width 18 mm 1x double solenoid, width 26 mm 	•	•	-	-			
Nanifol	d sub-base for single solenoid valv	es							
		VABV-S4-2HS-G18-CB-2T1		_	- 1	-	2 (2)		
F		VABV-S4-1HS-G14-CB-2T1	-	•	_	_	2 (2)		
G		VABV-S2-1HS-G38-CB-T1		_	•		1 (1)		
1		VABV-52-1115-050-05-11 VABV-52-2S-G12-CB-T1		+ -	-		1 (1)		
I		VADV-52-23-012-CD-1	_	-	-	•	1(1)		

1) The value in brackets is the max. number of solenoid coils that can be actuated


Code		Туре	Width	Width					
			18 mm	26 mm	40 mm	52 mm	(solenoid coils) ¹⁾		
Manifo	ld sub-base for soft-start valve								
PV		VABV-S6-1Q-G38-CB1-T5	-	-	•	-	1		
PS		VABV-S6-1Q-G38-CB-T5	-	_	•	_	1		
Manifo	Id sub-base for pilot air switching v	valve			I		1		
YB		VABV-S4-2HS-G18-CB-2T5	•	_	_	_	2 (4)		
YC		VABV-S4-12HS-G-CB-2T5	•	•	_	_	2 (4)		

1) The value in brackets is the max. number of solenoid coils that can be actuated

Angled connection plate for working ports 2 and 4

Angled c	onnection plate for working ports 2	and 4											
Code		Type Width		Width			Width Conr			pe Width		Connections	Working ports (2, 4) on the
			18 mm	26 mm	42 mm	52 mm		90°-connection plate					
Р	P	VABF-S4A2G2-G	•	-	-	-	2 and 4	G1/8					
			-		-	-		G1/4					
			-	-		-		G3/8					
			-	-	_	•		G1/2					

Sub-base valve



All valves have a piston spool and patented sealing system, which ensures efficient sealing, a broad operating pressure range and long service life. Sub-base valves can be quickly replaced since the tubing connections remain on the manifold sub-base. Irrespective of the valve function, there are sub-base valves with one solenoid coil (single solenoid) or with two solenoid coils for double solenoid or double valve functions.

Reverse/vacuum operation

Select reverse operation (code Z) if you wish to operate an actuator (cylinder) with different pressures for the forward and return stroke. Please note that the valves must then be operated via a separate pressure zone.

The reversible 3/2-way solenoid valves are also suitable for vacuum operation.

Reverse operation is only possible in pressure zones with external pilot air supply.

📲 - Note

- If a pressure zone is in reverse operation, the supply pressure is connected to port 3/5 and the air is exhausted via port 1 at all valve positions in this pressure zone.
- Reversible pressure regulators cannot be selected when a pressure zone is in reverse operation.
- With reversible pressure regulators, only the valve at this position is in reverse operation.
- When 5/3-way valves are operated in reverse, the mid-position function is changed from exhausted to pressurised and vice versa.

Cover plate




Plate without valve function for reserving valve positions on a valve terminal. Valve and blanking plates are mounted on the manifold sub-base using screws.


Design Replacing valves

The valves are attached to the metal manifold sub-base using two or four screws, which means that they can be easily replaced. The sturdy mechanical structure of the sub-base ensures efficient, durable sealing.

Extension

Vacant positions can be fitted with valves at a later date. The dimensions, mounting points and existing pneumatic installations remain unchanged during this process. For more information and technical data on extension, refer to the user manual:

→ Internet: VTSA/VTSA-F



- 🖡 - Note

A filter must be installed upstream of valves operated in vacuum mode. This prevents any foreign matter in the intake air getting into the valve (e.g. when operating a suction cup).

Valve function Width Description Terminal Circuit symbol Valve code code 18 mm 26 mm 42 mm 52 mm Μ M52-A 5/2-way valve, single solenoid 14 12 · Reverse operation • Pneumatic spring return 0 M52-M 5/2-way valve, single solenoid Reverse operation · Mechanical spring return B52 J 5/2-way valve, double solenoid - \Box (14)D D52 5/2-way valve, double solenoid 14 • Dominant signal at port 14 on the control side -5 13 S0 5/2-way valve^{2),} single solenoid, as plug-in or via pilot M52-M G SQ valve with pneumatic interface to ISO 15218 SS _ See also special valve function in the separate chapter тWW "Solenoid valve with switching position sensing" → page 161 5/2-way valve^{2),} single solenoid, as plug-in or via pilot S0 M52-M 2 SQ valve with pneumatic interface to ISO 15218 [7]> 14 SS See also special valve function in the separate chapter "Solenoid valve with switching position sensing" → page 161 SP 2 T52-M 2x 5/2-way valve, single solenoid, with switching posi-2 SN tion sensing, pneumatically linked via two ducts for spe-G G cial valve function "control block with safety function" 14 75 → page 167 - MA <u>_</u>____W 14 5 1 3 P53U В 5/3-way solenoid valve 2 • Mid-position pressurised¹⁾ • Mechanical spring return (14)Ī3 5 G P53C 5/3-way solenoid valve Mid-position closed¹⁾ - Mechanical spring return P53E Ε 5/3-way solenoid valve • Mid-position exhausted¹⁾ Mechanical spring return 5


1) If neither solenoid coil is energised, the valve is moved to its mid-position by a mechanical spring. If the two coils are permanently energised one after the other, the valve remains in the switching position of the coil that was activated first.

2) The symbol represents a valve with a proximity switch with a switching output signal, in the illustration an N/O contact. This symbol applies to both N/O and N/C contacts, in accordance with ISO 1219-1. All sensors used here have an N/C contact as the switching element function.

Valve fun	tion						
Terminal	Circuit symbol	Valve	Width				Description
code		code	18 mm	26 mm	42 mm	52 mm	
SA		P53ED	•	•	_	_	 5/3-way solenoid valve, for special functions as switching position 14 is retained Pressureless switching, self-latching loop, pneumatic operation Mid-position exhausted, switching position 14 is retained Mechanical spring return
SB	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	P53AD	•	•	-	-	 5/3-way solenoid valve, for special functions as switching position 14 is retained Holding, blocking a movement (mechanically) Mid-position port 2 pressurised, port 4 exhausted, switching position 14 is retained Mechanical spring return
SD		P53BD	•	•	-	-	 5/3-way solenoid valve, for special functions as switching position 14 is retained Holding, blocking a movement (mechanically) Mid-position port 4 pressurised, port 2 exhausted, switching position 14 is retained Mechanical spring return
SE	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	P53EP	•		-	-	 5/3-way solenoid valve, for special functions as switching position 12 is retained Pressureless switching, self-latching loop, pneumatic operation Mid-position exhausted, switching position 12 is retained Mechanical spring return
VG		P53F	-	-	•	•	 5/3-way solenoid valve Positioning Mid-position port 2 pressurised, port 4 closed¹⁾ Mechanical spring return
VB	-	-	-		-	-	Vacuum generator with ejector pulse and adjustable air saving function (plate for 2 valve positions, sensor SDE3 with display and M12 connection)
L	-	-					For valve terminal only: Cover plate for vacant valve position

1) If neither solenoid coil is energised, the valve is moved to its mid-position by a mechanical spring. If the two coils are permanently energised one after the other, the valve remains in the switching position of the coil that was activated first.

Vertical stacking




Additional function units can be added to each valve position between the base plate (manifold sub-base) and the valve. These functions are known as vertical stacking modules and enable special functions or control of an individual valve position. It is possible to link several valve sizes on one valve terminal.

- Note

Certain combinations are not recommended due to the design of the individual vertical stacking components.

Vertical stacking components




The following component sequence is recommended for valve positions with vertical stacking:

- [1] Valve VSVA
- [2] Pressure regulator plate
- [3] Throttle plate
- [4] Vertical pressure shut-off plate
- [5] Vertical supply plate
- [6] Manifold sub-base

Vertical stacking

Pressure regulator plate



An adjustable pressure regulator can be installed between the base plate (manifold sub-base) and the valve to control the force of the triggered actuator. This pressure regulator maintains a largely constant output pressure (secondary side) independent of pressure fluctuations (primary side) and air consumption. Also suitable for valves with symmetrical design.

Standard version:

- Standard port pattern to ISO 15407-2 or ISO 5599-2
- For pressure regulation up to 6 bar or up to 10 bar
- Without pressure gauge (optional)
- Regulator knob with 3 positions (locked, reference position, freely positionable)

- 🕴 - Note

With the A, B and AB pressure regulators VABF-S...-1-..., the regulated pressure should not be less than 2 bar.

Use the reversible A, B or AB pressure regulators for regulated pressure of less than 2 bar.

- Note

Please note when reordering pressure regulators in sizes 42 mm and 52 mm: The part number printed on the regulator plate refers only to the standard version.

When reordering pressure regulators with additional equipment, such as an extended design, only use the VABF configurator.

[1] Pull the rotary knob upwards out of the locking position (1) into the setting

Set the desired pressure at the setting level (2) using the rotary knob

After setting the pressure, push the rotary knob back down to the locking


→ Internet: vabf-s2

position (2)


position (1)

[2] [3]

Rotary knob for pressure regulator for width 42 mm and 52 mm Setting the pressure



Rotary knob for pressure regulator for width 42 mm and 52 mm Locking the rotary knob



After setting the pressure, the rotary knob can be locked against unauthorised actuation.

To do this, the blue locking element is pushed out and secured with a padlock. The rotary knob is now fixed in place and cannot be moved.

· 📲 - Note

The position of the rotary knob and the locking element is determined by the pressure setting.

If a number of pressure regulators are installed next to one another, there may not always be enough space to push out the locking elements.

To ensure that the rotary knob can still be locked, it can be pulled off completely, rotated 60° or 120° and pushed back on.

[1] Locking element, pushed out

Vertical stacking

Energy efficiency through dual-pressure operation or through operation with reversible pressure regulators

Saving energy starts with compressed air generation. It is possible to achieve energy savings of up to 10% per 1 bar drop in pressure. Therefore, wherever possible reduce the pressure to the minimum required.

To save additional energy, you can operate valves in dual-pressure mode in a separate pressure zone.

To do this, the valves used must be operated in reverse mode, i.e. with reversed flow direction (see also information on \rightarrow page 107). In dual-pressure operation, the valves are then supplied with pressure separately via ducts 3 and 5.

The air is exhausted via duct 1.

Requirements for dual-pressure operation:

- Exhaust ducts 3 and 5 in the pressure zone are completely separate.
- Valves are used that can be operated in reverse mode.

Advantages of dual-pressure operation:


It is possible to save energy if a valve can be supplied with different pressures. The advantages are:

- Saves energy because the return stroke can be carried out using reduced force, e.g. 3 bar instead of 6 bar.
- Just one valve is required, as in the case of vacuum application with ejector pulse for example (e.g. duct 3 for vacuum switching, duct 5 for the ejector pulse).
- A reduction in compressed air consumption of up to 50% is possible if two different pressures can be applied to the valve (return stroke uses reduces pressure).


Advantages of reversible operation: If compressed air is applied to the pressure regulator upstream of the valve (circuit diagram 2), exhausting is directly via the solenoid valve. This has the following advantages:

- Increased exhaust capacity, exhausting is up to 50% quicker
- Lower wear on the pressure regulator
- Can be adjusted very accurately, perfect for very low operating pressures
- No quick exhaust valves are required.
- Fast cycle times
- The pressure regulator can be adjusted independently of the valve position because operating pressure is permanently present at the pressure regulator.

Dual-pressure operation with reversible controller








Circuit diagram 2: Pressure is regulated upstream of the valve

Dual-pressure operation with standard regulator

Vertical stacking

Mode of operation of the pressure regulator plate (P regulator) for port 1; code: ZA, ZAY, ZF, ZFY



Benefits

- The pressure regulator is not affected by exhausting, since the pressure is regulated upstream of the valve.
- The pressure regulator can always be adjusted, since the pressure from the valve terminal is always present.


This pressure regulator regulates the pressure upstream of the valve in duct 1. Ducts 2 and 4 thus have the same regulated pressure. During exhausting, the exhaust flow in the valve is from duct 2 to duct 3 and from duct 4 to duct 5.

- [1] Duct 3 (exhaust air)
- [2] Duct 1 (supply air)
- [3] Duct 5 (exhaust air)

Application examples

- An equal working pressure is required at working ports 2 and 4.
- A working pressure (e.g. 3 bar) lower than the operating pressure present at the valve terminal (e.g. 8 bar) is required.

Mode of operation of the pressure regulator plate (AB regulator) for ports 2 and 4; code: ZD, ZDY, ZI, ZIY



This pressure regulator regulates the pressure in ducts 2 and 4 after the pressure medium flows through the valve.

During exhausting, the exhaust flow in the valve is from duct 2 to duct 3 and from duct 4 to duct 5 via the pressure regulator. Example with the following switching position:

The supply air flows from duct 1 of the manifold sub-base via the valve to duct 2, it is then regulated and made available at port 2 of the manifold subbase. At the same time, exhausting takes place via duct 4 of the manifold sub-base, via the regulator and via the valve into duct 5 of the manifold subbase.

[1] Duct 3 (exhaust air)

- [2] Duct 1 (supply air)
- [3] Duct 5 (exhaust air)

Application examples


• Two different working pressures are required at ports 2 and 4 instead of the valve terminal operating pressure.

Constraints

• The pressure regulator cannot be adjusted in the exhaust position. For example, the pressure regulator for duct 4 cannot be adjusted when the valve is pressurised in the switching position from duct 1 to duct 2 and exhausted from duct 4 to duct 5.

Vertical stacking

Mode of operation of the pressure regulator plate (AB regulator, reversible) for ports 2 and 4, reversible; code: ZE, ZEY, ZJ, ZJY



Application examples

- Two different pressures are required in ducts 2 and 4 instead of the valve terminal's operating pressure.
- Quick exhausting is required.
- The pressure regulator must always be adjustable.

With this pressure regulator, the supply air (duct 1) is split and routed directly to both pressure regulators. In each case the regulated supply air is present in ducts 3 and 5 on the valve. The valve is thus operated in reverse mode.

This means that:

- Duct 3 routes the working pressure to port 2
- Duct 5 routes the working pressure to port 4

Example with the following switching position: The supply air in duct 1 is split be-

tween ducts 3 and 5 in the regulator and flows from here to the valve. In the valve, the supply air is routed to port 2 of the manifold sub-base. The exhaust air is simultaneously routed via duct 4 of the manifold sub-base and via the valve to regulator duct 1, where it is split between ducts 3 and 5 and then discharged via the manifold sub-base.

- [1] Duct 3 (exhaust air)
- [2] Duct 1 (supply air)
- [3] Duct 5 (exhaust air)

📲 - Note

- Reversible pressure regulator plates should only be combined with valves that can be operated in reverse mode.
- Valves in valve positions with vertical pressure shut-off plates are operated with internal pilot air, even when the valve terminal is operated with external pilot air supply.
- The following combination of reversible valve terminals with vertical stacking components is not permitted:
- Reversible pressure regulator plates
- Throttle plates
- Vertical pressure shut-off plates
- Vertical supply plates

Disadvantages

- 2x 3/2-way solenoid valves (code N, K, H) cannot be used, as pressure is present at ports 3 and 5.
- A practical combination with a throttle plate is not possible.

Benefits

- Fast cycle times
- 50% higher exhaust flow rate, as air is not exhausted via the pressure regulator. The load on the pressure regulator is also reduced.
- No quick exhaust valves are required.
- Operating pressure is always present at the pressure regulator, as the pressure is regulated upstream of the valve, i.e. the regulator can always be adjusted.

Code		Туре				Pressure up to	regulation	Description	
			18 mm	26 mm	42 mm	52 mm	6 bar	10 bar	
Pressure	e regulator plate for port 1 (P regulator)								
ZA	S 4 2	VABF-SR1C2-C-10					-		Regulates the operating pres-
ZAY ²⁾		VABF-SR1C2-C-10E				•	-		sure in duct 1 upstream of the
ZF		VABF-SR1C2-C-6			•	•	•	-	solenoid valve
ZFY ²⁾		VABF-SR1C2-C-6E	•		•	•		-	_
Pressure	regulator plate for port 2 (B regulator)								
ZC		VABF-SR2C2-C-10		•		•	-		Regulates the operating pres-
ZCY ²⁾		VABF-SR2C2-C-10E					-		sure in duct 2 downstream of
ZH		VABF-SR2C2-C-6						-	the solenoid valve
ZHY ²⁾		VABF-SR2C2-C-6E	•	•	-	•	•	-	
Pressure	e regulator plate for port 4 (A regulator)								
ZB ²⁾		VABF-SR3C2-C-10					-		Regulates the operating pres-
ZG ²⁾		VABF-SR3C2-C-6							sure in duct 4 downstream of the solenoid valve
						•	•	-	
Pressure	e regulator plate for ports 2 and 4 (AB reg	gulator)							_
ZD		VABF-SR4C2-C-10					-		Regulates the working pressu
ZDY ²⁾		VABF-SR4C2-C-10E					-		in ducts 2 and 4 downstream the solenoid valve
ZI ZIY ²⁾	┥╎┍ ┥╔╸┋ ┽┼┼┙╎└┼┼┽ <mark>╸╛</mark> ┽╖╷	VABF-SR4C2-C-6 VABF-SR4C2-C-6E	-					-	- 着 - Note
			•	•	-	-	•	-	These pressure regulator plates cannot be combined with re- versible 2x 3/2-way solenoid valves (code P, Q, R).

Width variants 42 mm and 52 mm (ISO 5599-2, ISO 1 and ISO 2) can be selected via the pressure regulator configurator VABFS2
 Also suitable for valves with symmetrical design


Code		Туре	Width 18 mm	26 mm	42 mm	52 mm	Pressure up to 6 bar	regulation	Description	
Pressure	regulator plate for port 2, reversible (B r	egulator)	l.	1						
ZL		VABF-SR6C2-C-10				-	-		Reversible pressure regulator fo	
ZLY ²⁾		VABF-SR6C2-C-10E	•				-		port 2	
ZN		VABF-SR6C2-C-6						-		
ZNY ²⁾ 14 ¹ 5 ¹ 1 ³ 12		VABF-SR6C2-C-6E	•	•	•	•	•	-		
Pressure	regulator plate for port 4, reversible (A re	egulator)								
ZK ²⁾		VABF-SR7C2-C-10					-		Reversible pressure regulator for	
ZM ²⁾		VABF-SR7C2-C-6		+	+	+		+ -	port 4	
			•	•	•	-	-	-		
Pressure	regulator plate for ports 2 and 4, reversi	ble (AB regulator)		•	•					
ZE		VABF-SR5C2-C-10					-		Reversible pressure regulato	
ZEY ²⁾		VABF-SR5C2-C-10E	•	•	•	•	_	•	 for ports 2 and 4 Pressure regulation upstrear of the solenoid valve Routes the operating pressu from duct 1 to ducts 3 and 5 Routes the exhaust air from duct 1 to ducts 3 and 5 	
ZJ		VABF-SR5C2-C-6						-	- 🛔 - Note	
ZJY ²⁾		VABF-SR5C2-C-6E							- 闄 - Note	
			•	•	•	-	•	-	These pressure regulator plates cannot be combined with stanc ard 2x 3/2-way solenoid valves (code N, K, H). Reversible 2x 3/2-way solenoid valves (code P, Q, R) must not b operated in a separate pressur zone in combination with these pressure regulators.	

1) Width variants 42 mm and 52 mm (ISO 5599-2, ISO 1 and ISO 2) can be selected via the pressure regulator configurator VABF-S2

2) Also suitable for valves with symmetrical design

Vertical stacking

Throttle plate




Equipped with two flow control valves at which the exhaust air flow rate at exhaust ports 3 or 5 can be adjusted. This enables the movement of the drive to be initiated and the required speed to be set on the valve terminal using the manual override. Ducts 3 and 5 can be adjusted independently of each other.

- Note

On reversible valve terminals, the supply air is controlled in ducts 3 and 5 upstream of the valve.

Code	Туре	Width			Description	
		18 mm	26 mm	42 mm	52 mm	
X	VABF-S4F1B1-C	•	•	•	•	• Controls the flow of exhaust air down- stream of the valve to ducts 3 and 5

Vertical pressure shut-off plate



This is equipped with a switch with which the compressed air supply can be shut off. A solenoid valve or downstream vertical stacking plate can thus be replaced without switching off the overall air supply. If the control chain has a redundant connection, the cycle can continue even in the case of a cyclical control system.

After the shut-off function has been activated, the exhaust air/return air is discharged from the activated valve. This takes place via an M5 threaded connection or via duct 3 in the case of width 18 and 26 mm, and via duct 3 in the case of width 42 and 52 mm.

- Note


The operating pressure of the valve terminal must lie within the range of the required pilot pressure (i.e. min. 3 bar). When using the end plate with pilot air selector, only the switching position with code W and U can be used.

Code		Туре	Width				Description
			18 mm	26 mm	42 mm	52 mm	
ZT	VABF-S4L1D1-C		•	_	_	 3/2-way valve for shutting off the operating pressure at the valve position Blocks ducts 1 and 14 for the valve position Supplies the valve position with inter- 	
	VABF-S2L1D1-C	-	_	•	•	 nal pilot air Pressure separation on the valve assembly 	
ZS		VABF-SL1D2-C	•	•	-	-	 3/2-way valve for shutting off the operating pressure at the valve position Blocks ducts 1 and 14 for the valve position Supplies the valve position with internal pilot air Pressure separation can be shut off on the valve assembly using a key

- 闄 - Note

The vertical pressure shut-off plates VABF-... are provided only in combination with VSVA-...T1L solenoid valves from Festo. In the vertical pressure shut-off plate only ducts 1 and 14 are blocked, and not duct 12.


Vertical supply plate



This plate enables a valve to be supplied with individual operating pressure independently of the operating pressure of the valve terminal. As additional compressed air supply for a valve. To supply an additional pressure zone.

Code		Туре	Width				Description
			26 mm	18 mm	42 mm	52 mm	
ZU	4 2 14 1 14 1	VABF-SP1A3	■	•	•	•	• Plate with port 11 for supplying individ- ual operating pressure to a valve posi- tion, duct 1
ZV	4 2 11 14	VABF-SP1A14	■		•	•	Plate with port 11 for supplying individ- ual operating pressure to a valve posi- tion, ducts 1 and 14

Compressed air supply and exhausting



with large-scale extensions.

Compressed air supply and exhaust


Supply plates for VTSA/VTSA-F, exhaust port 3/5 separate



• Code K

Supply plates/extension module, pneumatic and electric air supply plate for VTSA-F-CB, exhaust port 3/5 separate

- Code U
 - Code UW
 - Code UWS





• Code L

Supply plates/extension module, pneumatic and electric air supply plate for VTSA-F-CB, exhaust port 3/5 common



- Code U
- Code UW
- Code UWS

Additional compressed air supply/duct separation, VTSA/VTSA-F

Additional supply plates can be used to ensure the compressed air supply for larger valve terminals or to create additional pressure zones.

additional pressure zones. These can be selected at any point upstream or downstream of the manifold When

Depending on your order, the exhaust ducts are either ducted or exhausted via silencers.

Operation with ducted exhaust air: When the exhaust air is ducted, exhausting can take place via a supply plate or a right end plate (code V or X). If duct separation is required, there are a number of different options:

- Duct separation 1, 3, 5: code S
- Duct separation 1: code T
- Duct separation 3, 5: code R

If a combination of duct separation (S, T or R) and one or two supply plates is required, the following variants can be selected:

- Supply plate with duct separation on the left: code SU, TU, RU
- Supply plate with duct separation on the right: code US, UT, UR
- 2 supply plates with intermediate duct separation: code USU, UTU, URU.

Supply plates contain the ports:

• Compressed air supply (1)

sub-bases.

• Exhaust port (3/5) common or separate

Supply plates for VTSA/VTSA-F

Code	plates for VTSA/VTSA-F	Туре	Description
U		VABF-S6-10-P1A7-G12 VABF-S6-10-P1A6-G12	 Supply plate without duct separation (no R, S or T selected) Exhaust port 3/5 common (not shown) Exhaust port 3/5 separate
SU TU RU			 Supply plate with duct separation on the left, if R, S or T is selected Exhaust port 3/5 common (not shown) Exhaust port 3/5 separate
US UT UR		-	 Supply plate with duct separation on the right, if R, S or T is selected Exhaust port 3/5 common (not shown) Exhaust port 3/5 separate
USU UTU URU			 2 supply plates with duct separation in centre, if R, S or T selected Exhaust port 3/5 common (not shown) Exhaust port 3/5 separate

Additional compressed air supply/duct separation, VTSA-F-CB

Additional supply plates can be used to ensure the compressed air supply for larger valve terminals or to create additional pressure zones.

These can be selected at any point upstream or downstream of the manifold sub-bases. Supply plates contain the ports:

rate

Compressed air supply (1)Exhaust port (3/5) common or sepa-

Depending on your order, the exhaust ducts are either ducted or exhausted via silencers.

Operation with ducted exhaust air:

With ducted exhaust air, venting can be via a supply plate or a right end plate (code V or X).

If duct separation is required, there are a number of different options:

- Duct separation 1, 3, 5, 14: code K
- Duct separation 14: code L
- Duct separation 1, 3, 5: code S
- Duct separation 1: code T
- Duct separation 3, 5: code R

ode		Туре	Description
IJ		VABF-S6-1-P1A7-G12-CB	 Additional pneumatic supply Connecting thread G1/2 Exhaust port 3/5 common
JW		VABF-S6-1-P8A7-G12-CB	 Additional pneumatic and electrical supply Connecting thread G1/2 Generation of 24 additional valve addresses (electrical supply is provided internally from Uval) Exhaust port 3/5 common
JWS		VABF-S6-1-P8A7-G12-CB1	 Additional pneumatic and electrical supply Connecting thread G1/2 Generation of 24 additional valve addresses (electrical supply is provided from new (safe) voltage zone (internally from S2)) Exhaust port 3/5 common
J		VABF-S6-1-P1A6-G12-CB	 Additional pneumatic supply Connecting thread G1/2 Exhaust port 3/5 separate
IW	0.0	VABF-S6-1-P8A6-G12-CB	 Additional pneumatic and electrical supply Connecting thread G1/2 Generation of 24 additional valve addresses (electrical supply is provided internally from Uval) Exhaust port 3/5 separate
JWS		VABF-S6-1-P8A6-G12-CB1	 Additional pneumatic and electrical supply Connecting thread G1/2 Generation of 24 additional valve addresses (electrical supply is provided from new (safe) voltage zone (internally from S2)) Exhaust port 3/5 separate

Right end plate

Right end plates with different port sizes are available depending on the flow rate required.

With the following right end plates, the outlet direction of the ports is aligned with the horizontal stacking direction. Right end plates with pilot air supply/ pilot exhaust air (VTSA/VTSA-F)

- Internal pilot air supply: code V, V1 and V3 (ducts 1 and 14 are connected)
- External pilot air supply: code X, X1 and X3, as well as XP1, XP2, XP3 and XS

Right end plate, variants

Right end plates with pilot air supply/ pilot exhaust air (VTSA-F-CB)

• Internal pilot air supply: code NS, MS (ducts 1 and 14 are connected)

• External pilot air supply: code NZ, MZ For end plates with pilot air selector, the outlet direction of the ports is to the front of the valve terminal. This means that all the ports on the valve terminal can be combined in one outlet direction.

The special feature of the end plates with pilot air selector is the selector switch itself, which has four settings for different pilot air supply/pilot exhaust air. End plates with pilot air selector switch set at the factory for:

- External pilot air supply: selector position 1 (code Z)
- Internal pilot air supply: selector position 2 (code Y)
- External pilot air supply, ducted pilot exhaust air: selector position 3 (code W)
- Internal pilot air supply, ducted pilot exhaust air: selector position 4 (code U)

📲 - Note

- The end plate with pilot air selector must be used in combination with a supply plate.
- The reversible 3/2-way solenoid valves (code P, Q, R) must only be operated in selector position 1 or 2.
- Ducted pilot exhaust air via port 12 is only possible with rotated seals on the valve.

Code	Code	Blanking plug in duct	Pilot air supply Ducted pilot exhaust air ¹⁾		Connecting thread	
VTSA/VTSA-F	VTSA-F-CB			Position of the seal on solenoid valve ("ISO" is visible)	1, 3, 5	12, 14
V	NS	-	Internal	-	G1/2	G1/4
V1	MS	-		-	G3/4	G1/4
V3	-	-			G3/4	G1/4
Х	NZ	-	External	-	G1/2	G1/4
X1	MZ	-		-	G3/4	G1/4
Х3	-	-		•	G3/4	G1/4
XP1 ²⁾	NZAB	1	External, via soft-start valve	-	G1/2	G1/4
XP2 ³⁾	NZABCB	1, 14	("gradual pressure build-up")	-	G1/2	G1/4
XP3 ³⁾	NZABCBGB	1, 3, 5, 14		-	G1/2	G1/4
XS ⁴⁾	NZCB	14	External, via pilot air switching valve ("switchable pilot air")	-	G1/2	G1/4

1) Pilot exhaust air is ducted on the end plate via port 12 and exhausted (done by turning the seal on the solenoid valve to position "ISO")

2) Not possible in combination with soft-start valve code PQ, PP, PO (with internal pilot air supply)

3) Not possible in combination with soft-start valve code PN, PM, PK (with external pilot air supply)

4) Only possible in combination with pilot air switching valve/intermediate plate for switchable pilot air

Right end plate with pilot air selector

Right enu pla	te with pitot an	Selector			
Code VTSA/VTSA-F	Code VTSA-F-CB	Pilot air supply		Ducted pilot exhaust air ¹⁾ Position of the seal on solenoid valve	Connecting thread 12, 14
				("ISO" is visible)	
Z	YZ	External	1	_	G1/4
Υ	YS	Internal	2	-	G1/4
W	-	External (ducted)	3		G1/4
U	-	Internal (ducted)	4		G1/4

1) Pilot exhaust air is ducted on the end plate via port 12 and exhausted (done by turning the seal on the solenoid valve to position "ISO")

T

Right end pla	te			
Code	Code	Type of compressed air supply and pilo	t air supply	Description
VTSA/VTSA-F		()		
V V V1 V3	MS	epresentation)		 Internal pilot air supply Pilot air supply is branched internally from port 1 Port 14 is not available with code V Port 14 is sealed with a blanking plug for code V1, V3 Exhaust air via ports 3 and 5 For operating pressure in the range 3 10 bar Pilot exhaust air via port 12¹⁾ V1 cannot be selected in combination with a soft-start valve in the last pressure zone
X X1 X3	NZ MZ -			 External pilot air supply Pilot air supply between 2 and 10 bar is connected at port 14 Exhaust air via ports 3 and 5 For operating pressure in the range –0.9 10 bar (suitable for vacuum) Pilot exhaust air via port 12¹⁾ X1 cannot be selected in combination with a soft-start valve in the last
XP1	NZ			pressure zone External pilot air supply, compressed air supply via soft-start valve ²⁾ • Port 1 is sealed with a blanking plug • Exhaust air via ports 3 and 5 • Pilot exhaust air via port 12 ¹⁾
XP2	NZ			External pilot air supply, compressed air supply via soft-start valve ²⁾ Internal pilot air supply 14 via soft-start valve Ports 1 and 14 are sealed Exhaust air via ports 3 and 5 Pilot exhaust air via port 12 ¹⁾
XP3	NZ			 External pilot air supply, compressed air supply via soft-start valve ²⁾ Internal pilot air supply 14 via soft-start valve Ports 1, 3, 5 and 14 are sealed Pilot exhaust air via port 12¹⁾
XS	NZ			 External pilot air supply via pilot air switching valve ³⁾ Internal pilot air supply 14 via pilot air switching valve Port 14 is sealed Exhaust air via ports 3 and 5 Pilot exhaust air via port 12¹⁾

1) Ducted pilot exhaust air is only possible with rotated seals on the valve

2) Application with XP1, XP2, XP3 and soft-start valve in combination with valves of width 52 mm:

please note the maximum flow rate of the soft-start valve in this pressure zone

3) Application with XS and pilot air switching valve in conjunction with intermediate plate/intermediate plate for switchable pilot air

Right end pla	te				
Code ¹⁾ VTSA/VTSA-F	Code VTSA-F-CB	Type of compressed air supply and pilot air supply	Description		
End plate wit	h pilot air sele	ctor			
Z (1)	YZ		 External pilot air supply Pilot air supply is connected at port 14 Port 12 is sealed with a blanking plug Ports 12 and 14 are internally connected Pilot exhaust air unducted via valve housing 		
Y (2)	YS		 Internal pilot air supply Pilot air supply is branched internally from port 1 Ports 1, 12 and 14 are internally connected Ports 12 and 14 are sealed with blanking plugs Pilot exhaust air unducted via valve housing 		
W (3)	YZ		 External pilot air supply, ducted pilot exhaust air Pilot air supply is connected at port 14 Pilot exhaust air via port 12²⁾ Cannot be selected in combination with a soft-start valve in the last pressure zone 		
U (4)	YS		 Internal pilot air supply, ducted pilot exhaust air Pilot air supply is branched internally from port 1 Ports 1 and 14 are internally connected Port 14 is sealed with a blanking plug Pilot exhaust air via port 12²⁾ Cannot be selected in combination with a soft-start valve in the last pressure zone 		

1) Selector setting in brackets

2) Ducted pilot exhaust air is only possible with rotated seals on the valve (pilot exhaust air 82/84 including venting air for valves)

- 🗍 - Note

The reversible 3/2-way solenoid values (code P, Q, R) must only be operated in selector position 1 or 2.

Configuration of all pneumatic threaded connections


Code VTSA/VTSA-F	Code VTSA-F-CB			Connection (duct)	Designation	Code M Push-in connector, large	Code N Push-in connector small
Right end pla							
V	NS			1	Push-in fitting	QS-G1/2-16	QS-G1/2-12
				3 and 5	Silencer	U-1/2-B	U-1/2-B
					or	or	or
			14 -		Push-in fitting	QS-G1/2-16	QS-G1/2-12
				12	Silencer	U-1/4	U-1/4
					or	or	or
			Ê.		Push-in fitting	QS-G1/4-10	QS-G1/4-8
	NZ			1	Push-in fitting	QS-G1/2-16	QS-G1/2-12
				3 and 5	Silencer	U-1/2-B	U-1/2-B
					or	or	or
					Push-in fitting	QS-G1/2-16	QS-G1/2-12
			1	12	Silencer	U-1/4	U-1/4
					or	or	or
			<u>}</u>		Push-in fitting	QS-G1/4-10	QS-G1/4-8
			00	14	Push-in fitting	QS-G1/4-10	QS-G1/4-8
'1	MS			1	Barbed hose fitting	N-3/4-P-19 ¹⁾	-
'3	-			3 and 5	Silencer	U-3/4-B	-
					or	or	
			14 -		Barbed hose fitting	N-3/4-P-19 ¹⁾	
				12	Silencer	U-1/4	U-1/4
					or Push-in fitting	or QS-G1/4-12	or QS-G1/4-10
				14	Plug	B-1/4	B-1/4
				14	riug	D-1/4	D-1/4
1	MZ	\square		1	Barbed hose fitting	N-3/4-P-19 ¹⁾	-
3	-			3 and 5	Silencer	U-3/4-B	-
					or	or	
			14		Barbed hose fitting	N-3/4-P-19 ¹⁾	
				12	Silencer	U-1/4	U-1/4
					or	or	or
				4/	Push-in fitting	QS-G1/4-12	QS-G1/4-10
				14	Push-in fitting	QS-G1/4-12	QS-G1/4-10

1) For tubing with I.D. 19 mm. Use tubing clips to DIN 3017

	of all pneuma	tic threaded connections					
Code ¹⁾ VTSA/VTSA-F	Code VTSA-F-CB			Connection (duct)	Designation	Code M Push-in connector, large	Code N Push-in connector, small
End plate with		ctor					
Z (1)	YZ			12	Blanking plug	B-1/4	B-1/4
				14	Push-in fitting	QS-G1/4-10	QS-G1/4-8
Y (2)	YS		3 5 12	12	Blanking plug	B-1/4	B-1/4
				14	Blanking plug	B-1/4	B-1/4
W (3)	YZ			12	Silencer or Push-in fitting	U-1/4 or QS-G1/4-10	U-1/4 or QS-G1/4-8
				14	Push-in fitting	QS-G1/4-10	QS-G1/4-8
U (4)	YS			12	Silencer or Push-in fitting	U-1/4 or QS-G1/4-10	U-1/4 or QS-G1/4-8
				14	Blanking plug	B-1/4	B-1/4

1) Selector setting in brackets

Using the seals with ducted/unducted pilot exhaust air



Unducted pilot exhaust air:

The seal is visible in the display window on control side 14.
The "ISO" mark is visible on the

inscription label on the seal sur-

Ducted pilot exhaust air:

- The seal is visible in the display window on control side 12.
- The "ISO" mark is visible on the inscription label on the seal surface.

[1] Inscription label

face.

- [2] Display window on control side 14 ("ISO" is visible)
- [3] Display window on control side 12 ("ISO" is visible)

Designation	150	ISO
Pilot exhaust air	Ducted	Unducted (standard)
Display window on	Control side 12	Control side 14
Pilot exhaust port	12	-

Pilot air supply

The port for the pneumatic supply is located on the supply plates or the right end plate.

Internal pilot air supply

Internal pilot air supply can be selected if the working pressure is between 3 and 10 bar.

The ports differ for the following types of pilot air supply:

- InternalExternal
- LAternat

In this case the pilot air supply is branched from the compressed air supply 1 using an internal connection. Port 14 is not available with code V and is sealed with a blanking plug for code V1, V3.

📲 - Note

If a gradual pressure build-up is required in the system by using a soft-start valve, then external pilot air should be selected so that the pilot pressure is already applied in full at the point of switch-on.


External pilot air supply

If the supply pressure is less than 3 bar, you must operate your valve terminal VTSA/VTSA-F/VTSA-F-CB using external pilot air supply. The pilot air supply is then supplied via port 14 on the right end plate. This is the case even if the valve terminal is operated with different pressure zones.

Creating pressure zones and separating exhaust air

The valve terminal VTSA/VTSA-F/VTSA-F-CB offers a number of options for creating pressure zones if different working pressures are required.

Pressure zones are created by isolating the internal supply ducts between the manifold sub-bases by appropriate duct separation. Compressed air is supplied and exhausted via a supply plate. The position of the supply plates and duct separations can be freely selected for VTSA/VTSA-F/VTSA-F-CB. Duct separations are integrated exworks as per your order. Duct separations can be distinguished by their coding, even when the valve terminal is assembled.



Creating Code	pressure zones Separating seal			Width				Description
	Illustrated examples	Coding	Basic representation	18 mm	26 mm	42 mm	52 mm	
Т						•	•	Duct 1 separated
S					•	•	•	Ducts 1, 3 and 5 separate
R				•	•	•	-	Ducts 3 and 5 sepa- rate
TL		Colour-coded in red		•		•	•	Duct 1 and 14 sepa- rated
K		Colour-coded in green		•	•	•	■	Ducts 1, 3, 5 and 14 separate
L		Colour-coded in white		■	•	■	■	Duct 14 separated

2025/03 - Subject to change


Example: Compressed air supply and pilot air supply, right end plate

Internal pilot air supply, silencer/ducted exhaust air

Right end plate: code V and V1

The adjacent diagram shows an example of the configuration and connection of the compressed air supply with internal pilot air supply:

- Port 14 is not available with code V and is sealed with a blanking plug for code V1.
- The air is exhausted via the silencer at exhaust port 3/5.
- Duct separations can optionally be used to create pressure zones.



Example: Compressed air supply and pilot air supply, right end plate

External pilot air supply, silencer/ducted exhaust air

Right end plate: code X and X1

The adjacent diagram shows an example of the configuration and connection of the compressed air supply with external pilot air supply:

- Port 14 on the right end plate is equipped with a fitting for this.
- The air is exhausted via the silencer at exhaust port 3/5.
- Duct separations can optionally be used to create pressure zones.

Optional duct separation

Optional duct separation

Key features – Pneumatic components – Compressed air supply and pressure zones, examples


Example: Compressed air supply and pilot air supply via end plate with pilot air selector

Internal pilot air supply, ducted exhaust air/silencer

Right end plate: code U

The adjacent diagram shows an example of the configuration and connection of the compressed air supply with internal pilot air supply:

- Port 14 on the right end plate is tightly sealed.
- The air is ducted or discharged via the silencer at exhaust port 3/5.
- The selector switch on the pilot air selector is in position 4.
- Duct separations can optionally be used to create pressure zones.



Example: Compressed air supply and pilot air supply via end plate with pilot air selector


External pilot air supply, ducted exhaust air/silencer

Right end plate: code Z

The adjacent diagram shows an example of the configuration and connection of the compressed air supply with external pilot air supply:

- Port 14 on the right end plate is equipped with a fitting for this.
- Port 12 is sealed with a blanking plug since it is internally connected with port 14.
- The air is ducted or discharged via the silencer at exhaust port 3/5.
- The selector switch on the pilot air selector is in position 1.
- Duct separations can optionally be used to create pressure zones.

Optional duct separation




Key features – Pneumatic components – Compressed air supply and pressure zones, examples

Examples: Creating pressure zones

VTSA/VTSA-F/VTSA-F-CB with CPX terminal

With the VTSA/VTSA-F/VTSA-F-CB up to 16 pressure zones can be created (up to 32 pressure zones if only size 1, ISO 5599-2, is fitted). The diagram shows an example of the configuration and connection of three pressure zones using duct separations – with internal pilot air supply.



- Note

-

Examples with pressure zones and soft-start valve are described separately in the chapter "Soft-start valve"

→ page 193.

Key features – Mounting

Valve terminal mounting


Sturdy valve terminal mounting thanks to:

- Through-holes for wall mounting
- Additional mounting brackets
 DIN rail mounting for VTSA/VTSA-F (horizontal mounting position permitted)

- Note

Further information on mounting the valve terminal, arranged by valve terminal configuration, can be found online.

Wall mounting, general



2

1

[1] Drilled hole for M6 screw

[2] Drilled hole for DIN rail mounting

The valve terminal VTSA/VTSA-F/ VTSA-F-CB is screwed onto the mounting surface using M6 screws. The mounting holes are located at the following points:

- Multi-pin (4 pieces); 2 each on the multi-pin manifold block and the right end plate
- Fieldbus, CPX (6 pieces); 2 each on the left (CPX) and right (VTSA/VTSA-F) end plate and the pneumatic interface
- I-Port/IO-Link[®] (4 pieces); 2 each on the I-Port/IO-Link[®] interface and on the right end plate

Mounting brackets can be mounted on pneumatic supply plates and manifold sub-bases.

If using CPX components, see: → Internet: cpx




Wall mounting of the VTSA/VTSA-F/ VTSA-F-CB with more than 5 pneumatic modules

Note the following information to avoid damage to the valve terminal:

- Additionally use mounting brackets of the type VAME-6-W-M46
- Mount these on each fourth plate (manifold sub-base, supply plate or exhaust plate), counting from left to right, starting after the pneumatic interface.
- No mounting bracket is required next to the right end plate.
- Always use the pre-assembled mounting brackets when mounting factory pre-assembled valve terminals on a wall.

Key features - Mounting

Wall mounting with CPX polymer interface



- [1] Additional wall mounting for poly- [2] Pneumatic interface mer CPX terminal
- [3] Additional wall mounting for VTSA/VTSA-F/VTSA-F-CB


(with drilled hole for M5 and M6 screw)

In the case of polymer CPX terminals with 4 and more interlinking blocks, additional wall mountings of the type CPX-BG-RW must be used every 100 ...150 mm. These mountings are clipped in at the top and bottom between the CPX modules. In the case of the VTSA/VTSA-F/VTSA-F-CB, mounting brackets must be mounted on the wall as indicated above.

Brackets of the type VAME-S6-W-M46 must be used as an additional wall mounting.

Key features – Mounting

Wall mounting with CPX metal interface




- [1] Additional wall mounting for CPX [2] Pneumatic interface metal design
- [3] Additional wall mounting for VTSA/VTSA-F/VTSA-F-CB
- (with drilled hole for M5 and M6 screw)

In the case of metal CPX terminals with 4 and more interlinking blocks, additional wall mountings of the type CPX-M-BG-RW must be used every 100 ... 150 mm. These wall mountings are screwed in at the top of the corresponding CPX module.

Mounting on support system with CPX metal interface

In the case of the VTSA/VTSA-F/VTSA-F-CB, mounting brackets must be mounted on the wall as indicated above.

Brackets of the type VAME-S6-W-M46 must be used as an additional wall mounting.



- [1] Support system (DIN mounting rail)
- [3] Lower mounting for metal CPX on DIN mounting rail with mounting bracket CPX-M-BG-VT-2X
- [4] Mounting for pneumatic interface on DIN mounting rail
- [5] Mounting for right end plate on DIN mounting rail

- [2] Upper mounting for metal CPX, left end plate on DIN mounting rail


If a metal terminal CPX with VTSA pneumatic components is mounted on DIN mounting rails, it may be necessary to have one or more mounting brackets on the CPX side to compensate for the length. It is possible to compensate for the length by using special mounting brackets CPX-M-BG-VT-2X. The mounting bracket connects the metal terminal CPX to the DIN mounting rail.

- Note
- Only metal CPX modules with VTSA/VTSA-F/VTSA-F-CB modules of width 18 ... 52 mm must be used.
- The number of mounting brackets required depends on the number of CPX modules installed and whether any system feeds are present. Further information about mounting the valve terminal can be found in the assembly instructions in the Festo Support Portal

2025/03 - Subject to change

Key features – Mounting

DIN rail mounting (not permitted for all VTSA-F-CB combinations)



The valve terminal VTSA/VTSA-F/ VTSA-F-CB is hooked onto the DIN rail (see arrow A).

The valve terminal VTSA/VTSA-F/VTSA-F-CB is then swivelled onto the DIN rail and secured in place with the clamping element (see arrow B).

To mount the valve terminal VTSA/VT-SA-F/VTSA-F-CB on a DIN rail, you will need the mounting kit CPX-CPA-BG-NRH:


This enables the valve terminal to be mounted on a DIN rail to EN 60715.

🚪 - Note

- Wall mounting is recommended if more than one vertical stacking element or a long valve terminal design is required.
- Vibration/shock loads are not permitted for DIN rail mounting.
- Only horizontal installation is permitted for DIN rail mounting.
- Valve terminals VTSA-F-CB with pneumatic interface with voltage zones are not approved for DIN rail mounting.

[1] Vertical mounting holes

The individual sub-base for wall mounting is designed for integration into a system or machine. It is mounted vertically.



Individual valve mounting

Key features – Display and operation

Display and operation

Each solenoid coil is allocated an LED which indicates its switching status.

- Indicator 12 shows the switching status of the pilot control for output 2
- Indicator 14 shows the switching status of the pilot control for output 4

Manual override (MO):

The manual override enables the valve to be switched when not electrically actuated or energised.

The valve is switched by pushing the manual override. The set switching status can also be locked by turning the manual override.


Alternatives:

- The cover cap (code N) limits the function of the manual override, preventing it from being locked. The valve can then only be actuated as non-detenting.
- The cover cap (code V) can be used to secure the manual override against accidental actuation.

- Note

Special valve variants with pre-assembled cover caps for the manual override are available for valve terminal VTSA/VTSA-F/VTSA-F-CB.

Pneumatic connection and control elements



- [1] Pressure gauge (optional)
- [2] Adjusting knob for optional pressure regulator plate
- [3] Manual override (MO) (for each pilot solenoid coil, non-detenting
- or non-detenting/detenting)
- [4] Cover cap for MO, non-detenting
- [5] Cover cap for MO, concealed
- [6] Cover cap for MO, non-detenting heavy duty, detenting via accessory
- [7] Inscription label holder for valve
- [8] Adjusting screw of optional throttle plate
- [9] Exhaust ports "Valves" (3/5)

[10] Pilot ports 12 and 14 for supplying the external pilot air

• The heavy-duty cover cap protects

the manual override located on the

valve. The valve can be actuated as

non-detenting or as detenting via

accessory.


- [11] Inscription label holder for subbase
- [12] Supply port 1 (operating pressure)
- [13] Working ports 2 and 4, per valve position

A manually operated valve (manual override) cannot be reset electrically. Conversely, an electrically actuated valve cannot be reset using the mechanical manual override.


Key features – Display and operation

Display and operation

Electrical connection and display elements for VTSA/VTSA-F




Electrical connection and display elements for VTSA-F-CB



- [1] Inscription area and cover for DIN rail mounting
- [2] Yellow LEDs: signal status indication for the pilot solenoid coils
- [3] Power supply connection
- [4] Earthing connection
- [5] Fieldbus interface (bus-specific)
- [6] Service interface for handheld unit, etc.
- [7] Red LED: common error display for valves

- [1] LED indicators for operating status/diagnostics of the pneumatic interface
- [2] Yellow LEDs: signal status indication for the pilot solenoid coils
- [3] Power supply connection
- [4] Earthing connection
- [5] Fieldbus interface (bus-specific)
- [6] Service interface for handheld unit, etc.

Electrical connection and display elements for AP interface




- [1] LED indicators for operating status/diagnostics of the pneumatic interface
- [2] Yellow LEDs: signal status indication for the pilot solenoid coils
- [3] AP interface with connections

Key features – Display and operation


Manual override (MO) - Function

MO with automatic return (non-detenting),



- [1] Press in the plunger of the manual override using a pointed object or screwdriver.
- The valve is in the switching position.
- Remove the pointed object or [2] screwdriver. The spring force pushes the plunger of the manual override back.
 - The valve returns to its normal position (not with double solenoid valve code J or D).

MO with lock (detenting)



Cover cap for MO, with automatic return (non-detenting)

[1] Press in the plunger of the manual override using a pointed object or screwdriver until the valve switches and then turn the plunger 90° clockwise until the stop is reached.

Valve remains in the switching position.

[2] Turn the plunger 90° anticlockwise until the stop is reached and then remove the pointed object or screwdriver. The spring force pushes the plunger of the manual override back. The valve returns to its normal position (not with double solenoid valve code J or D).

Cover caps for manual override

Cover cap for MO, heavy-duty, with automatic reset (non-detenting/detenting via accessory)






[1] Non-detenting: Push in key for MO. The valve is in the switching position. Detenting: Turn the coded key in switching position 90° clockwise until the stop is reached. Valve remains in

the switching position. In this position the key is latched and cannot be removed.

[2] Turn the key 90° anticlockwise until the stop is reached. The key is now unlatched. The spring force of the manual override pushes the key back out. The valve returns to its normal position (not with double solenoid valve code J or D).

1

[1] Restricted function, non-detenting: push in the plunger of the MO cap using a pointed object or screwdriver. The valve is in the switching position.



[2] Remove the pointed object or screwdriver. The spring force pushes the plunger of the manual override back. The valve returns to its normal position (not with double solenoid valve code J or D).

Cover cap for MO, concealed



When concealed by the cover cap, the MO can be secured against accidental actuation.

Note

Cover caps for the manual override can be ordered separately as accessories. There are also variants of the VSVA valve with ready-fitted cover caps.

Key features - Display and operation

Overview of valve variants and cover caps for manual override (MO)

Illustration	Terminal code	Description of valve terminal order code	Manual override (MO)	Valve code identification on the rating plate sticker ¹⁾
Solenoid valve VSVA without	cover cap			
	R	Without cover cap on MO	Non-detenting, detenting	VSVA-B MZD
Solenoid valve VSVA with rea	dy-fitted cover of	cap on MO		1
	В	MO non-detenting/heavy duty with cover cap, can be used as detent- ing via accessory (key), as valve variant	Non-detenting, detenting via accessory (key)	VSVA-BMZTR
	C	MO can only be used as non-detenting with coded cover cap, as valve variant	Non-detenting	VSVA-B •MZH
	D	MO concealed by cover cap – operation of MO prevented, as valve variant	Concealed	VSVA-B MZ
Cover caps for MO			1	
Ŷ	N	MO can only be used as non-detenting with coded cover cap	Non-detenting	VSVA-BMZD
\mathbf{Q}	V	MO concealed by cover cap – use of MO prevented	Concealed	VSVA-BMZD
	A	MO non-detenting/heavy duty with cover cap, detenting via accessory (key)	Non-detenting, detenting via accessory	VSVA-BMZD
Accessories for manual overri	de, heavy duty			
	-	Coded key (accessory) for actuating the MO, non-detenting/heavy duty, for detenting position	For manual override, detenting	-

1) As an example, the part code for a 5/2-way single solenoid valve, mechanical spring return is used here (e.g. VSVA-B-M52-MZTR-A2-1T1L)

- 🛔 - Note

Cover caps for non-detenting/heavy duty manual override, detenting via accessory, are provided for one-off use only.

If they are used more than once, reliable locking of the cover cap cannot be guaranteed.

Key features – Display and operation, VTSA-F-CB

Illustration	Terminal code	Description of valve terminal order code	Manual override (MO)	Valve code identification on the rating plate sticker ¹⁾
Solenoid valve VABF, va	cuum generator			
	ZQN	MO can only be used as non-detenting with coded cover cap, as valve variant	Non-detenting	VABF-S4-2-V2B1-G38
	ZQR	Non-detenting MO, can be used as detenting, as valve variant	Non-detenting, detenting with- out accessories	VABF-S4-2-V2B1-G38
	ZQV	MO concealed by cover cap – operation of MO prevented, as valve variant	Concealed	VABF-S4-2-V2B1-G38
	ZQA	MO non-detenting/heavy duty with cover cap, can be used as detent- ing via accessory (key), as valve variant	Non-detenting, detenting via accessory (key)	VABF-S4-2-V2B1-G38
Solenoid valve VABF, so	ft-start valve			
	ZQZ	The manual override can be reset in two ways: • manually or • electrically via control signal	Detenting, electrically self-resetting	VABF-S6-1-P5A4 YE
	ZQX	Manual override, concealed	None	VABF-S6-1-P5A4 S
olenoid valve VSVA, pi	lot air switching valv	e	•	
		The manual override can be reset in two ways: manually or electrically via control signal 	Detenting, electrically self-resetting	VSVA-BT-M32CS YE
	ZX	Non-detenting manual override	Non-detenting	VSVA-BT-M32CS MH
· ·	ZZ	Manual override, concealed	None	VSVA-BT-M32CS S
Accessories for manual	override, heavy duty			
	-	Coded key (accessory) for actuating the MO, non-detenting/heavy duty, for detenting position	For manual override, detenting	-

1) As an example, the part code for a 5/2-way single solenoid valve, mechanical spring return is used here (e.g. VSVA-B-M52-MZTR-A2-1T1L)

-- Note


Cover caps for non-detenting/heavy duty manual override, detenting via accessory, are provided for one-off use only.

If they are used more than once, reliable locking of the cover cap cannot be

guaranteed.

Key features – Electrical components

Inscription system




[1] Inscription area (approx. 20 x 45 mm)

- [2] Inscription label holder for valve ASCF-T-S6 (17 x 12.5 mm), ASCF-T-S6-Z
- [3] Inscription label holder for manifold sub-base ASCF-M-S6, ASCF-M-S2-2

Protective circuit

Each solenoid coil VSVA is provided with a spark arresting protective circuit and protected against polarity reversal. The version with width 52 mm also has integrated holding current reduction.

Width 18 to 42 mm



📲 - Note


- All control signals of the solenoid coils of a valve terminal share a common load (independent of whether multi-pin, AS-i or CPX).
- With the valve terminal VTSA-F-CB, the common load always refers to a common voltage zone.
- A configuration combining VTSA/VTSA-F and VTSA-F-CB is not permitted.

Inscription label holders can be applied to the valves and manifold sub-bases to identify them. They can be ordered by entering the code B or T in the order code for accessories. Scope of delivery: inscription label holder including inscription label. The following inscription labels can be used as spares:

- Inscription label holder for valve type ASCF-T-S6: part no. 540888
- Inscription label holder with additional fields for marking valve type ASCF-T-S6-Z: part no. 8106532

- Inscription label holder for manifold sub-base type ASCF-M-S6: part no. 540889
- Inscription label holder for manifold sub-base (for valve width 52 mm) type ASCF-M-S2-2: part no. 562577
 Large inscription labels can be attached to the pneumatic interface as an alternative or in addition to the smaller labels.

Width 52 mm



Individual valve

Valves on individual sub-bases can be used for actuators that are further away from the valve terminal.

- Electrical connection M12, 4-pin 24 V DC
- 4-pin clamped terminal connection for configuration by the user 24 V DC
- Cable (open end) for configuration by the user 24 V DC

Individual electrical connection

A maximum of 20 solenoid coils can be actuated. 2 solenoid coils per valve can be addressed.

- Individual electrical connection:
- M12
- 6-way or 10-way
- 5-pin
- 24 V DC

Electrical multi-pin plug connection

The following multi-pin plug connection variants are offered for the valve terminal VTSA/VTSA-F:

- Sub-D multi-pin plug connection (37-pin): This valve terminal can be equipped with 1 ... 16 valve positions (with double solenoid valves), or with 1 ... 32 valve positions (with single solenoid valves). A maximum of 32 solenoid coils can be actuated.
- Terminal box (terminal strip): This valve terminal can be equipped with 1 ... 16 valve positions (with double solenoid valves), or with 1 ... 32 valve positions (with single solenoid valves).

AS-Interface connection

Valve terminals VTSA/VTSA-F with AS-Interface connection can be expanded with up to 8 valves with max. 8 solenoid coils.

A maximum of 32 solenoid coils can be actuated.

• Multi-pin node (round plug): electrical multi-pin plug connection with round plug, 19-pin to CNOMO E03.62.530.N, connecting thread M23 for 24 V DC. The valve terminal can be fitted with max. 16 solenoid coils.

The valves are switched by positive or negative logic (PNP or NPN). Mixed operation is not permissible because all control signals of the solenoid coils of a valve terminal share a common load. Each pin on the multi-pin plug (Sub-D) or terminal box (terminal strip) can actuate exactly one solenoid coil. If the maximum configurable number of valve positions is 32, this means that 32 valves can be addressed, each with a single solenoid coil.

With 16 or fewer valve positions, 2 solenoid coils per valve can be addressed.

Note

Use the following 37-pin connecting cables from Festo to connect the valve terminal VTSA/VTSA-F with Sub-D multi-pin plug connection:

- NEBV-...-LE10 for max. 8 solenoid coils
- NEBV-...-LE26 for max. 22 solenoid coils
- NEBV-...-LE27 for max. 23 solenoid coils
- NEBV-...-LE37 for max. 32 solenoid coils
- NECV-S1W37 pre-assembled plug connector

The valve terminal with AS-Interface connection is based on the same electrical links as the valve terminal with multi-pin plug connection.

This means a valve terminal with multi-pin plug connection can be converted using an AS-Interface module. The technical specifications of the AS-Interface system must be observed in this case.

AS-i module VAEM-S6-S-FAS-4-4E.

Note

Always operate the AS-i module with additional power supply if max. 4 solenoid coils (width 52 mm) are simultaneously supplied with current. More information can be found at: → Internet: as-interface

Fieldbus interface/control block

All functions and features of the electrical peripherals CPX are permitted in connection with the CPX interface. This means that:

- The valves and electrical outputs are supplied via the operating voltage connection CPX
- The valves are supplied and switched off independently via a separate connection on the CPX

Note

More information can be found at: → Internet: cpx

I-Port/IO-Link®

Valve terminals VTSA/VTSA-F with I-Port/IO-Link[®] connection can be expanded with up to 16 valves with max. 32 solenoid coils. The valve terminal with I-Port/IO-Link[®] connection is based on the same electrical interlinking as the valve terminal with multi-pin plug connection.

This means a valve terminal with multi-pin plug connection can be converted using an I-Port/IO-Link[®] module. The technical specifications of the I-Port/IO-Link[®] system must be observed in this case.

- Note

AS-i module VAEM-S6-S-FAS-4-4E. Always operate the AS-i module with additional power supply if max. 4 solenoid coils (width 52 mm) are simultaneously supplied with current. More information can be found at: → Internet: i-port, io-link

AP interface

VTSA/VTSA-F valve terminals with AP interface can be expanded with up to 12 valves with a maximum of 24 solenoid coils.

The valve terminal with AP interface is based on the same electrical linkage as the valve terminal with multi-pin plug connection. This means a valve terminal with multi-pin plug connection can be converted using an AP interface. The technical specifications of the AP interface must be observed in this case.

- Note

AS-i module VAEM-S6-S-FAS-4-4E. Always operate the AS-i module with additional power supply if max. 4 solenoid coils (width 52 mm) are simultaneously supplied with current. More information can be found at: → Internet: ap

Rules for addressing

Address allocation

Address allocation doesn't depend on whether single or double solenoid valves are fitted.

Addresses are assigned in ascending order without gaps, from left to right.

Single solenoid valve

A valve position for actuating one solenoid coil (VABV...T1) occupies one address.

Double solenoid valve

A valve position for actuating two solenoid coils (VABV...T2) occupies two addresses. The following allocation applies in this case:

- Coil 14: lower-value address
- Coil 12: higher-value address

Connecting cable

The wire colours refer to the following pre-assembled connecting cables from Festo:

- NEBV-...-LE10 for valve terminal with max. 8 solenoid coils
- NEBV-...-LE26 for valve terminal with max. 22 solenoid coils
- NEBV-...-LE27 for valve terminal with max. 23 solenoid coils
- NEBV-...-LE37 for valve terminal with max. 32 solenoid coils

Pin assignment – Multi-pin plug, Sub-D socket, electrical control code MP1

		,	Pin ²⁾	Address/coil	Wire colour 1)	Pin ²⁾	Address/coil	Wire colour ¹⁾
			1	0	WH	17	16	WH PK
		\	2	1	BN	18	17	PK BN
PIN 1 -		+ PIN 20	3	2	GN	19	18	WH BU
	000		4	3	YE	20	19	BN BU
	000		5	4	GY	21	20	WH RD
	000		6	5	РК	22	21	BN RD
			7	6	BU	23	22	GY GN
			8	7	RD	24	23	YE GY
	000		9	8	GY PK	25	24	PK GN
	000		10	9	RD BU	26	25	YE PK
	000		11	10	WH GN	27	26	GN BU
			12	11	BN GN	28	27	YE BU
	000		13	12	WH YE	29	28	GN RD
	000		14	13	YE BN	30	29	YE RD
PIN 19 -	° °	- PIN 37	15	14	WH GY	31	30	GN BK
)	16	15	GY BN	32	31	GY BU
			Conduct	or		·	•	·
- 🏺 - Note			33	0 V ³⁾	YE BK	35	0 V ³⁾	BN BK
The drawing shows a plan view of the Sub-D plug socket at the connecting cable NEBV			34	0 V ³⁾	WH BK	36	0 V ³⁾	ВК
			Earthing					
			37	FE	VT	-	-	-

1) To IEC 757

2) Pin 9 ... 35: not allocated in the case of connecting cable NEBV-...-LE10


Pin 23 ... 33: not allocated in the case of connecting cable NEBV-...-LE26

Pin 24 ... 33: not allocated in the case of connecting cable NEBV-...-LE27

3) Connect 0 V for positive-switching control signals, 24 V for negative-switching control signals. Mixed operation is not permissible because all control signals of the solenoid coils of a valve terminal share a common load!

Dimensions

Connecting cable NEBV-S1W37



Download CAD data \rightarrow <u>www.festo.com</u>

T

[1] Cable connector M20x1.5

 $\square \oplus$

Туре	B1	H1	H2	H3	L1	L2
NEBV-S1W37	54	41	36	11.6	142	27

Ordering data – Connecting cable, Sub-D, electrical control code MP1

	Cable sheath	Connecting cable	Length	Part no.	Туре
^	TPE-U(PUR)	For more Queslandid coile 10 mins	[m]	5202/0	
(* <	TPE-U(PUR)	For max. 8 solenoid coils, 10-wire	2.5	539240	NEBV-S1W37-E-2.5-LE10
			5	539241	NEBV-S1W37-E-5-LE10
			10	539242	NEBV-S1W37-E-10-LE10
	2	For max. 22 solenoid coils, 26-core	2.5	539243	NEBV-S1W37-E-2.5-LE26
\checkmark			5	539244	NEBV-S1W37-E-5-LE26
			10	539245	NEBV-S1W37-E-10-LE26
		For max. 32 solenoid coils, 37-core	2.5	539246	NEBV-S1W37-K-2.5-LE37
			5	539247	NEBV-S1W37-K-5-LE37
			10	539248	NEBV-S1W37-K-10-LE37
	PVC	For max. 8 solenoid coils, 10-wire	2.5	543271	NEBV-S1W37-KM-2.5-LE10
		For max. 23 solenoid coils, 27-core	5	543272	NEBV-S1W37-KM-5-LE10
			10	543273	NEBV-S1W37-KM-10-LE10
			2.5	543274	NEBV-S1W37-KM-2.5-LE27
			5	543275	NEBV-S1W37-KM-5-LE27
			10	543276	NEBV-S1W37-KM-10-LE27
		For max. 32 solenoid coils, 37-core	2.5	543277	NEBV-S1W37-KM-2.5-LE37
			5	543278	NEBV-S1W37-KM-5-LE37
			10	543279	NEBV-S1W37-KM-10-LE37

	Terminal	Coil/address	Terminal	Coil/address
ach solenoid coil is assigned to a specific terminal on the terminal strip order for the valves to be actuated.				
	1	0	17	16
	2	1	18	17
0 19	3	2	19	18
	4	3	20	19
$\mathbf{F}_{\mathbf{n}}$	5	4	21	20
	6	5	22	21
	7	6	23	22
	8	7	24	23
	9	8	25	24
	10	9	26	25
	11	10	27	26
0V ¹⁾ 20 31	12	11	28	27
	13	12	29	28
	14	13	30	29
	15	14	31	30
	16	15	32	31
🛔 - Note	Conductor			
e drawing shows a plan view of the multi-pin terminal strip (Cage	33	0 V	35	0 V
imp).	34	0 V	36	0 V

Pin assignment – Multi-pin, round plug; electrical control code MP4

$\langle \frown \rangle$	
$\begin{pmatrix} 4 + 4 + 4 + 5 + 4 + 8 \\ 4 + 4 + 4 + 4 + 5 + 4 + 6 + 8 \\ 3 + 4 + 4 + 4 + 7 + 9 \\ 2 + 4 + 4 + 4 + 6 + 7 + 10 \end{pmatrix}$	
┃ ₃ ⊥ ⁺ [*] ⊉ ⁺ [*] ⊥。┃┃	
$(_{2} + '_{2} + '_{3} + '_{10}))$	
\\	


Address	Pin ¹⁾	Address	Pin ¹⁾
0	15	8	17
1	7	9	9
2	5	10	2
3	4	11	13
4	16	12	11
5	8	13	10
6	3	14	1
7	14	15	18


Discontinuos ant Multi sin slus	, round plug; electrical actuation – CNOMO allocation
Pin assignment - Millitlenin nillg	r_{0}

	Pin	Valve position/sole- noid coil	Pin	Valve position/sole- noid coil
	1	8/14	10	7/12
\frown	2	6/14	11	7/14
	3	4/14	12	FE
110 120 10	4	2/12	13	6/12
	5	2/14	14	4/12
	6	0 V ¹⁾	15	1/14
	7	1/12	16	3/14
07 06 05	8	3/12	17	5/14
	9	5/12	18	8/12
			19	Not assigned

1) Pin 6: 0 V for positive-switching control signals; connect 24 V for negative-switching control signals; mixed operation is not permitted! Pin 12: earth 1

Electrical connection, individual valve with connector plug M12 up to width 52 mm







[1] Plug M12x1, 4-pin to EN 61076-2-101

With negative logic: Pin1 – Not allocated Pin2 – 0 V for coil 12 Pin3 – U_B for coil 12 and 14

Pin4 -0 V for coil 14

Electrical connection, individual valve terminal strip up to width 52 mm





Pin assignment for assembly by the					
ositive logic:					
 Not allocated 					
– U _B for coil 12					
– 0 V for coil 12 and 14					
– U _B for coil 14					

 With negative logic:


 Pin1
 – Not allocated

 Pin2
 – 0 V for coil 12

 Pin3
 – U_B for coil 12 and 14

 Pin4
 – 0 V for coil 14

Individual electrical connection, 6-way or 10-way, code MP2/MP3 for valve terminal up to width 52 mm



Pin as	Pin assignment M12					
With positive logic:						
Pin1	 Not allocated 					
Pin2	$-U_B$ for coil 12					
Pin3	– 0 V for coil 12 and 14					
Pin4	– U _B for coil 14					
Pin5	 Functional earth 					

Pin assignment M12 With negative logic: Pin1 – Not allocated Pin2 – 0 V for coil 12 Pin3 – U_B for coil 12 and 14 Pin4 – 0 V for coil 14 Pin5 – Functional earth

- Note

- Mixed operation of positive-switching (PNP) and negative-switching (NPN) control signals is not permissible because all control signals of the solenoid coils of a valve terminal share a common load.
- All M12 connections (MP2/MP3) within a valve terminal share a common load.

Instructions for use

Operating materials

Operate your system with unlubricated compressed air, if possible. Festo valves and cylinders are designed so that, if used as intended, they will not require additional lubrication and will still achieve a long service life. The quality of compressed air downstream of the compressor must correspond to that of unlubricated compressed air. If possible, do not operate the entire system with lubricated compressed air. The lubricators should, where possible, always be installed directly upstream of the actuator requiring them. Incorrect additional oil and too high an oil content in the compressed air reduce the service life of the valve terminal. Use Festo special oil OFSW-32 or the alternatives listed in the Festo catalogue (as specified in DIN 51524 HLP32; basic oil viscosity 32 CST at 40°C).

Bio-oils


When using bio-oils (oils which are based on synthetic or native esters, e.g. rapeseed oil methyl ester), the maximum residual oil content of 0.1 mg/m³ must not be exceeded (see ISO 8573-1:2010 Class 2).

Mineral oils

When using mineral oils (e.g. HLP oils to DIN 51524, parts 1 to 3) or similar oils based on poly-alpha-olefins (PAO), the maximum residual oil content of 5 mg/m³ must not be exceeded (see ISO 8573-1:2010 Class 4). A higher residual oil content is not permitted, regardless of the compressor oil, because the permanent lubrication would otherwise be flushed out over a period of time.

Datasheet – AP interface

Control signals from the controller to the valve terminal are transmitted via the AP bus protocol from Festo.



Application

The AP interface connects the VTSA valve terminal with up to 12 valves (24 valve coils) to a CPX-AP system.

Implementation

The AP interface is used for direct integration of the VTSA valve terminal into the decentralised IO system.

General technical data	
AP interface	
Connection position	On top
Reverse polarity protection	Yes
Number of pins/cores	4
Maximum number of valve positions	12
Max. no. of solenoid coils	24

Datasheet – AP interface

General data

Diagnostics via LED	Diagnostics per module
	Power supply load
Communication	Load switch-off
Diagnostics via internal communication	Electronics/sensors overvoltage
	Undervoltage load
Module parameters	Configuration of voltage monitoring load supply PL
	Response in error state

Technical data – Electrical components

Nominal operating voltage	[V AC]	110			
	[V DC]	24			
Nominal operating voltage for electrics/sensors	[V DC]	24			
Nominal operating voltage, load	[V DC]	24			
Permissible voltage fluctuations, electrics/sensors	[%]	± 25			
Permissible voltage fluctuations, load	[%]	± 10			
Intrinsic current consumption of electrics/sensors	[mA]	typ. 34 mA			
Intrinsic current consumption of load	[mA]	typ. 16 mA			
Max. power supply	[A]	2 x 4 A (external fuse required)			
Power failure buffering	[ms]	10			
Mains buffering of load	[ms]	3			
Fuse protection (short circuit)		Internal electronic fuse per channel			
Power supply					
Function		Incoming electronics/sensors and load			
Connection type		Plug			
Connection technology		M8x1, A-coded			
Number of pins/cores		4			
Voltage transmission					
Function		Outgoing electronics/sensors and load			
Connection type		Socket			
Connection technology		M8x1, A-coded			
Number of pins/cores		4			

Technical data – Mechanical components

· · · ·		
Product weight	[g]	712
Dimensions W x L x H	[mm]	71 x 142 x 84

Materials

Cover	Die-cast aluminium
Threaded sleeve	Nickel-plated brass
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B2-L

Datasheet – AP interface

Operating and environmental conditions

Operating and environmental conditions		
Ambient temperature	[°C]	+5 +50
Note on ambient temperature		Note ambient temperature derating to IEC 61131-2:2017
Storage temperature	[°C]	-20 +60
Relative humidity	[%]	5 95
		Non-condensing
Corrosion resistance class CRC ¹⁾		2
CE marking (see declaration of conformity) ²⁾		To EU EMC Directive
		To EU RoHS Directive
Certification		RCM
Degree of protection		IP65
Note on degree of protection		In mounted state
		Seal unused connections
Nominal operating altitude	[m]	≤ 2000 above sea level
Maximum cable length	[m]	50, system communication
Maximum setup altitude	[m]	3500
Note on the maximum setup altitude		> 2000 m ASL (< 79.5 kPa)
		Note ambient temperature derating to IEC 61131-2:2017

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.


2) More information www.festo.com/catalogue/... \rightarrow Support/Downloads.

Pin assignment			
	Pin	Assignment	Description
M8, D-coded, socket			
AP in (AP-COM)	1	TX-	AP bus, transmission signal positive
1	2	RX+	AP bus, receive signal positive
	3	TX+	AP bus, receive signal negative
$4 \bigcirc \bigcirc \bigcirc 2$	4	RX-	AP bus, transmission signal negative
AP out (AP-COM)	1	RX-	AP bus, transmission signal positive
	2	TX+	AP bus, receive signal positive
1	3	RX+	AP bus, receive signal negative
	4	TX-	AP bus, transmission signal negative
Power out (voltage transmission)	1	24 V PS	Supply voltage for electronics and sensors
_	2	0 V PL	Supply voltage for valves and outputs
4 2	3	0 V PS	Supply voltage for electronics and sensors
$3 \bigcirc 0 1$	4	24 V PL	Supply voltage for valves and outputs
M8, D-coded, plug			
Power In (power supply)	1	24 V PS	Supply voltage for electronics and sensors
	2	0 V PL	Supply voltage for valves and outputs
2 4	3	0 V PS	Supply voltage for electronics and sensors
$1 \left(\begin{array}{c} + & + \\ + & + \\ \end{array} \right) 3$	4	24 V PL	Supply voltage for valves and outputs


Download CAD data → <u>www.festo.com</u>


Datasheet – AP interface

Connection and display components



Dimensions





Туре	B1	B2	B3	B4	D1		D2	H1	H2
VABA-S6-1-AP	71.3	27.5	9.8	3	6.6		4.5	85.5	44.4
Туре	L1	L2	L3		_4	l	L5	L6	L7
VABA-S6-1-AP	142	121	105.2	2 8	5.7	60	6.2	46.7	10.5

 $\bigcirc \bigcirc$

Ordering data – AP inter	ace		
	Description	Part no.	Туре
0	AP interface for operation in an AP system	8152356	VABA-S6-1-AP

Valve terminals VTSA

Datasheet - Valve terminal

- **[]** - Valve width

to ISO 15407-2


- 18 mm
- 26 mm
- to ISO 5599-2
- 42 mm
- 52 mm

Y - Voltage 24 V DC

- N - Flow rate¹⁾ Width 18 mm: up to 550 (700) l/min Width 26 mm: up to 1100 (1350) l/min Width 42 mm: up to 1300 (1860) l/min Width 52 mm: up to 2900 l/min

Repair service

· **/**-



1) Flow rates in brackets apply to VTSA-F

General technical data for VTSA/VTSA-F

General technical data for VIS	4.1.0.1.1						
Terminal type VTSA/VTSA-F		VTSA is the standard version, VTSA-F is the version with optimised flow rate					
Valve sizes		Width 18 mm, 26 mm, 42 mm, 52 mm					
Actuation type		lectrical					
Electrical control		With multi-pin plug: multi-pin, IO-Link®					
		With fieldbus: integrated controller, fieldbus, Industrial Ethernet					
Pilot air supply		Internal/external					
Exhaust function, can be throttled		Via throttle plate					
Type of mounting		Wall mounting					
		n DIN rail to EN 60715					
Mounting position		ny					
Signal status indication		LED					
Manual override		Detenting, non-detenting, concealed					
Suitable for vacuum		Yes					
Valve terminal design		Modular, valve sizes can be mixed					
Max. no. of valve positions		32 ¹⁾					
Pneumatic connections – Threa	ded connec	tion					
Pneumatic connection		Via manifold sub-base					
Supply port	1	Dependent on the end plate or supply plate used (and adapter plate when using ISO size 3 valves)					
Exhaust port	3/5	Dependent on the end plate or supply plate used (and adapter plate when using ISO size 3 valves)					
Working ports	2/4	Dependent on the connection type selected					
External pilot air supply port	14	Dependent on the end plate used (and adapter plate when using ISO size 3 valves)					
Pilot exhaust air port	12	Dependent on the end plate used (and adapter plate when using ISO size 3 valves)					

1) Dependent on the electrical interface and the manifold sub-bases used


• I Note: This product conforms to ISO 1179-1 and ISO 228-1.

I

Datasheet – Valve terminal VTSA-F-CB




- 18 mm • 26 mm
- 42 mm to ISO 5599-2
- 52 mm
- Voltage



- 11 -

up to 700 l/min Width 26 mm: up to 1350 l/min Width 42 mm: up to 1860 l/min Width 52 mm: up to 2900 l/min



24 V DC



1) Flow rates apply to 5/2-way solenoid valve

General technical data for VTSA-F-CB

General technical data for									
Terminal type CPX/VTSA-F-Cl	В	Type 46							
Design		Piston spool valve							
Valve functions		5/2-way solenoid valve							
		• 5/3-way solenoid valve ¹⁾							
			• 2x 3/2-way solenoid valve						
			• 2x 2/2-way solenoid valve						
				haust valve, switchable pilot air					
Valve sizes, width	[mm]	18	26	42	52				
Grid dimension	[mm]	38	54	43	59				
Number of valves/plates		2	2	1	1				
To standard		-	-	-	Standardised				
Actuation type		Electrical							
Electrical control		Fieldbus: CPX							
Pilot air supply		Internal/external							
Exhaust function, can be thr	rottled	Via throttle plate							
Type of mounting		Wall mounting							
		On DIN rail to EN 60715 (not possible in combination with CPX-FVDA-P2 (safety module))							
Mounting position		Any							
Signal status indication		LED							
Manual override		Non-detenting/detenting; non-detenting/concealed; non-detenting-heavy duty/detenting with accessories; self-resetting via electrical con-							
		trol signal							
Suitable for vacuum		Yes							
Valve terminal design		Modular, valve sizes c	an be mixed						
Note on forced checking pro	ice-	Switching frequency n	nin. once a month						
dure									
Max. no. of valve positions		Max. 24 per voltage zo	one: max. 4 x 24 = 96						
Number of voltage zones		≤ 6	£6						
Pneumatic connection		Via manifold sub-base							
Supply port	1	Via right end plate (G1	/2 and G3/4) or supply plate o	r soft-start valve					
Exhaust port	3/5	Via right end plate (G1	/2 and G3/4) or supply plate o	r soft-start valve					
Pilot air connection 12		Optional: ducted							
Working ports	2/4	G1/8	G1/4	G3/8	G1/2				
Tubing size: small	[mm]	6	8	10	12				
Tubing size: large	[mm]	8	10	12	16				
Fittings		QS fittings, tubing din	nensions metric or imperial (hyb	orid)					

1) If neither solenoid coil is energised, the valve is moved to its mid-position by spring force. If both solenoid coils are energised at the same time, the valve remains in the previously assumed switching position

Standard nominal flow rate of valve/valve terminal [l/min]

Valve function (with valve code)	Terminal	Width 18 mm					Width 26 mm			
	code	Valve	Valve on va	Valve on valve terminal			Valve on va	lve terminal		
			VTSA	VTSA-F	VTSA-F-CB		VTSA	VTSA-F	VTSA-F-CB	
5/2-way double solenoid (B52)	J	750	550	700	700	1400	1100	1350	1350	
5/2-way double solenoid with dominant signal (D52)	D	750	550	700	700	1400	1100	1350	1350	
5/2-way single solenoid, pneumatic spring (M52A)	M	750	550	700	700	1400	1100	1350	1350	
5/2-way single solenoid, mechanical spring (M52M)	0	750	550	700	700	1400	1100	1350	1350	
5/3-way closed (P53C)	G	700	450	650	650	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	
5/3-way exhausted (P53E)	E	700 ¹⁾ 330 ²⁾	450 ¹⁾ 330 ²⁾	480 ¹⁾ 330 ²⁾	480 ¹⁾ 330 ²⁾	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	
5/3-way pressurised (P53U)	В	700 ¹⁾ 330 ²⁾	450 ¹⁾ 330 ²⁾	480 ¹⁾ 330 ²⁾	480 ¹⁾ 330 ²⁾	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	
5/3-way, exhausted, switching position 14 detenting (P53ED) ³⁾	SA	-	380 ¹⁾ 310 ²⁾	430 ¹⁾ 360 ²⁾	430 ¹⁾ 360 ²⁾	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	
5/3-way, exhausted, switching position 12 detenting (P53EP) ³⁾	SE	-	380 ¹⁾ 300 ²⁾	460 ¹⁾ 350 ²⁾	460 ¹⁾ 350 ²⁾	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD) ³⁾	SB	-	380 ¹⁾ 350 ²⁾	440 ¹⁾ 400 ²⁾	440 ¹⁾ 400 ²⁾	700 ¹⁾ 700 ²⁾	700 ¹⁾ 700 ²⁾	700 ¹⁾ 700 ²⁾	700 ¹⁾ 700 ²⁾	
5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD) ³⁾	SD	-	370 ¹⁾ 340 ²⁾	430 ¹⁾ 360 ²⁾	430 ¹⁾ 360 ²⁾	-	850 ¹⁾ 820 ²⁾	950 ¹⁾ 860 ²⁾	950 ¹⁾ 860 ²⁾	
2x3/2-way single solenoid, closed (T32C)	К	600	400	550	550	1250	900	1150	1150	
2x3/2-way single solenoid, open (T32U)	N	600	400	550	550	1250	900	1150	1150	
2x3/2-way single solenoid, open/closed (T32H)	Н	600	400	550	550	1250	900	1150	1150	
2x3/2-way single solenoid, closed (T32N)	Q	600	400	550	550	1250	900	1150	1150	
2x3/2-way single solenoid, open (T32F)	Р	600	400	550	550	1250	900	1150	1150	
2x3/2-way single solenoid, open/closed (T32W)	R	600	400	550	550	1250	900	1150	1150	
2x2/2-way single solenoid, closed (T22C)	VC	700	500	650	650	1350	1000	1300	1300	
2x2/2-way single solenoid, closed (T22CV)	VV	700	500	650	650	1350	1000	1300	1300	

1) Switching position

Mid-position
 The valve functions P53ED, P53EP, P53AD and P53BD are only available in the 24 V DC version. Values only apply to 24 V DC.


Datasheet – Valve terminal

Standard nominal flow rate of valve/valve terminal [l/min]

Valve function (with valve code)	Terminal	Width 42 mm				Width 52 mm			
	code	Valve	Valve on valve terminal			Valve	Valve on valve terminal		
			VTSA	VTSA-F	VTSA-F-CB		VTSA	VTSA-F	VTSA-F-CB
5/2-way double solenoid (B52)	J	2000	1300	1860	1860	4000	2900	2900	2900
5/2-way double solenoid with dominant signal (D52)	D	2000	1300	1860	1860	4000	2900	2900	2900
5/2-way single solenoid, pneumatic spring (M52A)	M	2000	1300	1860	1860	4000	2900	2900	2900
5/2-way single solenoid, mechanical spring (M52M)	0	2000	1300	1860	1860	4000	2900	2900	2900
5/3-way closed (P53C)	G	1900 ¹⁾	1200 ¹⁾	1690 ¹⁾	1690 ¹⁾	3600 ¹⁾	28001)	28001)	28001)
		950 ²⁾	800 ²⁾	830 ²⁾	830 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾
5/3-way exhausted (P53E)	E	1900 ¹⁾	1200 ¹⁾	1690 ¹⁾	1690 ¹⁾	3600 ¹⁾	2800 ¹⁾	2800 ¹⁾	2800 ¹⁾
		950 ²⁾	800 ²⁾	830 ²⁾	830 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾
5/3-way pressurised (P53U)	В	1900 ¹⁾	1200 ¹⁾	1690 ¹⁾	1690 ¹⁾	3600 ¹⁾	28001)	2800 ¹⁾	2800 ¹⁾
		950 ²⁾	800 ²⁾	830 ²⁾	830 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F) ³⁾	VG	1700 ¹⁾	1400 ¹⁾	1700 ¹⁾	1700 ¹⁾	3000 ¹⁾	2300 ¹⁾	2300 ¹⁾	2300 ¹⁾
		700 ²⁾	800 ²⁾	700 ²⁾	700 ²⁾	900 ²⁾	900 ²⁾	900 ²⁾	900 ²⁾
2x3/2-way single solenoid, closed (T32C)	К	1600	1200	1300	1300	3000	2400	2400	2400
2x3/2-way single solenoid, open (T32U)	N	1600	1200	1300	1300	3000	2400	2400	2400
2x3/2-way single solenoid, open/closed (T32H)	Н	1600	1200	1300	1300	3000	2400	2400	2400
2x3/2-way single solenoid, closed (T32N)	Q	1600	1200	1300	1300	3000	2400	2400	2400
2x3/2-way single solenoid, open (T32F)	Р	1600	1200	1300	1300	3000	2400	2400	2400
2x3/2-way single solenoid, open/closed (T32W)	R	1600	1200	1300	1300	3000	2400	2400	2400
2x2/2-way single solenoid, closed (T22C)	VC	1600	1400	1500	1500	4000	2800	2800	2800
2x2/2-way single solenoid, closed (T22CV)	VV	1600	1400	1500	1500	-	-	-	-


1) Switching position

Mid-position
 The valve function P53F is only available in the 24 V DC version. Values only apply to 24 V DC.




→Internet: www.festo.com/catalogue/...





Width 42 mm

Width 52 mm



Flow rate qn as a function of output pressure p2 with pressure regulator plates (AB regulator plates, rev.) for ports 4/2, reversible 10 bar 6 bar

Width 42 mm


0

qn [l/min]


Width 52 mm

qn [l/min]

Flow rate qn as a function of flow control




------ Width 18 mm



Width 42 mm

- Flow control screw from $2 \rightarrow 3$
- **- .. - ..** Flow control screw from $4 \rightarrow 5$

n = revolutions of the adjusting screw




Width 52 mm


Flow control screw from $2 \rightarrow 3$


••• Flow control screw from $4 \rightarrow 5$

n = revolutions of the adjusting screw

Pilot pressure p12/14 as a function of operating pressure p1








p1 [bar]

[1] Operating range for valves with external pilot air supply



Standard nominal flow rate with vertical stacking [l/min]

Standard nominal flow rate with vertical stacking [l/min]												
Widths	18 mm	26 mm	42 mm	52 mm								
Throttle plate												
VABF-S4-2-F1B1-C	See characteristic curve	-	-	-								
VABF-S4-1-F1B1-C	-	See characteristic curve	-	-								
VABF-S2-1-F1B1-C	-	-	1100	-								
VABF-S2-2-F1B1-C	-	-	-	See characteristic curve								
Vertical supply plate												
VABF-S4-2-P1AG18	430	-	-	-								
VABF-S4-1-P1AG14	-	900	-	-								
VABF-S2-1-P1AG38	-	-	1300	-								
VABF-S2-2-P1AG12	-	-	-	2800								
Vertical pressure shut-off plate												
VABF-S4-2-L1D1-C	400	-	-	-								
VABF-S4-2-L1D2-C ¹⁾	320	-	-	-								
VABF-S4-1-L1D1-C	-	800	-	-								
VABF-S4-1-L1D2-C ¹⁾	-	620	-	-								
VABF-S2-1-L1D1-C	-	-	1200	-								
VABF-S2-2-L1D1-C	-	-	-	1950								

1) Lockable with key

T

Datasheet – Valve terminal

Operating and environmental conditions

Type		VTSA/VTSA-F	VTSA-F-CB				
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	Compressed air to ISO 8573-1:2010 [7:4:4]				
Notes on operating/pilot medium		Lubricated operation possible (in which case lubricated opera- tion will always be required)	Lubricated operation not possible				
External	[bar]	-0.9 +10	-0.9 +10				
	[MPa]	-0.09 +1	-0.09 +1				
Internal	[bar]	310	310				
	[MPa]	0.3 1	0.3 1				
Pilot pressure	[bar]	3 10	310				
	[MPa]	0.3 1	-				
Noise level LpA	[dB(A)]	85	-				
Ambient temperature	[°C]	-5 +50	-5 +50				
Temperature of medium	[°C]	-5 +50	-				
Storage temperature	[°C]	-20 +60	-20 +60				
Relative humidity	[%]	0 90	090				
Certification		BIA	-				
		C-Tick	-				
		c UL us – Recognized (OL)	c UL us – Recognized (OL)				
Certificate-issuing authority		-	UL E322346				
CE marking (see declaration of confor	mity)	To EU Low Voltage Directive (only for VTSA-MP)	-				
		To EU EMC Directive 1)	To EU EMC Directive ¹⁾				
		To EU Explosion Protection Directive (ATEX, EX1E ³⁾)	-				
KC marking		KC EMC	KC EMC				
ATEX category for gas		II 3G (EX1E ³⁾)	-				
Type of (ignition) protection for gas		Ex ec IIC T3 Gc X (EX1E ³⁾)	-				
Explosion-proof ambient temperature	e [°C]	-5 +50 (EX1E ³⁾)	-				
Corrosion resistance class CRC ⁴⁾		0	0				
Corrosion resistance class CRC for IO-	Link ^{®4)}	2	-				

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

2) Solenoid valves with code VC (2/2-way type ... T22C), N (3/2-way type ... T32U), K (3/2-way type ... T32C), H (3/2-way type ..

3) Certification is valid for VTSA/VTSA-F-MP, VTSA/VTSA-F-FB

4) More information www.festo.com/x/topic/crc

Electrical data – Individual electrical connection

Load voltage supply for valves (U _{val})		
Operating voltage	[V DC]	24 ±10%
Max. total current at 24 V DC	[A]	10
Duty cycle		100%
Degree of protection		IP65, NEMA 4 (for all types of signal transmission when mounted)

Electrical data – Multi-pin plug connection

Load voltage supply for valves (U _{val})										
Operating voltage	[V DC]	24 ±10%								
Max. total current	[A]	6								
Current rating at 40 °C	[A]	1								
Surge resistance	[kV]	1.5								
Pollution degree		3								
Duty cycle		100%								
Degree of protection		IP65, NEMA 4 (for all types of signal transmission when mounted)								

Electrical data – With CPX terminal										
Power supply for electronics (U _{EL/SEN})										
Operating voltage	[V DC]	24 ±10%								
Max. intrinsic current consumption at	[mA]	20								
24 V DC										
Duty cycle	_	100%								
Load voltage supply for valves (U _{val})										
Operating voltage	[V DC]	24 ±10%								
Diagnostic message undervoltage U _{OFF} ,	[V]	21.6 21.5								
load voltage outside the functional range										
Degree of protection		IP65, NEMA 4 (for all types of signal transmission when mounted)								

Materials Manifold sub-base Die-cast aluminium Die-cast aluminium, PA Valve FPM, NBR, HNBR Seals Supply plate, supply plate cover Die-cast aluminium Die-cast aluminium Right end plate Pneumatic interface for CPX Die-cast aluminium Throttle plate Die-cast aluminium Pressure regulator plate Die-cast aluminium, PA Multi-pin manifold block Die-cast aluminium IO-Link[®] interface Die-cast aluminium, PA Cover for the pneumatic interface and multi-pin plug PA connection Note on materials RoHS-compliant LABS (PWIS) conformity (exclusively for IO-Link®) VDMA24364-B2-L

i.

Product weight				
	Width			
	[g] 18 mm	26 mm	42 mm	52 mm
Multi-pin node with Sub-D or terminal strip for VTSA/VTSA-F ¹⁾	550			
Multi-pin node with M12 individual connection for VTSA/VTSA-F	760			
Pneumatic interface CPX for VTSA/VTSA-F				
 With diagnostics for undervoltage of valves (VABA-S6-1-X1/X2/X2-D) 	590			
Pneumatic interface CPX for VTSA-F-CB				
 With 3x load supplies (VABA-S6-1-X1/X2-3V-CB) 	580			
 For PROFIsafe, with diagnostics for undervoltage, short circuit of valves, wire break per solenoid coil (VABA-S6-1-X2-F1/F2-CB) 	734			
 With diagnostics for undervoltage, short circuit of valves, wire break per solenoid coil (VABA-S6-1-X1/X2-CB) 	560			
IO-Link [®] interface	690			
Electrical interface for AS-Interface for VTSA/VTSA-F	300			
AS-Interface module for VTSA/VTSA-F	850			
Supply plate for valve terminal VTSA/VTSA-F ²⁾				
• Exhaust plate with 3 and 5 common	617			
• Exhaust air cover with 3 and 5 separate	597			
Supply plate/extension module for VTSA-F-CB ²				
• Exhaust plate with 3 and 5 common	611			
• Exhaust air cover with 3 and 5 separate	600			
Right end plate ³⁾				
With threaded connections	339			336
Selector switch	281			_
Manifold sub-base for VTSA/VTSA-F ⁴⁾	447	634	340, 330 ⁵⁾	610
Manifold sub-base for VTSA-F-CB ⁴⁾	434	579	330	610
Hybrid manifold sub-base for VTSA/VTSA-F ⁴⁾	512	512	-	-
Angled connection plate ³⁾	170	230	176	359
Pressure regulator plate				
• For port 1 (P)	350	402	640	1190
• For port 4 or 2 (A or B)	367	448	640	1230
• For ports 4 and 2 (A/B)	611	692	920	1990
Throttle plate	228	320	220	565
Vertical supply plate ³⁾	140	191	340	605
Vertical pressure shut-off plate	209	273	600	1030
Vertical pressure shut-off plate (lockable with key)	231	290	-	-
Valves	→ Solenoid valv	es, widths	1	1
Cover plate	34	73	68	146


1) With sheet metal seal, printed circuit board

With sheet metal seal and electrical link
 With screws

4) 4) With sheet metal seal, electrical interlinking module, inscription label holder, 4 screws

5) Manifold sub-base optimised for flow rate, HS

Download CAD data → <u>www.festo.com</u>



[mm]	150.5	142	12	21	57 4	6 3	3 18	48	26	2	24 21	.3 1	2 2	9.6	23	19.6	19.5	19	10.5	6.6	4.5
Dim.	L2	L3	L	4	L5	L6	L7	L8	L9		L10	L11	L12	L13	L14	L1	5 L'	16	L17	L18	L19
[mm]	92.4	71.3	n2>	x59	n01x54	54	n1x43	43	43.5	5 n(02x38	nx38	38	37.3	24	20	5 2	20 2	14.1	9.8	6.3
Dim.	L20	L21	L22	D1ø	D2Ø	H1	H2	H3	H4	H5	H6	H7	H8	H9	H10	H11	H12	H13	H14	H15	H16
[mm]	5.5	3	2	18.5	4.5	125	121.3	118.2	118	103	107.8	90.3	87	65	44	25.7	24.5	12	6	3.5	0.5

Width	11
18 mm	71.3 + n02 x 38 + n x 38 + 37.3
26 mm	71.3 + n01 x 54 + n x 38 + 37.3
42 mm	71.3 + n1 x 43 + n x 38 + 37.3
52 mm	71.3 + n2 x 59 + n x 38 + 37.3
Mix 18 mm, 26 mm, 42 mm, hybrid manifold sub-base 46 mm and 52 mm	71.3 + n02 x 38 + n01 x 54 + n1 x 43 + nh x 46 + n2x59 + n x 38 + 37.3


• Note: This product conforms to ISO 1179-1 and ISO 228-1.

B20

Dimensions

Download CAD data → www.festo.com


Valve terminal with multi-pin plug connection:



18 mm	71.3 + n02 x 38 + n x 38 + 37.3
26 mm	71.3 + n01 x 54 + n x 38 + 37.3
42 mm	71.3 + n1 x 43 + n x 38 + 37.3
52 mm	71.3 + n2 x 59 + n x 38 + 37.3
Mix 18 mm, 26 mm, 42 mm, hybrid manifold sub-base 46 mm and 52 mm	71.3 + n02 x 38 + n01 x 54 + n1 x 43 + nh x 46 + n2 x 59 + n x 38 + 37.3


I Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions



Туре	H1	H2	H3	D1ø	L1	L2	L3	L4	L5	B1
VABE-S6-1LF-C-M1-C	106.1	65	44	4.5	142	121	27	10.5	6.6	9.8
VABE-S6-1LF-C-M1-R	101	65	44	4.5	142	121	25	10.5	6.6	9.8





2025/03 – Subject to change


Number of manifold sub-bases

5)

Dimensions

Valve terminal with AS-Interface connection

Download CAD data → <u>www.festo.com</u>



59

38 + 54 + 43 + 59

108.6 + n2 * 59 + nZWP * 38 + nDA * 43

108.6 + n02 * 38 + n01 * 54 + n1 * 43 + nZWP * 38 + n2 * 59 + nDA * 43

2

mix 02 + 01 + 1 + 2


Valve terminals VTSA

Download CAD data → www.festo.com

Datasheet - Valve terminal

Dimensions

Valve terminal with fieldbus interface




• Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions

Valve terminal VTSA-F-CB with fieldbus interface

Download CAD data → <u>www.festo.com</u>



- [1] Threaded connection 1/2
- [2] Threaded connection 1/4
- [3] Threaded connection 1/8
- [4] Pressure gauge, freely positionable
- [5] Manual override
- [6] Mounting holes
- [7] Inscription label
- [8] Inscription label
- [9] DIN rail mounting
- [10] Electrical connection to
- DIN EN 175301-803, type C
- [11] Proximity switch M12x1

[12]	Plug socket M12x1	

- [13] Additional mounting
- [14] Pneumatic interface CPX

n02 Number of manifold subbases ISO 02

- n01 Number of manifold subbases ISO 01
- n1 Number of manifold subbases ISO 1
- n2 Number of manifold subbases ISO 2
- nZWP Number of intermediate feed plates
- nDA Number of soft-start valves

m

Number of CPX modules

Dim.	B1	B2	B4	B5	B6	B7	B8	B9	B10	B1	1	B12	B13	B14	B15	B16	B17	B 1 8	B19	B20
[mm]	108.1	78	150.5	108.1	21.6	29.4	57	12	18	66		33	48	26	65	19.3	66.3	7.9	142.6	121
Dim.	D4	H1	H2	H3	H4	H5	Н6	H7	н	з н	9	H10	H11	H12	H13	H14	H15	H16	H17	H18
[mm]	6.6	195.2	103.3	133.4	128.7	125	106.		_	_	_	118.8	65	0.4	24.4	12	29.3	3.5	53.8	24.5
Dim.	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11	L1:	3 L15	L16	L17	L18	L19	L20	L21	L22
[mm]	557	93.2	80.3	59	38	43	54	38.6	37.3	20.5	19	1.5	5 36	25.9	1	30.4	23.7	mx50.1	22.3	50.1

ISO size	Sub-base width	Overall length
02 + ZWP	38	117.7 + n02 * 38 + nZWP * 38 + nDA * 43
01	54	117.7 + n01 * 54 + nZWP * 38 + nDA * 43
1 + DA	43	117.7 + n1 * 43 + nZWP * 38 + nDA * 43
2	59	117.7 + n2 * 59 + nZWP * 38 + nDA * 43
mix 02 + 01 + 1 + 2	38 + 54 + 43 + 59	117.7 + n02 * 38 + n01 * 54 + n1 * 43 + nZWP * 38 + n2 * 59 + nDA * 43


Download CAD data → <u>www.festo.com</u>

Datasheet - Valve terminal


Dimensions

Vertical stacking components, width 18 mm L1 on p 1 3 £۲ 13 [1] Solenoid valve with two sole-L4 4 ΨĽ 6) Ŧ noid coils, width 18 mm Throttle plate [3] L6 5 £ [4] Vertical pressure shut-off plate lockable (code ZT), optionally 6 £ lockable with key (code ZS) ž 7 [5] Vertical supply plate Ŷ Manifold sub-base [6] H L5 [7] Angled connection plate Dim. L5 H3 L1 L2 L3 L4 L3 L4 L6 Η1 H4 H5 H6 H7 (Code ZT) (Code ZT) (Code ZS) (Code ZS) [mm] 133.8 130 184.1 222.3 198.3 46 142 224 65 64 35 19 3.5 _


Vertical stacking components, width 18 mm




Vertical stacking components, width 18 mm, with the pressure regulator plate also suitable for valves with symmetrical design




- [1] Solenoid valve with two solenoid coils, width 18 mm
- [2] Pressure regulator plate
- [3] Throttle plate
- [6] Manifold sub-base
- [7] Angled connection plate
- [8] Pressure gauge, freely positionable



Vertical stacking components, width 26 mm



Vertical stacking components, width 26 mm, with the pressure regulator plate also suitable for valves with symmetrical design



Dimensions

Dim. [mm]

Vertical stacking components, width 42 mm

Download CAD data → <u>www.festo.com</u>

[1] Solenoid valve


[3]

[4] [5]


Throttle plate


Vertical supply plate

Vertical pressure shut-off plate



<u>} </u>			L2								-	l sub-base onnection pl	late	
	L1	L2	L3	L4	L5	L6	H1	H3	H4	H5	H6	H7	H8	ĺ
าไ	137.8	142	105.3	173.8	46	117.6	236	65	64	45.3	25.7	35	28	l





- 📲 - Note

• Pressure regulator plates for symmetrical valves with widths of 42 mm and 52 mm can only be ordered via the pressure regulator configurator VABF-S2.

The following can be selected using the pressure regulator configurator VABF-S2:

- Rotary knob, short version with locking element (standard)
- Rotary knob, long version with locking element
- Rotary knob with integrated lock

→ Internet: vabf-s2

Dimensions


Vertical stacking components, width 52 mm

L1 ட 1 З ۳. ۳ L3 L4 띺 4 Ŧ .6 Ψ 5 6 Ψ Ŧ ¥ 7 L5 L2

Download CAD data → <u>www.festo.com</u>

- [1] Solenoid valve[3] Throttle plate[4] Vertical pressure shut-off plate
- [5] Vertical supply plate
- [6] Manifold sub-base
- [7] Angled connection plate

Dim.	L1	L2	L3	L4	L5	L6	H1	H3	H4	H5	H6	H8
[mm]	160.7	142	131	191.2	46	136	287.4	65	63.5	58.7	21.2	45




- - Note


- Pressure regulator plates for symmetrical valves with widths of 42 mm and 52 mm can only be ordered via the pressure regulator configurator VABF-S2.
- → Internet: vabf-s2

The following can be selected using the pressure regulator configurator VABF-S2:

- Rotary knob, short version with locking element (standard)
- Rotary knob, long version with locking element
- Rotary knob with integrated lock




Right end plate, VABE-S6-1R...



[1] Blanking plug

Right end plate, VABE-S6-2R...



[1] Blanking plug


Туре	L1	L2	L3	L4	L5	L6	L7	L8	L9	D1	D2	H1	H2	H3	H4	H5	H6	B1	B2	B3	B4	With ¹⁾
VABE-S6-1R-G12	142	121	66	57	18	22	12	10.5	6.6	G1/2	G1/4	65	12 5	24 E	12	6		27.2	22	63	2	[1]
VABE-S6-1RZ-G12	142	121	66	57	10	22	12	10.5	6.6	01/2	01/4	65	12.5	24.5	12	0	_	57.5	22	0.5	2	-
VABE-S6-2R-G34	142	101	49.9	74.6	36.9	21.2	17.0	10.5	6.6	G3/4	G1/4	45	125	1 2	2.2	24.5	11	37.3	24.5	63	2	[1]
VABE-S6-2RZ-G34	142	121	49.9	74.0	50.9	21.2	17.2	10.5	6.6	05/4	01/4	65	12.5	2.5	2.2	24.5	11	57.5	24.5	6.3)	-

 With blanking plug = internal pilot air supply, - without blanking plug = external pilot air supply Special feature: There is no port 14 for VABE-S6-1R-G12 (code V).

+ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions

Right end plate with pilot air selector, VABE-S6-1RZ-G-B1




VABE-S6-1RZ-G-B1 142 121 41.3 10.5 6.6 G1/4 37 65.4 12.5 23	33	33	21	37.3	20	6.3	3	12	10.5


• Note: This product conforms to ISO 1179-1 and ISO 228-1.

Download CAD data → <u>www.festo.com</u>

Datasheet - Solenoid valves VSVA



- N - Flow rate¹⁾ Width 18 mm: up to 550 (700) l/min Width 26 mm: up to 1100 (1350) l/min Width 42 mm: up to 1300 (1860) l/min Width 52 mm up to 2900 l/min



1) Flow rates in brackets apply to VTSA-F and VTSA-F-CB

General technical data for solenoid valves

	Piston spool valve
	Soft
	Positive overlap (excluding types P53AD, P53BD)
	Negative overlap (types P53AD, P53BD)
	Mechanical or pneumatic, depending on the type used
	Electrical
	Plug to ISO 15407-2, 2-pin (single solenoid types) or 4-pin (double solenoid and 5/3-way types)
	Piloted
	IP65, NEMA 4 (for all types of signal transmission when mounted)
d	Via individual sub-base, via throttle plate (not with valve type T22)
	On manifold sub-base, on individual sub-base
	Any
	Detenting, non-detenting, concealed
	LED (except types with signal status display sensor, and part nos.: 560727 and 560728)
	Yellow LED
[%]	100
	3
[kV]	2.5
[V DC]	24 (dependent on valve type)
[%]	±10
1	Via the manifold sub-base of the valve terminal or via individual sub-base
3/5	
2/4	
1 2/14	
8 2/84	Either ducted or unducted
	[%] [kV] [V DC] [%] 1 3/5 2/4 1 2/14

Datasheet - Solenoid valves

Pneumatic characteristic data

Terminal code	VC	W	Ν	К	Н	Р	Q	R	Μ	0
Valve code	T22C	T22CV	T32U	T32C	T32H	T32F	T32N	T32W	M52-A	M52-M
Flow direction										
Any	-	•	-	-	-	-	-	-	•	•
Reversible only	-	-	-	-	-	•		•	-	-
Not reversible		-				-	-	-	-	-
Reset method										
Pneumatic spring		•	•					•	-	-
Mechanical spring	-	-	-	-	-	-	-	-	-	•
Pneumatic character	ristic data	1-		1-		1	1			l
Pneumatic character Terminal code	J	D	В	G	E	SA	SB	SD	SE	VG
Pneumatic character Terminal code	ristic data J B52	D D52	B P53U	G P53C	E P53E	SA P53ED	SB P53AD	SD P53BD		VG P53F
Pneumatic character Terminal code Valve code	J									-
Pneumatic character Terminal code Valve code Flow direction	J				P53E		P53AD	P53BD	P53EP	-
Pneumatic character Terminal code Valve code Flow direction Any	J B52	D52	P53U	P53C	P53E	P53ED	P53AD	P53BD	P53EP	P53F
Pneumatic character Terminal code Valve code Flow direction Any Reversible only	J B52	D52	P53U	P53C	P53E	P53ED	P53AD	P53BD	P53EP	P53F
Pneumatic character Terminal code Valve code Flow direction Any Reversible only Not reversible	J B52	D52	P53U	P53C	P53E	P53ED	P53AD	P53BD	P53EP	P53F
	J B52	D52	P53U	P53C	P53E	P53ED	P53AD	P53BD	P53EP	P53F

Flow direction of solenoid valves

Solenoid valves only with reversible flow direction

- These valves must only be operated on pressure zones with reversible supply (3 and 5 with supply pressure 1 as exhaust air) or on a reversible pressure regulator. If necessary, create separate pressure zones with duct separation.
- Reversible 3/2-way solenoid valves do not permit the special function "ducted pilot exhaust air"
- Ports 12 and 14 on the end plate variants must be supplied with the same pressure.
- Right end plate with pilot air selector: can be realised via position 1 or 2
- Right end plate with threaded connections: 12 and 14 must be supplied with the same pressure level

Solenoid valves with any flow direction

- Valves with any flow direction such as the 5/2-way solenoid valve, code M, are suitable for vacuum operation (standard valves such as the 2x 2/2-way solenoid valve with code VC must not be used for vacuum operation).
- An exception is the 2x 2/2-way solenoid valve with code VV (T22CV), which only allows vacuum operation at ports 3 and 5. The solenoid valve with code VV (T22CV) cannot be combined with other valve functions; a separate pressure zone is required.

Т

Datasheet – Solenoid valves

Operating and environmental conditions

Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium			Compressed air to ISO 8573-1:2010 [7:4:4]				
Notes on operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure, pilot air sup-		[bar]	-0.9 +10 (valves with any flow direction and reversible valves)				
ply ¹⁾			3 10 (non-reversible valves)				
		[MPa]	-0.09 +1 (valves with any flow direction and reversible valves)				
			0.3 1 (non-reversible valves)				
Pilot pressure		[bar]	310				
		[MPa]	0.3 1				
Pilot air supply			External				
			Internal via valve terminal				
Ambient temperature		[°C]	-5 +50				
Relative humidity		[%]	090				
Certification			BIA (for characteristic SP and/or SN only)				
	Direct voltage 24 V		C-Tick (only size 52 mm and solenoid valves with sensor (position sensing))				
			c UL us – Recognized (OL)				

1) Solenoid valves with code VC (2/2-way type ... T22C), N (3/2-way type ... T32U), K (3/2-way type ... T32C), H (3/2-way type ..

Valve terminals VTSA

Datasheet - Solenoid valve width 18 mm

- **[]** - Valve width to ISO 15407-2 18 mm

> Voltage 24 V DC

- N - Flow rate

Valve width 18 mm: VTSA up to 550 l/min VTSA-F up to 700 l/min VTSA-F-CB up to 700 l/min



Safety characteristics for valve

Conforms to standard	EN 13849-1/2				
Shock resistance	Shock test with severity level 2, to EN 60068-2-27				
Vibration resistant	Transport application test with severity level 2, to EN 60068-2-6				

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Safety characteristics for valve

Valve function (with valve code)	Terminal	Test pulses					
	code	Max. positive test pulse with logic 0 [µs]	Max. negative test pulse with logic 1 [µs]				
5/2-way double solenoid (B52)	J	1500	800				
5/2-way double solenoid with dominant signal (D52)	D	1700	1200				
5/2-way single solenoid (M52A)	М	1500	800				
5/2-way single solenoid (M52M)	0	1500	800				
5/3-way closed (P53C)	G	1500	800				
5/3-way exhausted (P53E)	E	1500	800				
5/3-way pressurised (P53U)	В	1500	800				
5/3-way exhausted, switching position 14 detenting (P53ED)	SA	1500	800				
5/3-way exhausted, switching position 12 detenting (P53EP)	SE	1500	800				
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD)	SB	1500	800				
5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD)	SD	1500	800				
2x3/2-way single solenoid, closed (T32C)	К	1700	1200				
2x3/2-way single solenoid, open (T32U)	N	1700	1200				
2x3/2-way single solenoid, open/closed (T32H)	Н	1700	1200				
2x3/2-way single solenoid, closed (T32N)	Q	1700	1200				
2x3/2-way single solenoid, open (T32F)	Р	1700	1200				
2x3/2-way single solenoid, open/closed (T32W)	R	1700	1200				
2x2/2-way single solenoid, closed (T22C)	VC	1700	1200				
2x2/2-way single solenoid, closed (T22CV)	VV	1700	1200				

1

Datasheet - Solenoid valve width 18 mm

Datasheet for valve

Valve function (with valve code)	Terminal	Flow directio	n		Reset method	Weight	
	code	Any	Reversible only	Not reversible	Pneumatic spring	Mechanical spring	[g]
5/2-way double solenoid (B52)	J		-	-	-	-	172
5/2-way double solenoid with dominant signal (D52)	D		-	-	-	-	172
5/2-way single solenoid (M52A)	М		-	-		-	163
5/2-way single solenoid (M52M)	0		-	-	-		163
5/3-way closed ¹⁾ (P53C)	G		-	-	-		191
5/3-way exhausted ¹⁾ (P53E)	E		-	-	-		191
5/3-way pressurised ¹⁾ (P53U)	В		-	-	-		191
5/3-way exhausted, switching position 14 detenting (P53ED)	SA	-	-		-		170
5/3-way exhausted, switching position 12 detenting (P53EP)	SE	-	-		-		170
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD)	SB	•	-	-	-	•	172
5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD)	SD	-	-		-	•	172
2x3/2-way single solenoid, closed (T32C)	К	-	-	•	•	-	190
2x3/2-way single solenoid, open (T32U)	N	-	-		•	-	190
2x3/2-way single solenoid, open/closed (T32H)	Н	-	-	•	•	-	190
2x3/2-way single solenoid, closed (T32N)	Q	-	•	-	•	-	190
2x3/2-way single solenoid, open (T32F)	Р	-	•	-	•	-	190
2x3/2-way single solenoid, open/closed (T32W)	R	-	•	-	•	-	190
2x2/2-way single solenoid, closed (T22C)	VC	-	-	•	•	-	190
2x2/2-way single solenoid, closed (T22CV)	VV	•	-	-	•	-	190

1) If neither solenoid coil is energised, the valve is moved to its mid-position by spring force.

If both solenoid coils are energised at the same time, the valve remains in the previously assumed switching position.

Datasheet - Solenoid valve width 18 mm

Standard nominal flow rate of valve/valve terminal [l/min]

Valve function (with valve code)	Terminal						
	code	Valve	Valve on valve	Valve on valve terminal			
			VTSA	VTSA-F	VTSA-F-CB	sub-base	
5/2-way double solenoid (B52)	J	750	550	700	700	600	
5/2-way double solenoid with dominant signal (D52)	D	750	550	700	700	600	
5/2-way single solenoid (M52A)	М	750	550	700	700	600	
5/2-way single solenoid (M52M)	0	750	550	700	700	600	
5/3-way closed (P53C)	G	700	450	650	650	550	
5/3-way exhausted (P53E)	E	700 ¹⁾ 330 ²⁾	450 ¹⁾ 330 ²⁾	480 ¹⁾ 330 ²⁾	480 ¹⁾ 330 ²⁾	500 ¹⁾ 330 ²⁾	
5/3-way pressurised (P53U)	В	700 ¹⁾ 330 ²⁾	450 ¹⁾ 330 ²⁾	480 ¹⁾ 330 ²⁾	480 ¹⁾ 330 ²⁾	500 ¹⁾ 330 ²⁾	
5/3-way exhausted, switching position 14 detenting (P53ED)	SA	-	380 ¹⁾ 310 ²⁾	430 ¹⁾ 360 ²⁾	430 ¹⁾ 360 ²⁾	390 ¹⁾ 310 ²⁾	
5/3-way exhausted, switching position 12 detenting (P53EP)	SE	-	380 ¹⁾ 300 ²⁾	460 ¹⁾ 350 ²⁾	460 ¹⁾ 350 ²⁾	390 ¹⁾ 320 ²⁾	
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD)	SB	-	380 ¹⁾ 350 ²⁾	440 ¹⁾ 400 ²⁾	440 ¹⁾ 400 ²⁾	380 ¹⁾ 360 ²⁾	
5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD)	SD	-	370 ¹⁾ 340 ²⁾ 360 ³⁾ 360 ⁴⁾	430 ¹⁾ 360 ²⁾ 450 ³⁾ 450 ⁴⁾	430 ¹⁾ 360 ²⁾ 450 ³⁾ 450 ⁴⁾	400 ¹⁾ 350 ²⁾ 390 ³⁾ 380 ⁴⁾	
2x3/2-way single solenoid, closed (T32C)	К	600	400	550	550	500	
2x3/2-way single solenoid, open (T32U)	N	600	400	550	550	500	
2x3/2-way single solenoid, open/closed (T32H)	Н	600	400	550	550	500	
2x3/2-way single solenoid, closed (T32N)	Q	600	400	550	550	500	
2x3/2-way single solenoid, open (T32F)	Р	600	400	550	550	500	
2x3/2-way single solenoid, open/closed (T32W)	R	600	400	550	550	500	
2x2/2-way single solenoid, closed (T22C)	VC	700	500	650	650	500	
2x2/2-way single solenoid, closed (T22CV)	VV	700	500	650	650	500	

1) Switching position

2) Mid-position

3) Switching position 4 \rightarrow 5

4) Mid-position 2 a 3

- 🏺 - Note

When using the solenoid valves VSVA-B-P53AD-...- or VSVA-B-P53BD-...- (terminal code SB or SD) for unobstructed exhausting $(1 \rightarrow 2 \text{ or } 1 \rightarrow 4)$ in the detenting or mid-position, the flow rate can reduce or drop to 0 l/min if the operating pressure is greater than 6 bar. This does not happen if a tube measuring at least 15 cm in length is used at port 2/4.

T

Datasheet - Solenoid valve width 18 mm

Valve switching times in [ms]

Valve switching times in [ms]										
Valve function (with valve code)	Terminal	On	Off	Changeover						
	code									
5/2-way double solenoid (B52)	1	_	_	11						
5/2-way double solenoid with dominant signal (D52)	D	_	_	13						
5/2-way single solenoid (M52A)	M	22	28	-						
5/2-way single solenoid (M52M)	0	12	38	_						
5/3-way closed (P53C)	G	15	44	_						
5/3-way exhausted (P53E)	E	15	44							
5/3-way pressurised (P53U)	B	15	44	_						
5/3-way exhausted, switching position 14 detenting (P53ED)	SA	13 for control side 12	37 for control side 12	(24)						
sys way exhausted, switching position 14 detenting (1996b)	SIL	10 for control side 14	57 101 controt side 12	(24)						
5/3-way exhausted, switching position 12 detenting (P53EP)	SE	10 for control side 12	30 for control side 12	(23)						
		13 for control side 14		()						
5/3-way, port 2 pressurised, 4 exhausted, switching position	SB	12 for control side 12	28 for control side 12	-						
14 detenting (P53AD)		9 for control side 14								
5/3-way, port 4 pressurised, 2 exhausted, switching position	SD	12 for control side 12	28 for control side 12	-						
14 detenting (P53BD)		9 for control side 14								
2x3/2-way single solenoid, closed (T32C)	К	12	30	-						
2x3/2-way single solenoid, open (T32U)	N	12	30	-						
2x3/2-way single solenoid, open/closed (T32H)	Н	12	30	-						
2x3/2-way single solenoid, closed (T32N)	Q	25	12	_						
2x3/2-way single solenoid, open (T32F)	Р	25	12	-						
2x3/2-way single solenoid, open/closed (T32W)	R	25	12	-						
2x2/2-way single solenoid, closed (T22C)	VC	12	30	-						
2x2/2-way single solenoid, closed (T22CV)	VV	12	30	-						
Characteristic coil data Valve function (with valve code)	Terminal code	C	Characteristic coil data at 24 V DC in [W]							
5/2-way double solenoid (B52)	J		1.6							
5/2-way double solenoid with dominant signal (D52)	D		1.3							
5/2-way single solenoid (M52A)	M		1.6							
5/2-way single solenoid (M52M)	0		1.6							
5/3-way closed (P53C)	G		1.6							
5/3-way exhausted (P53E)	E		1.6							
5/3-way pressurised (P53U)	В		1.6							
5/3-way, exhausted, switching position 14 detenting (P53ED)	SA		1.6							
5/3-way exhausted, switching position 12 detenting (P53EP)	SE		1.6							
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD)	SB		1.6							
5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD)	SD		1.6							
2x3/2-way single solenoid, closed (T32C)	К		1.3							
	N									
2x3/2-way single solenoid open (T3211)		1.3								
2x3/2-way single solenoid, open (T32U)			13	1.3						
2x3/2-way single solenoid, open/closed (T32H)	Н									
2x3/2-way single solenoid, open/closed (T32H) 2x3/2-way single solenoid, closed (T32N)	H Q		1.3							
2x3/2-way single solenoid, open/closed (T32H)2x3/2-way single solenoid, closed (T32N)2x3/2-way single solenoid, open (T32F)	H Q P		1.3 1.3							
2x3/2-way single solenoid, open/closed (T32H)2x3/2-way single solenoid, closed (T32N)2x3/2-way single solenoid, open (T32F)2x3/2-way single solenoid, open/closed (T32W)	H Q P R		1.3 1.3 1.3							
2x3/2-way single solenoid, open/closed (T32H)2x3/2-way single solenoid, closed (T32N)2x3/2-way single solenoid, open (T32F)	H Q P		1.3 1.3							

Materials

Housing	Die-cast aluminium, PA
Seals	FPM, NBR, HNBR
Screws	Galvanised steel
Note on materials	RoHS-compliant

Ordering data – Solenoid valve VSVA, MO non-detenting/detenting (D)

	Terminal	A, MO non-detenting/detenting (D) Valve function	Valve	Width	Part no.	Туре
	code		code	wiath	Part no.	Туре
	couc		couc			
Solenoid valves	110		Taac	1.40		
	VC	2x 2/2-way valve, single solenoid,	T22C	18 mm	561155	VSVA-B-T22C-AZD-A2-1T1L
		normally closed,				
	10/	pneumatic spring return	Taaciu	10	54450	
	VV	2x 2/2-way valve, single solenoid,	T22CV	18 mm	561159	VSVA-B-T22CV-AZD-A2-1T1L
		normally closed, pneumatic spring return,				
		vacuum operation possible at 3 and 5				
	N	2x 3/2-way valve, single solenoid,	Table	10	520470	
	N	normally open	T32U	18 mm	539178	VSVA-B-T32U-AZD-A2-1T1L
	К	2x 3/2-way valve, single solenoid,	T32C	18 mm	539176	VSVA-B-T32C-AZD-A2-1T1L
	ĸ	normally closed	1520	10 11111	559170	V3VA-D-132C-AZD-AZ-111L
	Н	2x 3/2-way valve, single solenoid,	T32H	18 mm	539180	VSVA-B-T32H-AZD-A2-1T1L
	п	1x normally open, 1x normally closed	15211	10 11111	559100	V3VA-D-1321-AZD-AZ-111L
	Р	2x 3/2-way valve, single solenoid,	T32F	10 mm	520170	
	r	reverse operation,	1326	18 mm	539179	VSVA-B-T32F-AZD-A2-1T1L
		normally open				
	Q	2x 3/2-way valve, single solenoid,	T32N	10 mm	520177	VSVA-B-T32N-AZD-A2-1T1L
	Q	reverse operation,	1321	18 mm	539177	V3VA-D-132N-A2D-A2-111L
		normally closed				
	R	2x 3/2-way valve, single solenoid,	T32W	18 mm	539181	VSVA-B-T32W-AZD-A2-1T1L
	ĸ	reverse operation,	13200	18 11111	539101	VSVA-D-132W-AZD-AZ-111L
		1x normally open, 1x normally closed				
	м	5/2-way valve, single solenoid,	M52-A	18 mm	539184	VSVA-B-M52-AZD-A2-1T1L
	141	pneumatic spring return	M32-A	10 11111	559104	V3VA-D-W32-A2D-A2-111L
	0	5/2-way valve, single solenoid,	M52-M	18 mm	539185	VSVA-B-M52-MZD-A2-1T1L
		mechanical spring return	101.52-101	10 11111	559105	V3VA-D-WJ2-WZD-A2-111L
	1	5/2-way valve, double solenoid	B52	18 mm	539182	VSVA-B-B52-ZD-A2-1T1L
	,	5/2-way valve, double solenoid	0.52	10 1111	555102	V3VR-0-052-20-R2-111L
	D	5/2-way valve, double solenoid,	D52	18 mm	539183	VSVA-B-D52-ZD-A2-1T1L
		with dominant signal	0.52		555105	
	В	5/3-way solenoid valve,	P53U	18 mm	539186	VSVA-B-P53U-ZD-A2-1T1L
		mid-position pressurised	1 5 5 0		555100	
	G	5/3-way solenoid valve,	P53C	18 mm	539188	VSVA-B-P53C-ZD-A2-1T1L
	0	mid-position closed	1550		555100	
	E	5/3-way solenoid valve.	P53E	18 mm	539187	VSVA-B-P53E-ZD-A2-1T1L
	-	mid-position exhausted		10		
	SA	5/3-way solenoid valve,	P53ED	18 mm	8031814	VSVA-B-P53ED-ZD-A2-1T1L
		mid-position exhausted, switching position 14 detenting,				
		mechanical spring return				
	SE	5/3-way solenoid valve,	P53EP	18 mm	8031818	VSVA-B-P53EP-ZD-A2-1T1L
		mid-position exhausted, switching position 12 detenting,				
		mechanical spring return				
	SB	5/3-way solenoid valve,	P53AD	18 mm	8031815	VSVA-B-P53AD-ZD-A2-1T1L
		mid-position 1x exhausted from 4 to 5, 1x pressurised from 1 to				
		2, switching position 14 detenting,				
		same function in both switching positions: pressurised from 1 to				
		4 and exhausted from 2 to 3,				
		mechanical spring return				
	SD	5/3-way solenoid valve,	P53BD	18 mm	8031817	VSVA-B-P53BD-ZD-A2-1T1L
		mid-position 1x exhausted from 2 to 3, 1x pressurised from 1 to				
		4, switching position 14 detenting,				
		same function in both switching positions: pressurised from 1 to				
		2 and exhausted from 4 to 5,				
	<u> </u>	mechanical spring return	MEDIM	10	E70004	
	SS	5/2-way valve, single solenoid, mechanical spring return, induc-	M52-M	18 mm	573201	VSVA-B-M52-MZD-A2-1T1L-APX-0.5
		tive sensor with PNP output with 0.5 m connecting cable and				
	50	4-pin sensor push-in connector M12x1	MEDIM	10	F73303	VSVA D MED MOD AD 4741 ADD
	SO	5/2-way valve, single solenoid, mechanical spring return, induc- tive sensor with PNP output and 3-pin sensor push-in connector	M52-M	18 mm	573202	VSVA-B-M52-MZD-A2-1T1L-APP
		M8x1				

	Terminal	Valve function	Valve	Width	Part no.	Туре
	code		code)T -
enoid valves						
	VC	2x 2/2-way valve, single solenoid,	T22C	18 mm	8033457	VSVA-B-T22C-AZTR-A2-1T1L
		normally closed,				
		pneumatic spring return				
North Contraction	VV	2x 2/2-way valve, single solenoid,	T22CV	18 mm	8033458	VSVA-B-T22CV-AZTR-A2-1T1L
		normally closed,				
		pneumatic spring return, vacuum operation possible at 3 and 5				
V	N	2x 3/2-way valve, single solenoid,	T32U	18 mm	8033446	VSVA-B-T32U-AZTR-A2-1T1L
	N	normally open	1920	10 1111	0055440	
	К	2x 3/2-way valve, single solenoid,	T32C	18 mm	8033444	VSVA-B-T32C-AZTR-A2-1T1L
		normally closed				
	Н	2x 3/2-way valve, single solenoid,	T32H	18 mm	8033448	VSVA-B-T32H-AZTR-A2-1T1L
		1x normally open, 1x normally closed				
	Р	2x 3/2-way valve, single solenoid,	T32F	18 mm	8033447	VSVA-B-T32F-AZTR-A2-1T1L
		reverse operation,				
		normally open				
	Q	2x 3/2-way valve, single solenoid,	T32N	18 mm	8033445	VSVA-B-T32N-AZTR-A2-1T1L
		reverse operation, normally closed				
	R	2x 3/2-way valve, single solenoid,	T32W	18 mm	8033449	VSVA-B-T32W-AZTR-A2-1T1L
	iX.	reverse operation,	1.52 W	10 11111	0033447	VOVA-D-IOZW-AZIN-AZ-111L
		1x normally open, 1x normally closed				
	Μ	5/2-way valve, single solenoid,	M52-A	18 mm	8033452	VSVA-B-M52-AZTR-A2-1T1L
		pneumatic spring return				
	0	5/2-way valve, single solenoid,	M52-M	18 mm	8033453	VSVA-B-M52-MZTR-A2-1T1L
		mechanical spring return				
	J	5/2-way valve, double solenoid	B52	18 mm	8033450	VSVA-B-B52-ZTR-A2-1T1L
			0.50	10		
	D	5/2-way valve, double solenoid, with dominant signal	D52	18 mm	8033451	VSVA-B-D52-ZTR-A2-1T1L
	В	5/3-way solenoid valve,	P53U	18 mm	8033454	VSVA-B-P53U-ZTR-A2-1T1L
	D	mid-position pressurised	1,220	10 1111	8033434	V3VA-D-F330-21R-A2-111L
	G	5/3-way solenoid valve.	P53C	18 mm	8033456	VSVA-B-P53C-ZTR-A2-1T1L
		mid-position closed				
	E	5/3-way solenoid valve,	P53E	18 mm	8033455	VSVA-B-P53E-ZTR-A2-1T1L
		mid-position exhausted				
	SA	5/3-way solenoid valve,	P53ED	18 mm	8039181	VSVA-B-P53ED-ZTR-A2-1T1L
		mid-position exhausted, switching position 14 detenting,				
		mechanical spring return				
	SE	5/3-way solenoid valve,	P53EP	18 mm	8039190	VSVA-B-P53EP-ZTR-A2-1T1L
		mid-position exhausted, switching position 12 detenting, mechanical spring return				
	SB	5/3-way solenoid valve,	P53AD	18 mm	8039184	VSVA-B-P53AD-ZTR-A2-1T1L
	30	mid-position 1x exhausted from 4 to 5, 1x pressurised from 1 to	FSSAD	10 11111	6039164	VSVA-D-F55AD-ZIR-AZ-111L
		2, switching position 14 detenting,				
		same function in both switching positions: pressurised from 1 to				
		4 and exhausted from 2 to 3,				
		mechanical spring return				
	SD	5/3-way solenoid valve,	P53BD	18 mm	8040110	VSVA-B-P53BD-ZTR-A2-1T1L
		mid-position 1x exhausted from 2 to 3, 1x pressurised from 1				
		to 4, switching position 14 detenting, same function in both switching positions: pressurised from 1 to				
		2 and exhausted from 4 to 5,				
		mechanical spring return				
9	SS	5/2-way valve, single solenoid, mechanical spring return,	M52-M	18 mm	8033459	VSVA-B-M52-MZTR-A2-1T1L-APX-0.
		inductive sensor with PNP output with 0.5 m connecting cable				
		and 4-pin sensor push-in connector M12x1				
I Re L	S0	5/2-way valve, single solenoid, mechanical spring return,	M52-M	18 mm	8033460	VSVA-B-M52-MZTR-A2-1T1L-APP
		inductive sensor with PNP output and 3-pin sensor push-in				
> >> >>> >>>>>>>>>>>>>>>>>>>>>>>>>>>		connector M8x1	1	1		

Ordering data – Solenoid valve VSVA with cover cap for MO, non-detenting (H)

	1	Valve function	Valve code	Width	Part no.	Туре
Solenoid valves						
	VC	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return	T22C	18 mm	8033475	VSVA-B-T22C-AZH-A2-1T1L
	VV	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return,	T22CV	18 mm	8033476	VSVA-B-T22CV-AZH-A2-1T1L
· · ·	N	vacuum operation possible at 3 and 5 2x 3/2-way valve, single solenoid, normally open	T32U	18 mm	8033464	VSVA-B-T32U-AZH-A2-1T1L
	К	2x 3/2-way valve, single solenoid, normally closed	T32C	18 mm	8033462	VSVA-B-T32C-AZH-A2-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	T32H	18 mm	8033466	VSVA-B-T32H-AZH-A2-1T1L
	Ρ	2x 3/2-way valve, single solenoid, reverse operation, normally open	T32F	18 mm	8033465	VSVA-B-T32F-AZH-A2-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, normally closed	T32N	18 mm	8033463	VSVA-B-T32N-AZH-A2-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	T32W	18 mm	8033467	VSVA-B-T32W-AZH-A2-1T1L
	М	5/2-way valve, single solenoid, pneumatic spring return	M52-A	18 mm	8033470	VSVA-B-M52-AZH-A2-1T1L
	0	5/2-way valve, single solenoid, mechanical spring return	M52-M	18 mm	8033471	VSVA-B-M52-MZH-A2-1T1L
	J	5/2-way valve, double solenoid	B52	18 mm	8033468	VSVA-B-B52-ZH-A2-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	D52	18 mm	8033469	VSVA-B-D52-ZH-A2-1T1L
	G	5/3-way solenoid valve, mid-position pressurised 5/3-way solenoid valve,	P53U P53C	18 mm	8033472	VSVA-B-P53U-ZH-A2-1T1L VSVA-B-P53C-ZH-A2-1T1L
	E	mid-position closed 5/3-way solenoid valve,	P53E	18 mm	8033473	VSVA-B-P53E-ZH-A2-1T1L
	SA	mid-position exhausted 5/3-way solenoid valve,	P53ED	18 mm	8039182	VSVA-B-P53ED-ZH-A2-1T1L
		mid-position exhausted, switching position 14 detenting, mechanical spring return				
	SE	5/3-way solenoid valve, mid-position exhausted, switching position 12 detenting, mechanical spring return	P53EP	18 mm	8039191	VSVA-B-P53EP-ZH-A2-1T1L
	SB	5/3-way solenoid valve, mid-position 1x exhausted from 4 to 5, 1x pressurised from 1 to 2, switching position 14 detenting, same function in both switching positions: pressurised from 1 to 4 and exhausted from 2 to 3, mechanical spring return	P53AD	18 mm	8039185	VSVA-B-P53AD-ZH-A2-1T1L
	SD	5/3-way solenoid valve, mid-position 1x exhausted from 2 to 3, 1x pressurised from 1 to 4, switching position 14 detenting, same function in both switching positions: pressurised from 1 to 2 and exhausted from 4 to 5, mechanical spring return	P53BD	18 mm	8040111	VSVA-B-P53BD-ZH-A2-1T1L
	SS	5/2-way valve, single solenoid, mechanical spring return, induc- tive sensor with PNP output with 0.5 m connecting cable and 4-pin sensor push-in connector M12x1	M52-M	18 mm	8033477	VSVA-B-M52-MZH-A2-1T1L-APX-0.5
	SO	5/2-way valve, single solenoid, mechanical spring return, induc- tive sensor with PNP output and 3-pin sensor push-in connector M8x1	M52-M	18 mm	8033478	VSVA-B-M52-MZH-A2-1T1L-APP

Ordering data – Solenoid valve width 18 mm

Ordering data – Solenoid valve VSVA with cover cap for MO, concealed

	Terminal	Valve function	Valve	Width	Part no.	Туре
	code		code			
Solenoid valves		1				
	VC	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return	T22C	18 mm	8033493	VSVA-B-T22C-AZ-A2-1T1L
	VV	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return,	T22CV	18 mm	8033494	VSVA-B-T22CV-AZ-A2-1T1L
*	N	vacuum operation possible at 3 and 5 2x 3/2-way valve, single solenoid, normally open	T32U	18 mm	8033482	VSVA-B-T32U-AZ-A2-1T1L
	K	2x 3/2-way valve, single solenoid, normally closed	T32C	18 mm	8033480	VSVA-B-T32C-AZ-A2-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	T32H	18 mm	8033484	VSVA-B-T32H-AZ-A2-1T1L
	Ρ	2x 3/2-way valve, single solenoid, reverse operation, normally open	T32F	18 mm	8033483	VSVA-B-T32F-AZ-A2-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, normally closed	T32N	18 mm	8033481	VSVA-B-T32N-AZ-A2-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	T32W	18 mm	8033485	VSVA-B-T32W-AZ-A2-1T1L
	М	5/2-way valve, single solenoid, pneumatic spring return	M52-A	18 mm	8033488	VSVA-B-M52-AZ-A2-1T1L
	0	5/2-way valve, single solenoid, mechanical spring return	M52-M	18 mm	8033489	VSVA-B-M52-MZ-A2-1T1L
	J D	5/2-way valve, double solenoid 5/2-way valve, double solenoid,	B52	18 mm	8033486	VSVA-B-B52-Z-A2-1T1L
	B	with dominant signal 5/3-way solenoid valve,	D52 P53U	18 mm	8033487	VSVA-B-D52-Z-A2-1T1L VSVA-B-P53U-Z-A2-1T1L
	G	mid-position pressurised 5/3-way solenoid valve,	P53C	18 mm	8033492	VSVA-B-P53C-Z-A2-1T1L
	E	Mid-position closed 5/3-way solenoid valve,	P53E	18 mm	8033491	VSVA-B-P53E-Z-A2-1T1L
	SA	mid-position exhausted 5/3-way solenoid valve, mid-position exhausted, switching position 14 detenting, mechanical spring return	P53ED	18 mm	8039183	VSVA-B-P53ED-Z-A2-1T1L
	SE	5/3-way solenoid valve, mid-position exhausted, switching position 12 detenting, mechanical spring return	P53EP	18 mm	8039192	VSVA-B-P53EP-Z-A2-1T1L
	SB	5/3-way solenoid valve, mid-position 1x exhausted from 4 to 5, 1x pressurised from 1 to 2, switching position 14 detenting, same function in both switching positions: pressurised from 1 to 4 and exhausted from 2 to 3, mechanical spring return	P53AD	18 mm	8039186	VSVA-B-P53AD-Z-A2-1T1L
	SD	5/3-way solenoid valve, mid-position 1x exhausted from 2 to 3, 1x pressurised from 1 to 4, switching position 14 detenting, same function in both switching positions: pressurised from 1 to 2 and exhausted from 4 to 5, mechanical spring return	P53BD	18 mm	8040112	VSVA-B-P53BD-Z-A2-1T1L
	SS	5/2-way valve, single solenoid, mechanical spring return, induc- tive sensor with PNP output with 0.5 m connecting cable and 4-pin sensor push-in connector M12x1	M52-M	18 mm	8033495	VSVA-B-M52-MZ-A2-1T1L-APX-0.5
	SO	5/2-way valve, single solenoid, mechanical spring return, induc- tive sensor with PNP output and 3-pin sensor push-in connector M8x1	M52-M	18 mm	8033496	VSVA-B-M52-MZ-A2-1T1L-APP

Valve terminals VTSA

Datasheet - Solenoid valve width 26 mm

- **[]** - Valve width to ISO 15407-2 26 mm

> Voltage 24 V DC

- N - Flow rate

Valve width 26 mm: VTSA up to 1100 l/min VTSA-F up to 1350 l/min VTSA-F-CB up to 1350 l/min



Safety characteristics for valve

Conforms to standard		EN 13849-1/2
CE marking (see declaration of conformity)	Direct voltage 24 V DC	To EU EMC Directive ¹⁾ (solenoid valves with sensor only)
Shock resistance		Shock test with severity level 2, to EN 60068-2-27
Vibration resistant		Transport application test with severity level 2, to EN 60068-2-6

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Safety characteristics for valve

Valve function (with valve code)	Terminal	l Test pulses					
		Max. positive test pulse with logic 0 $[\mu s]$	Max. negative test pulse with logic 1 [µs]				
5/2-way double solenoid (B52)	J	1200	1100				
5/2-way double solenoid with dominant signal (D52)	D	1200	1100				
5/2-way single solenoid (M52A)	M	1200	1100				
5/2-way single solenoid (M52M)	0	1200	1100				
5/3-way closed (P53C)	G	1200	1100				
5/3-way exhausted (P53E)	E	1200	1100				
5/3-way pressurised (P53U)	В	1200	1100				
5/3-way exhausted, switching position 14 detenting (P53ED)	SA	1200	1100				
5/3-way exhausted, switching position 12 detenting (P53EP)	SE	1200	1100				
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD)	SB	1200	1100				
5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD)	SD	1200	1100				
2x3/2-way single solenoid, closed (T32C)	К	1500	1200				
2x3/2-way single solenoid, open (T32U)	N	1500	1200				
2x3/2-way single solenoid, open/closed (T32H)	Н	1500	1200				
2x3/2-way single solenoid, closed (T32N)	Q	1500	1200				
2x3/2-way single solenoid, open (T32F)	Р	1500	1200				
2x3/2-way single solenoid, open/closed (T32W)	R	1500	1200				
2x2/2-way single solenoid, closed (T22C)	VC	1500	1200				
2x2/2-way single solenoid, closed (T22CV)	VV	1500	1200				

Datasheet - Solenoid valve width 26 mm

Datasheet for valve

Valve function (with valve code)	Terminal	Flow direction			Reset method	Weight	
	code	Any	Reversible only	Not reversible	Pneumatic spring	Mechanical spring	[g]
5/2-way double solenoid (B52)	J	•	-	-	-	-	276
5/2-way double solenoid with dominant signal (D52)	D		-	-	-	-	276
5/2-way single solenoid (M52A)	М		-	-		-	293
5/2-way single solenoid (M52M)	0		-	-	-		293
5/3-way closed ¹⁾ (P53C)	G	•	-	-	-	•	320
5/3-way exhausted ¹⁾ (P53E)	E		-	-	-		320
5/3-way pressurised ¹⁾ (P53U)	В		-	-	-		320
5/3-way exhausted, switching position 14 detenting (P53ED)	SA	-	-	•	-		291
5/3-way exhausted, switching position 12 detenting (P53EP)	SE	-	-	•	-	•	291
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD)	SB	•	-	-	-	•	301
5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD)	SD	-	-		-	•	301
2x3/2-way single solenoid, closed (T32C)	К	-	-	•		-	335
2x3/2-way single solenoid, open (T32U)	N	-	-	•	•	-	335
2x3/2-way single solenoid, open/closed (T32H)	Н	-	-	•	•	-	335
2x3/2-way single solenoid, closed (T32N)	Q	-	•	-	•	-	335
2x3/2-way single solenoid, open (T32F)	Р	-	•	-		-	335
2x3/2-way single solenoid, open/closed (T32W)	R	-		-		-	335
2x2/2-way single solenoid, closed (T22C)	VC	-	-	•	•	-	335
2x2/2-way single solenoid, closed (T22CV)	VV	•	-	-	•	-	335

1) If neither solenoid coil is energised, the valve is moved to its mid-position by spring force.

If both solenoid coils are energised at the same time, the valve remains in the previously assumed switching position.

Datasheet - Solenoid valve width 26 mm

Standard nominal flow rate of valve/valve terminal [l/min]

Valve function (with valve code)	Terminal	Il Flow rate							
	code	Valve	Valve on valve	Valve on valve terminal					
			VTSA	VTSA-F	VTSA-F-CB	sub-base			
5/2-way double solenoid (B52)	J	1400	1100	1350	1350	1200			
5/2-way double solenoid with dominant signal (D52)	D	1400	1100	1350	1350	1200			
5/2-way single solenoid (M52A)	М	1400	1100	1350	1350	1200			
5/2-way single solenoid (M52M)	0	1400	1100	1350	1350	1200			
5/3-way closed (P53C)	G	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾			
5/3-way exhausted (P53E)	E	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾			
5/3-way pressurised (P53U)	В	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾			
5/3-way exhausted, switching position 14 detenting (P53ED)	SA	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾			
5/3-way exhausted, switching position 12 detenting (P53EP)	SE	1400 ¹⁾ 700 ²⁾	1000 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1350 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾			
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD)	SB	700 ¹⁾ 700 ²⁾							
5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD)	SD	-	850 ¹⁾ 820 ²⁾	950 ¹⁾ 860 ²⁾	950 ¹⁾ 860 ²⁾	900 ¹⁾ 840 ²⁾			
2x3/2-way single solenoid, closed (T32C)	К	1250	900	1150	1150	1100			
2x3/2-way single solenoid, open (T32U)	N	1250	900	1150	1150	1100			
2x3/2-way single solenoid, open/closed (T32H)	Н	1250	900	1150	1150	1100			
2x3/2-way single solenoid, closed (T32N)	Q	1250	900	1150	1150	1100			
2x3/2-way single solenoid, open (T32F)	P	1250	900	1150	1150	1100			
2x3/2-way single solenoid, open/closed (T32W)	R	1250	900	1150	1150	1100			
2x2/2-way single solenoid, closed (T22C)	VC	1350	1000	1300	1300	1100			
2x2/2-way single solenoid, closed (T22CV)	VV	1350	1000	1300	1300	1100			

1) Switching position

2) Mid-position

- 🗍 - Note

The solenoid valves VSVA-B-P53BD...-A1-1T1L (terminal code SD) can be operated without restrictions at an operating pressure of less than 6 bar. At an operating pressure of more than 6 bar, the actual flow rate must not exceed 1900 l/min (e.g. 10-->2 bar) or these solenoid valves may switch unintentionally (to the mid-position or switching position 14).

At pressures above 6 bar, it is possible to prevent the flow rate from becoming too high by using a flow control valve or orifice (e.g. a reducing nipple on port 2 or 4 from G1/4 to G1/8).

Datasheet - Solenoid valve width 26 mm

Valve switching times in [ms]

Valve function (with valve code)	Terminal	On	Off	Changeover
	code			
5/2-way double solenoid (B52)	J	-	-	18
5/2-way double solenoid with dominant signal (D52)	D	_	_	21
5/2-way single solenoid (M52A)	M	25	45	_
5/2-way single solenoid (M52M)	0	20	65	_
5/3-way closed (P53C)	G	22	65	_
5/3-way exhausted (P53E)	E	22	65	_
5/3-way pressurised (P53U)	В	22	65	_
5/3-way exhausted, switching position 14 detenting (P53ED)	SA	22 for control side 12 9 for control side 14	49 for control side 12	33
5/3-way exhausted, switching position 12 detenting (P53EP)	SE	10 for control side 12 22 for control side 14	50 for control side 14	40
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD)	SB	19 for control side 12 9 for control side 14	36 for control side 12	32
5/3-way, port 4 pressurised, 2 exhausted, switching position	SD	16 for control side 12	26 for control side 12	-
14 detenting (P53BD)		9 for control side 14	36 for control side 14	
2x3/2-way single solenoid, closed (T32C)	К	20	38	-
2x3/2-way single solenoid, open (T32U)	N	20	38	-
2x3/2-way single solenoid, open/closed (T32H)	Н	20	38	-
2x3/2-way single solenoid, closed (T32N)	Q	32	30	-
2x3/2-way single solenoid, open (T32F)	Р	32	-	
2x3/2-way single solenoid, open/closed (T32W)	R	32	30	-
2x2/2-way single solenoid, closed (T22C)	VC	20	38	-
2x2/2-way single solenoid, closed (T22CV)	VV	20	38	-
Characteristic coil data				
Characteristic coil data Valve function (with valve code)	Terminal	C	haracteristic coil data at 24 V DC in [W]	
Valve function (with valve code)	Terminal code	C		
Valve function (with valve code) 5/2-way double solenoid (B52)	code J	C	1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52)	code J D		1.6 1.3	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A)	code J D M	C	1.6 1.3 1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M)	code J D M O		1.6 1.3 1.6 1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C)	code J D M O G	C	1.6 1.3 1.6 1.6 1.6 1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E)	code J D M O G E	C	1.6 1.3 1.6 1.6 1.6 1.6 1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way pressurised (P53U)	code J D M O G E B	C	1.6 1.3 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way pressurised (P53U) 5/3-way exhausted, switching position 14 detenting (P53ED)	code J D M O G G E B B SA		1.6 1.3 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way pressurised (P53U) 5/3-way exhausted, switching position 14 detenting (P53ED) 5/3-way exhausted, switching position 12 detenting (P53EP) 5/3-way, port 2 pressurised, 4 exhausted, switching position	code J D M O G E B		1.6 1.3 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way exhausted (P53U) 5/3-way exhausted, switching position 14 detenting (P53ED) 5/3-way exhausted, switching position 12 detenting (P53EP) 5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD) 5/3-way, port 4 pressurised, 2 exhausted, switching position	code J D M O G G E B B SA SE		1.6 1.3 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way pressurised (P53E) 5/3-way exhausted (P53U) 5/3-way exhausted, switching position 14 detenting (P53ED) 5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD) 5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD)	code J D M O G E B SA SE SB SB		$ \begin{array}{r} 1.6 \\ 1.3 \\ 1.6 \\ $	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way exhausted (P53U) 5/3-way exhausted, switching position 14 detenting (P53ED) 5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD) 5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD) 2x3/2-way single solenoid, closed (T32C)	code J D M O G E B SA SE SB SD SD		1.6 1.3 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way pressurised (P53U) 5/3-way exhausted, switching position 14 detenting (P53ED) 5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD) 5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD) 2x3/2-way single solenoid, closed (T32C) 2x3/2-way single solenoid, open (T32U)	code J J D M O G E B S SA S SB S SD K		1.6 1.3 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.3	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way exhausted (P53U) 5/3-way exhausted, switching position 14 detenting (P53ED) 5/3-way exhausted, switching position 12 detenting (P53EP) 5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD) 5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD) 2x3/2-way single solenoid, closed (T32C) 2x3/2-way single solenoid, open/closed (T32H)	code J D M O G G E B SA SE SB SD K N		1.6 1.3 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.3 1.3	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way pressurised (P53U) 5/3-way exhausted, switching position 14 detenting (P53ED) 5/3-way exhausted, switching position 12 detenting (P53EP)	code J D M O G G E B SA SE SB SD K N H		1.6 1.3 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.3 1.3 1.3	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way exhausted, switching position 14 detenting (P53ED) 5/3-way exhausted, switching position 12 detenting (P53EP) 5/3-way exhausted, switching position 12 detenting (P53ED) 5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD) 5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD) 2x3/2-way single solenoid, closed (T32C) 2x3/2-way single solenoid, open/closed (T32H) 2x3/2-way single solenoid, closed (T32N)	code J D M O G E B SA SE SB SD K N Q Q U		1.6 1.3 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.6 1.3 1.3 1.3 1.3	
Valve function (with valve code) 5/2-way double solenoid (B52) 5/2-way double solenoid with dominant signal (D52) 5/2-way single solenoid (M52A) 5/2-way single solenoid (M52M) 5/3-way closed (P53C) 5/3-way exhausted (P53E) 5/3-way exhausted (P53U) 5/3-way exhausted, switching position 14 detenting (P53ED) 5/3-way exhausted, switching position 12 detenting (P53EP) 5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD) 5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD) 2x3/2-way single solenoid, closed (T32C) 2x3/2-way single solenoid, open/closed (T32H) 2x3/2-way single solenoid, closed (T32N) 2x3/2-way single solenoid, open (T32F)	code J J D M O G E B D SA SE SB SB SD K N H Q P		$ \begin{array}{r} 1.6 \\ 1.3 \\ 1.6 \\ 1.6 \\ 1.6 \\ 1.6 \\ 1.6 \\ 1.6 \\ 1.6 \\ 1.6 \\ 1.6 \\ 1.6 \\ 1.3 \\ 1$	

Materials

Housing	Die-cast aluminium, PA
Seals	FPM, NBR, HNBR
Screws	Galvanised steel
Note on materials	RoHS-compliant

Ordering data – Solenoid valve VSVA, MO non-detenting/detenting (D)

	Terminal	VA, MO non-detenting/detenting (D)	Valve	Width	Part no.	Туре
	code		code	Width		Type
lenoid valves						
	VC	2x 2/2-way valve, single solenoid,	T22C	26 mm	561149	VSVA-B-T22C-AZD-A1-1T1L
		normally closed,				
		pneumatic spring return				
	VV	2x 2/2-way valve, single solenoid,	T22CV	26 mm	561153	VSVA-B-T22CV-AZD-A1-1T1L
		normally closed,				
		pneumatic spring return,				
		vacuum operation possible at 3 and 5	Taall			
	N	2x 3/2-way valve, single solenoid, normally open	T32U	26 mm	539152	VSVA-B-T32U-AZD-A1-1T1L
	K	2x 3/2-way valve, single solenoid,	T32C	26 mm	539150	VSVA-B-T32C-AZD-A1-1T1L
	K	normally closed	1520	20 11111	555150	V5VA-D-152C-A2D-A1-111L
	н	2x 3/2-way valve, single solenoid,	T32H	26 mm	539154	VSVA-B-T32H-AZD-A1-1T1L
		1x normally open, 1x normally closed				
	Р	2x 3/2-way valve, single solenoid,	T32F	26 mm	539153	VSVA-B-T32F-AZD-A1-1T1L
		reverse operation,				
		normally open				
	Q	2x 3/2-way valve, single solenoid,	T32N	26 mm	539151	VSVA-B-T32N-AZD-A1-1T1L
		reverse operation,				
		normally closed				
	R	2x 3/2-way valve, single solenoid,	T32W	26 mm	539155	VSVA-B-T32W-AZD-A1-1T1L
		reverse operation, 1x normally open, 1x normally closed				
	M	5/2-way valve, single solenoid,	M52-A	26 mm	539158	VSVA-B-M52-AZD-A1-1T1L
	141	pneumatic spring return	M52-A	20 11111	559156	VSVA-D-WI52-AZD-AI-IIIL
	0	5/2-way valve, single solenoid,	M52-M	26 mm	539159	VSVA-B-M52-MZD-A1-1T1L
		mechanical spring return				
	J	5/2-way valve, double solenoid	B52	26 mm	539156	VSVA-B-B52-ZD-A1-1T1L
	D	5/2-way valve, double solenoid,	D52	26 mm	539157	VSVA-B-D52-ZD-A1-1T1L
		with dominant signal				
	В	5/3-way solenoid valve,	P53U	26 mm	539160	VSVA-B-P53U-ZD-A1-1T1L
		mid-position pressurised		-		
	G	5/3-way solenoid valve,	P53C	26 mm	539162	VSVA-B-P53C-ZD-A1-1T1L
	E	mid-position closed 5/3-way solenoid valve,	P53E	26 mm	539161	VSVA-B-P53E-ZD-A1-1T1L
		mid-position exhausted	POSE	26 11111	539101	VSVA-B-P33E-2D-A1-111L
	SA	5/3-way solenoid valve,	P53ED	26 mm	560727	VSVA-B-P53ED-ZD-A1-1T1L
	5/1	mid-position exhausted, switching position 14 detenting,	1 5520	20 1111	500727	
		mechanical spring return				
	SE	5/3-way solenoid valve,	P53EP	26 mm	8026638	VSVA-B-P53EP-ZD-A1-1T1L
		mid-position exhausted, switching position 12 detenting,				
		mechanical spring return				
	SB	5/3-way solenoid valve,	P53AD	26 mm	560728	VSVA-B-P53AD-ZD-A1-1T1L
		mid-position 1x exhausted from 4 to 5, 1x pressurised from 1 to				
		2, switching position 14 detenting, same function in both switching positions: pressurised from 1 to				
		4 and exhausted from 2 to 3,				
		mechanical spring return				
	SD	5/3-way solenoid valve,	P53BD	26 mm	8031816	VSVA-B-P53BD-ZD-A1-1T1L
		mid-position 1x exhausted from 2 to 3, 1x pressurised from 1 to				
		4, switching position 14 detenting,				
		same function in both switching positions: pressurised from 1 to				
		2 and exhausted from 4 to 5,				
x	SS	mechanical spring return 5/2-way valve, single solenoid, mechanical spring return, induc-	M52-M	26 mm	570950	VSVA-B-M52-MZD-A1-1T1L-APX-0.5
	33	5/2-way valve, single solenoid, mechanical spring return, induc- tive sensor with PNP output with 0.5 m connecting cable and	111.5 2-111	26 mm	570850	v3vA-D-W32-W2D-A1-111L-APX-0.5
		4-pin sensor push-in connector M12x1				
	SO	5/2-way valve, single solenoid, mechanical spring return, induc-	M52-M	26 mm	560724	VSVA-B-M52-MZD-A1-1T1L-APP
		tive sensor with PNP output and 3-pin sensor push-in connector				
> ™01	1	M8x1	1	1		

	Terminal	Valve function	Valve	Width	Part no.	Туре
	code		code)r ·
olenoid valves						
	VC	2x 2/2-way valve, single solenoid,	T22C	26 mm	8033032	VSVA-B-T22C-AZTR-A1-1T1L
		normally closed,				
		pneumatic spring return				
	VV	2x 2/2-way valve, single solenoid,	T22CV	26 mm	8033033	VSVA-B-T22CV-AZTR-A1-1T1L
		normally closed,				
		pneumatic spring return, vacuum operation possible at 3 and 5				
	N	2x 3/2-way valve, single solenoid,	T32U	26 mm	8033015	VSVA-B-T32U-AZTR-A1-1T1L
	IN .	normally open	1520	20 11111	8055015	VSVA-D-1520-AZIR-AT-IIIL
	К	2x 3/2-way valve, single solenoid,	T32C	26 mm	8033013	VSVA-B-T32C-AZTR-A1-1T1L
		normally closed				
	Н	2x 3/2-way valve, single solenoid,	T32H	26 mm	8033017	VSVA-B-T32H-AZTR-A1-1T1L
		1x normally open, 1x normally closed				
	Р	2x 3/2-way valve, single solenoid,	T32F	26 mm	8033016	VSVA-B-T32F-AZTR-A1-1T1L
		reverse operation,				
		normally open				
	Q	2x 3/2-way valve, single solenoid,	T32N	26 mm	8033014	VSVA-B-T32N-AZTR-A1-1T1L
		reverse operation,				
	D	normally closed	TOOM	26.000	0000040	
	R	2x 3/2-way valve, single solenoid, reverse operation,	T32W	26 mm	8033018	VSVA-B-T32W-AZTR-A1-1T1L
		1x normally open, 1x normally closed				
	м	5/2-way valve, single solenoid,	M52-A	26 mm	8033021	VSVA-B-M52-AZTR-A1-1T1L
		pneumatic spring return	1115211	20 1111	0000022	
	0	5/2-way valve, single solenoid,	M52-M	26 mm	8033022	VSVA-B-M52-MZTR-A1-1T1L
		mechanical spring return				
	J	5/2-way valve, double solenoid	B52	26 mm	8033019	VSVA-B-B52-ZTR-A1-1T1L
	D	5/2-way valve, double solenoid,	D52	26 mm	8033020	VSVA-B-D52-ZTR-A1-1T1L
		with dominant signal				
	В	5/3-way solenoid valve,	P53U	26 mm	8033023	VSVA-B-P53U-ZTR-A1-1T1L
	6	mid-position pressurised	DEAC			
	G	5/3-way solenoid valve,	P53C	26 mm	8033025	VSVA-B-P53C-ZTR-A1-1T1L
	E	mid-position closed 5/3-way solenoid valve,	P53E	26 mm	8033024	VSVA-B-P53E-ZTR-A1-1T1L
	C	mid-position exhausted	POSE	20 11111	8033024	VSVA-D-P55E-Z1R-A1-111L
	SA	5/3-way solenoid valve,	P53ED	26 mm	8033028	VSVA-B-P53ED-ZTR-A1-1T1L
	5/1	mid-position exhausted, switching position 14 detenting,		201111	0000020	
		mechanical spring return				
	SE	5/3-way solenoid valve,	P53EP	26 mm	8033035	VSVA-B-P53EP-ZTR-A1-1T1L
		mid-position exhausted, switching position 12 detenting,				
		mechanical spring return				
	SB	5/3-way solenoid valve,	P53AD	26 mm	8033029	VSVA-B-P53AD-ZTR-A1-1T1L
		mid-position 1x exhausted from 4 to 5, 1x pressurised from 1 to				
		2, switching position 14 detenting, same function in both switching positions: pressurised from 1 to				
		4 and exhausted from 2 to 3,				
		Mechanical spring return				
	SD	5/3-way solenoid valve,	P53BD	26 mm	8039187	VSVA-B-P53BD-ZTR-A1-1T1L
		mid-position 1x exhausted from 2 to 3, 1x pressurised from 1 to				
		4, switching position 14 detenting,				
		same function in both switching positions: pressurised from 1 to				
		2 and exhausted from 4 to 5,				
		mechanical spring return	MEDIA	26	6000001	
	SS	5/2-way valve, single solenoid, mechanical spring return,	M52-M	26 mm	8033034	VSVA-B-M52-MZTR-A1-1T1L-APX-0.
		inductive sensor with PNP output with 0.5 m connecting cable and 4-pin sensor push-in connector M12x1				
	SO	5/2-way valve, single solenoid, mechanical spring return,	M52-M	26 mm	8033027	VSVA-B-M52-MZTR-A1-1T1L-APP
	50	inductive sensor with PNP output and 3-pin sensor push-in	101.52-101	20 11111	0033027	VSVA-D-MIS2-MZTR-AT-TTTL-AFP
		connector M8x1				
Ĭ N			1			

Ordering data - Solenoid valve VSVA with cover cap for MO, non-detenting (H)

	Termi-	Valve function	Valve	Width	Part no.	Туре
	nal		code			
	code					
enoid valves					r	
	VC	2x 2/2-way valve, single solenoid,	T22C	26 mm	8033055	VSVA-B-T22C-AZH-A1-1T1L
		normally closed,				
		pneumatic spring return				
	≫ VV	2x 2/2-way valve, single solenoid, normally closed,	T22CV	26 mm	8033056	VSVA-B-T22CV-AZH-A1-1T1L
	او	pneumatic spring return,				
\		vacuum operation possible at 3 and 5				
	N	2x 3/2-way valve, single solenoid,	T32U	26 mm	8033038	VSVA-B-T32U-AZH-A1-1T1L
		normally open				
	К	2x 3/2-way valve, single solenoid,	T32C	26 mm	8033036	VSVA-B-T32C-AZH-A1-1T1L
		normally closed				
	н	2x 3/2-way valve, single solenoid,	T32H	26 mm	8033040	VSVA-B-T32H-AZH-A1-1T1L
		1x normally open, 1x normally closed				
	Р	2x 3/2-way valve, single solenoid,	T32F	26 mm	8033039	VSVA-B-T32F-AZH-A1-1T1L
		reverse operation, normally open				
	Q	2x 3/2-way valve, single solenoid,	T32N	26 mm	8033037	VSVA-B-T32N-AZH-A1-1T1L
		reverse operation,		20		
		normally closed				
	R	2x 3/2-way valve, single solenoid,	T32W	26 mm	8033041	VSVA-B-T32W-AZH-A1-1T1L
		reverse operation,				
		1x normally open, 1x normally closed				
	М	5/2-way valve, single solenoid,	M52-A	26 mm	8033044	VSVA-B-M52-AZH-A1-1T1L
		Pneumatic spring return	MEDIM	26	00000/5	
	0	5/2-way valve, single solenoid, mechanical spring return	M52-M	26 mm	8033045	VSVA-B-M52-MZH-A1-1T1L
		5/2-way valve, double solenoid	B52	26 mm	8033042	VSVA-B-B52-ZH-A1-1T1L
	ľ		0,52	20 1111	0000012	
	D	5/2-way valve, double solenoid,	D52	26 mm	8033043	VSVA-B-D52-ZH-A1-1T1L
		with dominant signal				
	В	5/3-way solenoid valve,	P53U	26 mm	8033046	VSVA-B-P53U-ZH-A1-1T1L
		mid-position pressurised				
	G	5/3-way solenoid valve,	P53C	26 mm	8033048	VSVA-B-P53C-ZH-A1-1T1L
	-	mid-position closed	DEDE	26	00220/7	
	E	5/3-way solenoid valve, mid-position exhausted	P53E	26 mm	8033047	VSVA-B-P53E-ZH-A1-1T1L
	SA	5/3-way solenoid valve,	P53ED	26 mm	8033051	VSVA-B-P53ED-ZH-A1-1T1
	5/1	mid-position exhausted, switching position 14 detenting,		20 1111	0000001	
		mechanical spring return				
	SE	5/3-way solenoid valve,	P53EP	26 mm	8033058	VSVA-B-P53EP-ZH-A1-1T1L
		mid-position exhausted, switching position 12 detenting,				
		mechanical spring return				
	SB	5/3-way solenoid valve,	P53AD	26 mm	8033052	VSVA-B-P53AD-ZH-A1-1T1L
		mid-position 1x exhausted from 4 to 5, 1x pressurised from 1 to 2, switching position 14 detenting,				
		same function in both switching positions: pressurised from 1 to				
		4 and exhausted from 2 to 3,				
		mechanical spring return				
	SD	5/3-way solenoid valve,	P53BD	26 mm	8039188	VSVA-B-P53BD-ZH-A1-1T1L
		mid-position 1x exhausted from 2 to 3, 1x pressurised from 1 to				
		4, switching position 14 detenting, same function in both switching positions: pressurised from 1 to				
		2 and exhausted from 4 to 5,				
		mechanical spring return				
<u></u>	SS	5/2-way valve, single solenoid, mechanical spring return, induc-	M52-M	26 mm	8033057	VSVA-B-M52-MZH-A1-1T1L-APX-0.5
		tive sensor with PNP output with 0.5 m connecting cable and				
		4-pin sensor push-in connector M12x1				
	≥ S0	5/2-way valve, single solenoid, mechanical spring return, induc-	M52-M	26 mm	8033050	VSVA-B-M52-MZH-A1-1T1L-APP
		tive sensor with PNP output and 3-pin sensor push-in connector				
× 4)	M8x1				

Ordering data – Solenoid valve VSVA with cover cap for MO, concealed

oracing add - Solenoid		VA with cover cap for MO, concealed	Valve	Width	Part no.	Turne
	Termi-	Valve function	code	width	Part no.	Туре
	nal code		code			
	couc					
Solenoid valves	[1	1	<u> </u>		
	VC	2x 2/2-way valve, single solenoid,	T22C	26 mm	8033078	VSVA-B-T22C-AZ-A1-1T1L
		normally closed,				
	201	pneumatic spring return	TaaCi			
	VV	2x 2/2-way valve, single solenoid,	T22CV	26 mm	8033079	VSVA-B-T22CV-AZ-A1-1T1L
		normally closed,				
		pneumatic spring return,				
	N	vacuum operation possible at 3 and 5	Table	26	00220/1	
	Ν	2x 3/2-way valve, single solenoid, normally open	T32U	26 mm	8033061	VSVA-B-T32U-AZ-A1-1T1L
	К	· · ·	T220	26	0000050	
	ĸ	2x 3/2-way valve, single solenoid, normally closed	T32C	26 mm	8033059	VSVA-B-T32C-AZ-A1-1T1L
	Н	2x 3/2-way valve, single solenoid,	T32H	26 mm	8033063	VSVA-B-T32H-AZ-A1-1T1L
	п	1x normally open, 1x normally closed	1520	20 11111	8055065	V3VA-D-132R-AZ-A1-111L
	Р	2x 3/2-way valve, single solenoid,	T32F	26 mm	8033062	VSVA-B-T32F-AZ-A1-1T1L
	r	reverse operation,	1521	20 11111	8055082	V3VA-D-132F-AZ-A1-111L
		normally open				
	Q	2x 3/2-way valve, single solenoid,	T32N	26 mm	8033060	VSVA-B-T32N-AZ-A1-1T1L
	Q	reverse operation,	1920	20 11111	0055000	
		normally closed				
	R	2x 3/2-way valve, single solenoid,	T32W	26 mm	8033064	VSVA-B-T32W-AZ-A1-1T1L
		reverse operation,		20		
		1x normally open, 1x normally closed				
	М	5/2-way valve, single solenoid,	M52-A	26 mm	8033067	VSVA-B-M52-AZ-A1-1T1L
		pneumatic spring return		-		
	0	5/2-way valve, single solenoid,	M52-M	26 mm	8033068	VSVA-B-M52-MZ-A1-1T1L
	-	mechanical spring return		-		
	J	5/2-way valve, double solenoid	B52	26 mm	8033065	VSVA-B-B52-Z-A1-1T1L
	-					
	D	5/2-way valve, double solenoid,	D52	26 mm	8033066	VSVA-B-D52-Z-A1-1T1L
		with dominant signal				
	В	5/3-way solenoid valve,	P53U	26 mm	8033069	VSVA-B-P53U-Z-A1-1T1L
		mid-position pressurised				
	G	5/3-way solenoid valve,	P53C	26 mm	8033071	VSVA-B-P53C-Z-A1-1T1L
		mid-position closed				
	E	5/3-way solenoid valve,	P53E	26 mm	8033070	VSVA-B-P53E-Z-A1-1T1L
		mid-position exhausted				
	SA	5/3-way solenoid valve,	P53ED	26 mm	8033074	VSVA-B-P53ED-Z-A1-1T1L
		mid-position exhausted, switching position 14 detenting,				
		mechanical spring return				
	SE	5/3-way solenoid valve,	P53EP	26 mm	8033081	VSVA-B-P53EP-Z-A1-1T1L
		mid-position exhausted, switching position 12 detenting,				
		mechanical spring return				
	SB	5/3-way solenoid valve,	P53AD	26 mm	8033075	VSVA-B-P53AD-Z-A1-1T1L
		mid-position 1x exhausted from 4 to 5, 1x pressurised from 1 to				
		2, switching position 14 detenting,				
		same function in both switching positions: pressurised from 1 to				
		4 and exhausted from 2 to 3,				
		mechanical spring return				
	SD	5/3-way solenoid valve,	P53BD	26 mm	8039189	VSVA-B-P53BD-Z-A1-1T1L
		mid-position 1x exhausted from 2 to 3, 1x pressurised from 1 to				
		4, switching position 14 detenting, same function in both switching positions: pressurised from 1 to				
		2 and exhausted from 4 to 5,				
		mechanical spring return				
	SS	5/2-way valve, single solenoid, mechanical spring return, induc-	M52-M	26 mm	8033080	VSVA-R-M52-M7-A1 1T1L ADV O F
	33	tive sensor with PNP output with 0.5 m connecting cable and	11152-111	26 mm	8033080	VSVA-B-M52-MZ-A1-1T1L-APX-0.5
		4-pin sensor push-in connector M12x1				
	S0	5/2-way valve, single solenoid, mechanical spring return, induc-	M52-M	26 mm	8033073	VSVA-B-M52-MZ-A1-1T1L-APP
	30	tive sensor with PNP output and 3-pin sensor push-in connector	10132-101	20 11111	00330/3	v 5 vA-D-1v152-1v12-A1-1111-AFF
		M8x1				
		INOAL				

Valve terminals VTSA

Datasheet – Solenoid valve width 42 mm

- **[]** - Valve width to ISO 5599-2 42 mm (ISO 1)

. I

- Voltage 24 V DC
- 11 -Flow rate
 - Valve width 42 mm: VTSA up to 1300 l/min VTSA-F up to 1860 l/min VTSA-F-CB up to 1860 l/min



Safety characteristics for valve

Conforms to standard	EN 13849-1/2
Shock resistance	Shock test with severity level 2, to EN 60068-2-27
Vibration resistant	Transport application test with severity level 2, to EN 60068-2-6

Safety characteristics for valve

Valve function (with valve code)	Terminal	Test pulses			
	code	Max. positive test pulse with 0 signal $[\mu s]$	Max. negative test pulse with 1 signal [µs]		
5/2-way double solenoid (B52)	J	1400	900		
5/2-way double solenoid with dominant signal (D52)	D	1600	1100		
5/2-way single solenoid (M52A)	М	1400	900		
5/2-way single solenoid (M52M)	0	1400	900		
5/3-way closed (P53C)	G	1400	900		
5/3-way exhausted (P53E)	E	1400	900		
5/3-way pressurised (P53U)	В	1400	900		
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	-	-		
2x3/2-way single solenoid, closed (T32C)	К	1600	1100		
2x3/2-way single solenoid, open (T32U)	N	1600	1100		
2x3/2-way single solenoid, open/closed (T32H)	Н	1600	1100		
2x3/2-way single solenoid, closed (T32N)	Q	1600	1100		
2x3/2-way single solenoid, open (T32F)	Р	1600	1100		
2x3/2-way single solenoid, open/closed (T32W)	R	1600	1100		
2x2/2-way single solenoid, closed (T22C)	VC	1600	1100		
2x2/2-way single solenoid, closed (T22CV)	VV	1600	1100		

I

Datasheet – Solenoid valve width42 mm

Datasheet for valve

Valve function (with valve code)	Terminal	Flow direction			Reset method		Weight
	code	Any	Reversible only	Not reversible	Pneumatic spring	Mechanical spring	[g]
5/2-way double solenoid (B52)	J		-	-	-	-	439
5/2-way double solenoid with dominant signal (D52)	D	•	-	-	-	-	439
5/2-way single solenoid (M52A)	M	•	-	-		-	426
5/2-way single solenoid (M52M)	0	•	-	-	-	•	426
5/3-way closed ¹⁾ (P53C)	G	•	-	-	-	•	456
5/3-way exhausted ¹⁾ (P53E)	E	•	-	-	-	•	456
5/3-way pressurised ¹⁾ (P53U)	В	•	-	-	-	•	456
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	•	-	-	-	-	456
2x3/2-way single solenoid, closed (T32C)	K	-	-	•	•	-	442
2x3/2-way single solenoid, open (T32U)	N	-	-		•	-	442
2x3/2-way single solenoid, open/closed (T32H)	Н	-	-		•	-	442
2x3/2-way single solenoid, closed (T32N)	Q	-	•	-		-	442
2x3/2-way single solenoid, open (T32F)	Р	-	•	-		-	442
2x3/2-way single solenoid, open/closed (T32W)	R	-	•	-	•	-	442
2x2/2-way single solenoid, closed (T22C)	VC	-	-	•	•	-	442
2x2/2-way single solenoid, closed (T22CV)	VV	•	-	-		-	442

1) If neither solenoid coil is energised, the valve is moved to its mid-position by spring force.

If both solenoid coils are energised at the same time, the valve remains in the previously assumed switching position.

Standard nominal flow rate of valve/valve terminal [l/min]

Valve function (with valve code)	Terminal	Flow rate				Valve on individua
	code	Valve		Valve on valve terminal		
			VTSA	VTSA-F	VTSA-F-CB	sub-base
5/2-way double solenoid (B52)	J	2000	1300	1860	1860	1500
5/2-way double solenoid with dominant signal (D52)	D	2000	1300	1860	1860	1500
5/2-way single solenoid (M52A)	Μ	2000	1300	1860	1860	1500
5/2-way single solenoid (M52M)	0	2000	1300	1860	1860	1500
5/3-way closed (P53C)	G	1900 ¹⁾	1200 ¹⁾	1690 ¹⁾	1690 ¹⁾	1400 ¹⁾
		950 ²⁾	800 ²⁾	830 ²⁾	830 ²⁾	800 ²⁾
5/3-way exhausted (P53E)	E	1900 ¹⁾	1200 ¹⁾	1690 ¹⁾	1690 ¹⁾	1400 ¹⁾
		950 ²⁾	8002)	830 ²⁾	830 ²⁾	800 ²⁾
5/3-way pressurised (P53U)	В	1900 ¹⁾	1200 ¹⁾	1690 ¹⁾	1690 ¹⁾	1400 ¹⁾
		950 ²⁾	800 ²⁾	830 ²⁾	830 ²⁾	800 ²⁾
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	1700 ¹⁾	1400 ¹⁾	1700 ¹⁾	1700 ¹⁾	1400 ¹⁾
		700 ²⁾	800 ²⁾	700 ²⁾	700 ²⁾	700 ²⁾
2x3/2-way single solenoid, closed (T32C)	К	1600	1200	1300	1300	1200
2x3/2-way single solenoid, open (T32U)	N	1600	1200	1300	1300	1200
2x3/2-way single solenoid, open/closed (T32H)	Н	1600	1200	1300	1300	1200
2x3/2-way single solenoid, closed (T32N)	Q	1600	1200	1300	1300	1200
2x3/2-way single solenoid, open (T32F)	Р	1600	1200	1300	1300	1200
2x3/2-way single solenoid, open/closed (T32W)	R	1600	1200	1300	1300	1200
2x2/2-way single solenoid, closed (T22C)	VC	1600	1400	1500	1500	1400
2x2/2-way single solenoid, closed (T22CV)	VV	1600	1400	1500	1500	1400

Switching position
 Mid-position

Datasheet - Solenoid valve width42 mm

Valve switching times in [ms]

Valve switching times in [ms]				
Valve function (with valve code)	Terminal code	On	Off	Changeover
5/2-way double solenoid (B52)	J	-	-	16
5/2-way double solenoid with dominant signal (D52)	D	-	-	19
5/2-way single solenoid (M52A)	M	27	45	-
5/2-way single solenoid (M52M)	0	22	60	-
5/3-way closed (P53C)	G	22	65	38
5/3-way exhausted (P53E)	E	22	65	38
5/3-way pressurised (P53U)	В	22	65	38
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	22	65	38
2x3/2-way single solenoid, closed (T32C)	К	20	38	_
2x3/2-way single solenoid, open (T32U)	N	20	38	-
2x3/2-way single solenoid, open/closed (T32H)	Н	20	38	_
2x3/2-way single solenoid, closed (T32N)	Q	34	28	-
2x3/2-way single solenoid, open (T32F)	Р	34	28	-
2x3/2-way single solenoid, open/closed (T32W)	R	34	28	-
2x2/2-way single solenoid, closed (T22C)	VC	20	38	-
2x2/2-way single solenoid, closed (T22CV)	VV	20	38	-

Characteristic coil data

Characteristic coil data		
Valve function (with valve code)	Terminal code	Characteristic coil data in [W]
5/2-way double solenoid (B52)	J	1.6
5/2-way double solenoid with dominant signal (D52)	D	1.3
5/2-way single solenoid (M52A)	M	1.6
5/2-way single solenoid (M52M)	0	1.6
5/3-way closed (P53C)	G	1.6
5/3-way exhausted (P53E)	E	1.6
5/3-way pressurised (P53U)	В	1.6
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	1.6
2x3/2-way single solenoid, closed (T32C)	K	1.3
2x3/2-way single solenoid, open (T32U)	N	1.3
2x3/2-way single solenoid, open/closed (T32H)	Н	1.3
2x3/2-way single solenoid, closed (T32N)	Q	1.3
2x3/2-way single solenoid, open (T32F)	Р	1.3
2x3/2-way single solenoid, open/closed (T32W)	R	1.3
2x2/2-way single solenoid, closed (T22C)	VC	1.3
2x2/2-way single solenoid, closed (T22CV)	VV	1.3

Max. current consumption per solenoid coil						
Туре		T22, T32	B52, D52, M52, P53			
At nominal voltage 24 V DC (valves with holding current reduction)						
Nominal pick-up current	[mA]	60	72			
Nominal current following current reduction	[mA]	-	-			
Time until current reduction	[ms]	30	30			

Materials

Materials					
Housing	Die-cast aluminium, PA				
Seals	FPM, NBR, HNBR				
Screws	Galvanised steel				
Note on materials	RoHS-compliant				

Ordering data – Solenoid valve VSVA, MO non-detenting/detenting (D)

Ordering data – Sole	1	/A, MO non-detenting/detenting (D)	Ι	1	1	I.
	Terminal	Valve function	Valve	Width	Part no.	Туре
	code		code			
Solenoid valves						
×	VC	2x 2/2-way valve, single solenoid,	T22C	42 mm	561340	VSVA-B-T22C-AZD-D1-1T1L
		normally closed,				
		pneumatic spring return				
	W	2x 2/2-way valve, single solenoid,	T22CV	42 mm	561344	VSVA-B-T22CV-AZD-D1-1T1L
	1	normally closed,				
		pneumatic spring return,				
		vacuum operation possible at 3 and 5	Taali			
	N	2x 3/2-way valve, single solenoid,	T32U	42 mm	543692	VSVA-B-T32U-AZD-D1-1T1L
	К	normally open	Taac	(2)	5/2/00	
	ĸ	2x 3/2-way valve, single solenoid, normally closed	T32C	42 mm	543690	VSVA-B-T32C-AZD-D1-1T1L
	Н	2x 3/2-way valve, single solenoid,	T32H	42 mm	543694	VSVA-B-T32H-AZD-D1-1T1L
	п	1x normally open, 1x normally closed	1520	42 1111	545054	V3VA-D-132H-AZD-D1-111L
	Р	2x 3/2-way valve, single solenoid,	T32F	42 mm	543693	VSVA-B-T32F-AZD-D1-1T1L
		reverse operation,	1521	42 1111	545075	VSVA-D-ISZI-AZD-DI-IIIL
		normally open				
	Q	2x 3/2-way valve, single solenoid,	T32N	42 mm	543691	VSVA-B-T32N-AZD-D1-1T1L
		reverse operation,				
		normally closed				
	R	2x 3/2-way valve, single solenoid,	T32W	42 mm	543695	VSVA-B-T32W-AZD-D1-1T1L
		reverse operation,				
		1x normally open, 1x normally closed				
	м	5/2-way valve, single solenoid,	M52-A	42 mm	543698	VSVA-B-M52-AZD-D1-1T1L
		pneumatic spring return				
	0	5/2-way valve, single solenoid,	M52-M	42 mm	543699	VSVA-B-M52-MZD-D1-1T1L
		mechanical spring return				
	J	5/2-way valve, double solenoid	B52	42 mm	543696	VSVA-B-B52-ZD-D1-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	D52	42 mm	543697	VSVA-B-D52-ZD-D1-1T1L
	В	5/3-way solenoid valve,	Drau	(2	F (2700	
	D	mid-position pressurised	P53U	42 mm	543700	VSVA-B-P53U-ZD-D1-1T1L
	G	5/3-way solenoid valve,	P53C	42 mm	543702	VSVA-B-P53C-ZD-D1-1T1L
	U	mid-position closed		42 1111	545702	131A-D-F 33C-20-01-111L
	E	5/3-way solenoid valve.	P53E	42 mm	543701	VSVA-B-P53E-ZD-D1-1T1L
		mid-position exhausted		12 1111	515701	
	VG	5/3-way solenoid valve.	P53F	42 mm	8000464	VSVA-B-P53F-ZD-D1-1T1L
		mid-position pressurised 1 to 2, 4 to 5 closed		12 1111	0000104	
		· · · · · · · · · · · · · · · · · · ·				

Ordering data – Solenoid valve VSVA with cover cap for MO non-detenting/heavy duty, detenting via accessory (TR)

	Terminal code	Valve function	Valve code	Width	Part no.	Туре
d valves						
	VC	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return	T22C	42 mm	8034781	VSVA-B-T22C-AZTR-D1-1T1L
	W	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return, vacuum operation possible at 3 and 5	T22CV	42 mm	8034782	VSVA-B-T22CV-AZTR-D1-1T1L
	N	2x 3/2-way valve, single solenoid, normally open	T32U	42 mm	8034770	VSVA-B-T32U-AZTR-D1-1T1L
	К	2x 3/2-way valve, single solenoid, normally closed	T32C	42 mm	8034768	VSVA-B-T32C-AZTR-D1-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	Т32Н	42 mm	8034772	VSVA-B-T32H-AZTR-D1-1T1L
	Р	2x 3/2-way valve, single solenoid, reverse operation, normally open	T32F	42 mm	8034771	VSVA-B-T32F-AZTR-D1-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, normally closed	T32N	42 mm	8034769	VSVA-B-T32N-AZTR-D1-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	T32W	42 mm	8034773	VSVA-B-T32W-AZTR-D1-1T1L
	М	5/2-way valve, single solenoid, Pneumatic spring return	M52-A	42 mm	8034776	VSVA-B-M52-AZTR-D1-1T1L
	0	5/2-way valve, single solenoid, mechanical spring return	M52-M	42 mm	8034777	VSVA-B-M52-MZTR-D1-1T1L
	J	5/2-way valve, double solenoid	B52	42 mm	8034774	VSVA-B-B52-ZTR-D1-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	D52	42 mm	8034775	VSVA-B-D52-ZTR-D1-1T1L
	В	5/3-way solenoid valve, mid-position pressurised	P53U	42 mm	8034778	VSVA-B-P53U-ZTR-D1-1T1L
	G	5/3-way solenoid valve, mid-position closed	P53C	42 mm	8034780	VSVA-B-P53C-ZTR-D1-1T1L
	E	5/3-way solenoid valve, mid-position exhausted	P53E	42 mm	8034779	VSVA-B-P53E-ZTR-D1-1T1L
	VG	5/3-way solenoid valve, mid-position pressurised 1 to 2, 4 to 5 closed	P53F	42 mm	8034783	VSVA-B-P53F-ZTR-D1-1T1L

Ordering data - Solenoid valve VSVA with cover cap for MO, non-detenting (H)

ordering data - Sot	1	A with cover cap for MO, non-detenting (H)	Value	14/: -141-	Destant	Time
	Terminal	Valve function	Valve	Width	Part no.	Туре
	code		code			
Solenoid valves						
	VC	2x 2/2-way valve, single solenoid,	T22C	42 mm	8034812	VSVA-B-T22C-AZH-D1-1T1L
$\langle \rangle \rangle = \langle \rangle \rangle$		normally closed,				
\ \@ ``e	▶	pneumatic spring return				
	W N	2x 2/2-way valve, single solenoid,	T22CV	42 mm	8034813	VSVA-B-T22CV-AZH-D1-1T1L
		normally closed,				
		pneumatic spring return,				
		vacuum operation possible at 3 and 5				
	N	2x 3/2-way valve, single solenoid,	T32U	42 mm	8034801	VSVA-B-T32U-AZH-D1-1T1L
		normally open				
	К	2x 3/2-way valve, single solenoid,	T32C	42 mm	8034799	VSVA-B-T32C-AZH-D1-1T1L
		normally closed				
	Н	2x 3/2-way valve, single solenoid,	T32H	42 mm	8034803	VSVA-B-T32H-AZH-D1-1T1L
		1x normally open, 1x normally closed				
	Р	2x 3/2-way valve, single solenoid,	T32F	42 mm	8034802	VSVA-B-T32F-AZH-D1-1T1L
		reverse operation,				
		normally open				
	Q	2x 3/2-way valve, single solenoid,	T32N	42 mm	8034800	VSVA-B-T32N-AZH-D1-1T1L
		reverse operation,				
		normally closed				
	R	2x 3/2-way valve, single solenoid,	T32W	42 mm	8034804	VSVA-B-T32W-AZH-D1-1T1L
		reverse operation,				
		1x normally open, 1x normally closed				
	Μ	5/2-way valve, single solenoid,	M52-A	42 mm	8034807	VSVA-B-M52-AZH-D1-1T1L
		pneumatic spring return				
	0	5/2-way valve, single solenoid,	M52-M	42 mm	8034808	VSVA-B-M52-MZH-D1-1T1L
		mechanical spring return				
	J	5/2-way valve, double solenoid	B52	42 mm	8034805	VSVA-B-B52-ZH-D1-1T1L
	D	5/2-way valve, double solenoid,	D52	42 mm	8034806	VSVA-B-D52-ZH-D1-1T1L
		with dominant signal				
	В	5/3-way solenoid valve,	P53U	42 mm	8034809	VSVA-B-P53U-ZH-D1-1T1L
		mid-position pressurised				
	G	5/3-way solenoid valve,	P53C	42 mm	8034811	VSVA-B-P53C-ZH-D1-1T1L
		mid-position closed				
	E	5/3-way solenoid valve,	P53E	42 mm	8034810	VSVA-B-P53E-ZH-D1-1T1L
		mid-position exhausted				
	VG	5/3-way solenoid valve,	P53F	42 mm	8034814	VSVA-B-P53F-ZH-D1-1T1L
	1.0	mid-position pressurised 1 to 2, 4 to 5 closed		1.2		

Ordering data – Solenoid valve VSVA with cover cap for MO, concealed

	Terminal code	Valve function	Valve code	Width	Part no.	Туре
valves, 24	V DC					
	VC	2x 2/2-way valve, single solenoid, normally closed, Pneumatic spring return	T22C	42 mm	8034843	VSVA-B-T22C-AZ-D1-1T1L
	W	2x 2/2-way valve, single solenoid, normally closed, pneumatic spring return, vacuum operation possible at 3 and 5	T22CV	42 mm	8034844	VSVA-B-T22CV-AZ-D1-1T1L
	N	2x 3/2-way valve, single solenoid, normally open	T32U	42 mm	8034832	VSVA-B-T32U-AZ-D1-1T1L
	К	2x 3/2-way valve, single solenoid, normally closed	T32C	42 mm	8034830	VSVA-B-T32C-AZ-D1-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	T32H	42 mm	8034834	VSVA-B-T32H-AZ-D1-1T1L
	Р	2x 3/2-way valve, single solenoid, reverse operation, normally open	T32F	42 mm	8034833	VSVA-B-T32F-AZ-D1-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, normally closed	T32N	42 mm	8034831	VSVA-B-T32N-AZ-D1-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	T32W	42 mm	8034835	VSVA-B-T32W-AZ-D1-1T1L
	М	5/2-way valve, single solenoid, pneumatic spring return	M52-A	42 mm	8034838	VSVA-B-M52-AZ-D1-1T1L
	0	5/2-way valve, single solenoid, mechanical spring return	M52-M	42 mm	8034839	VSVA-B-M52-MZ-D1-1T1L
	J	5/2-way valve, double solenoid	B52	42 mm	8034836	VSVA-B-B52-Z-D1-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	D52	42 mm	8034837	VSVA-B-D52-Z-D1-1T1L
	В	5/3-way solenoid valve, mid-position pressurised	P53U	42 mm	8034840	VSVA-B-P53U-Z-D1-1T1L
	G	5/3-way solenoid valve, mid-position closed	P53C	42 mm	8034842	VSVA-B-P53C-Z-D1-1T1L
	E	5/3-way solenoid valve, mid-position exhausted	P53E	42 mm	8034841	VSVA-B-P53E-Z-D1-1T1L
	VG	5/3-way solenoid valve, mid-position pressurised 1 to 2, 4 to 5 closed	P53F	42 mm	8034845	VSVA-B-P53F-Z-D1-1T1L

Datasheet – Solenoid valve width 52 mm

- **[]** - Valve width

to ISO 5599-2 52 mm (ISO 2)

Voltage

24 V DC

- 11 -Flow rate

Valve width 52 mm: VTSA up to 2900 l/min VTSA-F up to 2900 l/min VTSA-F-CB up to 2900 l/min



Safety characteristics for valve

Conforms to standard		EN 13849-1/2
CE marking (see	Direct voltage	To EU EMC Directive ¹⁾
declaration of conformity)	24 V DC	
KC marking		KC EMC
Shock resistance		Shock test with severity level 2, to EN 60068-2-27
Vibration resistant		Transport application test with severity level 2, to EN 60068-2-6

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Safety characteristics for valve

Valve function (with valve code)	Terminal	Test pulses		
	code	Max. positive test pulse with logic 0 [µs]	Max. negative test pulse with logic 1 [µs]	
5/2-way double solenoid (B52)	J	1000	3500	
5/2-way double solenoid with dominant signal (D52)	D	1000	3500	
5/2-way single solenoid (M52A)	M	1000	3500	
5/2-way single solenoid (M52M)	0	1000	3500	
5/3-way closed (P53C)	G	1000	3500	
5/3-way exhausted (P53E)	E	1000	3500	
5/3-way pressurised (P53U)	В	1000	3500	
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	-	-	
2x3/2-way single solenoid, closed (T32C)	К	1000	3500	
2x3/2-way single solenoid, open (T32U)	N	1000	3500	
2x3/2-way single solenoid, open/closed (T32H)	Н	1000	3500	
2x3/2-way single solenoid, closed (T32N)	Q	1000	3500	
2x3/2-way single solenoid, open (T32F)	Р	1000	3500	
2x3/2-way single solenoid, open/closed (T32W)	R	1000	3500	
2x2/2-way single solenoid, closed (T22C)	VC	1000	3500	

Datasheet – Solenoid valve width52 mm

Datasheet for valve

Valve function (with valve code)	Terminal	Flow direction			Reset method		Weight
	code	Any	Reversible only	Not reversible	Pneumatic spring	Mechanical spring	[g]
5/2-way double solenoid (B52)	J	•	-	-	-	-	732
5/2-way double solenoid with dominant signal (D52)	D	•	-	-	-	-	732
5/2-way single solenoid (M52A)	М		-	-		-	702
5/2-way single solenoid (M52M)	0	•	-	-	-		702
5/3-way closed ¹⁾ (P53C)	G	•	-	-	-	•	780
5/3-way exhausted ¹⁾ (P53E)	E	•	-	-	-	•	780
5/3-way pressurised ¹⁾ (P53U)	В	•	-	-	-	•	780
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	•	-	-	-	-	780
2x3/2-way single solenoid, closed (T32C)	K	-	-	•		-	740
2x3/2-way single solenoid, open (T32U)	N	-	-	•		-	740
2x3/2-way single solenoid, open/closed (T32H)	Н	-	-	•		-	740
2x3/2-way single solenoid, closed (T32N)	Q	-	•	-		-	740
2x3/2-way single solenoid, open (T32F)	Р	-	•	-		-	740
2x3/2-way single solenoid, open/closed (T32W)	R	-		-		-	740
2x2/2-way single solenoid, closed (T22C)	VC	-	-	•		-	740

1) If neither solenoid coil is energised, the valve is moved to its mid-position by spring force.

If both solenoid coils are energised at the same time, the valve remains in the previously assumed switching position

Standard nominal flow rate of valve/valve terminal [l/min]

Valve function (with valve code)	Terminal	Flow rate					
	code	Valve	Valve on valve	Valve on valve terminal			
			VTSA	VTSA-F	VTSA-F-CB	sub-base	
5/2-way double solenoid (B52)	J	4000	2900	2900	2900	3400	
5/2-way double solenoid with dominant signal (D52)	D	4000	2900	2900	2900	3400	
5/2-way single solenoid (M52A)	М	4000	2900	2900	2900	3400	
5/2-way single solenoid (M52M)	0	4000	2900	2900	2900	3400	
5/3-way closed (P53C)	G	3600 ¹⁾	2800 ¹⁾	2800 ¹⁾	2800 ¹⁾	3200 ¹⁾	
		1700 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾	
5/3-way exhausted (P53E)	E	3600 ¹⁾	2800 ¹⁾	2800 ¹⁾	2800 ¹⁾	3200 ¹⁾	
		1700 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾	
5/3-way pressurised (P53U)	В	3600 ¹⁾	28001)	28001)	28001)	3200 ¹⁾	
		1700 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾	1700 ²⁾	
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	3000 ¹⁾	2300 ¹⁾	2300 ¹⁾	2300 ¹⁾	2600 ¹⁾	
		900 ²⁾	900 ²⁾	900 ²⁾	900 ²⁾	900 ²⁾	
2x3/2-way single solenoid, closed (T32C)	К	3000	2400	2400	2400	2600	
2x3/2-way single solenoid, open (T32U)	N	3000	2400	2400	2400	2600	
2x3/2-way single solenoid, open/closed (T32H)	Н	3000	2400	2400	2400	2600	
2x3/2-way single solenoid, closed (T32N)	Q	3000	2400	2400	2400	2600	
2x3/2-way single solenoid, open (T32F)	Р	3000	2400	2400	2400	2600	
2x3/2-way single solenoid, open/closed (T32W)	R	3000	2400	2400	2400	2600	
2x2/2-way single solenoid, closed (T22C)	VC	4000	2800	2800	2800	3400	

1) Switching position

2) Mid-position

L

Datasheet – Solenoid valve width52 mm

Valve switching times in [ms]

Valve switching times in [ms]				
Valve function (with valve code)	Terminal code	On	Off	Changeover
5/2-way double solenoid (B52)	J	-	_	18
5/2-way double solenoid with dominant signal (D52)	D	-	_	18
5/2-way single solenoid (M52A)	М	40	45	-
5/2-way single solenoid (M52M)	0	20	60	-
5/3-way closed (P53C)	G	23	60	38
5/3-way exhausted (P53E)	E	23	60	38
5/3-way pressurised (P53U)	В	23	60	38
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	23	60	38
2x3/2-way single solenoid, closed (T32C)	K	20	35	-
2x3/2-way single solenoid, open (T32U)	Ν	20	35	-
2x3/2-way single solenoid, open/closed (T32H)	Н	20	35	-
2x3/2-way single solenoid, closed (T32N)	Q	20	35	-
2x3/2-way single solenoid, open (T32F)	Р	20	35	-
2x3/2-way single solenoid, open/closed (T32W)	R	20	35	-
2x2/2-way single solenoid, closed (T22C)	VC	14	35	_

Characteristic coil data

Valve function (with valve code)	Terminal code	Characteristic coil data in [W]
5/2-way double solenoid (B52)	J	4.6
5/2-way double solenoid with dominant signal (D52)	D	4.6
5/2-way single solenoid (M52A)	М	4.6
5/2-way single solenoid (M52M)	0	4.6
5/3-way closed (P53C)	G	4.6
5/3-way exhausted (P53E)	E	4.6
5/3-way pressurised (P53U)	В	4.6
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F)	VG	4.6
2x3/2-way single solenoid, closed (T32C)	К	4.6
2x3/2-way single solenoid, open (T32U)	N	4.6
2x3/2-way single solenoid, open/closed (T32H)	Н	4.6
2x3/2-way single solenoid, closed (T32N)	Q	4.6
2x3/2-way single solenoid, open (T32F)	Р	4.6
2x3/2-way single solenoid, open/closed (T32W)	R	4.6
2x2/2-way single solenoid, closed (T22C)	VC	4.6

Max. current consumption per solenoid coil

At nominal voltage 24 V DC (valves with holding current reduction)						
Nominal pick-up current	[mA]	165				
Nominal current following current reduction	[mA]	35				
Time until current reduction	[ms]	30				

Materials

inateriato	
Housing	Die-cast aluminium, PA
Seals	FPM, NBR, HNBR
Screws	Galvanised steel
Note on materials	RoHS-compliant

1

Ordering data – Solenoid valve VSVA, MO non-detenting/detenting (D)

	Terminal code	Valve function	Valve code	Width	Part no.	Туре
oid valves						
	VC	2x 2/2-way valve, single solenoid, Normally closed, Pneumatic spring return	T22C	52 mm	560831	VSVA-B-T22C-AZD-D2-1T1L
	N	2x 3/2-way valve, single solenoid, Normally open	T32U	52 mm	560827	VSVA-B-T32U-AZD-D2-1T1L
4	К	2x 3/2-way valve, single solenoid, Normally closed	T32C	52 mm	560825	VSVA-B-T32C-AZD-D2-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	Т32Н	52 mm	560829	VSVA-B-T32H-AZD-D2-1T1L
	Р	2x 3/2-way valve, single solenoid, reverse operation, Normally open	T32F	52 mm	560828	VSVA-B-T32F-AZD-D2-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, Normally closed	T32N	52 mm	560826	VSVA-B-T32N-AZD-D2-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	T32W	52 mm	560830	VSVA-B-T32W-AZD-D2-1T1L
	м	5/2-way valve, single solenoid, Pneumatic spring return	M52-A	52 mm	560820	VSVA-B-M52-AZD-D2-1T1L
	0	5/2-way valve, single solenoid, Mechanical spring return	M52-M	52 mm	560821	VSVA-B-M52-MZD-D2-1T1L
	J	5/2-way valve, double solenoid	B52	52 mm	560818	VSVA-B-B52-ZD-D2-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	D52	52 mm	560819	VSVA-B-D52-ZD-D2-1T1L
	В	5/3-way solenoid valve, Mid-position pressurised	P53U	52 mm	560822	VSVA-B-P53U-ZD-D2-1T1L
	G	5/3-way solenoid valve, Mid-position closed	P53C	52 mm	560824	VSVA-B-P53C-ZD-D2-1T1L
	E	5/3-way solenoid valve, Mid-position exhausted	P53E	52 mm	560823	VSVA-B-P53E-ZD-D2-1T1L
	VG	5/3-way solenoid valve, mid-position pressurised 1 to 2, 4 to 5 closed	P53F	52 mm	8000465	VSVA-B-P53F-ZD-D2-1T1L

	Terminal code	Valve function	Valve code	Width	Part no.	Туре
oid valves						
	VC	2x 2/2-way valve, single solenoid, Normally closed, Pneumatic spring return	T22C	52 mm	8034967	VSVA-B-T22C-AZTR-D2-1T1L
	N	2x 3/2-way valve, single solenoid, Normally open	T32U	52 mm	8034963	VSVA-B-T32U-AZTR-D2-1T1L
	К	2x 3/2-way valve, single solenoid, Normally closed	T32C	52 mm	8034961	VSVA-B-T32C-AZTR-D2-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	Т32Н	52 mm	8034965	VSVA-B-T32H-AZTR-D2-1T1L
	Р	2x 3/2-way valve, single solenoid, reverse operation, Normally open	T32F	52 mm	8034964	VSVA-B-T32F-AZTR-D2-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, Normally closed	T32N	52 mm	8034962	VSVA-B-T32N-AZTR-D2-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	T32W	52 mm	8034966	VSVA-B-T32W-AZTR-D2-1T1L
	м	5/2-way valve, single solenoid, Pneumatic spring return	M52-A	52 mm	8034956	VSVA-B-M52-AZTR-D2-1T1L
	0	5/2-way valve, single solenoid, Mechanical spring return	M52-M	52 mm	8034957	VSVA-B-M52-MZTR-D2-1T1L
	J	5/2-way valve, double solenoid	B52	52 mm	8034954	VSVA-B-B52-ZTR-D2-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	D52	52 mm	8034955	VSVA-B-D52-ZTR-D2-1T1L
	В	5/3-way solenoid valve, Mid-position pressurised	P53U	52 mm	8034958	VSVA-B-P53U-ZTR-D2-1T1L
	G	5/3-way solenoid valve, Mid-position closed	P53C	52 mm	8034960	VSVA-B-P53C-ZTR-D2-1T1L
	E	5/3-way solenoid valve, Mid-position exhausted	P53E	52 mm	8034959	VSVA-B-P53E-ZTR-D2-1T1L
	VG	5/3-way solenoid valve, mid-position pressurised 1 to 2, 4 to 5 closed	P53F	52 mm	8034968	VSVA-B-P53F-ZTR-D2-1T1L

Ordering data – Solenoid valve VSVA with cover cap for MO, non-detenting (H)

	Terminal	Valve function	Valve	Width	Part no.	Туре
	code		code			
olenoid valves						
<u>i</u>	VC	2x 2/2-way valve, single solenoid,	T22C	52 mm	8034982	VSVA-B-T22C-AZH-D2-1T1L
\$K_ *		Normally closed,				
l Re		Pneumatic spring return				
\$. ``	N	2x 3/2-way valve, single solenoid,	T32U	52 mm	8034978	VSVA-B-T32U-AZH-D2-1T1L
Je la		Normally open				
	К	2x 3/2-way valve, single solenoid,	T32C	52 mm	8034976	VSVA-B-T32C-AZH-D2-1T1L
		Normally closed				
	Н	2x 3/2-way valve, single solenoid,	T32H	52 mm	8034980	VSVA-B-T32H-AZH-D2-1T1LL
		1x normally open, 1x normally closed				
	Р	2x 3/2-way valve, single solenoid,	T32F	52 mm	8034979	VSVA-B-T32F-AZH-D2-1T1L
		reverse operation,				
		Normally open				
	Q	2x 3/2-way valve, single solenoid,	T32N	52 mm	8034977	VSVA-B-T32N-AZH-D2-1T1L
		reverse operation,				
		Normally closed				
	R	2x 3/2-way valve, single solenoid,	T32W	52 mm	8034981	VSVA-B-T32W-AZH-D2-1T1L
		reverse operation,				
		1x normally open, 1x normally closed				
	М	5/2-way valve, single solenoid,	M52-A	52 mm	8034971	VSVA-B-M52-AZH-D2-1T1L
		Pneumatic spring return				
	0	5/2-way valve, single solenoid,	M52-M	52 mm	8034972	VSVA-B-M52-MZH-D2-1T1L
		Mechanical spring return				
	J	5/2-way valve, double solenoid	B52	52 mm	8034969	VSVA-B-B52-ZH-D2-1T1L
	D	5/2-way valve, double solenoid,	D52	52 mm	8034970	VSVA-B-D52-ZH-D2-1T1L
		with dominant signal				
	В	5/3-way solenoid valve,	P53U	52 mm	8034973	VSVA-B-P53U-ZH-D2-1T1L
		Mid-position pressurised				
	G	5/3-way solenoid valve,	P53C	52 mm	8034975	VSVA-B-P53C-ZH-D2-1T1L
		Mid-position closed				
	E	5/3-way solenoid valve,	P53E	52 mm	8034974	VSVA-B-P53E-ZH-D2-1T1L
		Mid-position exhausted				
	VG	5/3-way solenoid valve,	P53F	52 mm	8034983	VSVA-B-P53F-ZH-D2-1T1L
		mid-position pressurised 1 to 2, 4 to 5 closed				

T

Ordering data – Solenoid valve width 52 mm

Ordering data – Solenoid valve VSVA with cover cap for MO, concealed

	Terminal	Valve function	Valve	Width	Part no.	Туре
	code		code			
olenoid valves						
	VC	2x 2/2-way valve, single solenoid, Normally closed, Pneumatic spring return	T22C	52 mm	8034997	VSVA-B-T22C-AZ-D2-1T1L
	N	2x 3/2-way valve, single solenoid, Normally open	T32U	52 mm	8034993	VSVA-B-T32U-AZ-D2-1T1L
	К	2x 3/2-way valve, single solenoid, Normally closed	T32C	52 mm	8034991	VSVA-B-T32C-AZ-D2-1T1L
	Н	2x 3/2-way valve, single solenoid, 1x normally open, 1x normally closed	Т32Н	52 mm	8034995	VSVA-B-T32H-AZ-D2-1T1L
	Р	2x 3/2-way valve, single solenoid, reverse operation, Normally open	T32F	52 mm	8034994	VSVA-B-T32F-AZ-D2-1T1L
	Q	2x 3/2-way valve, single solenoid, reverse operation, Normally closed	T32N	52 mm	8034992	VSVA-B-T32N-AZ-D2-1T1L
	R	2x 3/2-way valve, single solenoid, reverse operation, 1x normally open, 1x normally closed	T32W	52 mm	8034996	VSVA-B-T32W-AZ-D2-1T1L
	М	5/2-way valve, single solenoid, Pneumatic spring return	M52-A	52 mm	8034986	VSVA-B-M52-AZ-D2-1T1L
	0	5/2-way valve, single solenoid, Mechanical spring return	M52-M	52 mm	8034987	VSVA-B-M52-MZ-D2-1T1L
	J	5/2-way valve, double solenoid	B52	52 mm	8034984	VSVA-B-B52-Z-D2-1T1L
	D	5/2-way valve, double solenoid, with dominant signal	D52	52 mm	8034985	VSVA-B-D52-Z-D2-1T1L
	В	5/3-way solenoid valve, Mid-position pressurised	P53U	52 mm	8034988	VSVA-B-P53U-Z-D2-1T1L
	G	5/3-way solenoid valve, Mid-position closed	P53C	52 mm	8034990	VSVA-B-P53C-Z-D2-1T1L
	E	5/3-way solenoid valve, Mid-position exhausted	P53E	52 mm	8034989	VSVA-B-P53E-Z-D2-1T1L
	VG	5/3-way solenoid valve, mid-position pressurised 1 to 2, 4 to 5 closed	P53F	52 mm	8034998	VSVA-B-P53F-Z-D2-1T1L

Accessories – Pneumatic components

rdering data – Mani	Code	Description	Width	Part no.	Туре
TSA, port pattern to	ISO 15407-	2 and ISO 5599-2			
\sim	A	2 valve positions, 4 addresses, for double solenoid valves	18 mm	539224	VABV-S4-2S-G18-2T2
	В	2 valve positions, 4 addresses, for double solenoid valves	26 mm	539220	VABV-S4-1S-G14-2T2
	YA	2 valve positions, 4 addresses, for double solenoid valves ¹⁾	18/26 mm	8068911	VABV-S4-12HS-G-CB-2T2
	С	1 valve position, 2 addresses, for double solenoid valves	42 mm	542458	VABV-S2-1S-G38-T2
	D	1 valve position, 2 addresses, for double solenoid valves	52 mm	560841	VABV-S2-2S-G12-T2
-	E	2 valve positions, 2 addresses, for single solenoid valves	18 mm	539226	VABV-S4-2S-G18-2T1
	F	2 valve positions, 2 addresses, for single solenoid valves	26 mm	539222	VABV-S4-1S-G14-2T1
	G	1 valve position, 1 address, for single solenoid valves	42 mm	542459	VABV-S2-1S-G38-T1
	Н	1 valve position, 1 address, for single solenoid valves	52 mm	560842	VABV-S2-2S-G12-T1
SA-F, optimised for	flow rate	•			
	A	2 valve positions, 4 addresses, for double solenoid valves	18 mm	546215	VABV-S4-2HS-G18-2T2
	B	2 valve positions, 4 addresses, for double solenoid valves	26 mm	546211	VABV-54-2113-618-212 VABV-S4-1HS-G14-2T2
	XA	2 valve positions, 4 addresses, for double solenoid valves	18/26 mm	8190411	VABV-54-113-014-212
	C	1 valve position, 2 addresses, for double solenoid valves	42 mm	546219	VABV-54-1215-0-212
	D	1 valve position, 2 addresses, for double solenoid valves	52 mm	560841	VABV-52-1115-050-12
	E	2 valve position, 2 addresses, for single solenoid valves	18 mm	546214	VABV-52-25-612-12 VABV-S4-2HS-G18-2T1
	F	2 valve positions, 2 addresses, for single solenoid valves	26 mm	546210	VABV-54-2115-618-211
	G	1 valve positions, 2 addresses, for single solenoid valves	42 mm	546218	VABV-54-1115-614-211 VABV-S2-1HS-638-T1
	Н	1 valve position, 1 address, for single solenoid valves	52 mm	560842	VABV-52-115-050-11
			52 mm	500042	1101 52 25 012 11
SA-F-CB, with CBUS	S loop-throu				_
\sim	A	2 valve positions, 4 addresses, for double solenoid valves ¹⁾	18 mm	8067932	VABV-S4-2HS-G18-CB-2T2
S. Alexan	В	2 valve positions, 4 addresses, for double solenoid valves $^{1\!\mathrm{)}}$	26 mm	8067940	VABV-S4-1HS-G14-CB-2T2
	C	1 valve position, 2 addresses, for double solenoid valves ¹⁾	42 mm	8068154	VABV-S2-1HS-G38-CB-T2
	D	1 valve position, 2 addresses, for double solenoid valves ¹⁾	52 mm	8068146	VABV-S2-2S-G12-CB-T2
AND THE	E	2 valve positions, 2 addresses, for single solenoid valves ¹⁾	18 mm	8067934	VABV-S4-2HS-G18-CB-2T1
	F	2 valve positions, 2 addresses, for single solenoid valves ¹⁾	26 mm	8067942	VABV-S4-1HS-G14-CB-2T1
	G	1 valve position, 1 address, for single solenoid valves ¹⁾	42 mm	8068156	VABV-S2-1HS-G38-CB-T1
	Н	1 valve position, 1 address, for single solenoid valves ¹⁾	52 mm	8068148	VABV-S2-2S-G12-CB-T1
SA-F-CB, with CBUS	S loop-throu	gh for pilot air switching valve			
<u>~</u>	YB	2 valve positions, 2 addresses, for pilot air switching valve	18 mm	8068913	VABV-S4-2HS-G18-CB-2T5
		 1 valve position, width 18 mm, with CBUS communication 	10		
		• 1 valve position, width 18 mm, double solenoid			
		Sensor evaluation: internal			
$\overline{}$	YC	2 valve positions, 2 addresses, for pilot air switching valve	18/26 mm	8068912	VABV-S4-12HS-G-CB-2T5
		• 1 valve position, width 18 mm, with CBUS communication			
		• 1 valve position, width 26 mm, double solenoid			
		Sensor evaluation: internal			
SA-F-CR with CRU	S loon-throw	gh for soft-start valve			
~ · · · · · · · · · · · · · · · · · · ·	PV	With CBUS loop-through and new voltage zone	41 mm	8068609	VABV-S6-1Q-G38-CB1-T5
•		 Pressure sensor plug-in 	41		
		Sensor evaluation: internal			
		(Ports 2 and 4 are combined),			
		pneumatic connection G3/8, M5			
~	PS	With CBUS loop-through in the same voltage zone	41 mm	8068610	VABV-S6-1Q-G38-CB-T5
		Pressure sensor plug-in			
		 Sensor evaluation: internal 	1		
		(Ports 2 and 4 are combined),			

1) When using single solenoid valves on double solenoid sub-bases, one address will be lost!

Accessories – Pneumatic components

Ordering data – S	upply plate/exte		1		1	1
	Code	Description		Width	Part no.	Туре
/TSA/VTSA-F, sup	ply plate					
	L With exhaust plate, 3/5 common, G1/2				539231	VABF-S6-1-P1A7-G12
	K With exhaust air cover, 3/5 separated (for dual-pressure operation), G1				539230	VABF-S6-1-P1A6-G12
/TSA-F-CB, extens	sion module, pn	eumatic and electric air supply plate				
e (U	Additional air supply With exhaust plate, 3/5 common, G1/2		38 mm	8092506	VABF-S6-1-P1A7-G12-CB
	UW	Additional pneumatic and electrical supply With exhaust plate, 3/5 common, G1/2 Generation of 24 additional valve addresses (electrical supply is provided internally from Uval)			8104042	VABF-S6-1-P8A7-G12-CB
	USW	Additional pneumatic and electrical supply With exhaust plate, 3/5 common, G1/2 Generation of 24 additional valve addresses (electrical supply is provided from new (safe) voltage zone (internally from S2))			8104044	VABF-S6-1-P8A7-G12-CB1
	U	Additional air supply With exhaust air cover, 3/5 separated (for dual-	38 mm	8092502	VABF-S6-1-P1A6-G12-CB	
	UW	Additional pneumatic and electrical supply With exhaust air cover, 3/5 separated (for dual-pressure operation), G1/2 Generation of 24 additional valve addresses (electrical supply is provided internally from Uval)			8104041	VABF-S6-1-P8A6-G12-CB
	USW	Additional pneumatic and electrical supply With exhaust air cover, 3/5 separated (for dual-pressure operation), G1/2 Generation of 24 additional valve addresses (electrical supply is provided from new (safe) voltage zone (internally from S2))			8104043	VABF-S6-1-P8A6-G12-CB1
0°-connection p	late for VTSA/VT	SA-F				
88	P		ting thread G1/8	18 mm	539719	VABF-S4-2-A2G2-G18
				26 mm	539721	VABF-S4-1-A2G2-G14
				42 mm	546097	VABF-S2-1-A1G2-G38
			• ·	52 mm	555702	VABF-S2-2-A1G2-G12

Accessories – Pneumatic components

Ordering data – Vertical	stacking Code	Description			Width	Part no.	Туре
Vertical supply plate							
e 🛱	ZU	Individual compressed air supply,	Connecting thre	ad G1/8	18 mm	540173	VABF-S4-2-P1A3-G18
		duct 1	Connecting thre	ad G1/4	26 mm	540171	VABF-S4-1-P1A3-G14
			Connecting thre	ad G3/8	42 mm	546093	VABF-S2-1-P1A3-G38
			Connecting thread G1/2		52 mm	555786	VABF-S2-2-P1A3-G12
	ZV	Individual compressed air supply,	Connecting thread G1/8		18 mm	8000693	VABF-S4-2-P1A14-G18
		ducts 1 and 14	Connecting thre	ad G1/4	26 mm	8000689	VABF-S4-1-P1A14-G14
			Connecting thre	ad G3/8	42 mm	8000536	VABF-S2-1-P1A14-G38
			Connecting thre	ad G1/2	52 mm	8000549	VABF-S2-2-P1A14-G12
Vertical supply plate for	valves with	central plug, VTSA-F-CB					
\sim	ZU	Individual compressed air supply,	Connecting thre	ad G1/8	18 mm	544435	VABF-S3-2-P1A3-G18
A Contraction		duct 1	Connecting thread G1/4		26 mm	544434	VABF-S3-1-P1A3-G14
			Connecting thread G3/8		42 mm	549100	VABF-S1-1-P1A3-G38
			Connecting thre		52 mm	555785	VABF-S1-2-P1A3-G12
Ordering data – Vertical	stacking						
Sidering uata - vertildi		Pressure regulation for port	Regulating range		Width	Part no.	Туре
	Code		[bar]	[MPa]		i urt no.	1,990
Desulator plate width 1	0		[201]	[α]			
Regulator plate, width 1	1	1	0.5 8.5	0.05 0.85	18 mm	540153	VABF-S4-2-R1C2-C-10
	ZA ZF	1		0.05 0.85	18 mm		
	ZC	2	0.5 6	0.2 0.85	18 mm	540151 540161	VABF-S4-2-R1C2-C-6 VABF-S4-2-R2C2-C-10
	ZH	2	26	0.2 0.6	18 mm	540159	VABF-S4-2-R2C2-C-10
	ZB	4	2 8.5	0.2 0.85	18 mm	540157	VABF-S4-2-R3C2-C-10
	ZG	4	26	0.20.6	18 mm	540155	VABF-S4-2-R3C2-C-6
	ZD	2 and 4	2 8.5	0.2 0.85	18 mm	540165	VABF-S4-2-R4C2-C-10
	ZI	2 and 4	26	0.2 0.6	18 mm	540163	VABF-S4-2-R4C2-C-6
	ZE	2 and 4, reversible	0.5 8.5	0.05 0.85	18 mm	540169	VABF-S4-2-R5C2-C-10
	ZJ	2 and 4, reversible	0.5 6	0.05 0.6	18 mm	540167	VABF-S4-2-R5C2-C-6
	ZL	2. reversible	0.5 8.5	0.05 0.85	18 mm	546252	VABF-S4-2-R6C2-C-10
	ZN	2, reversible	0.5 6	0.05 0.6	18 mm	546248	VABF-S4-2-R6C2-C-10
	ZK	4, reversible	0.5 8.5	0.05 0.85	18 mm	546254	VABF-S4-2-R7C2-C-10
	ZM	4, reversible	0.5 6	0.05 0.6	18 mm	546250	VABF-S4-2-R7C2-C-10
			1 3.5 0	0.05 0.0		5-10250	
Regulator plate, width 2		1	1		1		
S.	ZA	1	0.5 8.5	0.05 0.85	26 mm	540154	VABF-S4-1-R1C2-C-10
	ZF	1	0.5 6	0.05 0.6	26 mm	540152	VABF-S4-1-R1C2-C-6
	ZC	2	2 8.5	0.2 0.85	26 mm	540162	VABF-S4-1-R2C2-C-10
	ZH	2	2 6	0.20.6	26 mm	540160	VABF-S4-1-R2C2-C-6
	ZB	4	2 8.5	0.2 0.85	26 mm	540158	VABF-S4-1-R3C2-C-10
	ZG	4	2 6	0.20.6	26 mm	540156	VABF-S4-1-R3C2-C-6
	ZD	2 and 4	2 8.5	0.2 0.85	26 mm	540166	VABF-S4-1-R4C2-C-10
	ZI	2 and 4	2 6	0.20.6	26 mm	540164	VABF-S4-1-R4C2-C-6
	ZE	2 and 4, reversible	0.5 8.5	0.05 0.85	26 mm	540170	VABF-S4-1-R5C2-C-10
	ZJ	2 and 4, reversible	0.5 6	0.05 0.6	26 mm	540168	VABF-S4-1-R5C2-C-6
	ZL	2, reversible	0.5 8.5	0.05 0.85	26 mm	546251	VABF-S4-1-R6C2-C-10
	ZN	2, reversible	0.5 6	0.05 0.6	26 mm	546247	VABF-S4-1-R6C2-C-6
	ZK	4, reversible	0.5 8.5	0.05 0.85	26 mm	546253	VABF-S4-1-R7C2-C-10
	ZM	4, reversible	0.5 6	0.05 0.6	26 mm	546249	VABF-S4-1-R7C2-C-6

Ordering data – Vertica					lue u		l -
	Code	Pressure regulation for port	Regulating ran	° .	Width	Part no.	Туре
			[bar]	[MPa]			
Regulator plate, width 4	2 mm						
9	ZA	1	0.5 8.5	0.05 0.85	42 mm	546084	VABF-S2-1-R1C2-C-10
	ZF	1	0.5 6	0.05 0.6	42 mm	546083	VABF-S2-1-R1C2-C-6
	ZC	2	1.0 10	0.1 1	42 mm	546088	VABF-S2-1-R2C2-C-10
	ZH	2	1.0 6	0.1 0.6	42 mm	546087	VABF-S2-1-R2C2-C-6
	ZB	4	1.0 10	0.1 1	42 mm	546086	VABF-S2-1-R3C2-C-10
	ZG	4	0.5 6	0.05 0.6	42 mm	546085	VABF-S2-1-R3C2-C-6
	ZD	2 and 4	1.0 10	0.1 1	42 mm	546090	VABF-S2-1-R4C2-C-10
	ZI	2 and 4	1.0 6	0.1 0.6	42 mm	546089	VABF-S2-1-R4C2-C-6
	ZE	2 and 4, reversible	0.5 10	0.05 1	42 mm	546092	VABF-S2-1-R5C2-C-10
	ZJ	2 and 4, reversible	0.5 6	0.05 0.6	42 mm	546091	VABF-S2-1-R5C2-C-6
	ZL	2, reversible	0.5 10	0.05 1	42 mm	546832	VABF-S2-1-R6C2-C-10
	ZN	2, reversible	0.5 6	0.05 0.6	42 mm	546831	VABF-S2-1-R6C2-C-6
	ZK	4, reversible	0.5 10	0.05 1	42 mm	546834	VABF-S2-1-R7C2-C-10
	ZM	4, reversible	0.5 6	0.05 0.6	42 mm	546833	VABF-S2-1-R7C2-C-6
Regulator plate, width 5	2 mm						
0	ZA	1	0.5 10	0.05 1	52 mm	555772	VABF-S2-2-R1C2-C-10
	ZF	1	0.5 6	0.05 0.6	52 mm	555771	VABF-S2-2-R1C2-C-6
	ZC	2	1.0 10	0.1 1	52 mm	555774	VABF-S2-2-R2C2-C-10
	ZH	2	1.0 6	0.1 0.6	52 mm	555773	VABF-S2-2-R2C2-C-6
	ZB	4	1.0 10	0.1 1	52 mm	555776	VABF-S2-2-R3C2-C-10
	ZG	4	1.0 6	0.1 0.6	52 mm	555775	VABF-S2-2-R3C2-C-6
	ZD	2 and 4	1.0 10	0.1 1	52 mm	555778	VABF-S2-2-R4C2-C-10
	ZI	2 and 4	1.0 6	0.1 0.6	52 mm	555777	VABF-S2-2-R4C2-C-6
	ZE	2 and 4, reversible	0.5 10	0.05 1	52 mm	555780	VABF-S2-2-R5C2-C-10
	ZJ	2 and 4, reversible	0.5 6	0.05 0.6	52 mm	555779	VABF-S2-2-R5C2-C-6
	ZL	2, reversible	0.5 10	0.05 1	52 mm	555782	VABF-S2-2-R6C2-C-10
	ZN	2, reversible	0.5 6	0.05 0.6	52 mm	555781	VABF-S2-2-R6C2-C-6
	ZK	4, reversible	0.5 10	0.05 1	52 mm	555784	VABF-S2-2-R7C2-C-10
	ZM	4, reversible	0.5 6	0.05 0.6	52 mm	555783	VABF-S2-2-R7C2-C-6

Ordering data – Vertical	stacking						
	Code	Pressure regulation for port	Regulating rang	ge	Width	Part no.	Туре
			[bar]	[MPa]			
Regulator plate for valves	s with symm	netrical design, width 18 mm					
<u></u>	ZAY	1	0.5 8.5	0.05 0.85	18 mm	560756	VABF-S4-2-R1C2-C-10E
	ZFY	1	0.5 6	0.05 0.6	18 mm	560758	VABF-S4-2-R1C2-C-6E
	ZCY	2	2 8.5	0.2 0.85	18 mm	560763	VABF-S4-2-R2C2-C-10E
	ZHY	2	2 6	0.2 0.6	18 mm	560765	VABF-S4-2-R2C2-C-6E
	ZDY	2 and 4	2 8.5	0.2 0.85	18 mm	560767	VABF-S4-2-R4C2-C-10E
	ZIY	2 and 4	2 6	0.2 0.6	18 mm	560769	VABF-S4-2-R4C2-C-6E
	ZEY	2 and 4, reversible	0.5 8.5	0.05 0.85	18 mm	560771	VABF-S4-2-R5C2-C-10E
	ZJY	2 and 4, reversible	0.5 6	0.05 0.6	18 mm	560773	VABF-S4-2-R5C2-C-6E
	ZLY	2, reversible	0.5 8.5	0.05 0.85	18 mm	560775	VABF-S4-2-R6C2-C-10E
	ZNY	2, reversible	0.5 6	0.05 0.6	18 mm	560777	VABF-S4-2-R6C2-C-6E
Regulator plate for valves	with symm	netrical design, width 26 mm					
	ZAY	1	0.5 8.5	0.05 0.85	26 mm	560757	VABF-S4-1-R1C2-C-10E
	ZFY	1	0.5 6	0.05 0.6	26 mm	549876	VABF-S4-1-R1C2-C-6E
	ZCY	2	2 8.5	0.2 0.85	26 mm	560764	VABF-S4-1-R2C2-C-10E
	ZHY	2	2 6	0.2 0.6	26 mm	560766	VABF-S4-1-R2C2-C-6E
	ZDY	2 and 4	2 8.5	0.2 0.85	26 mm	560768	VABF-S4-1-R4C2-C-10E
	ZIY	2 and 4	2 6	0.2 0.6	26 mm	560770	VABF-S4-1-R4C2-C-6E
	ZEY	2 and 4, reversible	0.5 8.5	0.05 0.85	26 mm	560772	VABF-S4-1-R5C2-C-10E
	ZJY	2 and 4, reversible	0.5 6	0.05 0.6	26 mm	560774	VABF-S4-1-R5C2-C-6E
	ZLY	2, reversible	0.5 8.5	0.05 0.85	26 mm	560776	VABF-S4-1-R6C2-C-10E
	ZNY	2, reversible	0.5 6	0.05 0.6	26 mm	560778	VABF-S4-1-R6C2-C-6E
			0.5 0	0.05 0.0	20 1111	500770	
Regulator plate for valves	with symm	netrical design, width 42 mm ¹⁾					1
<u>9</u>	ZAY	1	0.5 10	0.05 1	42 mm	-	VABF-S2-1-R1C2-C-10E
	ZFY	1	0.5 6	0.05 0.6	42 mm	-	VABF-S2-1-R1C2-C-6E
	ZCY	2	0.5 10	0.05 1	42 mm	-	VABF-S2-1-R2C2-C-10E
	ZHY	2	0.5 6	0.05 0.6	42 mm	-	VABF-S2-1-R2C2-C-6E
	ZBY	4	0.5 10	0.05 1	42 mm	-	VABF-S2-1-R3C2-C-10E
< Dar	ZGY	4	0.5 6	0.05 0.6	42 mm	-	VABF-S2-1-R3C2-C-6E
	ZDY	2 and 4	0.5 10	0.05 1	42 mm	-	VABF-S2-1-R4C2-C-10E
	ZIY	2 and 4	0.5 6	0.05 0.6	42 mm	-	VABF-S2-1-R4C2-C-6E
	ZEY	2 and 4, reversible	0.5 10	0.05 1	42 mm	-	VABF-S2-1-R5C2-C-10E
	ZJY	2 and 4, reversible	0.5 6	0.05 0.6	42 mm	-	VABF-S2-1-R5C2-C-6E
	ZLY	2, reversible	0.5 10	0.05 1	42 mm	-	VABF-S2-1-R6C2-C-10E
	ZNY	2, reversible	0.5 6	0.05 0.6	42 mm	-	VABF-S2-1-R6C2-C-6E
	ZKY	4, reversible	0.5 10	0.05 1	42 mm	-	VABF-S2-1-R7C2-C-10E
	ZMY	4, reversible	0.5 6	0.05 0.6	42 mm	-	VABF-S2-1-R7C2-C-6E
Pegulator plate for values	with symm	netrical design, width 52 mm ¹⁾					
	ZAY		0.5 10	0.05 1	52 mm	-	VABF-S2-2-R1C2-C-10E
eŭ	ZFY	1	0.5 6	0.05 0.6	52 mm	-	VABF-S2-2-R1C2-C-0E
	ZCY	2	0.5 6	0.05 0.6	52 mm		VABF-S2-2-R1C2-C-6E
	ZHY	2			52 mm	-	VABF-S2-2-R2C2-C-10E
	ZBY	4	0.5 6	0.05 0.6		_	
	ZGY	4	0.5 10	0.05 1	52 mm 52 mm	-	VABF-S2-2-R3C2-C-10E VABF-S2-2-R3C2-C-6E
	ZDY	2 and 4				-	
		2 and 4 2 and 4	0.5 10	0.05 1	52 mm	-	VABF-S2-2-R4C2-C-10E
	ZIY ZEY	2 and 4 2 and 4, reversible	0.5 6	0.05 0.6	52 mm	-	VABF-S2-2-R4C2-C-6E
				0.05 1	52 mm	-	VABF-S2-2-R5C2-C-10E
	ZJY	2 and 4, reversible	0.5 6	0.05 0.6	52 mm	-	VABF-S2-2-R5C2-C-6E
	ZLY	2, reversible	0.5 10	0.05 1	52 mm	-	VABF-S2-2-R6C2-C-10E
	ZNY	2, reversible	0.5 6	0.05 0.6	52 mm	-	VABF-S2-2-R6C2-C-6E
	ZKY	4, reversible	0.5 10	0.05 1	52 mm	-	VABF-S2-2-R7C2-C-10E
	ZMY	4, reversible	0.5 6	0.05 0.6	52 mm	-	VABF-S2-2-R7C2-C-6E

1) These functions are only available via the pressure regulator configurator VABF-S2 for width 42 mm and 52 mm only (ISO 5599-2, ISO 1 and ISO 2)

Ordering data – Vertical stacking for valves with central plug. VTSA-F-CB

	Code	Pressure regulation for port	Regulating ran	-	Width	Part no.	Туре
			[bar]	[MPa]			
egulator plate, width	18 mm						
\sim	ZA	1	0.5 8.5	0.05 0.85	18 mm	543526	VABF-S3-2-R1C2-C-10
	ZF	1	0.5 6	0.05 0.6	18 mm	543524	VABF-S3-2-R1C2-C-6
	C ZC	2	2 8.5	0.2 0.85	18 mm	543534	VABF-S3-2-R2C2-C-10
	SA ZH	2	2 6	0.2 0.6	18 mm	543532	VABF-S3-2-R2C2-C-6
	ZB	4	2 8.5	0.2 0.85	18 mm	543530	VABF-S3-2-R3C2-C-10
	ZG	4	2 6	0.2 0.6	18 mm	543528	VABF-S3-2-R3C2-C-6
	ZD	2 and 4	2 8.5	0.2 0.85	18 mm	543538	VABF-S3-2-R4C2-C-10
	ZI	2 and 4	2 6	0.2 0.6	18 mm	543536	VABF-S3-2-R4C2-C-6
	ZE	2 and 4, reversible	0.5 8.5	0.05 0.85	18 mm	543542	VABF-S3-2-R5C2-C-10
	ZJ	2 and 4, reversible	0.5 6	0.05 0.6	18 mm	543540	VABF-S3-2-R5C2-C-6
	ZL	2, reversible	0.5 8.5	0.05 0.85	18 mm	546788	VABF-S3-2-R6C2-C-10
	ZN	2, reversible	0.5 6	0.05 0.6	18 mm	546786	VABF-S3-2-R6C2-C-6
	ZK	4, reversible	0.5 8.5	0.05 0.85	18 mm	546792	VABF-S3-2-R7C2-C-10
	ZM	4, reversible	0.5 6	0.05 0.6	18 mm	546790	VABF-S3-2-R7C2-C-6
egulator plate, width	26 mm						
		1	0.5 8.5	0.05 0.85	26 mm	543527	VABF-S3-1-R1C2-C-10
Ka S	ZA ZF	1	0.5 6				
	a, ZC	2		0.05 0.6	26 mm	543525	VABF-S3-1-R1C2-C-6
	9		2 8.5	0.2 0.85	26 mm	543535	VABF-S3-1-R2C2-C-10
No and a second	ZH	2	2 6	0.2 0.6	26 mm	543533	VABF-S3-1-R2C2-C-6
\checkmark	ZB	4	2 8.5	0.2 0.85	26 mm	543531	VABF-S3-1-R3C2-C-10
	ZG	4	2 6	0.2 0.6	26 mm	543529	VABF-S3-1-R3C2-C-6
	ZD	2 and 4	2 8.5	0.2 0.85	26 mm	543539	VABF-S3-1-R4C2-C-10
	ZI	2 and 4	2 6	0.2 0.6	26 mm	543537	VABF-S3-1-R4C2-C-6
	ZE	2 and 4, reversible	0.5 8.5	0.05 0.85	26 mm	543543	VABF-S3-1-R5C2-C-10
	ZJ	2 and 4, reversible	0.5 6	0.05 0.6	26 mm	543541	VABF-S3-1-R5C2-C-6
	ZL	2, reversible	0.5 8.5	0.05 0.85	26 mm	546789	VABF-S3-1-R6C2-C-10
	ZN	2, reversible	0.5 6	0.05 0.6	26 mm	546787	VABF-S3-1-R6C2-C-6
	ZK	4, reversible	0.5 8.5	0.05 0.85	26 mm	546793	VABF-S3-1-R7C2-C-10
	ZM	4, reversible	0.5 6	0.05 0.6	26 mm	546791	VABF-S3-1-R7C2-C-6
egulator plate, width	42 mm						
\wedge	ZA	1	0.5 10	0.05 1	42 mm	546818	VABF-S1-1-R1C2-C-10
	ZF	1	0.5 6	0.05 0.6	42 mm	546817	VABF-S1-1-R1C2-C-6
UN AL	ZC	2	1.0 10	0.1 1	42 mm	546822	VABF-S1-1-R2C2-C-10
	ZL ZH	2	1.0 6	0.1 0.6	42 mm	546821	VABF-S1-1-R2C2-C-6
	劉	4	1.0 10	0.1 1	42 mm	546820	VABF-S1-1-R3C2-C-10
$\mathbf{\nabla}$	ZG	4	0.5 6	0.05 0.6	42 mm	546819	VABF-S1-1-R3C2-C-6
	ZD	2 and 4	1.0 10	0.1 1	42 mm	546824	VABF-S1-1-R4C2-C-10
	ZI	2 and 4	1.0 6	0.1 0.6	42 mm	546823	VABF-S1-1-R4C2-C-6
	ZE	2 and 4, reversible	0.5 10	0.05 1	42 mm	546826	VABF-S1-1-R5C2-C-10
	ZJ	2 and 4, reversible	0.5 6	0.05 0.6	42 mm	546825	VABF-S1-1-R5C2-C-6
	ZL	2, reversible	0.5 10	0.05 1	42 mm	546828	VABI-51-1-R6C2-C-10
	ZN	2, reversible	0.5 6	0.05 0.6	42 mm	546827	VABF-S1-1-R6C2-C-6
	ZK	4, reversible	0.5 10	0.05 0.0	42 mm	546830	VABF-S1-1-R7C2-C-10
	ZM	4, reversible	0.5 6	0.05 0.6	42 mm	546829	VABI-S1-1-R7C2-C-10

Ordering data – Vertical stacking for valves with central plug, VTSA-F-CB

	Code	Pressure regulation for port	Regulating ran	ge	Width	Part no.	Туре
			[bar]	[MPa]			
ulator plate, widt	th 52 mm						
\sim	ZA	1	0.5 10	0.05 1	52 mm	555758	VABF-S1-2-R1C2-C-10
	ZF	1	0.5 6	0.05 0.6	52 mm	555757	VABF-S1-2-R1C2-C-6
	ZC	2	1.0 10	0.1 1	52 mm	555760	VABF-S1-2-R2C2-C-10
	ZH ZH	2	1.0 6	0.1 0.6	52 mm	555759	VABF-S1-2-R2C2-C-6
Ų	ZB ZB	4	1.0 10	0.1 1	52 mm	555762	VABF-S1-2-R3C2-C-10
	ZG	4	1.0 6	0.1 0.6	52 mm	555761	VABF-S1-2-R3C2-C-6
	ZD	2 and 4	1.0 10	0.1 1	52 mm	555764	VABF-S1-2-R4C2-C-10
	ZI	2 and 4	1.0 6	0.1 0.6	52 mm	555763	VABF-S1-2-R4C2-C-6
	ZE	2 and 4, reversible	0.5 10	0.05 1	52 mm	555766	VABF-S1-2-R5C2-C-10
	ZJ	2 and 4, reversible	0.5 6	0.05 0.6	52 mm	555765	VABF-S1-2-R5C2-C-6
	ZL	2, reversible	0.5 10	0.05 1	52 mm	555768	VABF-S1-2-R6C2-C-10
	ZN	2, reversible	0.5 6	0.05 0.6	52 mm	555767	VABF-S1-2-R6C2-C-6
	ZK	4, reversible	0.5 10	0.05 1	52 mm	555770	VABF-S1-2-R7C2-C-10
	ZM	4, reversible	0.5 6	0.05 0.6	52 mm	555769	VABF-S1-2-R7C2-C-6
ering data							
	Code	Description			Width	Part no.	Туре
sure gauge							
\sim	Т	With cartridge connection for	scale in bar/psi,		18 mm	543487	PAGN-26-16-P10
		regulator, 10 bar	display range 01	6 bar/0240 psi,	26 mm		

Pressure gauge						
	T	With cartridge connection for	scale in bar/psi,	18 mm	543487	PAGN-26-16-P10
		regulator, 10 bar	display range 016 bar/0240 psi,	26 mm		
				42 mm	548010	PAGN-40-16-P10
				52 mm		
	U	With cartridge connection for	scale in bar/psi,	18 mm	543488	PAGN-26-10-P10
		regulator, 6 bar,	display range 010 bar/0145 psi,	26 mm		
		for regulator plate code ZF, ZG, ZH, ZI, ZJ,	42 mm	548009	PAGN-40-10-P10	
			ZM, ZN	52 mm		
		regulator, 10 bar display range 016 bar/01.6 MPa, for regulator plate code ZA, ZB, ZC, ZD, ZE, 4	18 mm	563735	PAGN-26-1.6M-P10	
			for regulator plate code ZA, ZB, ZC, ZD, ZE,	26 mm		
				42 mm	563737	PAGN-40-1.6M-P10
			ZK, ZL	52 mm	1	
	WU With cartridge connection for	Scale in MPa,	18 mm	563736	PAGN-26-1M-P10	
		regulator, 6 bar	display range 016 bar/01 MPa	26 mm]	
		for regulator plate code ZF, ZG, ZH, ZI, ZJ,	42 mm	563738	PAGN-40-1M-P10	
			ZM, ZN	52 mm	1	
	VT	With cartridge connection for	Scale in psi/bar,	18 mm	563731	PAGN-26-232P-P10
		regulator, 10 bar	display range 016 bar/0232 psi	26 mm		
			for regulator plate code ZA, ZB, ZC, ZD, ZE,	42 mm	563733	PAGN-40-232P-P10
			ZK, ZL	52 mm		
	PS	With cartridge connection for	Scale in psi/bar,	18 mm	563732	PAGN-26-145P-P10
		regulator, 6 bar	display range 010 bar/0145 psi	26 mm	1	
			for regulator plate code ZF, ZG, ZH, ZI, ZJ,	42 mm	563734	PAGN-40-145P-P10
			ZM, ZN	52 mm		
	SGR	Red-green scale, with cartridge	Scale in bar,	18 mm	8090378	PAGN-26-10-P10-RG
		connection for regulator, 6 bar	display range 010 bar	26 mm		

Ordering data – Vertica	al stacking Code	Description		Part no.	Туре
Cartridge for regulator p	olate				
	-	For tubing O.D. 4 mm	1 piece	172972	QSP10-4
	-	Adapter for pressure gauge (allows products with threaded connection G1/8 to be attached to the car- tridge connection)	Pack of 6	565811	QSP10-G1/8
Throttle plate			-		-
	X	Controls the flow of exhaust air downstream of the valve to ducts 3 and 5	18 mm	540176	VABF-S4-2-F1B1-C
•			26 mm	540175	VABF-S4-1-F1B1-C
Ne .			42 mm	546095	VABF-S2-1-F1B1-C
			52 mm	555789	VABF-S2-2-F1B1-C
Throttle plate for valves	with central	plug. VTSA-F-CB			
	X	For port pattern to ISO 15407-2 and ISO 5599-2,	18 mm	543603	VABF-S3-2-F1B1-C
		Controls the flow of exhaust air downstream of the valve to ducts 3 and 5	26 mm	543604	VABF-S3-1-F1B1-C
			42 mm	549102	VABF-S1-1-F1B1-C
			52 mm	555788	VABF-S1-2-F1B1-C
Vertical pressure shut-c	offiniate				
	ZT	3/2-way valve for shutting off the operating pressure at the valve position	18 mm	542884	VABF-S4-2-L1D1-C
		Pressure separation can be shut off on the valve assembly	26 mm	542885	VABF-S4-1-L1D1-C
			42 mm	546096	VABF-S2-1-L1D1-C
			52 mm	555791	VABF-S2-2-L1D1-C
\sim	ZS	3/2-way valve for shutting off the operating pressure at the valve position	18 mm	8001178	VABF-S4-2-L1D2-C
	>	Pressure separation can be shut off on the valve assembly using a key	26 mm	8001179	VABF-S4-1-L1D2-C
	ff mlata fam.				
ventical pressure shut-c		alves with central plug, VTSA-F-CB 3/2-way valve for shutting off the operating pressure at the valve position	18 mm	5//3601	VARE-53-2-1101-C
	ZT	Pressure separation can be shut off on the valve assembly	18 mm 26 mm	543601	VABF-S3-2-L1D1-C VABF-S3-1-L1D1-C
			42 mm	543602 549103	VABF-S3-1-L1D1-C
			52 mm	555790	VABF-S1-2-L1D1-C
Covering		·			
\sim	L	Blanking plate for vacant position	18 mm	539213	VABB-S4-2-WT
Non I			26 mm	539212	VABB-S4-1-WT
			42 mm	543186	VABB-S2-1-WT
			52 mm	560845	VABB-S2-2-WT
<u>ب</u>	-	Sealing cap for electrical links (with individual connection), size 18 mm and 26 mm	Pack of 10	547713	VABD-S4-E-C
	-	Seal (with individual connection), width 42 mm and 52 mm	2 pieces	571343	VABD-S2-1-S-C

Ordering data – Accessories for valves with central plug, VTSA-F-CB

	Description		Part no.	Туре
	Cover plate to seal spare or vacant valve positions	18 mm	161114	NDV-02-VDMA
		26 mm	161107	NDV-01-VDMA
0	Sealing cap for electrical links (with individual connection), size 18 mm and 26 mm	Pack of 10	547713	VABD-S4-E-C
	Seal (with individual connection), width 42 mm and 52 mm	2 pieces	571343	VABD-S2-1-S-C

Accessories – Electrical components

Ordering data	اما			lue u		1-
	Code	Description		Width	Part no.	Туре
Multi-pin node for VTS	A/VTSA-F	Transfer Later of size		r	5/2/42	
	MP1	Terminal strip, 36-pin	- 🗍 - Note	-	543412	VABE-S6-1LF-C-M1-C36M VABE-S6-1LT-C-M1-S37
	MP1 MP4	Sub-D plug, 37-pin Round plug, 19-pin	-	-	543414 543415	VABE-S6-1LF-C-M1-S37
	1111-4		Multi-pin node supplied without cover.	-	543415	VADE-S0-1LF-C-M1-R19
			Please order appropriate cover with ca-			
¥			ble separately.			
Individual electrical co	nnection for	VTSA/VTSA-F				
	MP2	Multi-pin node with individua	al connection M12, 6-way	-	549046	VABE-S6-LT-C-S6-R5
	MP3	Multi-pin node with individua		-	549047	VABE-S6-LT-C-S10-R5
	-	Cover for individual connection	on M12, 6-way	-	549048	VAEM-S6-C-S6-R5
	-	Cover for individual connection		-	549049	VAEM-S6-C-S10-R5
Pneumatic interface fo	r \/TCA /\/TCA	-F				
		For electrical terminal CPX in	nolvmer	_	543416	VABA-S6-1-X1
	_	For electrical terminal CPX in		-	550663	VABA-S6-1-X2
	-	For electrical terminal CPX in		-	573613	VABA-S6-1-X2-D
		with changed diagnostic func				
	-	For electrical terminal CPX-AP		-	8152356	VABA-S6-1-AP
Pneumatic interface fo						
	RA	For electrical terminal CPX in	nolymer		8082877	VABA-S6-1-X1-CB
			ort circuit and undervoltage of valves,		0002077	
		wire break per solenoid coi				
		For electrical terminal CPX in	metal	-	8082876	VABA-S6-1-X2-CB
			ort circuit and undervoltage of valves,			
· · ·		wire break per solenoid coi				
	RD		terface for PROFIsafe only) in metal with	-	8068241	VABA-S6-1-X2-F2-CB
		 2 safe voltage zones and 1 safe output (connection: 	M12)			
			ort circuit and undervoltage of valves,			
		wire break per solenoid coi				
	RC		terface for PROFIsafe only) in metal with	-	8068240	VABA-S6-1-X2-F1-CB
		• 3 safe voltage zones				
		 Integrated diagnostics (sho wire break per solenoid coil 	ort circuit and undervoltage of valves,			
		wire break per solenoid col	(()			
	RB	For electrical terminal CPX (in	terface for fieldbus only) in polymer	-	8082879	VABA-S6-1-X1-3V-CB
		 With 3 voltage zones 				
		With external power supply				
Contraction of the second seco			ort circuit and undervoltage of valves,			
		wire break per solenoid co		_		
	RB		terface for fieldbus only) in metal	-	8082878	VABA-S6-1-X2-3V-CB
		 With 3 voltage zones With external power supply 	/ 3xM12			
			ort circuit and undervoltage of valves,			
		wire break per solenoid coi				

Accessories – Electrical components

ordering data	1			1
	Code	Description	Part no.	Туре
ectrical interface IO	-Link®			
		IO-Link [®] interface for 16 valve positions	8152353	VABA-S6-1-PT
neumatic interface f	or VTSA-F-CB			
	XB	Pneumatic interface, for expansion by 3 external power supplies for the zones	8152438	VABA-S6-1-X2-3V-CB-AL
	XC	Pneumatic interface for extending by 3 safe internal zones (PROFIsafe)	8152437	VABA-S6-1-X2-F1-CB-AL
	XD XD	Pneumatic interface for extending by 2 safe internal zones + 1 safe output (PROFIsafe)	8152436	VABA-S6-1-X2-F2-CB-AL
	PC	Pneumatic interface with additional power supply for extending by 3 safe internal zones (PROFIsafe)	8152435	VABA-S6-1-X2-F1-CB2-AL
	PD	Pneumatic interface with additional power supply for extending by 2 safe internal zones + 1 safe output (PROFIsafe)	8152434	VABA-S6-1-X2-F2-CB2-AL
lectrical interface fo	r AS-Interface	for VTSA/VTSA-F		
	-	4 inputs/4 outputs	549042	VABE-S6-1LF-C-A4-E
		8 inputs/8 outputs	549043	VABE-S6-1LF-C-A8-E
S-Interface module	for VTSA/VTSA	·F		
	-	4 inputs/4 outputs	549044	VAEM-S6-S-FAS-4-4E
	- 79	8 inputs/8 outputs	549045	VAEM-S6-S-FAS-8-8E
Connection block for	AS-Interface fo	or VTSA/VTSA-F		
	Х	4x M12, 5-pin, double, socket	195704	CPX-AB-4-M12x2-5POL
	GW	4x M12, 5-pin, socket, metal thread	541254	CPX-AB-4-M12x2-5POL-R
U 488	R	8x M8, 3-pin, socket	195706	CPX-AB-8-M8-3POL
<u> </u>		8x spring-loaded terminal, Cage Clamp, 4-pin	195708	CPX-AB-8-KL-4POL
		ox spring-todueu terminat, cage clamp, 4-pm	195700	CFA-AD-O-AL-4FUL

Accessories – Electrical components

			Part no.	Туре
	Description			
Connecting cable fo	or electrical connection of individual valves with central plug, VSTA-F-	B		
OF WE A	 Straight socket, M12x1, 5-pin Open end, 4-core 	5 m	8078240	NEBA-M12G5-U-5-N-LE4
ALL	 Straight socket, M8x1, 3-pin Straight plug M12x1, 3-pin With 2x inscription label holders 	0.5 m	8078278	NEBA-M8G3-U-0.5-N-M12G3
Ordering data	Description		Part no	Tune
_	Description		Part no.	Туре
_	rt interface, for electrical interface IO-Link®			
_	rt interface, for electrical interface IO-Link® PROFIBUS bus node		570040	CTEU-PB
_	rt interface, for electrical interface IO-Link®			

Accessories – General

Ordering data					
	Code	Description		Part no.	Туре
Connecting cable, Sub	o-D (TPE-U(PL	JR), IP65)			
<u> </u>	GA	Connecting cable for max. 8 solenoid coils, 10-core	2.5 m	539240	NEBV-S1W37-E-2.5-LE10
	GB		5 m	539241	NEBV-S1W37-E-5-LE10
	GC		10 m	539242	NEBV-S1W37-E-10-LE10
	∂ GD	Connecting cable for max. 22 solenoid coils, 26-core	2.5 m	539243	NEBV-S1W37-E-2.5-LE26
	GE		5 m	539244	NEBV-S1W37-E-5-LE26
	GF	1	10 m	539245	NEBV-S1W37-E-10-LE26
	GG	Connecting cable for max. 32 solenoid coils, 37-core	2.5 m	539246	NEBV-S1W37-K-2.5-LE37
	GH		5 m	539247	NEBV-S1W37-K-5-LE37
	GI		10 m	539248	NEBV-S1W37-K-10-LE37
Connecting cable, Sub		5)			
	GK	Connecting cable for max. 8 solenoid coils, 10-core	2.5 m	543271	NEBV-S1W37-KM-2.5-LE10
	GL		5 m	543272	NEBV-S1W37-KM-5-LE10
	GM	-	10 m	543273	NEBV-S1W37-KM-10-LE10
- NA	> GN	Connecting cable for max. 23 solenoid coils, 27-core	2.5 m	543274	NEBV-S1W37-KM-2.5-LE27
\checkmark \checkmark	GO		5 m	543275	NEBV-S1W37-KM-5-LE27
	GP	-	10 m	543276	NEBV-S1W37-KM-10-LE27
	GQ	Connecting cable for max. 32 solenoid coils, 37-core	2.5 m	543277	NEBV-S1W37-KM-2.5-LE37
	GR		5 m	543278	NEBV-S1W37-KM-5-LE37
	GS	-	10 m	543279	NEBV-S1W37-KM-10-LE37
	05		10 11	545215	
Cover for multi-pin plu	ug for VTSA/V				
	-	For configuration by the user		545974	NECV-S1W37
Ordering data – End p	plates				
	Code	Description		Part no.	Туре

	Code	Description	Part no.	Туре
Right, with threaded	connection			
600	V	With supply air/exhaust air, internal pilot air supply, G1/2 (no port 14)	539234	VABE-S6-1R-G12
	V1	With supply air/exhaust air, internal pilot air supply, G3/4 (port 14 is sealed with a blanking plug)	560837	VABE-S6-2R-G34
600	X	With supply air/exhaust air, external pilot air supply, G1/2	539236	VABE-S6-1RZ-G12
	X1	With supply air/exhaust air, external pilot air supply, G3/4	560839	VABE-S6-2RZ-G34
With pilot air selector	•			

1) Code letter within the order code for a valve terminal configuration

Accessories – General

Code	Description	Weight	Part no.	Туре
S	Duct separation 1, 3, 5	57 g	539228	VABD-S6-1-P3-C
T	Duct separation 1	43 g	539227	VABD-S6-1-P1-C
R	Duct separation 3, 5	54 g	539229	VABD-S6-1-P2-C
L	Seal between sub-bases, duct 1, 3, 5 open, port 14 blocked (colour coding: white)	40 g	573191	VABD-S6-1-P7-C
TL	Seal between sub-bases, duct 1 blocked, port 14 blocked (colour coding: red) Note: additional pilot air supply required	43 g	8060483	VABD-S6-1-P8-C
К	Seal between sub-bases, duct 1, 3, 5 blocked, port 14 blocked (colour coding: green)	57 g	8034612	VABD-S6-1-P6-C

Ordering data	Code	Description		Part no.	Туре
Cover caps					
	N	Cover cap for manual override, non-detenting	Pack of 10	541010	VAMC-S6-CH
	V	Cover cap for manual override, concealed	Pack of 10	541011	VAMC-S6-CS
	A	Cover cap, heavy duty, for manual override, non-detenting heavy duty, detenting via accessory (key) (The cover cap is provided for one-off mounting only)	Pack of 10	4105147	VAMC-B-S6-CTR
Accessories for manua	Il override, l	heavy duty			
	-	Coded key (accessory) for actuating the cover cap, heavy duty, for detenting position (VAMC-B-S6-CTR)	1 piece	1662543	АНВ-МЕВ-В


- 🏺 - Note

There is a wide range of preconfigured solenoid valves with cover cap for manual override and correct valve type code available to order in the sections on solenoid valves.

Accessories – General

	Code	Description		Part no.	Туре
tion label hold	ers/inscripti	on labels			
\geq	В	Clip-on inscription label holder for valve cap	5 pieces	540888	ASCF-T-S6
>	BZ	Clip-on inscription label holder for valve cap with additional text fields (electrical and pneumatic zone separation)	4 pieces	8106532	ASCF-T-S6-Z
>	T	Inscription label holder for manifold blocks/manifold sub-bases VTSA/VTSA-F	5 pieces	540889	ASCF-M-S6
	TD	Inscription label holder for manifold blocks/manifold sub-bases VTSA/VTSA-F, size 52 mm	5 pieces	562577	ASCF-M-S2-2
	-	Identification clip for manifold blocks/manifold sub-bases VTSA-F-CB (code A, B, C, E, F, G, PV, PS)	-	8110689	ASCF-M-S6-1
× IIII	-	Inscription label for ISO 15407 valves with individual electrical connec- tion (20 labels in frames)	20 pieces	18182	IBS-9x20
	-	Inscription label for pressure zone separation • 4 inscription labels, duct 1/3/5 blocked • 4 inscription labels, duct 1 blocked • 4 inscription labels, duct 3/5 blocked	3x4 pieces	8003303	ASLR-L-S6-2016
lmounting					
		VTSA and VTSA-F	3 pieces	526032	CPX-CPA-BG-NRH
ounting			1		
	-	Mounting bracket with a mounting hole for M5 screw	5 pieces	539214	VAME-S6-10-W
	U	Mounting bracket with a mounting hole for M4 screw and a mounting hole for M6 screw	1 piece	567038	VAME-S6-W-M46
	AW	Mounting bracket for length compensation on the CPX side when mount- ing using support system Set comprising 1 angle bracket and 2 screws	1 piece	2721419	CPX-M-BG-VT-2X
ocumentation					
	D	User documentation for valve terminal VTSA/VTSA-F	German	538922	VTSA/VTSA-F-DE
Ì	≥ E		English	538923	VTSA/VTSA-F-EN
atic connection					
tion of possibl.	e fittings, bla	anking plugs, silencers and be found in the chapter Accessories \rightarrow page 242			

Internet \rightarrow connection technology, silencer, blanking plug



spring return in width 18 mm and 26 mm features valve diagnostics. It is available as a valve with plug-in or individual connection with pilot valves to ISO 15218 and square plug type C. The normal position of the piston spool is monitored by the inductive sensor. This valve is not a safety device in accordance with the Machinery Directive 2006/42/EC. When used in higher categories, the sensor signal from the valve must be evaluated by the control system.

This valve is suitable for use in safety-related parts of control systems to EN ISO 13849-1.

The control block has been developed and manufactured in accordance with the basic and proven safety principles of EN ISO 13849-2. in machines and automation systems and must only be used in industrial applications (high-demand mode).

Decentralised individual connection variant

Valve on individual sub-base (square plug or plug-in) with integrated switching position sensing. The electrical connection is established via either a standardised 4-pin M12 plug 24 V DC (ISO 15407-2), a 4-pin spring-loaded terminal or a cable (open end) 24 V DC, which can be configured by the user. The individual sub-base can be supplied with internal or external pilot air depending on the version.

Variant for valve terminal VTSA/VTSA-F



The valves with integrated switching position sensing in plug-in design for valve terminal VTSA/VTSA-F/VTSA-F-CB can be used regardless of the type of electrical actuation (individual, multi-pin plug or fieldbus/control block connection). Pilot air supply: The valve terminal can be supplied with internal or external pilot air via the various end plate variants.

- Note

Valves in plug-in design are always supplied with pilot air via duct 14 in the manifold sub-base.

1) The circuit diagram represents a valve with a proximity switch with a N/O switching output signal. In accordance with ISO 1219-1, this symbol is used for both N/O and N/C. The switching element function of the sensors used here is designed as an N/C contact.

- 🖡 - Note

Pilot exhaust air port 12 is exhausted directly at the valve, without a connection. If the customer requests a "turned seal", exhaust air is vented at the end plates of the valve terminal, which doesn't conform to the ISO standard.

Safety data

Safety data	
Conforms to standard	EN 13849-1/2
CE marking (see declaration of conformity)	To EU EMC Directive ¹⁾
Shock resistance	Shock test with severity level 2, to EN 60068-2-27
Vibration resistant	Transport application test with severity level 2, to EN 60068-2-6

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/sp → Certificates.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Safety characteristics

Valve function 5/2-way, single solenoid	Test pulses		
	Max. positive test pulse with logic 0 [µs]	Max. negative test pulse with logic 1 [µs]	
VSVA-B-M52-MZA1-1T1L	1200	1100	
VSVA-B-M52-MZA2-1T1L	1500	800	
VSVA-B-M52-MZ-A1-1C1	1800	800	

General technical data

ocherat teenneat aata				
Valve	VSVA-B-M52-MZD-A2-1T1L	VSVA-B-M52-MZD-A1-1T1L	VSVA-B-M52-MZ-A1-1C1	
Width	18 mm	26 mm	26 mm	
Conforms to	ISO 15407-2		ISO 15407-1	
Design	Piston spool valve			
Sealing principle	Soft			
Actuation type	Electrical	Electrical		
Type of control	Piloted	Piloted		
Exhaust function, can be throttled	Via individual sub-base, via throttle pl	Via individual sub-base, via throttle plate		
Lubrication	Lifetime lubrication			
Type of mounting	Via through-hole, on manifold sub-base			
Mounting position	Any			
Manual override	Concealed			
Individual sub-base	→ Page 228			
Valve terminal	→ Page 84			

Standard nominal flow rate [l/min]

Valve function	Flow rate			
	Valve	Valve on valve terminal VTSA	Valve on valve terminal VTSA-F	Valve on individual sub-base
VSVA-B-M52-MA1-1C1-ANC	1400	1100	-	1100
VSVA-B-M52-MA1-1C1-ANP	1400	1100	-	1100
VSVA-B-M52-MA1-1C1-APC	1400	1100	-	1100
VSVA-B-M52-MA1-1C1-APP	1400	1100	-	1100
VSVA-B-M52-MA1-1T1L-ANC	1400	1100	1350	1200
VSVA-B-M52-MA1-1T1L-ANP	1400	1100	1350	1200
VSVA-B-M52-MA1-1T1L-APC	1400	1100	1350	1200
VSVA-B-M52-MA1-1T1L-APP	1400	1100	1350	1200
VSVA-B-M52-MA1-1T1L-APX-0.5	1400	1100	1350	1200
VSVA-B-M52-MA2-1T1L-ANP	750	550	700	600
VSVA-B-M52-MA2-1T1L-APP	750	550	700	600
VSVA-B-M52-MA2-1T1L-APX-0.5	750	550	700	600

5000

Clocked

Inductive

For all electrical connections

Valve normal position via sensor

[Hz]

Valve		VSVA-B-M52-MZD-A2-1T1L	VSVA-B-M52-MZD-A1-1T1L	VSVA-B-M52-MZ-A1-1C1
Width		18 mm	26 mm	26 mm
Valve switching times	On	12	20	21
	Off	38	54	41
Sensor switching times	On	32	60	60
	Off	9	11	11
Electrical data for valve				
Valve		VSVA-B-M52-MZD-A2-1T1L	VSVA-B-M52-MZD-A1-1T1L	VSVA-B-M52-MZ-A1-1C1
Width		18 mm	26 mm	26 mm
Electrical connection		4-pin plug to ISO 15407-2		Plug to EN 175301-803, type C, without PE conductor
Nominal operating voltage	[V DC]	24		
Permissible voltage fluctuations	[%]	±10		-15/+10
Surge resistance	[kV]	2.5		
Pollution degree		3		
Power consumption	[W]	1.6 1.8		
Switching position sensing		Normal position via sensor		
Duty cycle	[%]	100		
Degree of protection to EN 60529		IP65, NEMA 4 (for all types of signal ti	ransmission when mounted)	
Signal status indication		LED		Via accessories
Electrical data for sensor				
Electrical connection		Cable, 3-core		
		1x M8 plug, 3-pin		
Cable length	[m]	2.5		
Switching output		PNP or NPN		
Switching element function		N/C		
Switching status indication		Yellow LED		
Operating voltage range	[V DC]	10 30		
Residual ripple	[%]	±10		
Sensor no-load current	[mA]	≤10		
Max. output current	[mA]	200		
Voltage drop	[V]	≤2		
Man anitabing fragments	[11-1	5000		

Max. switching frequency

Short circuit current rating

Switching position sensing

Measuring principle

Reverse polarity protection for sensor

Operating and environmental cond	itions		
Valve		VSVA-B-M521T1L	VSVA-B-M521C1
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Notes on operating/pilot medium		Lubricated operation possible (in which case lubricated operation wil	l always be required)
Operating pressure	[bar]	-0.9 10	-0.9 16
	[MPa]	-0.09 1	-0.09 1.6
Operating pressure for valve termi-	[bar]	3 10	
nal with internal pilot air supply	[MPa]	0.3 1	
Pilot pressure	[bar]	310	
	[MPa]	0.3 1	
Ambient temperature	[°C]	-5 +50	
Temperature of medium	[°C]	-5 +50	
Note on materials		RoHS-compliant	
Noise level LpA	[dB(A)]	85	
CE marking		To EU EMC Directive ¹)	
(see declaration of conformity)			
UKCA marking		To UK EMC regulations ¹⁾	
(see declaration of conformity)			
KC marking		KC EMC	
Certification		C-Tick	C-Tick
		c UL us - Recognized (OL)	-

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Materials


Materials	
Sub-base/manifold sub-base	Die-cast aluminium
Valve	Die-cast aluminium, PA
Seals	FPM, NBR
Screws	Galvanised steel
Sensor housing	High-alloy stainless steel
Sensor cable sheath	TPE-U(PUR)

Product weight [g]				
Width	18 mm	26 mm		
5/2-way solenoid valve type				
VSVA-B-M52-MA2-1T1L-APX-0.5	157	-		
VSVA-B-M52-MA2-1T1L-APP	140	-		
VSVA-B-M52-MA2-1T1L-ANP	140	-		
VSVA-B-M52-MA1-1T1L-APC	-	307		
VSVA-B-M52-MA1-1T1L-APP	-	264		
VSVA-B-M52-MA1-1C1-APC	-	332		
VSVA-B-M52-MA1-1C1-APP	-	289		
VSVA-B-M52-MA1-1T1L-ANC	-	307		
VSVA-B-M52-MA1-1T1L-ANP	-	264		
VSVA-B-M52-MA1-1C1-ANC	-	332		
VSVA-B-M52-MA1-1C1-ANP	-	289		
VSVA-B-M52-MA1-1T1L-APX-0.5	-	281		
Individual connection				
Individual sub-base	192	302		

Dimensions

Solenoid valve with sensor, width 26 mm


Download CAD data → www.festo.com



Dimensions

Download CAD data → <u>www.festo.com</u>

Solenoid valve with sensor, with plug type C, width 26 mm



Ordering data - Solenoid valve with switching position sensing

	Code	Valve function	Width	Part no.	Туре
5/2-way solenoid valve,	24 V DC, p	lug-in design for valve terminal VTSA/VTSA-F with proximity switch			
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with PNP output and cable, 3-core, 2.5 m	26 mm	560723	VSVA-B-M52-MZD-A1-1T1L-APC
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with NPN output and cable, 3-core, 2.5 m	26 mm	560742	VSVA-B-M52-MZD-A1-1T1L-ANC
<u> </u>	SS	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	573201	VSVA-B-M52-MZD-A2-1T1L-APX-0.5
		sensor with PNP output with 0.5 m connecting cable and 4-pin sensor push-in connector M12x1	26 mm	570850	VSVA-B-M52-MZD-A1-1T1L-APX-0.5
	SO	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	573202	VSVA-B-M52-MZD-A2-1T1L-APP
		sensor with PNP output and 3-pin sensor push-in connector M8x1	26 mm	560724	VSVA-B-M52-MZD-A1-1T1L-APP
	SQ	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	573203	VSVA-B-M52-MZD-A2-1T1L-ANP
		sensor with NPN output and 3-pin sensor push-in connector M8x1	26 mm	560743	VSVA-B-M52-MZD-A1-1T1L-ANP

	Code	Valve function	Width	Part no.	Туре
/2-way solenoid valve	24 V DC, p	lug-in design for valve terminal VTSA/VTSA-F with proximity switch			
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with PNP output and cable, 3-core, 2.5 m	26 mm	8033026	VSVA-B-M52-MZTR-A1-1T1L-APC
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with NPN output and cable, 3-core, 2.5 m	26 mm	8033030	VSVA-B-M52-MZTR-A1-1T1L-ANC
P	SS	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	8033459	VSVA-B-M52-MZTR-A2-1T1L-APX-0.5
		sensor with PNP output with 0.5 m connecting cable and 4-pin sensor push-in connector M12x1	26 mm	8033034	VSVA-B-M52-MZTR-A1-1T1L-APX-0.5
	S0	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	8033460	VSVA-B-M52-MZTR-A2-1T1L-APP
		sensor with PNP output and 3-pin sensor push-in connector M8x1	26 mm	8033027	VSVA-B-M52-MZTR-A1-1T1L-APP
	SQ	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	8033461	VSVA-B-M52-MZTR-A2-1T1L-ANP
		sensor with NPN output and 3-pin sensor push-in connector M8x1	26 mm	8033031	VSVA-B-M52-MZTR-A1-1T1L-ANP

Ordering data - Solenoid valve with switching position sensing

Ordering data - Solenoid valve VSVA with cover cap for MO, non-detenting (H)

_	Code	Valve function	Width	Part no.	Туре
5/2-way solenoid valve, 2					
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with PNP output and cable, 3-core, 2.5 m	26 mm	8033049	VSVA-B-M52-MZH-A1-1T1L-APC
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with NPN output and cable, 3-core, 2.5 m	26 mm	8033053	VSVA-B-M52-MZH-A1-1T1L-ANC
$\langle O \rangle$	SS	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	8033477	VSVA-B-M52-MZH-A2-1T1L-APX-0.5
		sensor with PNP output with 0.5 m connecting cable and 4-pin sensor push-in connector M12x1	26 mm	8033057	VSVA-B-M52-MZH-A1-1T1L-APX-0.5
	S0	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	8033478	VSVA-B-M52-MZH-A2-1T1L-APP
		sensor with PNP output and 3-pin sensor push-in connector M8x1	26 mm	8033050	VSVA-B-M52-MZH-A1-1T1L-APP
	SQ	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	8033479	VSVA-B-M52-MZH-A2-1T1L-ANP
		sensor with NPN output and 3-pin sensor push-in connector M8x1	26 mm	8033054	VSVA-B-M52-MZH-A1-1T1L-ANP

Ordering data - Solenoid valve VSVA with cover cap for MO, concealed

	Code	Valve function	Width	Part no.	Туре				
5/2-way solenoid valve, 2	5/2-way solenoid valve, 24 V DC, plug-in design for valve terminal VTSA/VTSA-F with proximity switch								
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with PNP output and cable, 3-core, 2.5 m	26 mm	8033072	VSVA-B-M52-MZ-A1-1T1L-APC				
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with NPN output and cable, 3-core, 2.5 m	26 mm	8033076	VSVA-B-M52-MZ-A1-1T1L-ANC				
AP.	SS	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	8033495	VSVA-B-M52-MZ-A2-1T1L-APX-0.5				
		sensor with PNP output with 0.5 m connecting cable and 4-pin sensor push-in connector M12x1	26 mm	8033080	VSVA-B-M52-MZ-A1-1T1L-APX-0.5				
	SO	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	8033496	VSVA-B-M52-MZ-A2-1T1L-APP				
		sensor with PNP output and 3-pin sensor push-in connector M8x1	26 mm	8033073	VSVA-B-M52-MZ-A1-1T1L-APP				
	SQ	5/2-way valve, single solenoid, mechanical spring return, inductive	18 mm	8033497	VSVA-B-M52-MZ-A2-1T1L-ANP				
		sensor with NPN output and 3-pin sensor push-in connector M8x1	26 mm	8033077	VSVA-B-M52-MZ-A1-1T1L-ANP				

1

Ordering data					
	Code	Valve function	Width	Part no.	Туре
Solenoid valves, 24 V DC	, with pneu	matic interface to ISO 15218 for individual sub-base			
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with PNP output and cable, 3-core, 2.5 m, electrical connection to EN 175301-803, type C	26 mm	560725	VSVA-B-M52-MZ-A1-1C1-APC
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with NPN output and cable, 3-core, 2.5 m, electrical connec- tion to EN 175301-803, type C	26 mm	560744	VSVA-B-M52-MZ-A1-1C1-ANC
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with PNP output and 3-pin sensor push-in connector M8x1, electrical connection to EN 175301-803, type C	26 mm	560726	VSVA-B-M52-MZ-A1-1C1-APP
	-	5/2-way valve, single solenoid, mechanical spring return, inductive sensor with NPN output and 3-pin sensor push-in connector M8x1, electrical connection to EN 175301-803, type C	26 mm	560745	VSVA-B-M52-MZ-A1-1C1-ANP

Ordering data - Solenoid valve with switching position sensing

- 📲 - Note

- The sensors integrated in the valves must not be replaced by the customer. Incorrect assembly can result in malfunctions or damage to the valve. Return the module to Festo for repair in the event of a fault.
- Valves with switching position sensing from the VSVA-B-M52-... series can only be ordered individually. If these are used on a valve terminal, appropriate vacant positions must be provided for them. Exceptions are the valves with ident. code SS, SO and SQ.

Accessories – Solenoid valve with switching position sensing

ividual sub-base, por	t pattern to	ISO 15407-2, electrical connection via plug M12 Threaded connection, internal pilot air supply, lateral connections	G1/8	10		
ividual sub-base, por	-		G1/8	10	F / / A=A	
ividual sub-base, por	-	lateral connections		18 mm	541070	VABS-S4-2S-G18-B-R3
ividual sub-base, por	-		G1/4	26 mm	541069	VABS-S4-1S-G14-B-R3
		Threaded connection, external pilot air supply,	G1/8	18 mm	541064	VABS-S4-2S-G18-R3
		lateral connections	G1/4	26 mm	541063	VABS-S4-1S-G14-R3
	t pattern to	ISO 15407-2, electrical connection via cable terminals			-	
• >>	-	Threaded connection, internal pilot air supply,	541067	VABS-S4-2S-G18-B-K2		
		lateral connections	G1/4	26 mm	541065	VABS-S4-1S-G14-B-K2
• 10 00 00 00 00 00 00 00 00 00 00 00 00	-	Threaded connection, external pilot air supply,	G1/8	18 mm	539723	VABS-S4-2S-G18-K2
		lateral connections	G1/4	26 mm	539725	VABS-S4-1S-G14-K2
socket for the elect	ical connec	tion of individual valves, type C				
	-	Angled socket, type C, 3-pin			151687	MSSD-EB
		 Straight plug, PG7 				
		• 230 V AC				
		• Angled socket, type C, 3-pin			539712	MSSD-EB-M12
		Straight plug, M12x1				
ninating seal for con	nection pat	tern to EN 175301-803, type C			Datasheets	→ Internet: meb-ld
	-	For plug socket MSSD, 12 24 V DC			151717	MEB-LD-12-24DC
necting cable for ele	Code	Description ection of individual valves, type C			Part no.	Туре
M	GG	Angled socket, type C, 3-pin, with LED	2	.5 m	151688	KMEB-1-24-2.5-LED
al a	GH	• Open end, 3-core	5	m	151689	KMEB-1-24-5-LED
Store Starter	GJ	• 24 V DC, PVC	1	.0 m	193457	KMEB-1-24-10-LED
Marke	·					
3						
necting cable for the	1	connection of sensors for switching position sensing	1			1
	GM	• Straight socket, M8x1, 3-pin	2	2.5 m	8078223	NEBA-M8G3-U-2.5-N-LE3
		• Open end, 3-core				
	GN	• Straight socket, M8x1, 3-pin	5	m	8078224	NEBA-M8G3-U-5-N-LE3
^	60	Open end, 3-core			00-00-0	
	GO	• Angled socket, M8x1, 3-pin	2	2.5 m	8078230	NEBA-M8W3-U-2.5-N-LE3
	CD	 Open end, 3-core Angled socket, M8x1, 3-pin 			0070330	
6	GP		5	m	8078230	NEBA-M8W3-U-5-N-LE3
		Open end, 3-core Angled cocket, rotatable, M8x1, 3 pin		5 m	8001660	NEBU-M8R3-K-2.5-LE3
	-	 Angled socket, rotatable, M8x1, 3-pin Open end, 3-core 	2	2.5 m	0001000	NLDU-WORD-N-2.3-LE3
	<u> </u>	Angled socket, rotatable, M8x1, 3-pin	c	m	8001661	NEBU-M8R3-K-5-LE3
	-	 Angled socket, rotatable, M8x1, 3-pin Open end, 3-core 	5	111	0001001	NLDU-WOK3-N-3-LE3
umatic connection ac	cessories					
	ttings blas	iking plugs, silencers and				


Internet \rightarrow connection technology, silencer, blanking plug

Datasheet - Control block with safety function for VTSA/VTSA-F

- N Flow rate on valve terminal: 830 l/min
- Solenoid valve width 26 mm
- Voltage 24 V DC



Operating pressure 0.3 ... 1 MPa 3 ... 10 bar



Description

The control block is designed for two-channel control of pneumatic drive components such as double-acting linear cylinders and can be used to realise the following protective measures:

- Protection against unexpected start-up (EN 1037)
- Reversing hazardous movements, provided the reversing motion will not result in further hazards

Version for valve terminal VTSA/VTSA-F

The control attributes of the control block enable Performance Level e to be achieved for the protective measures. The control block has been developed and manufactured in accordance with the basic and proven safety principles of EN ISO 13849-1 and EN ISO 13849-2. The requirements of EN ISO 13849-1 and EN ISO 13849-2 (e.g. CCF, DC) must be taken into consideration when installing and operating the component and when using it in higher categories (2 to 4).

When using this product in machines or systems subject to specific C standards, the requirements specified in these standards must be observed. The control block with safety function is designed for installation in machines and automation systems and must only be used in industrial applications (high-demand mode)! The control block with safety function is suitable for use as a press safety valve to EN 962.

The valves with integrated switching position sensing on manifold sub-base for valve terminal VTSA/VTSA-F need to be supplied with power regardless of the type of electrical actuation (individual, multi-pin plug or fieldbus/control block connection). The electrical connection for the solenoid valves is established separately via a standardised square plug to EN 175301-803, type C. The switching position sensing of the

inductive PNP or NPN proximity switch is via a push-in connector size M8x1 to EN 61076-2-104.

- Note

The appropriate manifold sub-base VABV-S4- ..., which is required for integration into the valve terminal, is not part of the control block. It is automatically allocated by the configurator when the control block is selected.

- 🕴 - Note

The control block with safety function (VOFA) is also available as a decentralised individual connection variant with electrical and pneumatic individual connection. For information see:

→ Internet: vofa

Datasheet - Control block with safety function for VTSA/VTSA-F

Pneumatic/electrical links Function


The safety function is achieved by linking two pneumatic ducts of two 5/2way single solenoid valves within the control block: port (4) is only pressurised if both solenoid valves are switched to the switching position (14). Port (2) is always supplied with compressed air if at least one of the two solenoid valves is in normal position.

The valves are reset via a mechanical spring.

The switching operation of the solenoid valves can be sensed using the proximity switches on the solenoid valves (switching position sensing). By connecting the control signal and the switching signal of the proximity switch it is possible to check if the piston spools of the solenoid valves have reached or left the normal position (expectations). The piston spools of the solenoid valves are designed to prevent pneumatic short circuits between the ports (2) and (4) are prevented (positive overlap).

The two solenoid valves must be actuated via two separate ducts to achieve the required category 4 (Performance Level e, to EN ISO 13849-1).

T



For the control block with safety function VOFA-B26-T52-... for the valve terminal, two 5/2-way solenoid valves of width 26 mm are pneumatically linked via two ducts, using an intermediate plate as vertical stacking element (output 2 is switched in parallel, output 4 is switched in series).

1) The circuit diagram represents a valve with a proximity switch with a N/O switching output signal. This symbol applies to both N/O and N/C contacts, in accordance with ISO 1219-1. The switching element function of the sensors used here is designed as an N/C contact.

Safety data

Safety data		
Conforms to standard	EN 13849-1	
Safety function	Protection against manipulation, prevention of unexpected start-up	
	Reversing a movement	
Performance level (PL)	Protection against manipulation, prevention of unexpected start-up/up to category 4, Performance Level e	
	Reversing a movement/up to category 4, Performance Level e	
Note on forced checking procedure	Switching frequency at least once a week	
Certificate-issuing authority	IFA 1001179	
CE marking (see declaration of conformity)	To EU EMC Directive ¹)	
	To EU Machinery Directive	
Max. positive test pulse [µs]	1000	
with logic 0		
Max. negative test pulse [µs]	800	
with logic 1		
Shock resistance	Shock test with severity level 2, to EN 60068-2-27	
Vibration resistant	Transport application test with severity level 2, to EN 60068-2-6	


1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Datasheet – Control block with safety function for VTSA/VTSA-F

Peripherals overview

Electrical connection option for control block with safety function via PROFIsafe shut-off module CPX-FVDA-P2 (safety module)



Peripherals overview

		Description	→ Page/Internet
[1]	Control block with safety function	Away from the valve terminal as a decentralised individual connection variant	vofa
[2]	Connecting cable KMEB	For electrical connection of the control block with safety function via PROFIsafe shut-off module CPX-FVDA-P2 (safety module)	kmeb
[3]	Push-in T-connector NEDU	For simultaneously actuating two valves, e.g. control block with safety function	nedu
[4]	Control block with safety function	Integrated in the pneumatic section of the valve terminal VTSA/VTSA-F	-
[5]	Pneumatic section of the valve terminal VTSA/VTSA-F	Pneumatic components of the valve terminal VTSA/VTSA-F	-
[6]	CPX-FVDA-P2 (safety module)	PROFIsafe shut-off module integrated in the CPX terminal of the valve terminal VTSA/VTSA-F	срх
[7]	CPX terminal of the valve terminal VTSA/VTSA-F	Electrical components of the valve terminal VTSA/VTSA-F	-

Datasheet -- Control block with safety function for VTSA/VTSA-F

General technical data

General technical data		
Design		Piston spool valve
Standard nominal flow rate [[l/min]	830
Reset method		Mechanical spring
Sealing principle		Soft
Exhaust air function		Can be throttled
Actuation type		Electrical
Overlap		Positive overlap
Type of control		Piloted
Flow direction		Not reversible
Exhaust air function		Can be throttled
Suitable for vacuum		-
Nominal width [[mm]	9
Pilot air supply		Via valve terminal
Type of mounting		Via through-hole, on manifold sub-base
Mounting position		Any
Manual override		-
Signal status display, valve		With accessories
Pneumatic connections		
Supply 1	1	Via the manifold sub-base of the valve terminal
Exhausting	3/5	
Working ports 2	2/4	
Pilot air supply 1	14	
Pressure gauge		G1/4

Operating and environmental co	onditions	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Notes on operating/pilot medium	1	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]	010
	[MPa]	01
Operating pressure for valve	[bar]	310
terminal with internal pilot air	[MPa]	0.3 1
supply		
Pilot pressure	[bar]	3 10
	[MPa]	0.3 1
Noise level LpA	[dB(A)]	85
Ambient temperature	[°C]	-5 +50
Temperature of medium	[°C]	-5 +50
CE marking (see declaration of co	nformity)	To EU EMC Directive ¹)
		To EU Machinery Directive

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Datasheet – Control block with safety function for VTSA/VTSA-F

Electrical data for control block

Electrical data for contr	rol block		
Electrical connection		-	Plug to EN 175301-803, type C, without PE conductor
Nominal operating volta	ige	[V DC]	24
Permissible voltage fluc	tuations	[%]	-15/+10
Surge resistance		[kV]	2.5
Pollution degree			3
Power consumption		[W]	1.8
Max. magnetic disruption	on field	[mT]	60
Switching position sens	ing		Normal position via sensor
Duty cycle		[%]	100
Protection rating to EN 6	60529		IP65, NEMA 4 (for all types of signal transmission when mounted)
Protection against direct and			PELV
indirect contact			Protection class to EN 60950/IEC 950
Valve switching time	On	[ms]	22
-	Off	[ms]	59
Valve sensor switch-	On	[ms]	60
ing time ¹⁾	Off	[ms]	11

1) Valve sensor switching time off: period of time from the coil being energised to the sensor being switched off when using a PNP sensor. Valve sensor switching time on: period of time from the coil being de-energised to 0-L edge at the sensor when using a PNP sensor.

-Note -

With a duty cycle of 100%, the control block must be de-energised once a week.


Electrical data – Sensor (to EN -60947-5-2)

Electrical connection Cable, 3-core 1x M8 plug, 3-pin Cable length [m] 2.5 Switching output PNP or NPN Switching element function N/C Signal status indication Yellow LED Operating voltage range [V DC] 10 30 Residual ripple [%] ±10 Sensor no-load current [mA] Max. 10 Max. output current [mA] 200 Voltage drop [V] Max. 2	Electrical data - Sensor (to EN -0	0941-9-2)	
Cable length[m]2.5Switching outputPNP or NPNSwitching element functionN/CSignal status indicationYellow LEDOperating voltage range[V DC]10 30Residual ripple[%]±10Sensor no-load current[mA]Max. 10Max. output current[mA]200Voltage drop[V]Max. 2	Electrical connection		Cable, 3-core
Switching output PNP or NPN Switching element function N/C Signal status indication Yellow LED Operating voltage range [V DC] 10 30 Residual ripple [%] ±10 Sensor no-load current [mA] Max. 10 Max. output current [mA] 200 Voltage drop [V] Max. 2			1x M8 plug, 3-pin
Switching element function N/C Signal status indication Yellow LED Operating voltage range [V DC] 10 30 Residual ripple [%] ±10 Sensor no-load current [mA] Max. 10 Max. output current [mA] 200 Voltage drop [V] Max. 2	Cable length	[m]	2.5
Signal status indicationYellow LEDOperating voltage range[V DC]10 30Residual ripple[%]±10Sensor no-load current[mA]Max. 10Max. output current[mA]200Voltage drop[V]Max. 2	Switching output		PNP or NPN
Operating voltage range [V DC] 10 30 Residual ripple [%] ±10 Sensor no-load current [mA] Max. 10 Max. output current [mA] 200 Voltage drop [V] Max. 2	Switching element function		N/C
Residual ripple [%] ±10 Sensor no-load current [mA] Max. 10 Max. output current [mA] 200 Voltage drop [V] Max. 2	Signal status indication		Yellow LED
Sensor no-load current [mA] Max. 10 Max. output current [mA] 200 Voltage drop [V] Max. 2	Operating voltage range	[V DC]	1030
Max. output current [mA] 200 Voltage drop [V] Max. 2	Residual ripple	[%]	±10
Voltage drop [V] Max. 2	Sensor no-load current	[mA]	Max. 10
	Max. output current	[mA]	200
Max switching frequency [Hz] 5000	Voltage drop	[V]	Max. 2
max. switching inqueries [12] 5000	Max. switching frequency	[Hz]	5000
Short circuit current rating Clocked	Short circuit current rating		Clocked
Reverse polarity protection for sensor For all electrical connections	Reverse polarity protection for ser	isor	For all electrical connections
Measuring principle Inductive	Measuring principle		Inductive

Materials	
Sub-base/manifold sub-base	Wrought aluminium alloy
Valve	Die-cast aluminium, PA
Seals	FPM, NBR, HNBR
Screws	Galvanised steel
Sensor housing	High-alloy stainless steel
Sensor cable sheath	PUR
Note on materials	RoHS-compliant

1

Datasheet - Control block with safety function for VTSA/VTSA-F



1) The control block with safety function can only be ordered via the valve terminal configurator and therefore does not have a separate part number. The appropriate manifold sub-base required for the valve terminal VTSA/VTSA-F is automatically allocated to the control block by the configurator

2) Code letter within the order code for a valve terminal configuration

- 🌡 - Note


The sensors integrated in the valves must not be replaced by the customer. Incorrect assembly can result in malfunctions or damage to the valve. Please contact Festo in the event of a malfunction.

Accessories – Control block with safety function for VTSA/VTSA-F

	Code	Description	Part no.	Туре	
lug socket for the elec	ctrical conne	ection of individual valves, type C			
	-	Angled socket, type C, 3-pin			MSSD-EB
		Screw terminal			
	-	Angled socket, type C, 3-pin		539712	MSSD-EB-M12
		Straight plug, M12x1			
		With switching position indication			
luminating seal for co	nnection pa	attern to EN 175301-803, type C		Datasheets	i → Internet: meb-ld
	-	For plug socket MSSD, 12 24 V DC		151717	MEB-LD-12-24DC
onnecting cable for e	ectrical con	Inection of individual valves, type C			
lenneeting cubic for e	GG	Angled socket, type C, 3-pin, with LED	2.5 m	151688	KMEB-1-24-2.5-LED
	GH	• Open end, 3-core	5 m	151689	KMEB-1-24-5-LED
1 Star	GI	• 24 V DC, PVC	10 m	193457	KMEB-1-24-10-LED
	0,		10.00		
v ⊘					
*					
onnecting cable for tr		connection of sensors for switching position sensing	2.5	0070222	
	GM	Straight socket, M8x1, 3-pin	2.5 m	8078223	NEBA-M8G3-U-2.5-N-LE3
C Land	GN	Open end, 3-core Straight acklet M8v1 2 pin	5 m	8078224	NEBA-M8G3-U-5-N-LE3
	GN	Straight socket, M8x1, 3-pinOpen end, 3-core	5 11	8078224	NEBA-M8G3-U-5-N-LE3
			2.5 m	8001660	NEBU-M8R3-K-2.5-LE3
	-	 Angled socket, rotatable, M8x1, 3-pin Open end, 3-core 	2.5 111	8001000	NEDU-MIOR3-N-2.3-LE3
C Martin		Angled socket, rotatable, M8x1, 3-pin	5 m	8001661	NEBU-M8R3-K-5-LE3
	-	Open end, 3-core	5 111	0001001	NEDU-MORS-R-S-LES
onnecting cable for th	ne electrical	connection of PROFIsafe shut-off module CPX-FVDA-P2 to the control block			-
\square	-	For the easy connection of one control block valve (power supply via	0.5 m	177677	KMEB-2-24-M12-0.5-LED
		PROFIsafe shut-off module CPX-FVDA-P2)			
		Angled socket, type C, 3-pin, with LED			
•		Straight plug M12x1, 5-pin			
		• 24 V DC, PUR			
ush-in T-connector for	dual electr	ical connection of PROFIsafe shut-off module CPX-FVDA-P2 to the control bl	ock		1
	-	For dual connection of two control block valves (power supply via		2839867	NEDU-L2R1-V10-M12G5-M12G5
		PROFIsafe shut-off module CPX-FVDA-P2)			
		• Straight plug, M12x1, 5-pin (A-coded)			
~		2x straight socket, M12x1, 5-pin (A-coded)			
		Operating voltage range 0 30 V DC			
Pneumatic connection	accessories				
		inking plugs, silencers and			
	•	be found in the chapter Accessories \rightarrow page: 242			
or on the website via th					
nternet -> connection	1 technolog	y, silencer, blanking plug			

Valve terminals VTSA

Datasheet - Intermediate plate for switchable pilot air for VTSA/VTSA-F



Description

The combination of a 5/2-way solenoid valve with switching position sensing and the intermediate plate VABF-S4-...-S enables the pilot air to be verifiably switched on and off (sensing function) from duct 1 to 14 for the entire pressure zone or valve terminal.

This combination is not a safety device in accordance with the Machinery Directive 2006/42/EC. When used in higher categories, the sensor signal from the valve must be evaluated by the control system.

Alternative switching position sensing with pressure switch

As an alternative to the sensing function in the solenoid valve, a pressure switch can be mounted (in place of the blanking plug) on the intermediate plate VABF-S4-...-S. With this pressure switch, the switching on and off (sensing function) of the pilot air supply can be verified.

This combination is suitable for use in safety-related parts of control systems to EN ISO 13849-1. This combination is designed for installation in machines and automation systems and must only be used in industrial applications (high-demand mode).


An ISO solenoid valve without a sensor can therefore be mounted on the intermediate plate to give the same function.

→ Internet: spba

- 📲 - Note

The pilot air switching valve/the intermediate plate for switchable pilot air can only be operated on the valve terminal VTSA/VTSA-F in combination with a right end plate for external pilot air type VABE-S6-1RZ-.... Port 14 on the right end plate must then be sealed.

Vertical stacking variant for valve terminal VTSA/VTSA-F, width 18 mm, 26 mm




The valves with integrated switching position sensing in plug-in design for valve terminal VTSA/VTSA-F can be used regardless of the type of electrical actuation (individual, multi-pin plug or fieldbus/control block connection). This module is supplied pre-assembled together with the valve terminal VTSA/VTSA-F. No other assembly steps are required before installation. Switching position sensing is carried out using an inductive PNP proximity switch with cable and M12x1 push-in connector to EN 61076-2-104. Alternatively, combinations with a pressure switch in the intermediate plate and ISO solenoid valves are possible.

- **Note** All solenoid valves VSVA to ISO 15407-1 can be used.

→ Internet: vsva

 The circuit diagram represents a valve with a proximity switch with a N/O switching output signal. This symbol applies to both N/O and N/C contacts, in accordance with ISO 1219-1. The switching element function of the sensors used here is designed as an N/C contact.

Function of pneumatic/electrical links



The function for switching off the pilot air is essentially achieved by combining the intermediate plate type VABF-S4-...S with the 5/2-way single solenoid valve.

The valve terminal is not supplied with any pilot air via the right end plate type VABE-S6-1 (ident. code XS, external pilot air). Port 14 on the end plate is sealed. The pilot air for the valve is branched from duct (1) in the intermediate plate and redirected to the pilot air duct (14) of the valve terminal when the valve is in the switching position. Ports (2) and (4) of the manifold sub-base are sealed with blanking plugs. By querying the proximity switch in the solenoid valve (or pressure switch in the intermediate plate VABE...), it is possible to monitor the switching process of the solenoid valve. By connecting the control signal and the switching signal of the proximity switch it is possible to check if the piston spools of the solenoid valves have reached or left the normal position (expectations).

The piston spool of the solenoid valve is designed so that pneumatic short circuits between the ports (2) and (4) are prevented (positive overlap).

Alternatively, combinations with a pressure switch in the intermediate plate and ISO solenoid valves are possible.

- 📲 - Note

A valve from the modular system VTSA/VTSA-F can be provided or configured to the right of the valve with switching position sensing on the intermediate plate of the pilot air switching valve.

Pilot air switching valve with integrated switching position monitoring The pilot air switching valve can be ordered as a combination of a 5/2-way solenoid valve with switching position sensing and intermediate plate VABF-S4-...-S.

Alternative switching position sensing with pressure switch

As an alternative to the pilot air switching valve with integrated switching position sensing, it is possible to combine an ISO solenoid valve and a pressure switch in the intermediate plate. To do this, various 5/2-way solenoid valves in combination with a pressure switch SPBA-... are available.

Safety data

Conforms to standard	EN 13849-1/2
CE marking (see declaration of conformity)	To EU EMC Directive ¹⁾
Shock resistance	Shock test with severity level 2, to EN 60068-2-27
Vibration resistant	Transport application test with severity level 2, to EN 60068-2-6

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Safety characteristics

Valve function 5/2-way, single solenoid	Test pulses				
	Max. positive test pulse with logic 0 [µs]	Max. negative test pulse with logic 1 [µs]			
VSVA-B-M52-MZA1-1T1L	1200	1100			
VSVA-B-M52-MZA2-1T1L	1500	800			
VSVA-B-M52-MZ-A1-1C1	1800	800			

General technical data									
		Ssolenoid valve type VSVA-	B-M52-MZD-A2-1T1L-APX-0.5	Ssolenoid valve type	VSVA-B-M52-MZD-A1-1T1L-APX-0.5				
		mounted on valve terminal	VTSA/VTSA-F	mounted on valve te	rminal VTSA/VTSA-F				
Width		18 mm		26 mm					
Design		Piston spool valve	Piston spool valve						
Sealing principle		Soft							
Overlap		Positive overlap							
Actuation type		Electrical							
Type of control		Piloted							
Type of mounting:									
Solenoid valve on intermediate		M3		M4					
Intermediate plate on manifold sub-base		M3x12 (captive)		M4x12 (captive)					
Mounting position		Any	Any						
Pneumatic connections									
Supply	1	Via the manifold sub-base	of the valve terminal						
Exhausting	3/5	Via the manifold sub-base	of the valve terminal						
Working ports	2/4	Sealed with blanking plug	type B-1/4						
Pilot air supply	14	Via the manifold sub-base	of the valve terminal						
Pressure gauge/pressure switch		G1/8	G1/8						
Switching times [ms]									
Width		18 mm	26 mm						
Valve type		5/2	5/2						
Identifier		MZD-A2	MZD-A1		MZ-A1				
Valve switching time	On	12	20		21				
	Off	38	54		41				

60

11

60

11

 Valve sensor switching time off: period of time from the coil being energised to the sensor being switched off when using a PNP sensor. Valve sensor switching time on: period of time from the coil being de-energised to 0-L edge at the sensor when using a PNP sensor.

32

9


Protective circuit

Valve sensor switching time¹⁾

Each solenoid coil VSVA is protected with a spark arresting protective circuit as well as against polarity reversal.


On

Off



Peripherals overview

Pilot air switching valve/intermediate plate for switchable pilot air with switching position monitoring



		Description	→ Page/Internet
[1]	Valve terminal VTSA/VTSA-F	Valve terminal with multi-pin plug interface	vtsa
[2]	Manifold sub-base VABF	Width 18 mm or 26 mm	142
[3]	Solenoid valve VSVA-B-M52	Width 18 mm or 26 mm, with sensor and integrated cable 0.5 m	180
[4]	Solenoid valve VSVA-B-M52	Width 18 mm or 26 mm, with sensor for external connecting cable	180
[5]	Connecting cable NEBU-M8	For connecting to the sensor	181
[6]	Solenoid valve VSVA-B-M52	Width 18 mm or 26 mm ¹⁾	180
[7]	Solenoid valve VSVA-B-M52	Width 18 mm or 26 mm, with plug to EN 175301, type C ¹⁾	180
[8]	Solenoid valve VSVA-B-M52	Width 18 mm or 26 mm, with round plug ¹⁾	vsva
[9]	Blanking plug	-	243

1) The switching position is sensed by pressure switches when the solenoid valves used have no integrated sensor.

The pressure switch is screwed into the intermediate plate in place of the blanking plug.

Electrical data							
Nominal operating voltage	[V DC]	24					
Permissible voltage fluctuations	[%]	±10	±10				
Surge resistance	[kV]	2.5					
Pollution degree		3					
Power consumption	[W]	1.6 (M52-MZD), 1.8 (M52	2-MZ)				
Max. magnetic disruption field	[mT]	60					
Switching position sensing		Normal position via sense	or				
Duty cycle	[%]	100					
Degree of protection		IP65, NEMA 4 (for all type	es of signal transmiss	sion when mounted)			
Electrical data for sensor							
Sensor designation		APP	ANP	APC	ANC	APX	
Switching output		PNP	NPN	PNP	NPN	PNP With fixed cable and plug	
Sensor connection		1x M8 plug, 3-pin	1x M8 plug, 3-pin With		With fixed cable and open end Wi		
Cable length	[m]	0.5 (with socket M8x1, p	lug M12x1)	2.5		0.5	
Switching element function		N/C					
Signal status indication		Yellow LED (on the senso	r)				
Operating voltage range	[V DC]	10 30					
Residual ripple	[%]	±10					
Rated operating voltage	[V DC]	24					
Max. no-load supply current	[mA]	10					
Max. output current	[mA]	200					
Max. voltage drop	[V]	2					
Max. switching frequency	[Hz]	5000					
Short circuit current rating		Clocked					
Reverse polarity protection		For all electrical connection	ons				
Measuring principle		Inductive					
Switching position sensing		Valve normal position via	sensor				

Operating and environment Valve		VSVA-B-M521T1L	VSVA-B-M521C1		Without sensor		
					Without sensor		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]					
Notes on operating/ Pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)					
	[h a s]				0.0 10		
Operating pressure	[bar] [MPa]	-0.9 10 -0.09 1	-0.9 16 -0.09 1		-0.9 10 -0.09 1		
Noise level LpA		85	85		-0.09 1		
	[dB(A)]				-		
Ambient temperature	[°C]	-5 +50 -5 +50	5 +50 5 +50		-5 +50		
Temperature of medium	[°C]				-		
Note on materials		RoHS-compliant	RoHS-compliant		RoHS-compliant		
KC marking		KC EMC	KC EMC		-		
UKCA marking		To UK EMC regulations	To UK EMC regulations	5	-		
Certification		C-Tick	C-Tick		-		
		c UL us Recognized (OL)	-		c UL us Recognized (OL)		
M							
Materials							
Sub-base/manifold sub-base		Die-cast aluminium					
Valve		Die-cast aluminium, PA					
Seals		FPM, NBR					
Screws		Galvanised steel					
Sensor housing		High-alloy stainless steel					
Sensor cable sheath		TPE-U(PUR)	TPE-U(PUR)				
Product weight [g]		1		1			
Width		18 mm		26 mm			
5/2-way solenoid valve type	·						
VSVA-B-M52-MA1-1T1L-AF	PC	-		307			
VSVA-B-M52-MA1-1T1L-AF	P	-		264			
VSVA-B-M52-MA1-1C1-AP	С	-		332			
VSVA-B-M52-MA1-1C1-AP	Р	-		289			
VSVA-B-M52-MA1-1T1L-AM	IC	-		307			
VSVA-B-M52-MA1-1T1L-AM	1P	-		264			
VSVA-B-M52-MA1-1C1-ANC		-		332			
VSVA-B-M52-MA1-1C1-ANP		-		289			
VSVA-B-M52-MA1-1T1L-AF	Х-0.5	-		281			
VSVA-B-M52-MA2-1T1L-AF	Х-0.5	157		-			
VSVA-B-M52-MA2-1T1L-AF	P	140		-			
VSVA-B-M52-MA2-1T1L-AM	IP	140		-			
		1		1			
VSVA-B-M52-MA1-1T1L		-		293			

	Code	Valve function			Part no.	Туре
/2-way solenoid valve	, 24 V DC, p	lug-in design with proximity switch				
()	SS	5/2-way valve, single solenoid, mechanical spring return,		18 mm	573201	VSVA-B-M52-MZD-A2-1T1L-APX-0.5
		with 0.5 m connecting cable and 4-pin sensor push-in con- nector M12x1		26 mm	570850	VSVA-B-M52-MZD-A1-1T1L-APX-0.5
	-	5/2-way valve, single solenoid, mechanical spring return,	PNP	26 mm	560723	VSVA-B-M52-MZD-A1-1T1L-APC
		with 2.5 m connecting cable	NPN	26 mm	560742	VSVA-B-M52-MZD-A1-1T1L-ANC
 ®	SO	5/2-way valve, single solenoid, mechanical spring return,	PNP	18 mm	573202	VSVA-B-M52-MZD-A2-1T1L-APP
		with 3-pin sensor push-in connector M8x1		26 mm	560724	VSVA-B-M52-MZD-A1-1T1L-APP
	SQ		NPN	18 mm	573203	VSVA-B-M52-MZD-A2-1T1L-ANP
				26 mm	560743	VSVA-B-M52-MZD-A1-1T1L-ANP
 @	-	5/2-way valve, single solenoid, mechanical spring return, with	PNP	26 mm	560725	VSVA-B-M52-MZ-A1-1C1-APC
		plug to EN 175301, type C, with 2.5 m connecting cable	NPN	26 mm	560745	VSVA-B-M52-MZ-A1-1C1-ANP
	-	5/2-way valve, single solenoid, mechanical spring return, with	PNP	26 mm	560726	VSVA-B-M52-MZ-A1-1C1-APP
		plug to EN 175301, type C, with 3-pin sensor push-in connec- tor M8x1	NPN	26 mm	560744	VSVA-B-M52-MZ-A1-1C1-ANC
/2-way solenoid valve	, 24 V DC, p					
	-	5/2-way valve, single solenoid, mechanical spring return		26 mm	539159	VSVA-B-M52-MZD-A1-1T1L
				18 mm	539185	VSVA-B-M52-MZD-A2-1T1L

- - Note

Further solenoid valves with switching position sensing can be ordered as distinct types. These are preconfigured with the required MO cover caps. \rightarrow Solenoid valve with switching position sensing, page 163

🖡 - Note

The sensors integrated in the valves must not be replaced by the customer. Incorrect assembly can result in malfunctions or damage to the valve. Please contact Festo in the event of a malfunction.

Ordering data					
	Code	Description		Part no.	Туре
ressure switch for	intermediate pl	ate			
	WL	Mechanical pressure switch for switchable pilot air supply (only in combinat intermediate plate ZO), with plug M12x1, 4-pin	tion with	8000033	SPBA-P2R-G18-W-M12-0.25X
	WH	Electrical pressure switch for switchable pilot air supply, switching output 2 (only in combination with intermediate plate ZO), with plug M12x1, 4-pin	2xPNP	8000210	SPBA-P2R-G18-2P-M12-0.25X
onnecting cable fo	or connection of	pressure switches			
STREET,	GE	Straight socket, M12x1, 5-pin Straight plug, M12x1, 4-pin	m	8000208	NEBU-M12G5-K-0.5-M12G4
connecting cable fo	or the electrical (connection of sensors for switching position sensing			1
STREET.	≥ -	Straight socket, M8x1, 3-pin Straight plug, M12x1, 3-pin	m	8078278	NEBA-M8G3-U-0.5-N-M12G3
	GM	Straight socket, M8x1, 3-pin Open end, 3-core	m	8078223	NEBA-M8G3-U-2.5-N-LE3
M Land	GN	Straight socket, M8x1, 3-pin Open end, 3-core	1	8078223	NEBA-M8G3-U-5-N-LE3
	GO	Angled socket, M8x1, 3-pin Open end, 3-core	m	8078230	NEBA-M8W3-U-2.5-N-LE3
	GP	Angled socket, M8x1, 3-pin Open end, 3-core	1	8078231	NEBA-M8W3-U-5-N-LE3
	-	Angled socket, rotatable, M8x1, 3-pin Open end, 3-core	m	8001660	NEBU-M8R3-K-2.5-LE3
	-	Angled socket, rotatable, M8x1, 3-pin Open end, 3-core		8001661	NEBU-M8R3-K-5-LE3

Ordering data – Intermediate plate for switchable pilot air for VTSA/VTSA-F

Ordering data – Pilot air switching valve for VTSA/VTSA-F

Ordering data					
	Code	Description		Part no.	Туре
Covering	-				
	N	Cover cap for manual override, non-detenting	Pack of 10	541010	VAMC-S6-CH
P	V	Cover cap for manual override, concealed	Pack of 10	541011	VAMC-S6-CS
	A	Cover cap, heavy duty, for manual override, non-detenting heavy duty, detenting via accessory (key) (The cover cap is provided for one-off mounting only)	Pack of 10	4105147	VAMC-B-S6-CTR
Accessories for manua	al override, h	eavy duty			
	-	Coded key (accessory) for actuating the cover cap, heavy duty, for detenting position (VAMC-B-S6-CTR)	1 piece	1662543	АНВ-МЕВ-В
Pneumatic connection	n accessories				
other pneumatic acce or on the website via	ssories can b the individua	nking plugs, silencers and e found in the chapter Accessories → page: 242 l search terms: r, silencer, blanking plug			

- 🌡 - Note

There is a wide range of preconfigured solenoid valves with cover cap for manual override and correct valve type code available to order in the sections on solenoid valves.

Datasheet - Pilot air switching valve for VTSA/VTSA-F-CB

- Flow rate 125 l/min
- **[]** Pilot air switching valve width 18 mm
 - Voltage 24 V DC
 - Operating pressure 0.3 ... 1 MPa

Description

Duct 14 of the valve terminal is supplied with pilot air via the pilot air switching valve. This can be used to realise the safety function "Protection against unexpected start-up". The pilot air switching valve is always supplied with internal pilot air from

the valve terminal can be operated

with internal pilot air (from duct 1 of the valve terminal) or with external pilot air (external compressed air supply via duct 2).

The pilot air switching valve can only be operated on the valve terminal

This information applies only for a single pressure zone.

The pilot air switching valve is actuated via an electromagnetic pilot control. It can be switched on and off manually using the manual override. The manual override can be shut off manually or using the electrical pilot control.

The pilot air switching valve enables the pilot air supply to be verifiably switched on and off (sensor function) from duct 1 to 14 for the entire pressure zone or valve terminal. This valve is not a safety device in accordance with the Machinery Directive 2006/42/EC. When used in higher categories, the sensor signal from the valve must be evaluated by the control system.

This valve is suitable for use in safetyrelated parts of control systems to EN ISO 13849-1. This valve is designed for installation in machines and automation systems and must only be used in industrial applications (high-demand mode). More information and technical data

VTSA/VTSA-F in combination with a right-hand end plate for external pilot air type VABE-S6-1RZ-.... Port 14 on the right end plate must then be sealed.

Note

Safety data		
Max. positive test pulse with logic 0	[µs]	2000
Max. negative test pulse	[µs]	1200
with logic 1		
Shock resistance		Shock test with severity level 2, to EN 60068-2-27
Vibration resistant		Transport application test with severity level 2, to EN 60068-2-6



Datasheet – Pilot air switching valve for VTSA/VTSA-F-CB

General technical data

General technical data		
Design		Poppet valve
Valve function		3/2-way closed, single solenoid
Standard nominal flow rate	[l/min]	125
Standard nominal flow rate for	[l/min]	125
exhaust		
Reset method		Mechanical spring and pneumatic spring
Sealing principle		Soft
Actuation type		Electrical
Overlap		Negative overlap
Type of control		Piloted
Mounting position		Any
Flow direction		Not reversible
Manual override		None (part no.: 8066575, 8066574, 8066571, 8066570)
		Detenting, self-resetting via electrical control signal (part no.: 8066573, 8066572, 8066569, 8066568)
		Non-detenting (part no.: 8171467, 8171468, 8171469, 8171470)
Pilot air supply		For pilot air switching valve: internal via valve terminal
		For the valve terminal: internal via valve terminal (duct 1) – (part nos.: 8066569, 8066568, 8066571, 8066570)
		For the valve terminal: external via compressed air supply (duct 2) – (part nos.: 8066573, 8066572, 8066575, 8066574)
Type of mounting		Via through-hole, on manifold sub-base
MTTF subcomponent		443 years, pressure switch
Width, manifold sub-base	[mm]	38 (for additional valve 18 mm)
	[mm]	46 (for additional valve 26 mm)
Pneumatic connections, pilot air s	witching va	lve
Supply	1	Via the manifold sub-base of the valve terminal
Exhausting	3/5	Via the manifold sub-base of the valve terminal
Compressed air supply port (external)	2	61/8
Exhaust air/exhaust	4	G1/8
Pilot air supply	14	Via the manifold sub-base of the valve terminal
Pneumatic connections, additiona	al valve posi	tion
Supply	1	Via the manifold sub-base of the valve terminal
Exhausting	3/5	Via the manifold sub-base of the valve terminal
Working ports (for valve 18 mm)	2/4	G1/8
Working ports (for valve 26 mm)	2/4	G1/4
Pilot air supply	14	Via the manifold sub-base of the valve terminal

Operating and environmental of	onditions	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Notes on operating/pilot mediu	n	Lubricated operation not possible
Operating pressure ²⁾	[bar]	310
	[MPa]	0.3 1
Pilot pressure	[bar]	310
	[MPa]	0.31
Ambient temperature ²)	[°C]	-5 +50
Temperature of medium ²⁾	[°C]	-5 +50
Corrosion resistance class CRC ¹⁾		0

1) More information www.festo.com/x/topic/crc

2) With an ambient temperature and a temperature of the medium from -5 °C to +5 °C and +40 °C to +50 °C, the maximum permissible operating pressure is 8 bar.

Datasheet - Pilot air switching valve for VTSA/VTSA-F-CB

Electrical data – Pilot air switching valve


Electrical data – Pilot air switchin	ng valve	
Nominal operating voltage	[V DC]	24
Permissible voltage fluctuations	[%]	±10
Electrical connection		Plug-in
Power consumption	[W]	1.6
Switching element function		N/C
Switching position sensing		Via pressure switch, exhausted status
Signal status indication		Yellow LED, valve control
		Green LED, pressure switch, exhausted status
Duty cycle	[%]	100
Degree of protection	_	IP65

Materials

Housing	Reinforced PA
Seals	NBR, HNBR
Screws	Galvanised steel
Note on materials	RoHS-compliant

Connection and display components

Pilot air switching valve VSVA-BT-M32CS... with manifold sub-base



Note


Detailed information on the manual override can be found in the user documentation.

- [1] Status LED for solenoid coil
- Status LED for pressure switch [2]
- M12 connection (optional) [3]
- [4] Manual override (MO) (optional)
- [5] Solenoid valve housing
- [6] Inscription label holder with additional fields for marking (ASCF-T-S6-Z)
- [7] Additional valve position
- [8] Working port (2) of the additional valve position
- [9] External compressed air supply port
- [10] Working port (4) of the additional valve position
- [11] Exhaust port
- [12] Pilot control

Datasheet – Pilot air switching valve for VTSA-F-CB

Valve function Description Terminal | Circuit symbol code • Pilot air supply via duct 2 (external pilot air) of manifold sub-base СТ (14)2P • Without manual override (MO) (2)1 3(4)СТ • Pilot air supply via duct 2 (external pilot air) of manifold sub-base (14)212 • With manual override (MO) (2)13(4) AT • Pilot air supply via duct 2 (external pilot air) of manifold sub-base (14)2• Without manual override (MO) (2)13(4) AT • Pilot air supply via duct 2 (external pilot air) of manifold sub-base (14)212 • With manual override (MO) (2)13(4) CS • Pilot air supply via duct 1 (internal pilot air) for the valve terminal's pressure zone (14)2(end plate/additional supply plate) • Without manual override (MO) 1 3(4) CS • Pilot air supply via duct 1 (internal pilot air) for the valve terminal's pressure zone (14)212 (end plate/additional supply plate) • With manual override (MO) 1 3(4) AS • Pilot air supply via duct 1 (internal pilot air) for the valve terminal's pressure zone (14)2(end plate/additional supply plate) • Without manual override (MO) 1 3(4) AS • Pilot air supply via duct 1 (internal pilot air) for the valve terminal's pressure zone (14)2 12 (end plate/additional supply plate) • With manual override (MO) 1 3(4)

Datasheet – Pilot air switching valve for VTSA/VTSA-F-CB



Datasheet – Pilot air switching valve for VTSA-F-CB

Ordering dat	a Terminal code	Terminal code	Description		Operati	ng pres-		ard nomi- w rate ²⁾	Wt. [g] ³⁾	Part no.	Туре
	VTSA-F-CB	VTSA/VTSA-F			[MPa]	[bar]	[l/ min]	Exhaust- ing [l/min]			
3/2-way sole		V DC, plug-in de	-								
		enoid valve NC,	external pilot air supply for the va	1	1	1	-		T		
	CT	-	Control plug-in, pressure switch plug-in, manual override (MO) self- resetting	18 mm	0.31	310	150	150	110	8066573	VSVA-BT-M32CS2-MYE-A2-1T5L-PA
	СТ	AT	Control plug-in, external M12 pressure switch, manual override (MO) self- resetting	18 mm	0.31	310	150	150	110	8066572	VSVA-BT-M32CS2-MYE-A2-1T1L-PZ
	СТ	-	Control plug-in, pressure switch plug-in, manual override (MO) con- cealed	18 mm	0.31	310	150	150	110	8066575	VSVA-BT-M32CS2-MS-A2-1T5L-PA
	СТ	AT	Control plug-in, external M12 pressure switch, manual override (MO) con- cealed	18 mm	0.31	310	150	150	110	8066574	VSVA-BT-M32CS2-MS-A2-1T1L-PZ
	СТ	-	Control plug-in, pressure switch plug-in, manual over- ride (MO) non-detenting	18 mm	0.31	310	125	125	110	8171467	VSVA-BT-M32CS2-MH-A2-1T5L-PA
	СТ	AT	Control plug-in, pressure switch plug-in, manual over- ride (MO) non-detenting	18 mm	0.31	310	125	125	110	8171469	VSVA-BT-M32CS2-MH-A2-1T1L-PZ
	3/2-way sol	enoid valve NC.	internal pilot air supply for the va	lve termin	al						
	CS	-	Control plug-in, pressure switch plug-in, manual override (MO) self- resetting	18 mm	0.31	310	150	150	110	8066569	VSVA-BT-M32CS1-MYE-A2-1T5L-PA
	CS	AS	Control plug-in, external M12 pressure switch, manual override (MO) self- resetting	18 mm	0.31	310	150	150	110	8066568	VSVA-BT-M32CS1-MYE-A2-1T1L-PZ
	CS	-	Control plug-in, pressure switch plug-in, manual override (MO) con- cealed	18 mm	0.31	310	150	150	110	8066571	VSVA-BT-M32CS1-MS-A2-1T5L-PA
	CS	AS	Control plug-in, external M12 pressure switch, manual override (MO) con- cealed	18 mm	0.31	310	150	150	110	8066570	VSVA-BT-M32CS1-MS-A2-1T1L-PZ
	CS	-	Control plug-in, external M12 pressure switch, manual over- ride (MO) non-detenting	18 mm	0.31	310	125	125	110	8171468	VSVA-BT-M32CS1-MH-A2-1T5L-PA
	CS	AS	Control plug-in, external M12 pressure switch, manual over- ride (MO) non-detenting	18 mm	0.31	310	125	125	110	8171470	VSVA-BT-M32CS1-MH-A2-1T1L-PZ

1) With an ambient temperature and temperature of medium of from -5 °C to +5 °C and 40 °C to 50 °C, the maximum permissible operating pressure is 0.8 MPA or 8 bar.

2) +/- 15% to FN 942032


3) Weight of pilot air switching valve without manifold sub-base

Datasheet – Pilot air switching valve for VTSA/VTSA-F-CB


Ordering data							
	Terminal code VTSA-F-CB	Terminal code VTSA/VTSA-F	Description			Part no.	Туре
Manifold sub-ba	ase for pilot ai	r switching valv	re	-			
	YB	_	For 2 valve positions (4 addresses) 1x valve position, 1x double solenoid valve, high flow	18 mm	434	8068913	VABF-S4-2HS-G18-CB-2T5
	YC	_	Hybrid manifold sub-base, width 18 and 26 mm For 2 valve positions (4 addresses) 1x valve position with CBUS communication, 1x double solenoid valve, high flow (with CBUS loop-through)	18 mm/26 mm	512	8068912	VABV-S4-12HS-G-CB-2T5
	_	ХА	Hybrid manifold sub-base, width 18 and 26 mm For 2 valve positions (4 addresses)	18 mm/26 mm	512	8190411	VABV-S4-12HS-G-2T2

Datasheet - Soft-start valve for VTSA/VTSA-F

Function without sensor



With sensor



Description


Function

The purpose of the soft-start valve is to slowly and safely build up the supply pressure in duct 1 of the valve terminal or to quickly exhaust it via duct 1. Switch-on takes place in two stages:

• First the working pressure for duct 1 gradually increases (the speed can be adjusted using a throttle screw).

- Flow rate
 Pressurisation:
 3000 l/min
 Exhausting: 3300 l/min
- Module width 43 mm
 - Temperature range
 -5 ... +50 °C

Operating pressure 0.2 ... 1.2 MPa 2 ... 12 bar



 Once the working pressure in duct 1 reaches a previously set value, the soft-start valve switches to full operating pressure at duct 1 of the valve terminal.

The switching point for full operating pressure is set to 4 bar at the factory, but can be changed using an adjusting screw.

The full operating pressure is applied at duct 14 (pilot air) at all times. This pressure causes the valves on the valve terminal to immediately move to the required switching position, so an unspecified position is not possible. Duct 1 of the valve terminal is exhausted via the soft-start valve's exhaust port only in the normal position, when the valve is not switched. The exhaust air can optionally be ducted with a QS fitting or using a silencer.

A detenting manual override with self-reset via an electrical control signal is available for maintenance and service purposes.

· 📲 - Note

When using "Protection against unexpected start-up": Protection against unexpected activation of the manual override (MO) must be guaranteed in all operating modes.

Diagnostics

The piston position of the soft-start valve can be monitored by a sensor with integrated LED display. This sensor registers whether the valve has switched and thus whether the valve terminal is being supplied with supply air.

Pilot air supply

The valve terminal can either be supplied with internal pilot air via the softstart valve or with internal or external pilot air via the various end plate variants or the pilot air switching valves. Pressure sensing via a pressure gauge (optional) is also possible.

The pilot air supply for the valve termi-

nal (internal/external) is determined

base and the soft-start valve.

by the seal between the manifold sub-

The soft-start valve can also be ordered with a sensor. A sensor cannot be retrofitted at a later date because of the calibration that is required. Connecting cables with integrated LED display are provided for displaying the signal status.

The scope of delivery of the soft-start valve includes both the seal for internal pilot air supply (with drilled hole) and the seal for external pilot air supply (no drilled hole). The soft-start valve itself is always supplied with internal pilot air.

Description

Creating pressure zones with a soft-start valve

The soft-start valve can be used for the pneumatic compressed air supply of the valve terminal or of a pressure zone. The soft-start valve can only be used as the sole compressed air supply component on valve terminals with one pressure zone or within a pressure zone.

If a soft-start valve in combination with a right end plate (code XP3) is chosen for a pressure zone, this pressure zone must have a supply plate with a blanking plug in duct 1 (code W).

When using a soft-start valve, a supply plate (with blanking plug in duct 1) is generally also required for this pressure zone to discharge the exhaust air (duct 3/5).

A supply plate is not required if the exhaust air (duct 3/5) in a pressure zone with soft-start valve can be discharged via the right end plate.

Constraints Compressed air supply Exhaust air Pilot air supply Reverse operation There must be no other elements sup-Exhaust air cannot be expelled via the If the soft-start valve is used for inter-The soft-start valve is not approved for plying compressed air in the pressure soft-start valve. If it is being used in a nal pilot air supply (duct 14), there reverse operation. zone in which the soft-start valve is bepressure zone with duct 3/5 separate, must be no other pilot air supply withing used. an exhaust plate is required. in the valve terminal. -Î -Note

Setting options as well as drawings with descriptions of the components for the soft-start valve can be found in the user documentation. The adjusting screws are freely accessible once they are fitted.

Safety characteristics

Conforms to standard	ISO 5599-2
Note on forced checking procedure	Switching frequency min. once a month
Max. positive test pulse [µs]	2500 ¹⁾
with logic 0	
Max. negative test pulse [µs]	1400 ¹⁾
with logic 1	
Shock resistance	Shock test with severity level 2, to EN 60068-2-27
Vibration resistant	Transport application test with severity level 2, to EN 60068-2-6

1) Values apply only to types with direct voltage 24 V DC

General technical data

Design	Piston spool
Actuation type	Electrical
Sealing principle	Soft
Type of mounting	On sub-base, ISO size 1 to ISO 5599-2
Mounting position	Any
Valve function	Soft-start function
Manual override	Detenting, self-resetting via electrical control signal, normal position on top, \rightarrow page 197
Reset method	Mechanical spring
Type of control	Piloted
Pilot air supply	Internal, external
Flow direction	Not reversible
Switching position sensing	Switching position with sensor

Standard nominal flow rate [l/min]

Pressurisation	3000
Exhausting	3300

Operating and environmental conditions

Operating and environmental conditions			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Notes on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[bar]	212	
	[MPa]	0.2 1.2	
Switchover pressure presetting	[bar]	4	
	[MPa]	0.4	
Ambient temperature	[°C]	-5 +50	
Note on materials		RoHS-compliant	

Valve switching times [ms]

Valve switching time	On	17
	Off	50

Electrical data for soft-start valve

Electrical connection		Plug, type C to EN 175301-803, square design
Nominal operating voltage	[V]	24 DC
Operating voltage range	[V]	24 DC ±10%
Characteristic coil data		24 V DC: 2.5 W
Degree of protection to EN 60529	9	IP65, NEMA 4 (for all types of signal transmission when mounted)

Electrical data for sensor

Туре		SIEN-M12B-PS-S-L	SIEN-M12B-NS-S-L	
Electrical connection		Plug M12x1 to EN 60947-5-2, 4-pin		
Switching output		PNP	NPN	
Switching element function		N/0		
Signal status indication		Yellow LED		
Operating voltage range	[V DC]	10 30		
Residual ripple	[%]	±10		
Rated operating voltage	[V DC]	24		
Max. no-load current for sensor	[mA]	10		
Max. output current	[mA]	200		
Max. voltage drop	[V]	2		
Max. switching frequency	[Hz]	3000		
Short circuit current rating		Clocked		
Reverse polarity protection for sensor		For all electrical connections		
Measuring principle		Inductive		
Switching position sensing		Switching position with sensor		

Materials		
	Soft-start valve	Manifold sub-base
Housing	Wrought aluminium alloy	Die-cast aluminium
Seals	NBR, HNBR	-
Screws	Galvanised steel	-

T

Example 1: Pressure zone with soft-start valve and pilot air supply

Internal, external pilot air supply

Requirements


- Compressed air supply via soft-start valve
- Right end plate^{1):} Blanking plug in duct 1

For internal pilot air supply:

- Seal (soft-start valve manifold subbase) with pilot air supply bore "open" and
- Right end plate: Blanking plug in duct 14

For external pilot air supply:

- Seal (soft-start valve manifold subbase) with pilot air supply bore "closed" and
- Pilot air supply via duct 14 in the right end plate



- [1] Seal for internal pilot air supply
- [2] Seal for external pilot air supply

1) A right end plate with pilot air selector cannot be used with this configuration, as it doesn't allow the exhaust air to be discharged

Example 2: Pressure zone with soft-start valve, supply plate and pilot air supply

Internal, external pilot air supply


Requirements

"open" and


duct 14 or

"closed" and


valve • Supply plate:



- [1] Seal for internal pilot air supply
- [2] Seal for external pilot air supply



• End plate with coding (position 1, external pilot air supply)



Pneumatic part:

44P-N-XP1-SMPM-BB-3JL+UGBP1


1 411 110	557217
Electrical part:	51E-F36GCQPNMKBLX-S+GSBA
Pneumatic part:	44P-N-XP2-SMPP-BB-3JL+UGBP1

→Internet: www.festo.com/catalogue/...

Practical example 2: Valve terminal VTSA with CPX terminal (metal design), soft-start valve and switching position sensing

With external pilot air (PM and XP2):

Part no.: 539217



- [1] Fieldbus node for EtherNet/IP or Modbus TCP
- [2] Input module (16 digital inputs)
- [3] Output module (8 digital outputs)
- [4] CPX pneumatic interface
- [5] Soft-start valve
 - (PM external pilot air)
- [6] 5/2-way single solenoid valve, spring return, switching status indication with PNP sensor with 0.5 m connecting cable and pushin connector M12x1 (SS), and intermediate plate for switchable pilot air supply (ZO)
- [7] 5/2-way double solenoid valve (J), width 26 mm
- [8] Vacant position (L)
- [9] Right end plate (XP2) with supply air/exhaust air, external pilot air supply, blanking plug in duct 1 and 14


Selection with external pilot air (PM and XP2), solenoid valve with switching position sensing (SS) and intermediate plate for switchable pilot air supply (ZO)

Part no.:	539217
Electrical part:	51E-F36GCQPNMKBLX-S+GSBA
Pneumatic part:	44P-N-XP2-SMPM-BB-SSZOJJL+UGCGBP1

Practical example 3: Valve terminal VTSA with CPX terminal (metal design), switching position sensing, soft-start valve and 2 pressure zones

With external pilot air (PM and XP2)

Part no.: 539217



- [1] Fieldbus node for EtherNet/IP or Modbus TCP
- [2] Input module (16 digital inputs)
- [3] Output module (8 digital outputs)
- [4] CPX pneumatic interface
- [5] Soft-start valve for one pressure zone (PM external pilot air)
- [6] 5/2-way single solenoid valve, spring return, switching status indication with PNP sensor with 0.5 m connecting cable and pushin connector M12x1 (SS), and intermediate plate for switchable auxiliary pilot air supply (ZO)

Selection with external pilot air (PM and XP2), solenoid valve with switching position sensing (SS) and intermediate plate for switchable pilot air supply and 2 pressure zones

 Part no.:
 539217

 Electrical part:
 51E-F36GCQPNMKBLX-S+GSBA

 Pneumatic part:
 44P-N-XP2-LSMPM-BWBSPMA-SSZOJJLJJ+UGCGBP1

Electrical connection of pneumatic components


The solenoid valve with switching position sensing (SS), with sensor connection M12 is connected to the CPX input module using an appropriate connecting cable in order to link the sensor signal to the CPX system. The soft-start valve (PM – with sensor PNP) is connected to the CPX input module using an appropriate connecting cable (GC) in order to integrate the sensor signal into the CPX system.

- [7] 5/2-way double solenoid valve (J), width 26 mm
- [8] Exhaust plate (W) for ducts 3/5
- [9] Vacant position (L)
- [10] Duct separation (S) 1, 3, 5
- [11] 5/2-way double solenoid valve (J), width 18 mm
- [12] Right end plate (XP2) with supply air/exhaust air, external pilot air supply, blanking plug in duct 1 and 14

A connecting cable (GBP1) to/from the CPX output module is used to control the soft-start valve (PM). (Control signal)

Dimensions

Download CAD data → <u>www.festo.com</u>



Type
 H1
 L1

 VABD-S6- ...
 40
 84.8

1) Seals are included with the soft-start valve


Ordering data	Terminal code	Description	Weight [g]	Part no.	Туре
Soft-start valve, 24 V I	DC		101		
	-	Without sensor output, pneumatic connection G1/2 (with seals for internal and external pilot air)	590	558230	VABF-S6-1-P5A4-G12-4-1
	PN	Seal for external pilot air (without drilled hole)			
- Bri	PQ	Seal for internal pilot air (with drilled hole)			
	-	With sensor output PNP, pneumatic connection G1/2 (with seals for internal and external pilot air)	605	557377	VABF-S6-1-P5A4-G12-4-1-P
	PM	Seal for external pilot air (without drilled hole)	_		
- Bir	PP	Seal for internal pilot air (with drilled hole)			
	-	With sensor output NPN, pneumatic connection G1/2 (with seals for internal and external pilot air)	605	558233	VABF-S6-1-P5A4-G12-4-1-N
	РК	Seal for external pilot air (without drilled hole)			
- Shi	PO	Seal for internal pilot air (with drilled hole)			
Manifold sub-base		1			
	-	Suitable for a soft-start valve (ports for ducts 2 and 4 are combined), pneumatic connection G1/2	570	556989	VABV-S6-1Q-G12


Accessories – Soft-start valve for VTSA/VTSA-F

signation	Code	Description		Part no.	Туре
over cap					
	-	M12, for sealing the sensor opening	Pack of 10	165592	ISK-M12
ectrical connectior	n for soft-start va	lve	· · · · · ·	÷ 	
	P1	 Angled socket, type C, 2-pin, with LED Straight plug M12x1, 2-pin 24 V DC 		188024	MSSD-EB-M12-MONO
M - Jan - B	GB	 Straight socket, M12x1, 5-pin Open end, 4-core 	5 m	8078240	NEBA-M12G5-U-5-N-LE4
- MA	-	 Angled socket, M12x1, 5-pin Open end, 4-core 	5 m	8078249	NEBA-M12W5-U-5-N-LE4
	GG	• Angled socket, type C, 3-pin, with LED	2.5 m	151688	KMEB-1-24-2.5-LED
-	GH	• Open end, 3-core	5 m	151689	KMEB-1-24-5-LED
· Martin	GJ	• 24 V DC, PVC	10 m	193457	KMEB-1-24-10-LED
\downarrow	GK	• Angled socket, type C, 3-pin	2.5 m	151690	KMEB-1-230AC-2.5
٥	GL	Open end, 3-core 230 V AC, PVC	5 m	151691	KMEB-1-230AC-5
Connecting cable for	r electrical conne	ection of the proximity switch			
M Lan .	-	 Straight socket, M12x1, 5-pin Open end, 4-core 	5 m	8078240	NEBA-M12G5-U-5-N-LE4
A	GC	 Angled socket, M12x1, 5-pin Open end, 4-core 	5 m	8078249	NEBA-M12W5-U-5-N-LE4
Silencer	I				
A BARA	U	Standard design, connecting thread (1 piece)	G1/2	6844	U-1/2-B
	A	Sintered design, connecting thread (pack of 10)	G1/2	1205863	AMTE-M-LH-G12
	ole fittings, blank cessories can be	ting plugs, silencers and found in the chapter Accessories → page: 242 search terms: silencer, blanking plug			1

Datasheet - Soft-start valve for VTSA-F-CB

Function





Description

Smart valve functions

The basic functions are the same as for the familiar soft-start valve.


There is a variant with internal pilot air supply (code PM) and a variant without internal pilot air supply (code PN). In addition, the new smart soft-start valve has:

- An integrated pressure sensor for sensing the exhausted position
- A revised design of the manual override with protection against unintended actuation, as well as an automatic reset

- N - Flow rate

Pressurisation: 3000 l/min Exhausting: 3300 l/min

- **[]** Module width 41 mm
 - Temperature range
 -5 ... +50 °C
 - Operating pressure
 2 ... 10 bar
 0.2 ... 1 MPa



Like the familiar soft-start valve, its purpose is to slowly and safely build up the supply pressure in duct 1 of the valve terminal or to quickly exhaust it. Switch-on takes place in two stages:

- First the working pressure for duct 1 gradually increases (the speed can be adjusted using a throttle screw).
- Once the working pressure in duct 1 reaches half the operating pressure, the soft-start valve switches to full operating pressure at duct 1 of the valve terminal.

The switching point is permanently set at 50% of the operating pressure. The full operating pressure is applied at duct 14 (pilot air) at all times. This pressure causes the valves on the valve terminal to immediately move to the required switching position, so an unspecified position is not possible. Duct 1 of the valve terminal is exhausted via the soft-start valve's exhaust port only in the normal position, when the valve is not switched. The exhaust air can optionally be ducted with fittings for compressed air tubing with standardised O.D. or using a silencer. A detenting manual override with self-reset via an electrical control signal is available for maintenance and service purposes.

Safety characteristics

Max. positive test pulse	[µs]	2000
with logic 0		
Max. negative test pulse	[µs]	1200
with logic 1		
Shock resistance		Shock test with severity level 2, to EN 60068-2-27
Vibration resistant		Transport application test with severity level 2, to EN 60068-2-6

Datasheet – Soft-start valve for VTSA-F-CB

General technical data

General technical data		
Design		Piston spool valve
Grid dimension	[mm]	41
Valve size	[mm]	40
Overlap		Negative overlap
Actuation type		Electrical
Sealing principle		Soft
Type of mounting		On sub-base
Mounting position		Any
Valve function		soft-start and exhaust function
Manual override		Detenting, self-resetting via electrical control signal (part numbers 8067407 and 8067405), normal position on top \rightarrow page 205
Manual override		None (part numbers 8161611, 8161610, 8067411 and 8067409)
Reset method		Mechanical spring
Type of control		Piloted
Pilot air supply		For soft-start valve: always internal via valve terminal
		For valve terminal: internal via soft-start valve (part nos. 8067407, 8067411)
		For valve terminal: internal, not via soft-start valve (part nos. 8067405, 8067409)
Flow direction		Not reversible
Pneumatic port 3		G1/2
MTTF, subcomponent		452 years, pressure switch

Standard nominal flow rate [l/min]

	•
Pressurisation	3000
Note pressurisation	MPA: 1200
-	VTSA: 3000
Exhausting	3300
Note exhausting	MPA: 1600
-	VTSA: 3300

Operating and environmental	Operating and environmental conditions				
Туре		VABF-S6-1-P5A4S1	VABF-S6-1-P5A4S2		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	Compressed air to ISO 8573-1:2010 [7:4:4]		
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	Compressed air to ISO 8573-1:2010 [7:4:4]		
Notes on operating/pilot mediu	um	Lubricated operation not possible			
Pilot pressure	[bar]	3 10	2 10		
	[MPa]	0.3 1	0.2 1		
Operating pressure	[bar]	3 10	2 10		
	[MPa]	0.3 1	0.2 1		
Relative humidity		Max. 90% at 40 °C			
Ambient temperature	[°C]	-5 +50			
Temperature of medium [°C]		-5 +50			
Storage temperature [°C]		-20 +60			
Corrosion resistance class CRC ¹	1)	0	0		

1) More information www.festo.com/x/topic/crc

Electrical data for soft-start valve


Electrical data for soft-start valve	
Electrical control	Fieldbus
Electrical connection	Plug-in
Nominal operating voltage [V]	24 DC
Operating voltage range [V]	24 DC ±10%
Characteristic coil data	24 V DC: 1.6 W
Permissible voltage fluctuations [%]	±10%
Degree of protection to EN 60529	IP65 (for all types of signal transmission when mounted)
Pressure sensor	Integrated (plug-in)
Sensor evaluation	Internal
Switching element function	N/C
Switching position sensing	Via pressure switch, exhausted status
Signal status indication	Yellow LED, valve control
	Green LED, pressure switch, exhausted status
Duty cycle [%]	100

Materials

	Soft-start valve	Manifold sub-base			
Housing	Wrought aluminium alloy	Die-cast aluminium			
Seals	NBR, HNBR	-			
Screws	Galvanised steel	-			
Note on materials	RoHS-compliant				

Connection and display components

Soft-start valve VABF-S6-1-P5A4-... with manifold sub-base




ļ -Note -

Detailed information on the manual override can be found in the user documentation.

- [1] Basic valve housing
- [2] Intermediate plate
- [3] Pilot control
- [4] Manual override (MO) (optional)
- [5] Exhaust air port for duct 1
- [6] Pressure sensing for duct 1


- [7] Compressed air supply port
- [8] Exhaust air port for duct 3/5




Datasheet – Soft-start valve for VTSA-F-CB

Dimensions


Download CAD data → <u>www.festo.com</u>



Seal ¹⁾ between soft-start valve and manifold sub-base



[1] With elongated hole, internal pilot air supply



[1] Without elongated hole, external pilot air supply

Туре	В1	L1
VABF-S6-1-P5A4Z	39	72.7

1) Seals are included with the soft-start valve

Accessories – Soft-start valve for VTSA-F-CB

Ordering data								
	Code	Description	Description Operating pressure		Weight	Part no.	Туре	
				[MPa]	[bar]	[g]		
Soft-start valve, wi	thout ma	nifold sub-base						
	PM	Pilot pressure build- up from duct 1 (S1)	Manual override (MO), self-resetting	0.3 1	3 10	466	8067407	VABF-S6-1-P5A4S1YE-G12-1T5-PA
			Manual override (MO), concealed	0.3 1	3 10	466	8067411	VABF-S6-1-P5A4S1S-G12-1T5-PA
\checkmark	PN No pilot pressure build-up from duct 1 (S2)	Manual override (MO), self-resetting	0.2 1	2 10	466	8067405	VABF-S6-1-P5A4S2YE-G12-1T5-PA	
		(S2)	Manual override (MO), concealed	0.2 1	2 10	466	8067409	VABF-S6-1-P5A4S2S-G12-1T5-PA
Ordering data								
	Code	Description				Weight [g]	Part no.	Туре
Manifold sub-base	for soft-	start valve						
	PV	 With CBUS loop-thrc Sensor evaluation: i Duct 3/5 combined Only in combination Pneumatic connection 	nternal with pneumatic interface with	voltage zone		421	8068609	VABV-S6-1Q-G38-CB1-T5

Datasheet - Pneumatic interface for VTSA-F-CB





Description

Up to three safe voltage zones can be formed in the pneumatic part of the valve terminal using the pneumatic interface. There is also a variant available which uses a safe voltage zone as an external output. The pneumatic interfaces (zone extensions) can be placed centrally in the pneumatic section of a valve terminal VTSA-F-CB and they extend the valve terminal by up to 3 additional (safe) voltage zones.

Function

Two different equipment levels:

- Creation of up to three safe internal voltage zones
- Creation of up to two safe internal voltage zones and one safe external voltage zone
- Integrated driver levels for addressing up to 24 valves within the first safe voltage zone
- Integrated diagnostics on short circuit and overload of the controlled valve coils
- Integrated diagnostics for load voltage undervoltage

Datasheet – Pneumatic interface for VTSA-F-CB

General technical data		
Туре		VABA-S6-1-X2-3V-CB-AL
Max. no. of valve positions		12 with double solenoid valves
		24 with single solenoid valves
Product weight	[g]	1388
Electrical data		
Туре		VABA-S6-1-X2-3V-CB-AL
Electrical connection		3x M12x1, A-coded
		5-pin
		Plug
		Via CPX
Operating voltage range	[V DC]	21.6 26.4
Intrinsic current consumption at	[mA]	Typically 11 (operating voltage supply for electronics)
nominal operating voltage		Typically 45 (load voltage supply for valves)
Max. power supply per channel	[A]	0.2
Max. total current per module	[A]	6
Nominal operating voltage	[V DC]	24
Degree of protection		IP65
		NEMA 4
Operating and environmental co	anditions	
Type	indicions.	VABA-S6-1-X2-3V-CB-AL
Ambient temperature	[°C]	-5 50
Materials		
Type		VABA-S6-1-X2-3V-CB-AL
	_	
Note on materials		RoHS-compliant
Information on materials: Housin	g	Die-cast aluminium
Information on materials: Cover		PA
Corrosion resistance class CRC		0 ¹⁾
LABS (PWIS) conformity		VDMA24364-B1/B2-L

1) More information www.festo.com/x/topic/crc

Datasheet – Pneumatic interface for VTSA-F-CB

General technical data					
Туре		VABA-S6-1-X2-F1-CB-AL	VABA-S6-1-X2-F1-CB2-AL		
Max. no. of valve positions		12 with double solenoid valves	12 with double solenoid valves		
		24 with single solenoid valves	24 with single solenoid valves		
Product weight	[g]	1542	1576		
Electrical data					
Type		VABA-S6-1-X2-F1-CB-AL	VABA-S6-1-X2-F1-CB2-AL		
I/O output, function		-	Power supply, valve		
I/O output, connection type		-	Plug		
I/O output, connection technolo	gy	-	7/8" round plug connector		
I/O output, number of pins		-	5		
Electrical connection		Via CPX	Via CPX		
Operating voltage range	[V DC]	21.6 26.4	21.6 26.4		
Intrinsic current consumption at	[mA]	Typically 15 El. w/o CPX-FVDA-P2	Typically 15 El. w/o CPX-FVDA-P2		
nominal operating voltage		Typically 25 El. with CPX-FVDA-P2	Typically 25 El. with CPX-FVDA-P2		
Max. power supply per channel	[A]	0.2	0.2		
Max. total current per module	[A]	2	2		
Nominal operating voltage	[V DC]	24	24		
Degree of protection		IP65	IP65		
Operating and environmental o Type	conditions	VABA-S6-1-X2-F1-CB-AL	VABA-S6-1-X2-F1-CB2-AL		
Storage temperature	[°C]	-20 60	-		
Ambient temperature	[°C]	-	-5 50		
Vibration resistant		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6		
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27		
Materials					
Туре		VABA-S6-1-X2-F1-CB-AL	VABA-S6-1-X2-F1-CB2-AL		
Note on materials		RoHS-compliant			
Information on materials: Sub-base		Die-cast aluminium			
Information on materials: Cover		PA			
Information on materials: Screws		Steel			
Information on materials: Seals		NBR	NBR		
Corrosion resistance class CRC		01)	0 ¹⁾		
CE marking		To EU EMC Directive ²)			
		To EU RoHS Directive			

1) Corrosion resistance class CRC 0 to Festo standard FN 940070

No corrosion stress. Applies to small, visually unimportant standard parts such as threaded pins, circlips and clamping sleeves which are usually only available on the market in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.

2) For information about the area of use, see the declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27

Datasheet – Pneumatic interface for VTSA-F-CB

General technical data					
Туре		VABA-S6-1-X2-F2-CB-AL	VABA-S6-1-X2-F2-CB2-AL		
Max. no. of valve positions		12 with double solenoid valves	12 with double solenoid valves		
		24 with single solenoid valves	24 with single solenoid valves		
Product weight	[g]	1562	1596		
Electrical data					
Туре		VABA-S6-1-X2-F2-CB-AL	VABA-S6-1-X2-F2-CB2-AL		
I/O output, function		Safe digital output			
I/O output, connection type		Socket			
I/O output, connection technology		M12x1, A-coded to EN 61076-2-101			
I/O output, number of pins		5			
I/O valve, function		-	Power supply, valve		
I/O valve, connection type		-	Plug		
I/O valve, connection technology		-	7/8" round plug connector		
I/O valve, number of pins		-	5		
Electrical connection		Via CPX			
Operating voltage range	[V DC]	21.6 26.4			
Intrinsic current consumption at	[mA]	Typically 15 El. w/o CPX-FVDA-P2			
nominal operating voltage		Typically 25 El. with CPX-FVDA-P2			
Max. power supply per channel	[A]	0.2			
Max. total current per module	[A]	2			
Nominal operating voltage	[V DC]	24			
Degree of protection		IP65			
Operating and environmental co	nditions				
Туре		VABA-S6-1-X2-F2-CB-AL	VABA-S6-1-X2-F2-CB2-AL		
Storage temperature	[°C]	-	-20 60		
Ambient temperature	[°C]	-5 50	1		
Vibration resistant		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6		

Materials

Shock resistance

Materials		
Туре	VABA-S6-1-X2-F2-CB-AL	VABA-S6-1-X2-F2-CB2-AL
Note on materials	RoHS-compliant	
Information on materials: Sub-base	Die-cast aluminium	
Information on materials: Cover	PA	
Information on materials: Screws	Steel	
Information on materials: Seals	NBR	
Corrosion resistance class CRC	0 ¹⁾	
CE marking	To EU EMC Directive ²)	
	To EU RoHS Directive	

Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27

1) Corrosion resistance class CRC 0 to Festo standard FN 940070

No corrosion stress. Applies to small, visually unimportant standard parts such as threaded pins, circlips and clamping sleeves which are usually only available on the market in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.

2) For information about the area of use, see the declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.


If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Ordering data

_	Code	Description	Part no.	Туре
	ХВ	Pneumatic interface for extending by 3 external voltage zones	8152438	VABA-S6-1-X2-3V-CB-AL
	XC	Pneumatic interface for extending by 3 safe internal zones (PROFIsafe)	8152437	VABA-S6-1-X2-F1-CB-AL
	XD	Pneumatic interface for extending by 2 safe internal zones + 1 safe output (PROFIsafe)	8152436	VABA-S6-1-X2-F2-CB-AL
	PC	Pneumatic interface with additional power supply for extending by 3 safe internal zones (PROFIsafe)	8152435	VABA-S6-1-X2-F1-CB2-AL
	PD	Pneumatic interface with additional power supply for extending by 2 safe internal zones + 1 safe output (PROFIsafe)	8152434	VABA-S6-1-X2-F2-CB2-AL

T

Datasheet – Vacuum block for VTSA/VTSA-F



Description

Function

Ejection

Vacuum block width 53 mm

Voltage 24 V DC

Operating pressure 0.4 ... 0.8 MPa 4 ... 8 bar



The vacuum block is used in conjunction with a suction gripper to pick up, hold and place components. The suction gripper uses vacuum for picking up and holding.

Once the component has been positioned, it is released by an ejector pulse. This ejector pulse is created by pressurising the vacuum system so that the vacuum briefly collapses. The ejector pulse can be set.

The vacuum block can be operated in combination with the vertical stacking for pilot air switch-off on the valve terminal VTSA/VTSA-F.

Note

The vacuum block VABF-S4-1-V2B1... is used to generate a vacuum. The generated vacuum and a suction gripper produce a force which is used to grip and transport a workpiece. The supply of compressed air for vacuum generation is controlled by a solenoid valve. The vacuum is generated by actuating

The vacuum block can be integrated

into the existing valve terminal VTSA/

VTSA-F. To do this, the vacuum block is

screwed to a manifold sub-base for 2

valve positions, width 26 mm.

The setpoint value set at duct B for the generated vacuum is monitored via a vacuum sensor (with switching output). Vacuum generation reverts to a self-holding phase after reaching the setpoint value. The vacuum block controls the vacuum generation process independently within the range of the set switching points (air saving funcThe integrated solenoid valve is used to generate an ejector pulse by activating coil 14. The workpiece is thus safely released from the suction cup with connector and the vacuum is rapidly reduced. The length of the ejector pulse can be influenced by the duration of the electrical pulse. The strength of the ejector pulse is influenced by the ad-

duct B (3) "vacuum sensing".

Note

If the electrical or pneumatic supply fails while the valve is in the "generate vacuum" or "air saving" state, the valve moves to the "generate vacuum" position.

solenoid coil 12.	set switching points (air saving func- tion).	ejector pulse is influenced by the ad- justable flow control.	
Operating mode of the air saving function	on (LS)		
If the desired threshold value (1) (turn off suction) is reached for the vacuum, vacuum generation is automatically switched off.	Check valves prevent the reduction of the vacuum. However, leakages (e.g. due to rough workpiece surfaces) will slowly reduce the vacuum.	If the vacuum drops below the set threshold value (2) (turn on suction), vacuum generation is switched on au- tomatically.	Vacuum is generated until the set threshold value (1) (turn off suction) is reached again.
Threshold value to turn off suction (air saving function) (1):		Threshold value to turn on suction (2):	
The vacuum generator is switched off simultaneously when the output Out A	The preset value is -700 mbar.	The threshold value (2) should always be above the switching point of	The gap between (2) and (3) should be at least 50 mbar.

Note

is set.

Setting options and further instructions are described in the operating instructions and/or documentation VABF-S4-1-V2B1... on the Support Portal from Festo.

Datasheet – Vacuum block for VTSA/VTSA-F

General technical data

General technical data			
Valve function		5/3-way, pressurised	
Design		Non-modular	
Mounting position		Any	
Nominal width of Laval nozzle	[mm]	2.0	
(vacuum generation)			
Ejector characteristics		High vacuum, standard	
Integrated functions		Ejector pulse valve, electric	
		Flow restrictor	
		On/offvalve, electric	
		Air-saving circuit, electric	
		Check valve	
		• Open silencer	
		Vacuum switch	
Silencer design		Open	
Measured variable		Relative pressure	
Measuring principle		Piezoresistive	
Switching function		Threshold-comparator	
Short circuit current rating		Yes	
Reverse polarity protection		For all electrical connections	
Inductive protective circuit		Adapted to MZ, MY, ME coils	
Switching element function		N/O	
Threshold-value setting range	[bar]	-0.999 0 (recommended operating range: -0.950.05)	
	[MPa]	-0.0999 0 (recommended operating range: -0.0950.005)	
Hysteresis setting range	[bar]	-0.9 0	
	[MPa]	-0.090	
Power supply, vacuum block		Via own M12 plug	
Pneumatic supply for vacuum blo	ck	Via valve terminal VTSA/VTSA-F	
Ejector pulse		Strength adjustable via flow control screw	
Actuation type			
 Solenoid valve 		Electrically actuated	
 Vacuum block 		Vacuum generation via Venturi nozzle	
Type of actuation for solenoid val	ve	Piloted	
Flow direction		Not reversible	
Exhaust air function		Can be throttled (duct 3 and 5)	
Type of mounting		Via through-hole, screwed onto manifold sub-base, width 26 mm	
Manual override		Detenting, non-detenting, concealed	
For vacuum generation		Yes, solenoid coil 12 (holding)	
For ejector pulse		Yes, solenoid coil 14 (spring return), (only effective when power supply is switched off)	
Signal status display, valve		LED	
Pneumatic connections			
Supply	1,3	Via the manifold sub-base of the valve terminal, width 26 mm	
Exhausting	3/5	Via the modular silencer for vacuum block	
Working port (vacuum port)	2	Via the manifold sub-base of the valve terminal (QS push-in fitting – vacuum), G1/4	
Connection	4	Via the manifold sub-base of the valve terminal (sealed with blanking plug type B-1/4)	

Datasheet – Vacuum block for VTSA/VTSA-F

| Technical data for pressure switch of vacuum block (delivery status)

Duct A: air saving function		
Switching behaviour		Threshold-comparator
Switching point	[mbar]	-700
	[MPa]	-0.07
Hysteresis	[mbar]	200
	[MPa]	0.02
Switching characteristic		NO (normally open contact)
Duct B: vacuum sensing		
Switching behaviour		Threshold-comparator
Switching point	[mbar]	-400
	[MPa]	-0.04
Hysteresis	[mbar]	5
	[MPa]	0.0005
Switching characteristic		NO (normally open contact)

-- Note

Setting options for duct A and duct B and further instructions can be found on the Support Portal from Festo in the operating instructions and/or documentation VABF-S4-1-V2B1...

Electrical data

Electrical data		
Electrical connection	-	4-pin plug to ISO 15407-2 (vacuum block supplied with power separately, not via valve terminal)
Nominal operating voltage	[V DC]	24
Operating voltage range	[V DC]	21.6 26.4
Duty cycle	[%]	100
Max. output current	[mA]	50
Voltage drop	[V]	<1.5
No-load current	[mA]	50 150 (dependent on the switching status of the solenoid coils)
Characteristic coil data	[V DC]	24
Power consumption	[W]	1.3
(Characteristic coil data)		
Overload protection		Available
Accuracy (full scale)	[% FS]	±3
Degree of protection to EN 60529		IP65, NEMA 4 (for all types of signal transmission when mounted)

Electrical connection 1)

	Plug M12x1, 4-pin to EN 61076-2-101	Pin1	– + 24 V DC (brown (BN))	Supply voltage
		Pin2	– Out B (white (WH))	Switching output B (duct B)
		Pin3	– 0 V DC (blue (BU))	0 V DC
3 4		Pin4	– Out A (black (BK))	Switching output A (duct A)

1) Max. permissible signal cable length: 5 m

Ι

Datasheet – Vacuum block for VTSA/VTSA-F

Operating and environmental conditions


Operating and environmental co	nditions	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Notes on the operating medium		Unlubricated operation
Operating pressure	[bar]	48
	[MPa]	0.4 0.8
Nominal operating pressure	[bar]	6
	[MPa]	0.6
Pressure measuring range	[bar]	-10
	[MPa]	-0.1 0
Negative pressure	[bar]	Up to approx. 0.9 (as a function of operating pressure)
	[MPa]	Up to approx. 0.09 (as a function of operating pressure)
Ambient temperature	[°C]	050
Temperature of medium	[°C]	050
Noise level LpA (at nominal operating pressure)	[dB(A)]	78

Materials

Materials	
Housing, jet nozzle	Wrought aluminium alloy
Screws	Galvanised steel
Seals	NBR
Plug housing	Nickel-plated die-cast zinc
Plug contacts	Gold-plated brass
Inspection window on pressure sensor	PA
Pressure sensor keypad	TPE-U
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III

Pressure ratios, air consumption and volumetric flow rate


Vacuum as a function of operating pressure



[1] Vacuum

[2] Operating pressure


Air consumption as a function of operating pressure



[1] Air consumption

[2] Operating pressure

Datasheet – Vacuum block for VTSA/VTSA-F




Datasheet – Vacuum block for VTSA/VTSA-F

	Code	Description		Part no.	Туре
	Coue	Description		rait iiu.	Туре
/acuum block					
	VB	Vacuum block for valve terminal VTSA/VTSA-F with air-saving function and adjustable ejector pulse	1120 g	571425	VABF-S4-1-V2B1-C-VH-20
Manifold sub-base			1		
	L ²⁾	For vacuum block 2 valve positions, 4 addresses, with 2 blanking plugs in port 4	26 mm	_ 1)	VABV-S4
ere	LK ²⁾	For vacuum block 2 valve positions, 4 addresses, with 2 blanking plugs in port 4, with small QS fitting	26 mm	_ 1)	VABV-S4
Connecting cable		-			
ME THE S	-	Straight socket, M12x1, 5-pinOpen end, 4-core	2.5 m	8078239	NEBA-M12G5-U-2.5-N-LE4
M M S	-	 Straight socket, M12x1, 5-pin Open end, 4-core 	5 m	8078240	NEBA-M12G5-U-5-N-LE4
- Martin	GC	 Angled socket, M12x1, 5-pin Open end, 4-core 	5 m	8078249	NEBA-M12W5-U-5-N-LE4
	e fittings, bla ssories can b	nking plugs, silencers and ne found in the chapter Accessories → page: 242			

1) The manifold sub-base for use with the vacuum block can only be ordered via the valve terminal configurator and therefore doesn't have a separate part number.

2) Code letter within the order code for a valve terminal configuration

Datasheet – Vacuum generator for VTSA-F-CB



Voltage
 24 V DC

Operating pressure 4 ... 8 bar 0.4 ... 0.8 MPa

Description

The vacuum generator VABF is designed for generating a vacuum. The vacuum generator can be integrated into the existing valve terminal VTSA-F-CB.

The valve terminal supplies both compressed air and power.

Extended functions with VTSA-F-CB

The VTSA-F-CB with serial communication provides the vacuum generator with extended functions:

- Opening and saving of up to four records (on a local computer)
- Teach-in functionality: recording homing runs, from gripping and holding the workpiece to setting it down. Configuration of switching points and monitoring.

A solenoid valve (solenoid coil 12, vacuum generation) controls the compressed air supply. Vacuum is generated using the Venturi principle when the vacuum generator is pressurised with compressed air.

The vacuum generator is used in conjunction with a suction gripper to pick up, hold and place components.

- Preventive maintenance: measurement of all vacuum times, comparison with the homing run, warning message if a definable level of deviation is reached
- Switching air-saving function on/off
 Changing the vacuum parameters per record

The suction gripper uses vacuum for picking up and holding. Once the component has been positioned, it is released by an ejector pulse. The ejector pulse can be set. The ejector pulse is generated using the solenoid valve (solenoid coil 14, ejector pulse). The vacuum collapses if the vacuum system is briefly pressurised.

The power ejector pulse variant (-AP) of the vacuum generator is a more energy- and air-saving option.

- Locking the ejector pulse:
 - When the Uval of the adjacent voltage zone is switched off (voltage zone with safe shut-off within the valve terminal)
 - When there is a fault with the valve load voltage (e.g. undervoltage)
- Extended diagnostic functions via CBUS and display of status LED (yellow) or error LED (red)

- Note

In the event of an "emergency off" of the valve terminal (shutdown U_{VAL}), the vacuum generator VABF remains in vacuum generation mode with air-saving function.

If there is a complete power failure (bus shutdown, U_{SEN}) when the vacuum generator is in "Generate vacuum" mode, the valve switches to the "Permanent suction" position.

Vacuum generation

The vacuum is generated according to the Venturi principle using the vacuum generator cartridges VN. For the large sizes 20 and 30, two vacuum generator cartridges are used and connected in parallel. For size 14, one vacuum generator cartridge is used (the second port is sealed with a blanking plug). Vacuum generation is activated when the output signal "vacuum generation" is applied for at least 50 ms. Since the vacuum generation is pulse-controlled, vacuum is also generated after the output signal is deactivated.



• Evacuation or pressurisation time

exceeded

Datasheet – Vacuum generator for VTSA-F-CB

• Pressurisation time t_B

• Process quality

Function overview

- Monitoring process parameters
- Pressure value at vacuum port
- Limit values
- Evacuation time t_F

 Evacuation time t_E 		Fault on air-saving functionVacuum value not reached	Process quality below limit valueTeach-in error
Static teach-in	Dynamic teach-in	Air saving function	Manual override
Switching points and cycle time can be configured using the FMT (Festo Main- tenance Tool).	Calculating and optimising existing process sequences. Switching points and monitoring func- tions can be configured during opera- tion.	 Is set at the factory. Can be switched off for "air-permeable workpieces" (otherwise there will be an unnecessarily high number of switching processes). 	Both solenoid coils, for vacuum gener- ation and ejector pulse, can be switched manually using the manual override.
Pressure value (vacuum)	Cycle time	Evacuation and pressurisation time	Blanking plug
Pressure values are measured continu- ously between the vacuum port and filter. If the operating voltage of the vacuum generator is switched off, the values are reset.	The time from the start of the evacua- tion through ejection to the start of the new evacuation.	The evacuation time t_E is measured from the start of the evacuation until the switching point is reached. The pressurisation time t_B is measured from the start of the pressurisation to the time at which the pressure value (vacuum) falls below –5 kPa.	A vacuum generator V*20 or V*30 can be converted at a later date to V*14 us- ing a blanking plug OASC-V1-P. This makes it possible to reduce the air consumption or reduce the suction rate (e.g. for evacuation of smaller vol- umes).
Emergency stop function			
If the emergency stop (switching off the load voltage supply) is triggered during vacuum generation, the vacuum gener- ator remains in vacuum generation mode.	If the air saving function was activated, it remains active. If the parameter "ejector pulse interlock" is activated (set to inactive at the factory), no ejec- tor pulse is triggered in the event of an emergency stop.	If there is a complete power failure (electronic supply voltage) during vacu- um generation, the valve switches to "generate vacuum" position.	When the power supply is switched on again, the valve remains in the "gener- ate vacuum" operating status until an ejection signal is received.
Error state			
If communication between the control- ler and the vacuum generator is inter- rupted, a specific status is set.	The following settings are defined in this state:	 Output bit "vacuum generation" is set to 0. Output bit "ejector pulse" is set to 0. 	Parameter set is set to 0Air saving function is not affected
Additional characteristics			
 Galvanic isolation between the vacuum generator VABF and valve terminal VTSA-F-CB 3 performance settings for vacuum generation (14, 20, 30) Integrated solenoid valve for vacu- 	 Air-saving ejector pulse with increased ejecting rate (power ejector pulse) Flow control screw to adjust the ejector pulse Integrated pressure sensor 	 Integrated air-saving function Integrated strainer for filtering process air in order to protect the vacuum generator [-AP] Switching of the solenoid valve for vacuum generation with mechanical 	 Open silencer for reduced noise levels A check valve prevents purging of the vacuum if vacuum generation is interrupted

Fault detection and diagnostic messages

• Supply voltage not reached

• Evacuation time exceeded

um generation (solenoid coil 12)

and ejector pulse (solenoid coil 14)

manual override

Туре		Functions with type code VABFA	Functions with type code VABFAP		
Valve function	-	5/3-way, pressurised			
Design		Non-modular			
Mounting position		Any			
Nominal width of Laval nozzle	14 [mm]	1.4			
(vacuum generation)	20 [mm]	2.0			
	30 [mm]	3.0			
Ejector characteristics					
• VABFV2B1VH		High vacuum, standard			
 VABFV2B1VL 		High suction rate, standard			
Integrated functions		Ejector pulse, electrical	Power ejector pulse, electrical		
		Flow restrictor	Flow restrictor		
		On/off valve, electric	On/off valve, electric		
		Air-saving circuit, electric	Air-saving circuit, electric		
		Check valve	Check valve		
		Open silencer	Open silencer		
		Vacuum switch	Vacuum switch		
Silencer design		Open			
Measured variable		Relative pressure			
Measuring principle		Piezoresistive			
Switching function		Window comparator			
		Threshold-comparator			
Reverse polarity protection		For all electrical connections			
Switching element function		N/O			
Pneumatic supply for vacuum gen	erator	Via valve terminal VTSA-F-CB			
Ejector pulse		Strength adjustable via flow control screw			
Solenoid valve actuation type		Electrically actuated			
Type of actuation for solenoid valv	re	Piloted			
Flow direction		Not reversible			
Type of mounting		Via through-hole, screwed onto manifold sub-base,	width 35 mm		
Manual override		Non-detenting (only non-detenting: with accessories), detenting, covered (with accessories)		
 For vacuum generation 		Yes, solenoid coil 12 (holding)			
 For ejector pulse 		Yes, solenoid coil 14 (spring return), (only effective v	vhen power supply is switched off)		
Pneumatic connections					
Supply	1	Compressed air is supplied via the valve terminal			
Exhausting	3	Via silencer (open)			
Working port (vacuum port)	2	G3/8			

Electrical data and sensors

Operating voltage range (UB)	[V DC]	21.6 30
Nominal operating voltage	[V DC]	24
Duty cycle	[%]	100
No-load current	[mA]	30
Electrical control		Fieldbus
Electrical connection		Via CPX
Pressure measuring range	[bar]	-10
	[MPa]	-0.1 0
Accuracy (full scale)	[% FS]	±3
Reproducibility,	[%]	1
switching value FS		
Degree of protection to EN 60529		IP65
Protection class to DIN EN 61140		

I

Datasheet – Vacuum generator for VTSA-F-CB

Display and operation

Display and operation		
Display type		LED display, 2-digit
Threshold-value setting range	[kPa]	099
Hysteresis setting range	[kPa]	090
Setting options		Teach-in
		Via parameter sets
Sensor switching status indication		LED
Display range start value	[kPa]	0
Display range end value	[kPa]	99
Displayable unit(s)	[kPa]	Vacuum
Signal status indication,		LED
solenoid valve		

Operating and environmental conditions


Type VABF		VH-14-A	VH-14-AP	VH-20-A	VH-20-AP	VH-30-A	VH-30-AP	VL-14-A	VL-14-AP	VL-20-A	VL-20-AP
Operating medium		Compresse	d air to ISO 8	573-1:2010	[7:4:4]						
Note on operating/pilot medium		Lubricated	operation no	t possible							
Pilot pressure pS	[bar]	4 10									
	[MPa]	0.4 1									
Operating pressure pB	[bar]	48									
	[MPa]	0.4 0.8									
Nominal operating pressure	[bar]	6									
Bnom	[MPa]	0.6									
Operating pressure for max.	[bar]	4		4		6		4		5	
suction rate	[MPa]	0.4		0.4		0.6		0.4		0.5	
Operating pressure for max.	[bar]	4		4		6		-		-	
/acuum pumax	[MPa]	0.4		0.4		0.6		-		-	
Max. vacuum pVmax	[kPa]	92						-		-	
Max. suction rate with respect to atmosphere	[l/min]	51		99		167		91		179	
Pressurisation time at nominal operating pressure	[s]	0.2	0.3	0.2	0.3	0.2	0.25	0.2	0.25	0.2	0.25
loise level LpA (at nominal operating pressure)	[dB(A)]	70		73		75		62		61	
Ambient temperature tamb	[°C]	-5 +50								·	
emperature of medium tmed	[°C]	-5 +50									
E marking (see declaration of conformity)		To EU EMC Directive									
Certification		RCM									
Corrosion resistance class CRC ¹⁾		0									

1) More information www.festo.com/x/topic/crc

Materials

Materials	
Housing, jet nozzle, blanking plug	Wrought aluminium alloy
Adjusting screw	High-alloy stainless steel
Screws	Steel
Vacuum generator seals	NBR, HNBR
Blanking plug seals	NBR
Plate	Die-cast aluminium
Female nozzle	POM
Silencer	PU foam, POM
Note on materials	RoHS-compliant (vacuum generator and blanking plug)

Connection and display components



[1] Solenoid valve VSVA

- [2] Vacuum port G3/8
- [3] Port for silencer UOM-3/8 [VH/L-14 (1x) and VH-20 (2x)]
- [4] Manifold sub-base for valve terminal VTSA-F-CB (pneumatic and electric)
- [5] Electrical link to valve terminal VTSA-F-CB
- [6] Flow control screw for adjusting the strength of the ejector pulse
- [7] The status LED (yellow) indicates the operating status of the vacuum generator and displays warnings in the event of a process fault
- [7] The error LED (red) indicates the status of the CBUS connection and displays errors
- [8] The 7-segment display (2-digit blue LED display) shows the pressure value (vacuum) in kPa
- [9] LED switching status indication for solenoid valve
- [10] Manual override for vacuum generation
- [11] Manual override for ejector pulse

Diagnostics and monitoring

The vacuum generator has monitoring functions that enable malfunctions or faults to be detected at an early stage during operation.

The following diagnostic functions are possible:

- Monitoring tE (evacuation time), reference via teach-in
- Monitoring tB (pressurisation time), reference via teach-in
- Monitoring air consumption via vacuum drop rate VDR (process quality) when air saving function is active (tLS)

Definition of diagnostic levels Normal operation Warning Faults Definition Device is OK Outside the specification Malfunction

Operating statuses of the vacuum generator

Actuation

Actuation		-	
Solenoid coil 12	Solenoid coil 14	Function/operating status	Comment
0	0	Normal position	No actuation or status after the end of the "ejection" signal/the "pressurisation" function
		Generating vacuum	Operating status after failure of the pilot air supply or the electrical supply of the vacuum
			generator (self-latching loop)
1	0	Generating vacuum	Pulse actuation with self-latching loop
0	1	Pressurisation	Accelerated vacuum reduction
		(ejector pulse)	
1	1	Saving air	Maintain vacuum (valve mid-position)
		(air saving function)	

Datasheet – Vacuum generator for VTSA-F-CB

Electrical and pneumatic status changes

Status change	Operating status before status change	Operating status after status change
Failure/deactivation of the electronics supply	Generating vacuum	Generating vacuum
or the pilot air supply of the vacuum generator		(The valve spool remains in the "generate vacuum" position)
	Saving air	Generating vacuum
		(The mechanical spring pushes the valve spool into the "generate vacuum"
		position)
	Pressurisation	Normal position ¹⁾
	Normal position ¹⁾	Normal position ¹⁾
Emergency stop/switch-off of the load voltage	Generating vacuum	Generating vacuum
supply	Saving air	Generating vacuum
		(vacuum is maintained)
	Pressurisation	Normal position or function is interrupted ²⁾
	Normal position ¹)	Normal position ¹⁾

1) Normal position means the vacuum block is not in the "generate vacuum", "air saving" or "ejection" operating status

2) Parameter "ejector pulse interlock" must be active


- 📲 - Note

If the compressed air or power supply to the valve terminal fails, this will result in the following statuses:


- 1. Compressed air failure:
- No vacuum can be generated, even if the valve is in the "generate vacuum" position.
- No ejector pulse can be generated, even if the valve is in the "ejection" position.
- 2. Power supply failure to the valve terminal:
- If both solenoid coils are de-energised at the same time, the valve switches to permanent suction because of the pilot air volume still present and remains in this state.

Circuit symbols, vacuum generator

VABF...V2B1...A









The vacuum generator is supplied internally via duct 1 of the manifold sub-base of the valve terminal. The pilot air is supplied internally via duct 12/14 of the manifold sub-base of the valve terminal.


Pressure ratios, negative pressure pu as a function of operating pressure p₁




Pressure ratios, evacuation time t_{evac} as a function of negative pressure p_u and operating pressure 4 bar for 1 l volume

VH-1 4/20/30: t_{evac(p1)} 8 7 6 5 t_{evac} [s] 4 3 2 1 0 0 10 20 30 40 50 60 70 80 90 100 pu[KPa] VH-14 VH-20 ... VH-30









Pressure ratios, suction rate \boldsymbol{q}_{ns} as a function of negative pressure $\boldsymbol{p}_u, \boldsymbol{p}_1$ and operating pressure 6 bar

VH-1 4/20/30

------ VH-20 ----- VH-30






VL-14

2025/03 – Subject to change

Dimensions

Download CAD data → <u>www.festo.com</u>



- 🖡 - Note


Silencer UOM-3/8, seal VABD-S6-1-C and screws for manifold sub-base are included with the order for the vacuum generator.

If required, the silencer extension UOMS-3/8 can be ordered separately.

Dimensions

Vacuum generator Laval nozzle 3.0 and Laval nozzle 2.0 with high suction rate

Download CAD data → www.festo.com




- 📲 - Note

Silencer UOM-3/8, seal VABD-S6-1-C and screws for manifold sub-base are included with the order for the vacuum generator.

If required, the silencer extension UOMS-3/8 can be ordered separately.

Dimensions

Download CAD data → <u>www.festo.com</u>



- 🕴 - Note

Silencer UOM-3/8, seal VABD-S6-1-C and screws for manifold sub-base are included with the order for the vacuum generator.

If required, the silencer extension UOMS-3/8 can be ordered separately.

Ordering data Terminal Description Weight Part no. Туре [g] code Vacuum generator for VTSA-F-CB, with integrated sensor With high suction rate 915 8088779 VABF-S4-2-V2B1-G38-CB-VL-14-A Ш Laval nozzle, 1.4 mm IIPH Laval nozzle, 1.4 mm with power ejector pulse 930 8088781 VABF-S4-2-V2B1-G38-CB-VL-14-AP IV VABF-S4-2-V2B1-G38-CB-VL-20-A Laval nozzle, 2.0 mm 955 8067141 IVPH Laval nozzle, 2.0 mm with power ejector pulse 970 8067144 VABF-S4-2-V2B1-G38-CB-VL-20-AP With high vacuum 915 VABF-S4-2-V2B1-G38-CB-VH-14-A 8088778 Laval nozzle, 1.4 mm L IPH Laval nozzle, 1.4 mm with power ejector pulse 930 8088780 VABF-S4-2-V2B1-G38-CB-VH-14-AP Ш VABF-S4-2-V2B1-G38-CB-VH-20-A Laval nozzle, 2.0 mm 920 8067140 IIIPH Laval nozzle, 2.0 mm with power ejector pulse 940 8067143 VABF-S4-2-V2B1-G38-CB-VH-20-AP ٧ 955 8067142 VABF-S4-2-V2B1-G38-CB-VH-30-A Laval nozzle, 3.0 mm VPH Laval nozzle, 3.0 mm with power ejector pulse 970 8067145 VABF-S4-2-V2B1-G38-CB-VH-30-AP Silencer extension UOMS-3/8 Can be attached to enclosed silencer UOM and secured in place. 17.5 538437 Blanking plug With connecting thread G3/8 23 8068144 OASC-V1-P (The blanking plug can be used to subsequently convert an existing vacuum generator V...20 to a vacuum generator V...14, or a vacuum generator V...30 to a vacuum generator V...20.) Pneumatic connection accessories A selection of possible fittings, blanking plugs, silencers and other pneumatic accessories can be found in the chapter Accessories \rightarrow page: 242 or on the website via the individual search terms: **Internet** \rightarrow connection technology, silencer, blanking plug

Datasheet – Vacuum generator for VTSA-F-CB

Valve terminals VTSA

Datasheet - Valves on individual sub-base

- [] -	Valve width to ISO 15407-2	- 11 -	Flow rate Width 18 mm: up to 600 l/
	• 18 mm		min
	• 26 mm		Width 26 mm: up to 1200 l/
	to ISO 5599-2		min
	• 42 mm		Width 42 mm: up to 1500 l/
	• 52 mm		min
			Width 52 mm
- 4 -	Voltage 24 V DC		up to 3400 l/min
	110 V AC		
- 5 -	0		

General technical data

Design		Piston spool valve						
Sealing principle		Soft						
Actuation type		Electrical						
Type of control		Piloted						
Exhaust function, can be throttle	ed	Via individual sub-base	9					
Lubrication		Lifetime lubrication						
Type of mounting		Screwed onto sub-base						
Valve Screwed via through-hole								
 Individual sub-base 								
Mounting position		Any	Any					
Manual override		Detenting, non-detenting, concealed						
Pneumatic connections – Threa	aded conne	ection						
Width		18 mm	26 mm	42 mm	52 mm			
Pneumatic connection		Via E-box	Via E-box					
Supply port	1	G1/8	G1/4	G3/8	G1/2			
Exhaust port	3/5	G1/8	G1/4	G3/8	G1/2			
Working ports	2/4	G1/8	G1/4	G3/8	G1/2			
External pilot air supply port	14	M5	G1/8	G1/8	G1/8			
Encennar phot an supply port				G1/8	G1/8			

Operating and environmental conditions, individual sub-base

Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Notes on operating/pilot mediun	ı	Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure	[bar]	-0.9 +10			
	[MPa]	-0.09+1			
Ambient temperature	[°C]	-5 +50			
Certification		c UL us - Recognized (OL)			
CE marking		To EU Low Voltage Directive (only for 110 V AC coils, not for variants with round plug M12)			
(see declaration of conformity)		To EU Explosion Protection Directive (ATEX, EX1E ¹⁾) (for variants with round plug M12 only)			
		To EU RoHS Directive			
UKCA marking		To UK EMC regulations			
(see declaration of conformity)		To UK explosion regulations			
		To UK RoHS regulations			
ATEX category for gas		II 3G (EX1E ¹)			
Type of (ignition) protection for g	as	Ex ec IIC T3 Gc X (EX1E ¹⁾)			
Explosion-proof ambient temper- [°C]		–5 +50 (EX1E ¹⁾)			
ature					
Explosion protection certification	I	EPL Gc (GB)			
outside the EU					

1) EX1E certification for installation in a housing

2) For information about the area of use, see the declaration of conformity at: www.festo.com/catalogue/... -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Standard nominal flow rate of valve/individual sub-base [l/min]

Valve function (with valve code)	Width 18 mm		Width 26 mm	
	Valve	Valve on individual sub-base	Valve	Valve on individual sub-base
5/2-way double solenoid (B52)	750	600	1400	1200
5/2-way double solenoid with dominant signal (D52)	750	600	1400	1200
5/2-way single solenoid, pneumatic spring (M52A)	750	600	1400	1200
5/2-way single solenoid, mechanical spring (M52M)	750	600	1400	1200
5/3-way closed (P53C)	700	550	1400 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾
5/3-way exhausted (P53E)	700 ¹⁾ 330 ²⁾	500 ¹⁾ 330 ²⁾	1400 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾
5/3-way pressurised (P53U)	700 ¹⁾ 330 ²⁾	500 ¹⁾ 330 ²⁾	1400 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾
5/3-way, exhausted, switching position 14 detenting (P53ED) ³⁾	-	390 ¹⁾ 310 ²⁾	1400 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾
5/3-way, exhausted, switching position 12 detenting (P53EP) ³⁾	-	390 ¹⁾ 320 ²⁾	1400 ¹⁾ 700 ²⁾	1200 ¹⁾ 700 ²⁾
5/3-way, port 2 pressurised, 4 exhausted, switching position 14 detenting (P53AD) ³⁾	-	380 ¹⁾ 360 ²⁾	700 ¹⁾ 700 ²⁾	700 ¹⁾ 700 ²⁾
5/3-way, port 4 pressurised, 2 exhausted, switching position 14 detenting (P53BD) ³⁾	-	400	-	900 ¹⁾ 840 ²⁾
2x3/2-way single solenoid, closed (T32C)	600	500	1250	1100
2x3/2-way single solenoid, open (T32U)	600	500	1250	1100
2x3/2-way single solenoid, open/closed (T32H)	600	500	1250	1100
2x3/2-way single solenoid, closed (T32N)	600	500	1250	1100
2x3/2-way single solenoid, open (T32F)	600	500	1250	1100
2x3/2-way single solenoid, open/closed (T32W)	600	500	1250	1100
2x2/2-way single solenoid, closed (T22C)	700	500	1350	1100
2x2/2-way single solenoid, closed (T22CV)	700	500	1350	1100

1) Switching position

2) Mid-position

3) The valve functions P53AD, P53BD, P53ED, P53EP are only available in the 24 V DC version. Values only apply to 24 V DC.

Standard nominal flow rate of valve/individual sub-base [l/min]

Valve function (with valve code)	Width 42 mm		Width 52 mm	
	Valve	Valve on individual sub-base	Valve	Valve on individual sub-base
5/2-way double solenoid (B52)	2000	1500	4000	3400
5/2-way double solenoid with dominant signal (D52)	2000	1500	4000	3400
5/2-way single solenoid, pneumatic spring (M52A)	2000	1500	4000	3400
5/2-way single solenoid, mechanical spring (M52M)	2000	1500	4000	3400
5/3-way closed (P53C)	1900 ¹⁾ 950 ²⁾	1400 ¹⁾ 800 ²⁾	3600 ¹⁾ 1700 ²⁾	3200 ¹⁾ 1700 ²⁾
5/3-way exhausted (P53E)	1900 ¹⁾ 950 ²⁾	1400 ¹⁾ 800 ²⁾	3600 ¹⁾ 1700 ²⁾	3200 ¹⁾ 1700 ²⁾
5/3-way pressurised (P53U)	1900 ¹⁾ 950 ²⁾	1400 ¹⁾ 800 ²⁾	3600 ¹⁾ 1700 ²⁾	3200 ¹⁾ 1700 ²⁾
5/3-way, 1 to 2 pressurised, 4 to 5 closed (P53F) ³⁾	1700 ¹⁾ 700 ²⁾	1400 ¹⁾ 700 ²⁾	3000 ¹⁾ 900 ²⁾	2600 ¹⁾ 900 ²⁾
2x3/2-way single solenoid, closed (T32C)	1600	1200	3000	2600
2x3/2-way single solenoid, open (T32U)	1600	1200	3000	2600
2x3/2-way single solenoid, open/closed (T32H)	1600	1200	3000	2600
2x3/2-way single solenoid, closed (T32N)	1600	1200	3000	2600
2x3/2-way single solenoid, open (T32F)	1600	1200	3000	2600
2x3/2-way single solenoid, open/closed (T32W)	1600	1200	3000	2600
2x2/2-way single solenoid, closed (T22C)	1600	1400	4000	3400
2x2/2-way single solenoid, closed (T22CV)	1600	1400	-	-

1) Switching position

2) Mid-position

3) The valve function P53F is only available in the 24 V DC version. Values only apply to 24 V DC.

Electrical data, individual sub-base

Electrical data, individual sub-	base	
Current rating at 40°C	[A]	2 (1 A per coil)
Protection rating to EN 60529		IP65, NEMA 4 (for all types of signal transmission when mounted)
Variants with round plug M12		
Operating voltage range	[V DC]	24 ±10% (for variants with round plug M12 VABSR3)
Surge resistance	[kV]	0.8
Pollution degree		3
Duty cycle	ED	100%
Variants with cable connector		
Operating voltage range	[V DC]	24 ±10% (for variants with cable terminal VABSK1/C1,K2)
	[V AC]	110 ±10% (50 60Hz) (for variants with cable and spring-loaded terminal VABSK1/C1,K2)
Surge resistance	[kV]	4
Pollution degree		3
Duty cycle	[ED]	100%


- 🌡 - Note


A cable connector is needed to ensure the IP degree of protection and to protect against tensile load, twisting and bending.

Materials				
Width	18 mm	26 mm	42 mm	52 mm
Connecting plate	Die-cast aluminium			Gravity die-cast aluminium
Valve	Die-cast aluminium, PA			
Seals	FPM, NBR			
Note on materials	RoHS-compliant			
Dro duct unight [2]				
Product weight [g] Width	18 mm	26 mm	42 mm	52 mm
Valves				
5/2-way solenoid valve, double solenoid (B52, D52)	172	276	439	732
5/2-way valve, single solenoid (M52A, M52M)	163	293	426	702
5/3-way solenoid valve (P53C, P53E, P53U)	191	320	456	780
5/3-way solenoid valve (P53BD)	172	301	-	-
5/3-way solenoid valve (P53ED, P53EP)	170	291	-	-
5/3-way solenoid valve (P53AD)	172	301	-	-
5/3-way solenoid valve (P53F)	-	-	456	780
2x 3/2-way solenoid valve (T32C, T32U, T32H, T32N, T32F, T32W)	190	335	442	740
2x 2/2-way solenoid valve (T22C, T22CV)	190	335	442	740
Individual connection				
Individual sub-base	192	302	386	815

Dimensions

Download CAD data → <u>www.festo.com</u>





[1] Plug to

EN 61076-2-101

Туре	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5ø	H1	H2	H3	H4	H5	H6	H7
VABS-S4-2S-G18-R3 ¹⁾ VABS-S4-2S-G18-B-R3 ²⁾	32.4	30	18	13	6	G1/8	M5	M5 -	M12x1	5.5	31	53.4	14.5	13	13.7	8.8	4
Туре	L1		L2		L3		L4	L5		L6	L7	,	L8		L9	L:	10
VABS-S4-2S-G18-R3 ¹⁾ VABS-S4-2S-G18-B-R3 ²⁾	133.	5	124.5		38.6	2	2.2	32.	4	33.2	16.	6	25.3		16.2	4	.5


1) External pilot air supply

2) Internal pilot air supply

• || • Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions

Download CAD data → <u>www.festo.com</u>



Туре	B1	B2	B3	B5	D1	D2	D3	D4	D5 Ø	H1	H2	H3	H4	H5	H6	H7
VABS-S4-2S-G18-K2 ¹⁾ VABS-S4-2S-G18-B-K2 ²⁾	32.4	30	18	6	G1/8	M5	M5 -	M20x1.5	5.5	31	53.4	14.5	13	13.7	8.8	4
Туре	L1		L2		L3	L4		L5	L6		L7	L8		L9	L1	10
VABS-S4-2S-G18-K2 ¹⁾ VABS-S4-2S-G18-B-K2 ²⁾	133.	5	124.5	3	38.6	22.2		32.4	33.2	1	6.6	25.3		16.2	4	.5


1) External pilot air supply

2) Internal pilot air supply

• I • Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions

Download CAD data → <u>www.festo.com</u>



VABS-S4-1S-G14-B-R3 2)	43	26	13	8.5	G1/4	G1/8	- M12X1	5.5	36.5	53.5	26.5	13	13	12.5	4
Туре	L1		L2	1	.3	L4	L5	L6		L7	L8		L9	L1	10
VABS-S4-1S-G14-R3 ¹⁾ VABS-S4-1S-G14-B-R3 ²⁾	150.6		141.5	53	3.6	23.2	41.4	37.9		24.2	29.3		20.7	4.	.5


1) External pilot air supply

2) Internal pilot air supply

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions

Download CAD data → <u>www.festo.com</u>



туре	DI	00	UJ	DI	DZ	05	04	050	111	112		114	U	110	117
VABS-S4-1S-G14-K2 ¹⁾	43	26	8.5	G1/4	G1/8	G1/8	M20x1.5	5.5	36.5	53.5	26.5	13	13	12.5	4
VABS-S4-1S-G14-B-K2 2)				,		-									
Туре	L1		L2	L3		L4	L5	L6		L7	L8		L9	L1	10
VABS-S4-1S-G14-K2 ¹⁾ VABS-S4-1S-G14-B-K2 ²⁾	150.6		141.5	53.	6	23.2	41.4	37.9	9	24.2	29.3		20.7	4.	.5


1) External pilot air supply

2) Internal pilot air supply

 $\cdot \ | \cdot$ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions

Download CAD data → <u>www.festo.com</u>



1) External pilot air supply

2) Internal pilot air supply

♦ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Download CAD data → <u>www.festo.com</u>

H2


 \bigcirc


(0

Datasheet - Valves on individual sub-base

Dimensions

Individual sub-base with spring-loaded terminal or for assembly by the user, width 42 mm





Туре	B1	B3	B5	B6	D1	D2	D3	D4	D5ø	H1	H2	H3	H4	H5	H6	H7	H8
VABS-S2-1S-G38-K1 ¹⁾ VABS-S2-1S-G38-C1 ¹⁾ VABS-S2-1S-G38-B-K1 ²⁾ VABS-S2-1S-G38-B-C1 ²⁾	50	42	4	2.2	G3/8	G1/8	G1/8	M20x1.5	5.5	42.5	55.3	29	13.6	17.1	16.3	4	47.5
Туре	- L	1	L	2	L3		L4	L5		L6	L7		L8		L9	L	.10
VABS-S2-1S-G38-K1 ¹⁾ VABS-S2-1S-G38-C1 ¹⁾ VABS-S2-1S-G38-B-K1 ²⁾ VABS-S2-1S-G38-B-C1 ²⁾	15	0.6	14	1.5	53.0	6	23.2	44		37	26		28		22	2	4.5

1) External pilot air supply

2) Internal pilot air supply

 $\cdot \ | \cdot$ Note: This product conforms to ISO 1179-1 and ISO 228-1.

- 🖡 - Note


Electrical connection

• VABS-...-K1: open end

• VABS-...-C1: spring-loaded terminal

Dimensions

Download CAD data → <u>www.festo.com</u>



[1] Plug to

EN 61076-2-101

Туре	B1	B3	B4	B5	B6	D1	D2	D3	D4	D5 Ø	H1	H2	H3	H4	H5	H6	H7	H8
VABS-S2-2S-G12-R3 ¹⁾ VABS-S2-2S-G12-B-R3 ²⁾	67	52	13	7.5	2.2	G1/2	G1/8	G1/8 -	M12x1	6.5	60	60	43.5	17	26.5	23.5	10	65
Туре	,	L1		L2		L3	1	.4	L5	L6		L7		L8		L9	L:	10
VABS-S2-2S-G12-R3 1)	1	85		172		17.5	1-	7.5	55.4	99.	-	33		88.3		27.7	6	

1) External pilot air supply


2) Internal pilot air supply
 ↓ Note: This product conforms to ISO 1179-1 and ISO 228-1.


Download CAD data → <u>www.festo.com</u>


Datasheet - Valves on individual sub-base

Dimensions

Individual sub-base with spring-loaded terminal or for assembly by the user, width 52 mm







Туре	B1	B3	B5	B6	D1	D2	D3	D4	D5 Ø	H1	H2	H3	H4	H5	H6	H7	H8
VABS-S2-2S-G12-K1 ¹) VABS-S2-2S-G12-C1 ¹) VABS-S2-2S-G12-B-K1 ²) VABS-S2-2S-G12-B-C1 ²)	67	52	7.5	2.2	G1/2	G1/8	G1/8 -	M20x1.5	6.5	60	60	43.5	17	26.5	23.5	10	65
Туре	L	.1	L	2	L3		L4	L5		L6	L7		L8		L9	L:	10
VABS-S2-2S-G12-K1 ¹⁾ VABS-S2-2S-G12-C1 ¹⁾ VABS-S2-2S-G12-B-K1 ²⁾ VABS-S2-2S-G12-B-C1 ²⁾	- 1	85	17	2	17.	5	17.5	55.4	2	99.5	33		88.3		27.7	6	.5

1) External pilot air supply

2) Internal pilot air supply

• || • Note: This product conforms to ISO 1179-1 and ISO 228-1.

- 📲 - Note

- Electrical connection
- VABS-...-K1: open end
- VABS-...-C1: spring-loaded terminal

Accessories – Individual connection

	Description			Width	Part no.	Туре
ividual cub baco, o	lectrical connection with plug M12 (without CE ma	rking)		matin	- diff indi	.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,
	Threaded connection, internal pilot air supply	Connections G1/8	_	18 mm	541070	VABS-S4-2S-G18-B-R3
			Explosion group of		8033156	VABS-S4-2S-G18-B-R3-EX1E
10000			assembly IIC		0000100	
		Connections G1/4	-	26 mm	541069	VABS-S4-1S-G14-B-R3
			Explosion group of	-	8033158	VABS-S4-1S-G14-B-R3-EX1E
			assembly IIC			
		Connections G3/8	-	42 mm	546104	VABS-S2-1S-G38-B-R3
			Explosion group of		8033160	VABS-S2-1S-G38-B-R3-EX1E
			assembly IIC			
		Connections G1/2	-	52 mm	555645	VABS-S2-2S-G12-B-R3
			Explosion group of		8033162	VABS-S2-2S-G12-B-R3-EX1E
		C	assembly IIC	40		
	Threaded connection, external pilot air supply	Connections G1/8	-	18 mm	541064	VABS-S4-2S-G18-R3
			Explosion group of assembly IIC		8033155	VABS-S4-2S-G18-R3-EX1E
		Connections G1/4	-	26 mm	541063	VABS-S4-1S-G14-R3
			Explosion group of assembly IIC		8033157	VABS-S4-1S-G14-R3-EX1E
		Connections G3/8	-	42 mm	546101	VABS-S2-1S-G38-R3
			Explosion group of assembly IIC		8033159	VABS-S2-1S-G38-R3-EX1E
		Connections G1/2	-	52 mm	555640	VABS-S2-2S-G12-R3
			Explosion group of assembly IIC		8033161	VABS-S2-2S-G12-R3-EX1E
dividual cub baca a	lastrical connection via coble terminals			1		
idividual sub-base, e	lectrical connection via cable terminals Threaded connection, internal pilot air supply	Connections G1/8		18 mm	541067	VABS-S4-2S-G18-B-K2
		Connections G1/8		26 mm	541067	VABS-54-25-018-B-K2
	Threaded connection, external pilot air supply	Connections G1/4		18 mm	539723	VABS-S4-13-G14-B-K2
		Connections G1/4		26 mm	539725	VABS-54-25-616-K2
ndividual sub-base, e	lectrical connection via spring-loaded terminal					
	Threaded connection, internal pilot air supply	Connections G3/8		42 mm	546762	VABS-S2-1S-G38-B-C1
A CONTRACTOR		Connections G1/2	1	52 mm	555643	VABS-S2-2S-G12-B-C1
	Threaded connection, external pilot air supply	Connections G3/8	1	42 mm	546760	VABS-S2-1S-G38-C1
		Connections G1/2		52 mm	555638	VABS-S2-2S-G12-C1
ıdividual sub-base, e	lectrical connection via cable (open end)					
	Threaded connection, internal pilot air supply	Connections G3/8		42 mm	546102	VABS-S2-1S-G38-B-K1
A CONTRACTOR		Connections G1/2		52 mm	555641	VABS-S2-2S-G12-B-K1
	Threaded connection, external pilot air supply	Connections G3/8		42 mm	546099	VABS-S2-1S-G38-K1
		Connections G1/2		52 mm	555636	VABS-S2-2S-G12-K1

Accessories – Individual connection

	Description		Part no.	Туре
Plug socket for the	electrical connection of individual valves			
	Angled socket, M12x1, 4-pin, type A, screw terminal		8162292	NECB-M12W4-C2
Connecting cable f	or electrical connection of individual valves, 6-way or 10-way			
	 Straight socket, M12x1, 5-pin Open end, 4-core 	5 m	8078240	NEBA-M12G5-U-5-N-LE4
DETWE				
	 Angled socket, M12x1, 5-pin, Open end, 4-core 	5 m	8078249	NEBA-M12W5-U-5-N-LE4
neumatic connec	tion accessories			
other pneumatic a	sible fittings, blanking plugs, silencers and ccessories can be found in the chapter Accessories → page: 242 <i>v</i> ia the individual search terms:			
nternet → conne	ction technology, silencer, blanking plug			

Valve terminals VTSA

Accessories

ī

Ordering data							
	Code	Description	n			Part no.	Туре
Multi-pin plug distribu	utor						
	-	15-pin Sub	b-D socket/8x 3-pin M8 plugs	8 inputs/outputs	177669	MPV-E/A08-M8	
b D. Galacia	-	15-pin Sub	b-D socket/12x 3-pin M8 plugs	12 inputs/outputs	177670	MPV-E/A12-M8	
Push-in fitting with co	nnecting th	read					
	<u> </u> _	G1/8 for	Tubing O.D. 6 mm	Plastic releasir	ng ring	186096	QS-G1/8-6
	E	1			Metal releasing ring		NPQM-D-G18-Q6-P10
	-	1	Tubing O.D. 8 mm		Plastic releasing ring		QS-G1/8-8
	E	-			Metal releasing ring		NPQM-D-G18-Q8-P10
	_	1	Tubing O.D. 10 mm	Plastic releasing ring		558663 190643	QS-G1/8-10
	_	G1/4 for	Tubing O.D. 8 mm		tic releasing ring 186		QS-G1/4-8
	E	-			Metal releasing ring		NPQM-D-G14-Q8-P10
	-	-	Tubing O.D. 10 mm	Plastic releasir		558665 186101	QS-G1/4-10
	E	_			Metal releasing ring		NPQM-D-G14-Q10-P10
	_		Tubing O.D. 12 mm	Plastic releasing	<u> </u>	558666 186350	QS-G1/4-12
	E	-			Metal releasing ring		NPQM-D-G14-Q12-P10
	_	G3/8 for	Tubing O.D. 10 mm	Plastic releasing		558667 186102	QS-G3/8-10
	E			Metal releasing	<u> </u>	558669	NPQM-D-G38-Q10-P10
	-	-	Tubing O.D. 12 mm	Plastic releasing		186114	QS-G3/8-12-I
	E	-			Metal releasing ring		NPQM-D-G38-Q12-P10
		G1/2 for	Tubing O.D. 12 mm		astic releasing ring		QS-G1/2-12
	E				Metal releasing ring		NPQM-D-G12-Q12-P10
		-	Tubing O.D. 14 mm		Metal releasing ring		
	E	-	Tubing O.D. 14 mm	Plastic releasing ring		570451	NPQM-D-G12-Q14-P10
			Tubing O.D. 16 mm			186105	QS-G1/2-16
Barbed hose fitting/pu	ush-in fitting	g					
AND -	-	For right er	end plate		G3/4	8040613	QS-G3/4-22
						572260	N-1-P-19
OM/	-	For adapter plate			R1	572260	N-1-P-19

- 闄 - Note

Metal push-in fittings type NPQM-... should be selected when the highest protection is required for electrical and electronic components (anti-static requirements).

Accessories

	Code	Description		Part no.	Туре
ilencer					
	U	Standard design, connecting thread	G1/8	2307	U-1/8
			G1/4	2316	U-1/4
			G3/8	6843	U-3/8-B
			G1/2	6844	U-1/2-B
			G3/4	6845	U-3/4-B
			G1	151990	U-1-B
	A	Sintered design, connecting thread	G1/8	1205860	AMTE-M-LH-G18
			G1/4	1205861	AMTE-M-LH-G14
			G3/8	1205862	AMTE-M-LH-G38
			G1/2	1205863	AMTE-M-LH-G12
			G3/4	1205864	AMTE-M-LH-G34
			G1	1205865	AMTE-M-LH-G1
Blanking plug					
	-	Connecting thread	M5	3843	B-M5
			G1/8	3568	B-1/8
			G1/4	3569	B-1/4
			G1/2	3571	B-1/2
			G3/4	3572	B-3/4
			G1	5763	B-1
					·
ther pneumatic					
	ssible fittings, t ia the individua	blanking plugs and silencers can be found			