

Mini slides DGSL-N, NPT

FESTO



Mini slides DGSL-N, NPT


Key features

FESTO

General information

- Double-acting drives
- Wide range of options for mounting on:
 - Drives, grippers
- System product for handling and assembly technology
- Highly flexible thanks to wide range of assembly and connection options on:
 - Drive body, slide, yoke plate

The technology in detail



1 Cushioning



- Choice of four cushioning types:
 - Elastic cushioning without metal end position (P)
 - Elastic cushioning without metal end position, short design (E)
 - Elastic cushioning with metal end position (P1)
 - Hydraulic shock absorbers (Y3)

2 Cover



- The cover stops foreign parts or dirt getting into the guide
- The cover comes in different lengths and can be trimmed as required by the customer

3 Coarse stroke adjustment



- The end stop for the advanced end position can be adjusted mechanically, for example to shorten the stroke

4 Clamping unit




- Mechanical clamping, for fixing the slide in any position; frictional locking (C)

4 End-position locking



- Mechanical locking when the end position is reached, for fixing the slide in the unpressurised, retracted state; positive locking (E3)

5 Innovative guide unit




- Wide roller track, which provides extremely high rigidity
- High load capacity
- High precision
- Housing and steel slide form a guide: there are no accumulative tolerances

6 Position sensing



- Proximity sensors can be integrated, so there are no projecting parts
- Two slots for mounting
- Clearly visible from the side and from above

7 Supply ports




- Choice of two sides:
 - On front face
 - At the side

Mini slides DGSL-N, NPT

System example

FESTO

System product for handling and assembly technology




System components and accessories		
	Brief description	→ Page/Internet
1 Drives	Wide range of combinations possible within handling and assembly technology	drive
2 Grippers	Wide range of variations possible within handling and assembly technology	gripper
3 Adapters	For drive/drive and drive/gripper connections	adapter kit
4 Basic components	Profiles and profile connections as well as profile/drive connections	basic component
5 Installation components	For a clear, safe layout of electrical cables and tubing	installation component
– Axes	Wide range of combinations possible within handling and assembly technology	axis
– Motors	Servo and stepper motors, with or without gearing	motor

Mini slides DGSL-N, NPT

Peripherals overview

FESTO



 Note
End stops must not be removed.

Accessories		
	Brief description	→ Page/Internet
1	Proximity sensor SME/SMT-10	For position sensing. Can be integrated in sensor slot, so there are no projecting parts
2	Centring sleeve ZBH	For centring loads and attachments (centring sleeves are included in the scope of delivery of the mini slide)
3	One-way flow control valve GRLA	For regulating speed
4	Push-in fitting QB	For connecting compressed air tubing with standard O.D.
5	Cushioning with shock absorber Y3	For large loads and high speed. Ensures precise, metal-to-metal contact after the cushioning
6	Reducing sleeve DAYH	For installing a smaller shock absorber. For applications where the cushioning energy lies between the cushioning Y3 and P1
7	Shock absorber DYSW	→ 12 (shock absorber selection)
8	Cushioning with stop P1	Precision metal stop for small loads at low speed
9	Cushioning P	• Flexible stop for medium loads at medium speed • (standard design)
10	Cushioning E	• Flexible stop for medium loads at medium speed • (short design)
11	Cover DADS	• For protection, to stop foreign parts or dirt getting into the guide • The cover can be trimmed as required by the customer

Mini slides DGSL-N, NPT

Type codes

FESTO


		DGSL	–	N	–	10	–	100	–		E3	–	Y3	A
Type														
Double-acting														
DGSL	Mini slide													
System of units														
N	Imperial													
Size														
Stroke [mm]														
Clamping unit														
C	Integrated													
End-position locking														
E3	With piston rod in retracted position													
Cushioning														
P	Elastic cushioning without metal end position, both ends													
P1	Elastic cushioning with metal end position, both ends													
Y3	Progressive shock absorber, both ends													
E	Elastic cushioning without metal end position, both ends, short design													
Position sensing														
A	Via proximity sensor													

Mini slides DGSL-N, NPT

Technical data

FESTO

Function



Wearing parts kits

→ 40

- Ø - Size
10 ... 25

- I - Stroke length
10 ... 200 mm



General technical data						
Size		10	12	16	20	25
Pneumatic connection		M5, suitable for 10-32 UNF			1/8 NPT	
Design		Scotch yoke system				
Guide		Ball bearing cage guide				
Type of mounting		Via through-hole				
		Via female thread				
Cushioning	P	Flexible cushioning without metal end position, both ends				
	E	Flexible cushioning without metal end position, both ends, short design				
	P1	Flexible cushioning with metal end position, both ends, adjustable				
	Y3	With progressive shock absorber, both ends				
Position sensing		Via proximity sensor				
Mounting position		Any				
Max. advancing speed		[m/s]	0.8			
Max. retracting speed		[m/s]	0.8			
Repetition accuracy	P1/Y3	[mm]	±0.01			
	P	[mm]	0.3			

Operating and environmental conditions						
Size		10	12	16	20	25
Operating medium		Dried compressed air, lubricated or unlubricated				
Min. operating pressure	[bar]	1.5	1			
Max. operating pressure	[bar]	8				
Ambient temperature ¹⁾	[°C]	0 ... +60				

1) Note operating range of proximity sensors.

Piston Ø, forces and impact energy								
Size			10	12	16	20	25	
Piston Ø			[mm]	12	16	20	25	32
Theoretical force at 6 bar, advancing			[N]	68	121	188	295	483
Theoretical force at 6 bar, retracting			[N]	51	104	158	247	415
Impact energy in the end positions	P, E	[Nm]	0.12	0.25	0.35	0.45	0.55	
	P1	[Nm]	0.04	0.06	0.12	0.2	0.25	
	Y3	[Nm]	1.3	2.5	4	8	12	
	1)	[Nm]	0.8	1.3	2.5	4	8	

1) With reducing sleeve and next smallest shock absorber.

Mini slides DGSL-N, NPT

Technical data


FESTO

Weight [g]						
Size	Stroke	10	12	16	20	25
Product weight without cushioning component						
	10	396	604	896	1,535	2,520
	20	434	660	954	1,649	2,670
	30	470	711	1,008	1,746	2,824
	40	507	762	1,072	1,857	2,983
	50	548	813	1,143	1,991	3,137
	80	727	1,112	1,365	2,295	4,019
	100	813	1,229	1,712	2,921	4,519
	150	–	1,499	2,034	3,620	5,344
	200	–	–	–	4,248	6,139
Moving load without cushioning component						
	10	163	256	403	660	998
	20	180	279	432	710	1,052
	30	194	299	459	750	1,115
	40	208	320	486	801	1,181
	50	226	340	519	858	1,244
	80	299	456	618	998	1,567
	100	334	507	776	1,254	1,761
	150	–	614	910	1,566	2,102
	200	–	–	–	1,807	2,432
Cushioning component						
	P	14	23	45.6	82.4	106
	E	9	12	15	31	40
	P1	12	19.7	39.6	77.3	104
	Y3	11	21	42	67	91
	1)	18	33	52	91	131

1) With reducing sleeve and next smallest shock absorber.

Materials

Sectional view



Mini slide	
1 End cap	Anodised aluminium
2 Housing	Anodised aluminium
3 Piston rod	High-alloy steel
4 Yoke plate	Anodised aluminium
– Guide	Tempered steel
– Seals	Thermoplastic rubber, hydrogenated nitrile rubber, nitrile rubber
Note on materials	Free of copper and PTFE



Mini slides DGSL-N, NPT

Technical data

FESTO


Possible combinations without adapter plate

Pick & place




- 3 Centring sleeve ZBH
- 4 Connector sleeve ZBV

Piggy-back assembly



- 3 Centring sleeve ZBH
- 4 Connector sleeve ZBV

Mounting example with connector sleeve ZBV



	1 Basic drive					
	Size	10	12	16	20	25
2 Assembly drive	10	2x M4x14 2x ZBH-7 ¹⁾	ZBV-M5-7 ²⁾	ZBV-M5-7 ²⁾	–	–
	12	–	2x M5x14 2x ZBH-7 ¹⁾	2x M5x16 2x ZBH-7 ¹⁾	ZBV-M6-9 ²⁾	ZBV-M6-9 ²⁾
	16	–	–	2x M5x18 2x ZBH-7 ¹⁾	ZBV-M6-9 ²⁾	ZBV-M6-9 ²⁾
	20	–	–	–	2x M6x20 2x ZBH-9 ¹⁾	2x M6x20 2x ZBH-9 ¹⁾
	25	–	–	–	–	2x M6x30 2x ZBH-9 ¹⁾

1) Centring sleeves ZBH are included in the scope of delivery of the mini slide DGSL

2) Connector sleeves ZBV → 41


Mini slides DGSL-N, NPT

Technical data

FESTO

Parallelism [mm]


The term parallelism refers to the accuracy of alignment between the mounting surface and the slide surface.




Size	Stroke [mm]	10	12	16	20	25
Parallelism X	10	0.02	0.02	0.02	0.02	0.02
	20	0.02	0.025	0.025	0.025	0.025
	30	0.025	0.025	0.025	0.03	0.03
	40	0.025	0.03	0.03	0.035	0.035
	50	0.03	0.035	0.035	0.04	0.04
	80	0.035	0.04	0.04	0.045	0.045
	100	0.045	0.05	0.05	0.055	0.055
	150	–	0.075	0.075	0.08	0.08
	200	–	–	–	0.08	0.08

Linearity [mm]

The term linearity refers to the accuracy of alignment between the mounting surface and the slide surface as a function of the stroke.



Linear travel accuracy y as a function of stroke length l



Mini slides DGSL-N, NPT

Technical data

FESTO

Adjustable end-position range

Coarse adjustment of the advanced end position

The mini slide DGSL allows the front fixed stop to be adjusted by removing the cover.

This permits stroke reduction down to the next but one smaller standard stroke through a combination of coarse and precision adjustments.


Advantages:

- Can be flexibly adapted to the application
- Integrated, which means fewer conversion overheads
- Large setting range



Note

Removal of the fixed stops can result in the destruction of the mini slide DGSL.



Size Stroke [mm]	10		12		16		20		25	
	L6	L7	L6	L7	L6	L7	L6	L7	L6	L7
10	–	–	–	–	–	–	–	–	–	–
20	–	–	–	–	–	–	–	–	–	–
30	–	–	–	–	–	–	–	–	–	–
40	–	–	–	–	–	–	–	–	–	–
50	–	–	–	–	–	–	–	–	–	–
80	24	–	29	–	35	–	–	–	55	–
100	24	24	29	–	35	–	44	–	55	–
150	–	–	29	29	35	–	44	–	55	–
200	–	–	–	–	–	–	44	44	55	–

Example:

DGSL-N-12-150-...

Max. stroke = 150 mm

By adjusting the fixed stop

by the dimension **L6**:

Stroke = $150 - 29 = 121$ mm

By adjusting the fixed stop

by the dimension **L6** and **L7**:

Stroke = $150 - 29 - 29 = 92$ mm

The stroke can additionally be reduced by means of precision adjustment:

Stroke = $150 - 29 - 29 - 29 = 63$ mm

Precision adjustment
of the advanced and retracted end
position → 11

Mini slides DGSL-N, NPT

Technical data

FESTO

Adjustable end-position range

Precision adjustment of the advanced and retracted end position

Precision adjustment of the required stroke reduction is possible using the cushioning components (on the slide and in the end cap).

Advantages:

- Precision adjustment is precisely fixed by the clamping component
- No readjustment required, position is fully retained under load
- Quick and easy adjustment, only one tool required

Step 1:

Loosen the clamping component.

Step 2:

Position the slide by hand in the desired end position.


Step 3:

Turn the stop element using an Allen key until the end position is reached.


Step 4:

Tighten the clamping component.

Step 1



Step 2 ... 4




Adjustable end-position range [mm] per end position/stroke reduction						
Size		10	12	16	20	25
Advanced end position						
With cushioning	P	-27.5	-29	-37.5	-50.5	-55
	E	-13	-9	-3.5	-6.5	-11.5
	P1	-27.5	-29	-37.5	-50.5	-55
	Y3	-24	-29	-36.5	-44	-56
	1)	-24	-29	-36.5	-44	-56
Retracted end position						
With cushioning	P	-20	-25.5	-39.5	-49.5	-49
	E	-5.5	-5.5	-5.5	-5.5	-5.5
	P1	-20	-25.5	-39.5	-49.5	-49
	Y3	-15	-25.5	-38.5	-42	-51.5
	1)	-15	-25.5	-38.5	-42	-51.5

1) With reducing sleeve and next smallest shock absorber.

Note

The distance L of the cushioning component (→ operating instructions) must not be fallen below (factory setting).



Note

The setting range of the advanced and retracted end position is restricted when using the cushioning type "E".

Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Effective load m as a function of impact velocity v

The mini slide DGSL allows the shock absorber to be replaced and, in this way, the cushioning behaviour to be influenced (depending on the effective load).

This is done by removing the existing shock absorbers on the DGSL and replacing them with a smaller shock absorber as appropriate to the application (→ description below).

Graphs



for selecting a suitable shock absorber as a function of the mounting position of the mini slide → from 13.

Ordering data

Shock absorbers DYSW, DYEF and reducing sleeve DAYH → 41.



With smaller loads:

The next smallest shock absorber DYSW can be installed with the help of the reducing sleeve DAYH.



With very small loads:

The shock absorber DYEF can be installed in this case.



Selection example:

Existing drive:


Mini slide: DGSL-N-10-...-Y3-A

Given:

Effective load: 500 g

Impact velocity: 0.4 m/s

Mounting position: Horizontal



- DYSW-5-8 (cushioning Y3)
- DYSW-4-6 with DAYH-4
- DYEF-M8-Y1F

Result:

All cushioning curves above the point of intersection are suitable for this application.

The cushioning behaviour can be improved in this case by replacing the

shock absorber DYSW-5-8 installed in the mini slide with the reducing sleeve DAYH-4 and the next smallest shock absorber DYSW-4-6.

Mini slides DGSL-N, NPT


Technical data

FESTO

Shock absorber selection


Effective load m as a function of impact velocity v – horizontal mounting position

DGSL-N-10




- DYSW-5-8 (cushioning Y3)
- · - · - DYSW-4-6 with DAYH-4
- DYE-F-M8-Y1F

DGSL-N-12




- DYSW-7-10 (cushioning Y3)
- · - · - DYSW-5-8 with DAYH-5
- DYE-F-M10-Y1F

DGSL-N-16




- DYSW-8-14 (cushioning Y3)
- · - · - DYSW-7-10 with DAYH-7
- DYE-F-M12-Y1F

DGSL-N-20



- DYSW-10-17 (cushioning Y3)
- · - · - DYSW-8-14 with DAYH-8
- DYE-F-M14-Y1F

DGSL-N-25



- DYSW-12-20 (cushioning Y3)
- · - · - DYSW-10-17 with DAYH-10
- DYE-F-M16-Y1F

Mini slides DGSL-N, NPT


Technical data

FESTO

Shock absorber selection


Effective load m as a function of impact velocity v – vertical mounting position, effective load moving upwards

DGSL-N-10




- DYSW-5-8 (cushioning Y3)
- .-.-.- DYSW-4-6 with DAYH-4
- DYEF-M8-Y1F

DGSL-N-12




- DYSW-7-10 (cushioning Y3)
- .-.-.- DYSW-5-8 with DAYH-5
- DYEF-M10-Y1F

DGSL-N-16




- DYSW-8-14 (cushioning Y3)
- .-.-.- DYSW-7-10 with DAYH-7
- DYEF-M12-Y1F

DGSL-N-20



- DYSW-10-17 (cushioning Y3)
- .-.-.- DYSW-8-14 with DAYH-8
- DYEF-M14-Y1F

DGSL-N-25



- DYSW-12-20 (cushioning Y3)
- .-.-.- DYSW-10-17 with DAYH-10
- DYEF-M16-Y1F

Mini slides DGSL-N, NPT


Technical data

FESTO

Shock absorber selection


Effective load m as a function of impact velocity v – vertical mounting position, effective load moving downwards

DGSL-N-10




- DYSW-5-8 (cushioning Y3)
- · - · - DYSW-4-6 with DAYH-4
- DYE-F-M8-Y1F

DGSL-N-12




- DYSW-7-10 (cushioning Y3)
- · - · - DYSW-5-8 with DAYH-5
- DYE-F-M10-Y1F

DGSL-N-16




- DYSW-8-14 (cushioning Y3)
- · - · - DYSW-7-10 with DAYH-7
- DYE-F-M12-Y1F

DGSL-N-20



- DYSW-10-17 (cushioning Y3)
- · - · - DYSW-8-14 with DAYH-8
- DYE-F-M14-Y1F

DGSL-N-25



- DYSW-12-20 (cushioning Y3)
- · - · - DYSW-10-17 with DAYH-10
- DYE-F-M16-Y1F


Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning P/E – horizontal mounting position




The values in the graphs are determined by calculation.
The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 19


Advancing

Stroke 10 mm, size 10




Retracting


Stroke 10 mm, size 10




Stroke 10 mm, size 12 ... 16




Stroke 10 mm, size 12 ... 16




Stroke 10 mm, size 20 ... 25




Stroke 10 mm, size 20 ... 25



Stroke 30 mm, size 10



Stroke 30 mm, size 10



- DGSL-N-10
- DGSL-N-12
- DGSL-N-16
- DGSL-N-20
- DGSL-N-25

Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning P/E – horizontal mounting position




The values in the graphs are determined by calculation.
The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 19


Advancing

Stroke 30 mm, size 12 ... 25




Retracting


Stroke 30 mm, size 12 ... 16




Stroke 30 mm, size 20 ... 25




Stroke 50 mm, size 10 ... 12




Stroke 50 mm, size 10 ... 12



Stroke 50 mm, size 16 ... 25




Stroke 50 mm, size 16



..... DGSL-N-10 - - - - DGSL-N-20
 - · - · - DGSL-N-12 - · - · - DGSL-N-25
 - - - - DGSL-N-16

Stroke 50 mm, size 20 ... 25




Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning P/E – horizontal mounting position




The values in the graphs are determined by calculation.
The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 19


Advancing

Stroke 100 mm, size 10 ... 16




Retracting


Stroke 100 mm, size 10 ... 16




Stroke 100 mm, size 20 ... 25




Stroke 100 mm, size 20 ... 25




Stroke 150 mm, size 12 ... 16




Stroke 150 mm, size 12 ... 16



Stroke 150 mm, size 20 ... 25



Stroke 150 mm, size 20 ... 25



..... DGSL-N-10
 - - - - - DGSL-N-20
 - · - · - DGSL-N-12
 - - - - - DGSL-N-25
 - - - - - DGSL-N-16

Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning P/E – horizontal mounting position




The values in the graphs are determined by calculation.
The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 19

Advancing


Stroke 200 mm, size 20 ... 25



--- DGSL-N-20
- . - DGSL-N-25

Retracting

Stroke 200 mm, size 20 ... 25



Vertical mounting position

The travel times for a vertical mounting position are calculated by multiplying the data ascertained for horizontal mounting position by a correction factor k_a (advancing) and k_r (retracting), see adjacent table.

Given:

Stroke = 200 mm
Size = 20
Effective load = 3 kg
Ascertained travel time t_h (horizontal), see graph:
– Advancing = 500 ms
– Retracting = 600 ms
Calculated travel time t_v (vertical):
– Advancing: $t_v = t_h \times k_a$
 $t_v = 500 \text{ ms} \times 0.9 = 450 \text{ ms}$
– Retracting: $t_v = t_h \times k_r$
 $t_v = 600 \text{ ms} \times 1.1 = 660 \text{ ms}$

Stroke [mm]	Size	Advancing (k_a) ¹⁾	Retracting (k_r)
10	10	0.95	1.1
	12, 16, 20, 25	0.95	1.2
30	10	0.95	1.1
	12, 16, 20, 25	0.95	1.2
50	10, 12	0.9	1.1
	16, 20, 25	1.1	1.2
100	10, 12, 16, 20, 25	1	1.1
150	12, 16, 20, 25	1	1.1
200	20, 25	0.9	1.1

1) Downward.

Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning P1 – horizontal mounting position




The values in the graphs are determined by calculation.
The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 23


Advancing

Stroke 10 mm, size 10




Retracting


Stroke 10 mm, size 10




Stroke 10 mm, size 12 ... 16




Stroke 10 mm, size 12 ... 16




Stroke 10 mm, size 20 ... 25




Stroke 10 mm, size 20 ... 25



Stroke 30 mm, size 10



Stroke 30 mm, size 10



- DGSL-N-10
- DGSL-N-12
- DGSL-N-16
- DGSL-N-20
- DGSL-N-25

Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning P1 – horizontal mounting position




The values in the graphs are determined by calculation.
The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 23


Advancing

Stroke 30 mm, size 12 ... 16




Retracting


Stroke 30 mm, size 12 ... 16




Stroke 30 mm, size 20 ... 25




Stroke 30 mm, size 20 ... 25




Stroke 50 mm, size 10 ... 12




Stroke 50 mm, size 10 ... 12



Stroke 50 mm, size 16 ... 25



Stroke 50 mm, size 16 ... 25



..... DGSL-N-10
 - - - - - DGSL-N-12
 - . - . - DGSL-N-16
 - - - - - DGSL-N-20
 - . - . - DGSL-N-25

Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning P1 – horizontal mounting position




The values in the graphs are determined by calculation.
The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 23


Advancing

Stroke 100 mm, size 10 ... 16




Retracting


Stroke 100 mm, size 10 ... 25




Stroke 100 mm, size 20 ... 25



Stroke 150 mm, size 12 ... 25



Stroke 150 mm, size 12 ... 25



.....	DGSL-N-10	----	DGSL-N-20
-----	DGSL-N-12	-.-.-.-	DGSL-N-25
-----	DGSL-N-16		

Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning P1 – horizontal mounting position




The values in the graphs are determined by calculation.
The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 23


Advancing

Stroke 200 mm, size 20




Retracting


Stroke 200 mm, size 20



Stroke 200 mm, size 25



Stroke 200 mm, size 25



--- DGSL-N-20
--- DGSL-N-25

Vertical mounting position

The travel times for a vertical mounting position are calculated by multiplying the data ascertained for horizontal mounting position by a correction factor k_a (advancing) and k_r (retracting), see adjacent table.

Given:

Stroke = 200 mm
Size = 20
Effective load = 2 kg
Ascertained travel time t_h (horizontal), see graph:
– Advancing = 640 ms
– Retracting = 780 ms
Calculated travel time t_v (vertical):
– Advancing: $t_v = t_h \times k_a$
 $t_v = 640 \text{ ms} \times 0.9 = 576 \text{ ms}$
– Retracting: $t_v = t_h \times k_r$
 $t_v = 780 \text{ ms} \times 1.1 = 858 \text{ ms}$

Stroke [mm]	Size	Advancing (k_a) ¹⁾	Retracting (k_r)
10	10	1	1.1
	12, 16, 20, 25	1.1	1.2
30	10	1	1.1
	12, 16, 20, 25	1.1	1.2
50	10, 12	1	1.1
	16, 20, 25	0.9	1.1
100	10, 12, 16, 20, 25	0.95	1.1
150	12, 16, 20, 25	0.95	1.1
200	20, 25	0.9	1.1

1) Downward.


Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning Y3 – horizontal mounting position




The values in the graphs are determined by calculation.
The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 25


Advancing

Stroke 30 mm, size 10 ... 12




Retracting


Stroke 30 mm, size 10 ... 12




Stroke 30 mm, size 16 ... 25




Stroke 30 mm, size 16 ... 25




Stroke 50 mm, size 10 ... 12




Stroke 50 mm, size 10 ... 12



Stroke 50 mm, size 16 ... 25



Stroke 50 mm, size 16 ... 25



..... DGSL-N-10
 - - - - - DGSL-N-20
 - · - · - DGSL-N-12
 - - - - - DGSL-N-25
 - - - - - DGSL-N-16


Mini slides DGSL-N, NPT

Technical data

FESTO

Shock absorber selection

Travel time t as a function of effective load m and cushioning Y3 – horizontal mounting position




The values in the graphs are determined by calculation. The travel time as a function of effective load must not be reduced below

the values shown, because the kinetic impact or residual energy in the end positions can result in damage to the drive.

Vertical mounting position
→ 25


Advancing

Stroke 100 mm, size 10 ... 25




Retracting


Stroke 100 mm, size 10 ... 25




Stroke 150 mm, size 12 ... 25




Stroke 150 mm, size 12 ... 25



Stroke 200 mm, size 20 ... 25



Stroke 200 mm, size 20 ... 25



----- DGSL-N-10
----- DGSL-N-12
----- DGSL-N-16
----- DGSL-N-20
----- DGSL-N-25

Vertical mounting position

The travel times for a vertical mounting position are calculated by multiplying the data ascertained for horizontal mounting position by a correction factor k_a (advancing) and k_r (retracting), see adjacent table.

Given:

Stroke = 200 mm
Size = 20
Effective load = 10 kg
Ascertained travel time t_h (horizontal), see graph:
– Advancing = 405 ms
– Retracting = 490 ms
Calculated travel time t_v (vertical):
– Advancing: $t_v = t_h \times k_a$
 $t_v = 405 \text{ ms} \times 0.9 = 365 \text{ ms}$
– Retracting: $t_v = t_h \times k_r$
 $t_v = 490 \text{ ms} \times 1.5 = 735 \text{ ms}$

Stroke [mm]	Size	Advancing (k_a) ¹⁾	Retracting (k_r)
30	10, 12	0.95	1.2
	16, 20, 25	0.9	1.5
50	10, 12	0.9	1.5
	16, 20, 25	0.9	1.5
100	10, 12, 16, 20, 25	0.8	1.5
150	12, 16, 20, 25	0.9	1.5
200	20, 25	0.9	1.5

1) Downward.


Mini slides DGSL-N, NPT

Technical data

FESTO

Dynamic characteristic load values


Torques are indicated with reference to the centre of the guide.
These values must not be exceeded during dynamic operation. Special attention must be paid to the cushioning phase.



If the drive is simultaneously subjected to several of the indicated forces and torques, the following equation must be satisfied in addition to the indicated maximum loads:


$$\frac{|F_y|}{F_{y_{\max}}} + \frac{|F_z|}{F_{z_{\max}}} + \frac{|M_x|}{M_{x_{\max}}} + \frac{|M_y|}{M_{y_{\max}}} + \frac{|M_z|}{M_{z_{\max}}} \leq 1$$

Position of the guide centre



Calculation example

Given:



Mini slide	= DGSL-N-10
Stroke length	= 80 mm
Lever arm L_x	= 50 mm
Lever arm L_y	= 30 mm
Load F_z	= 0.8 kg
Acceleration a	= 0 m/s ²

To be calculated:

F_y, F_z, M_x, M_y, M_z
and
verification of operation
with combined load

Solution:

$L_{21} = 83 \text{ mm}$ from table

$F_y = 0 \text{ N}$

$F_z = m \times g$
 $= 0.8 \text{ kg} \times 9.81 \text{ m/s}^2 = 7.848 \text{ N}$

$M_x = m \times g \times L_y$
 $= 0.8 \text{ kg} \times 9.81 \text{ m/s}^2 \times 30 \text{ mm} = 0.236 \text{ Nm}$

$M_y = m \times g \times [(L_{21} + \text{stroke}) - L_x]$
 $= 0.8 \text{ kg} \times 9.81 \text{ m/s}^2 \times [(83 \text{ mm} + 80 \text{ mm}) - 50 \text{ mm}] = 0.886 \text{ Nm}$

$M_z = 0 \text{ Nm}$

Combined load:

$$\frac{|F_y|}{F_{y_{\max}}} + \frac{|F_z|}{F_{z_{\max}}} + \frac{|M_x|}{M_{x_{\max}}} + \frac{|M_y|}{M_{y_{\max}}} + \frac{|M_z|}{M_{z_{\max}}} = 0 + \frac{7.848 \text{ N}}{1200 \text{ N}} + \frac{0.236 \text{ Nm}}{18 \text{ Nm}} + \frac{0.886 \text{ Nm}}{12 \text{ Nm}} + 0 = 0.094 \leq 1$$

Mini slides DGSL-N, NPT

Technical data

FESTO

Permissible forces and torques						Geometric characteristics	
Size	Stroke [mm]	F _y _{max} [N]	F _z _{max} [N]	M _x _{max} [Nm]	M _y _{max} , M _z _{max} [Nm]	H13 [mm]	L21 [mm]
10							
	10	927	927	15	6	4.2	43
	20	1,003	1,003	15	7		46
	30	1,078	1,078	15	8		51
	40	1,152	1,152	15	9		56
	50	1,175	1,175	18	9		61
	80	1,200	1,200	18	12		83
	100	1,250	1,250	18	12		96
12							
	10	942	942	15	8	5.2	44
	20	1,006	1,006	15	9		49
	30	1,075	1,075	15	10		54
	40	1,142	1,142	18	11		59
	50	1,200	1,200	18	12		64
	80	1,280	1,280	20	15		88
	100	1,340	1,340	20	15		98
	150	1,400	1,400	20	15		124
16							
	10	1,769	1,769	35	20	6.4	54
	20	2,021	2,021	35	22		59
	30	2,274	2,274	35	22		64
	40	2,527	2,527	40	25		69
	50	2,780	2,780	40	25		74
	80	2,800	2,800	50	27		89
	100	2,850	2,850	50	43		113
	150	2,900	2,900	50	43		138
20							
	10	2,911	2,911	60	30	7.55	56
	20	3,143	3,143	60	30		61
	30	3,354	3,354	60	30		66
	40	3,612	3,612	60	40		71
	50	3,816	3,816	70	50		76
	80	4,032	4,032	80	50		91
	100	4,200	4,200	85	80		121
	150	4,400	4,400	90	80		152
	200	4,600	4,600	90	80		177
	25						
	10	3,270	3,270	100	60	8.55	64
	20	3,744	3,744	100	60		69
	30	4,205	4,205	100	60		74
	40	4,643	4,643	110	60		79
	50	4,650	4,650	120	60		84
	80	4,700	4,700	130	80		112
	100	4,750	4,750	130	80		129
	150	4,800	4,800	130	80		154
	200	4,800	4,800	130	80		179

Mini slides DGSL-N, NPT


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Size 10



General dimensions

Size	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	D1
10	50	49	39.2	19.65	10	6.8	12.35	20.1	49	5	29.2	28	37.7	27	M4

Size	D2 Ø	D3 Ø	D4 Ø	D5 Ø	D6	D7 Ø	EE ¹⁾	H1 ±0.08	H2	H3	H4	H5	H6	H7	H8
10	8	7 ^{H7}	4.3	8	M8x1	5 ^{H7}	M5	29	27.1	28	6.8	13.8	15.8	22.8	15.5

Size	H9	H10	H11	H12	H13	H14	H15	H16	H17	H18	H19	T3 +0.1	T4	T5	≈ 2 ¹⁾	≈ 3
10	0.6	1.4	10	12.5	4.2	8.75	11.75	4.8	19.25	0.4	9	1.6	5	7.5	2.5	3

1) Suitable for 10-32 UNF

Mini slides DGSL-N, NPT

Technical data


FESTO

Stroke-dependent dimensions															
Size	Stroke	L1	L2	L5	L6	L7	L8	L9	L10	L11	L15 ±0.05	L16	L17	L18 ±0.05	L21
10	10	103.1	66	41.3	–	–	11	10	11.6	2.5	6.4	18.5	7.5	5	43
	20	112.8	75.7	51											46
	30	122.8	85.7	61											51
	40	132.8	95.7	71											56
	50	142.8	105.7	81											61
	80	186.2	149.1	111	24	83									
	100	206.2	169.1	131	24	24									96


Cushioning-dependent dimensions					
Size	Cushioning	L3 max.	L4 max.	±0.1	
				For adjusting the cushioning stroke	For adjusting the end position
10	P	22.8	12.5	–	2.5
	E	8.8	0	–	2.5
	P1	20.5	10.2	2.5	5
	Y3	25.5	14.9	–	2.5

Hole pattern for mounting threads and centring holes


DGSL-N-10-10




DGSL-N-10-20



DGSL-N-10-30




DGSL-N-10-40 ... 100



Distances from yoke plate to mounting threads and centring holes

DGSL-N-10



- 1 Centring holes with thread
- 2 Through-holes for mounting the drive

- 1) Tolerance for centring hole ±0.02
- Tolerance for through-hole ±0.1

Size	L9	L15 ±0.05	L18
10	10	6.4	5

Mini slides DGSL-N, NPT


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Size 12/16



General dimensions

Size	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	D1
12	60	59	47.6	24	10	9.2	14.7	24.3	59	6.4	35.35	35.2	50	36.7	M5
16	66	65	53.5	26.7	10	11.1	16.7	27.5	65	7.75	37.9	38	50.4	36.7	M5

Size	D2	D3	D4	D5	D6	D7	EE ¹⁾	H1	H2	H3	H4	H5	H6	H7	H8
	Ø	Ø	Ø	Ø		Ø		±0.08							
12	8.8	7 ^{H7}	5.5	8.8	M10x1	8 ^{H7}	M5	36	34.8	34.7	8	15.1	20.35	28.2	19.3
16	8.8	7 ^{H7}	5.5	9.2	M12x1	8 ^{H7}	M5	40	38	39	8.5	16.7	20.6	31.7	20.8

Size	H9	H10	H11	H12	H13	H14	H15	H16	H17	H18	H19	T3	T4	T5	≈ 2	≈ 3
												+0.1				
12	0.8	0.95	10	17.9	5.2	10.75	15.75	5.5	24.9	0.5	10	1.6	5.6	7.5	3	3
16	0.5	1.5	10	20	6.4	10.5	16.7	7	26.6	0.5	12.4	1.6	6.1	9	4	4

1) Suitable for 10-32 UNF

Mini slides DGSL-N, NPT

Technical data

FESTO

Stroke-dependent dimensions															
Size	Stroke	L1	L2	L5	L6	L7	L8	L9	L10	L11	L15 ±0.05	L16	L17	L18 ±0.05	L21
12	10	106.2	68.6	42.4	–	–	12	10	11.6	2.5	5.8	18.5	9	4.5	44
	20	116.2	78.6	52.4											49
	30	126.2	88.6	62.4											54
	40	136.2	98.6	72.4											59
	50	146.2	108.6	82.4	29										64
	80	197.6	160	117											88
	100	217.6	180	137											98
	150	267.6	230	187		29									124
16	10	124.1	82.5	45	–	–	14	12	13.6	2.5	6.8	21	10	5.5	54
	20	134.6	93	54.6											59
	30	144.6	103	64.6											64
	40	154.6	113	74.6											69
	50	164.6	123	84.6	35										74
	80	194.6	153	114.6											89
	100	243.6	202	134.6											113
	150	293.6	252	184.6											138

Cushioning-dependent dimensions					
Size	Cushioning	L3 max.	L4 max.	≈ 1	
				For adjusting the cushioning stroke	For adjusting the end position
12	P	28.1	14.9	–	3
	E	8.8	0	–	3
	P1	26	12.8	3	6
	Y3	36.9	23.7	–	3
16	P	42.3	26.1	–	4
	E	8.8	0	–	4
	P1	40	23.8	4	8
	Y3	51.9	35.7	–	4


Mini slides DGSL-N, NPT

Technical data


FESTO

Hole pattern for mounting threads and centring holes


DGSL-N-12-10




DGSL-N-12-20




DGSL-N-12-30




DGSL-N-12-40




DGSL-N-12-50 ... 100




DGSL-N-12-150



DGSL-N-16-10




DGSL-N-16-20




Technical data

DGSL-N-16-40 ... 100

[illegible]

DGSL-N-12/16



- | | |
|---|--|
| 1) Centring holes with thread | 1) Tolerance for centring hole
± 0.02 |
| 2) Through-holes for mounting the drive | Tolerance for through-hole ± 0.1 |

Size	L9	L15 ±0.05	L18
12	10	5.8	4.5
16	12	6.8	5.5

Mini slides DGSL-N, NPT


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Size 20/25



General dimensions

Size	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	D1
20	85	84	68.85	34.5	20	14	21.4	36.35	83.4	10	48.9	49.2	64.1	48.6	M6
25	104	103	82.6	41.6	20	16.2	26.6	43.1	103	13.25	56.5	56.7	79.4	53.7	M6

Size	D2 Ø	D3 Ø	D4 Ø	D5 Ø	D6	D7 Ø	EE	H1 ±0.08	H2	H3	H4	H5	H6	H7	H8
20	11	9 ^{H7}	6.6	11	M14x1	8 ^{H7}	1/8 NPT	49	46.5	47.7	10.3	20.6	23.2	38.2	26.1
25	11	9 ^{H7}	6.6	11	M16x1	8 ^{H7}	1/8 NPT	60	57.5	58.5	10.5	23.4	31.2	48	34.5

Size	H9	H10	H11	H12	H13	H14	H15	H16	H17	H18	H19	T3 +0.1	T4	T5	∠ 2	∠ 3
20	0.5	2	20	19.6	7.55	14.7	14.7	10	33.3	0.8	14.5	2.1	8.8	10	4	5
25	1	2	20	27.5	8.55	16.6	22.2	11	42.7	0.5	15.5	2.1	15.1	12	5	6

Mini slides DGSL-N, NPT

Technical data

FESTO

Stroke-dependent dimensions															
Size	Stroke	L1	L2	L5	L6	L7	L8	L9	L10	L11	L15 ±0.05	L16	L17	L18 ±0.05	L21
20	10	141.2	84.6	59.1	–	–	17	14	15.6	4.6	7.8	29.3	12	6.5	56
	20	151.2	94.6	69.1											61
	30	161.2	104.6	79.1											66
	40	171.2	114.6	89.1											71
	50	183.2	126.6	99.1											76
	80	211.2	154.6	129.1											91
	100	270.2	213.6	149.1	44	44									121
	150	333.2	276.6	199.1											152
	200	383.2	326.6	252.1											177
25	10	157.1	96	63.7	–	–	22	15	16.6	4.6	8	30.9	14.5	6.5	64
	20	167.1	106	72.2											69
	30	177.1	116	82.2											74
	40	187.1	126	92.2											79
	50	197.1	136	102.2											84
	80	253.1	192	132.2	55	112									
	100	286.1	225	152.2		129									
	150	338.1	277	202.2		154									
	200	388.1	327	254.2		179									

Cushioning-dependent dimensions					
Size	Cushioning	L3 max.	L4 max.	≈ 1	
				For adjusting the cushioning stroke	For adjusting the end position
20	P	52.4	31.2	–	4
	E	8.8	0	–	4
	P1	50.1	28.9	4	8
	Y3	55.5	34.3	–	4
25	P	51.9	30.5	–	5
	E	8.8	0	–	5
	P1	49.6	28.2	5	10
	Y3	65.2	43.8	–	5


Mini slides DGSL-N, NPT

Technical data


FESTO

Hole pattern for mounting threads and centring holes


DGSL-N-20-10/20




DGSL-N-20-30/40




DGSL-N-20-50




DGSL-N-20-80




DGSL-N-20-100 ... 200



DGSL-N-25-10



DGSL-N-25-20




Mini slides DGSL-N, NPT

Technical data


FESTO

Hole pattern for mounting threads and centring holes


DGSL-N-25-30/40




DGSL-N-25-50



DGSL-N-25-80




DGSL-N-25-100 ... 200



Distances from yoke plate to mounting threads and centring holes

DGSL-N-20/25



- 1 Centring holes with thread
- 2 Through-holes for mounting the drive

- 1) Tolerance for centring hole ± 0.02
- Tolerance for through-hole ± 0.1

Size	L9	L15 ± 0.05	L18
20	14	7.8	6.5
25	15	8	6.5

Mini slides DGSL-N, NPT

Technical data

FESTO

Ordering data							
Size	Stroke [mm]	Part No.	Type	Size	Stroke [mm]	Part No.	Type
With cushioning P				With cushioning E			
10	10	566258	DGSL-N-10-10-PA	10	10	570213	DGSL-N-10-10-EA
	20	566259	DGSL-N-10-20-PA		20	570214	DGSL-N-10-20-EA
	30	566260	DGSL-N-10-30-PA		30	570215	DGSL-N-10-30-EA
	40	566261	DGSL-N-10-40-PA		40	570216	DGSL-N-10-40-EA
	50	566262	DGSL-N-10-50-PA		50	570217	DGSL-N-10-50-EA
	80	566263	DGSL-N-10-80-PA		80	570218	DGSL-N-10-80-EA
	100	566264	DGSL-N-10-100-PA		100	570219	DGSL-N-10-100-EA
12	10	566265	DGSL-N-12-10-PA	12	10	570220	DGSL-N-12-10-EA
	20	566266	DGSL-N-12-20-PA		20	570221	DGSL-N-12-20-EA
	30	566267	DGSL-N-12-30-PA		30	570222	DGSL-N-12-30-EA
	40	566268	DGSL-N-12-40-PA		40	570223	DGSL-N-12-40-EA
	50	566269	DGSL-N-12-50-PA		50	570224	DGSL-N-12-50-EA
	80	566270	DGSL-N-12-80-PA		80	570225	DGSL-N-12-80-EA
	100	566271	DGSL-N-12-100-PA		100	570226	DGSL-N-12-100-EA
16	10	566272	DGSL-N-12-150-PA	16	150	570227	DGSL-N-12-150-EA
	10	566273	DGSL-N-16-10-PA		10	570228	DGSL-N-16-10-EA
	20	566274	DGSL-N-16-20-PA		20	570229	DGSL-N-16-20-EA
	30	566275	DGSL-N-16-30-PA		30	570230	DGSL-N-16-30-EA
	40	566276	DGSL-N-16-40-PA		40	570231	DGSL-N-16-40-EA
	50	566277	DGSL-N-16-50-PA		50	570232	DGSL-N-16-50-EA
	80	566278	DGSL-N-16-80-PA		80	570233	DGSL-N-16-80-EA
20	100	566279	DGSL-N-16-100-PA	20	100	570234	DGSL-N-16-100-EA
	150	566280	DGSL-N-16-150-PA		150	570235	DGSL-N-16-150-EA
	10	566281	DGSL-N-20-10-PA		10	570236	DGSL-N-20-10-EA
	20	566282	DGSL-N-20-20-PA		20	570237	DGSL-N-20-20-EA
	30	566283	DGSL-N-20-30-PA		30	570238	DGSL-N-20-30-EA
	40	566284	DGSL-N-20-40-PA		40	570239	DGSL-N-20-40-EA
	50	566285	DGSL-N-20-50-PA		50	570240	DGSL-N-20-50-EA
25	80	566286	DGSL-N-20-80-PA	25	80	570241	DGSL-N-20-80-EA
	100	566287	DGSL-N-20-100-PA		100	570242	DGSL-N-20-100-EA
	150	566288	DGSL-N-20-150-PA		150	570243	DGSL-N-20-150-EA
	200	566289	DGSL-N-20-200-PA		200	570244	DGSL-N-20-200-EA
	10	566290	DGSL-N-25-10-PA		10	570245	DGSL-N-25-10-EA
	20	566291	DGSL-N-25-20-PA		20	570246	DGSL-N-25-20-EA
	30	566292	DGSL-N-25-30-PA		30	570247	DGSL-N-25-30-EA
	40	566293	DGSL-N-25-40-PA		40	570248	DGSL-N-25-40-EA
	50	566294	DGSL-N-25-50-PA		50	570249	DGSL-N-25-50-EA
	80	566295	DGSL-N-25-80-PA		80	570250	DGSL-N-25-80-EA
	100	566296	DGSL-N-25-100-PA		100	570251	DGSL-N-25-100-EA
	150	566297	DGSL-N-25-150-PA		150	570252	DGSL-N-25-150-EA
	200	566298	DGSL-N-25-200-PA		200	570253	DGSL-N-25-200-EA

Mini slides DGSL-N, NPT

Technical data

FESTO

Ordering data							
Size	Stroke [mm]	Part No.	Type	Size	Stroke [mm]	Part No.	Type
With cushioning P1				With cushioning Y3			
10	10	566299	DGSL-N-10-10-P1A	10	10	–	
	20	566300	DGSL-N-10-20-P1A		20	–	
	30	566301	DGSL-N-10-30-P1A		30	566340	DGSL-N-10-30-Y3A
	40	566302	DGSL-N-10-40-P1A		40	566341	DGSL-N-10-40-Y3A
	50	566303	DGSL-N-10-50-P1A		50	566342	DGSL-N-10-50-Y3A
	80	566304	DGSL-N-10-80-P1A		80	566343	DGSL-N-10-80-Y3A
	100	566305	DGSL-N-10-100-P1A		100	566344	DGSL-N-10-100-Y3A
12	10	566306	DGSL-N-12-10-P1A	12	10	–	
	20	566307	DGSL-N-12-20-P1A		20	–	
	30	566308	DGSL-N-12-30-P1A		30	566345	DGSL-N-12-30-Y3A
	40	566309	DGSL-N-12-40-P1A		40	566346	DGSL-N-12-40-Y3A
	50	566310	DGSL-N-12-50-P1A		50	566347	DGSL-N-12-50-Y3A
	80	566311	DGSL-N-12-80-P1A		80	566348	DGSL-N-12-80-Y3A
	100	566312	DGSL-N-12-100-P1A		100	566349	DGSL-N-12-100-Y3A
16	10	566313	DGSL-N-12-150-P1A		150	566350	DGSL-N-12-150-Y3A
	10	566314	DGSL-N-16-10-P1A	16	10	–	
	20	566315	DGSL-N-16-20-P1A		20	–	
	30	566316	DGSL-N-16-30-P1A		30	566351	DGSL-N-16-30-Y3A
	40	566317	DGSL-N-16-40-P1A		40	566352	DGSL-N-16-40-Y3A
	50	566318	DGSL-N-16-50-P1A		50	566353	DGSL-N-16-50-Y3A
	80	566319	DGSL-N-16-80-P1A		80	566354	DGSL-N-16-80-Y3A
	100	566320	DGSL-N-16-100-P1A		100	566355	DGSL-N-16-100-Y3A
20	150	566321	DGSL-N-16-150-P1A		150	566356	DGSL-N-16-150-Y3A
	10	566322	DGSL-N-20-10-P1A	20	10	–	
	20	566323	DGSL-N-20-20-P1A		20	–	
	30	566324	DGSL-N-20-30-P1A		30	566357	DGSL-N-20-30-Y3A
	40	566325	DGSL-N-20-40-P1A		40	566358	DGSL-N-20-40-Y3A
	50	566326	DGSL-N-20-50-P1A		50	566359	DGSL-N-20-50-Y3A
	80	566327	DGSL-N-20-80-P1A		80	566360	DGSL-N-20-80-Y3A
	100	566328	DGSL-N-20-100-P1A		100	566361	DGSL-N-20-100-Y3A
25	150	566329	DGSL-N-20-150-P1A		150	566362	DGSL-N-20-150-Y3A
	200	566330	DGSL-N-20-200-P1A		200	566363	DGSL-N-20-200-Y3A
	10	566331	DGSL-N-25-10-P1A	25	10	–	
	20	566332	DGSL-N-25-20-P1A		20	–	
	30	566333	DGSL-N-25-30-P1A		30	566364	DGSL-N-25-30-Y3A
	40	566334	DGSL-N-25-40-P1A		40	566365	DGSL-N-25-40-Y3A
	50	566335	DGSL-N-25-50-P1A		50	566366	DGSL-N-25-50-Y3A
	80	566336	DGSL-N-25-80-P1A		80	566367	DGSL-N-25-80-Y3A
	100	566337	DGSL-N-25-100-P1A		100	566368	DGSL-N-25-100-Y3A
	150	566338	DGSL-N-25-150-P1A		150	566369	DGSL-N-25-150-Y3A
	200	566339	DGSL-N-25-200-P1A		200	566370	DGSL-N-25-200-Y3A

Mini slides DGSL-N, NPT


Wearing parts kits and accessories

FESTO

Ordering data – Wearing parts kits		
Size	Part No.	Type
10	713746	DGSL-10-...
12	713747	DGSL-12-...
16	713748	DGSL-16-...
20	713749	DGSL-20-...
25	713750	DGSL-25-...

Cover DADS

Materials:
Anodised aluminium
Free of copper, PTFE and silicone
RoHS-compliant



Dimensions and ordering data																
For size	Length [mm]	B1	B2	B3	B4	D1	H1	H2	H3	L1	L2	W	$\varnothing 1$	Weight [g]	Part No.	Type
10	50	43.6	2.8	2.2	1.2	3.4	32	12	3.4	70	10	90°	2	11	1162400	DADS-AB-G6-10-50
	100									120				18	1090689	DADS-AB-G6-10-100
	500									500				75	1212479	DADS-AB-G6-10-500
12	50	51.7	2.7	2	0.5	3.4	38.8	12.8	4.25	72	10	90°	2	12	1162406	DADS-AB-G6-12-50
	150									170				28	1090732	DADS-AB-G6-12-150
	500									500				82	1212480	DADS-AB-G6-12-500
16	50	60	4.3	3.1	2.25	3.4	43.7	15.2	5	73	10	90°	2	21	1162410	DADS-AB-G6-16-50
	150									173				49	1066591	DADS-AB-G6-16-150
	500									500				141	1212503	DADS-AB-G6-16-500
20	50	74.8	3.6	2.8	1.2	4.4	53.2	18.9	6.5	74	10	90°	2.5	28	1162412	DADS-AB-G6-20-50
	100									124				46	1162415	DADS-AB-G6-20-100
	200									224				83	1090823	DADS-AB-G6-20-200
	500									500				184	1212521	DADS-AB-G6-20-500
25	50	88.4	3.5	2.7	0.7	4.4	64.7	18.3	6	78	10	90°	2.5	34	1162417	DADS-AB-G6-25-50
	100									128				55	1162419	DADS-AB-G6-25-100
	200									228				98	1090895	DADS-AB-G6-25-200
	500									500				213	1212523	DADS-AB-G6-25-500

-  - Note

With the 500 mm covers, the mounting hole must be made by the customer.

The cover can be trimmed as required by the customer.

Mini slides DGSL-N, NPT

Accessories

FESTO

Ordering data						
	For size	Brief description	Order code	Part No.	Type	PU ¹⁾
Centring sleeve ZBH						
			Technical data → Internet: zbh			
	10, 12, 16	For centring loads and attachments (the scope of delivery of the mini slide includes six centring sleeves)	–	186717	ZBH-7	10
	20, 25			150927	ZBH-9	
Connector sleeve ZBV						
			Technical data → Internet: zbv			
	10	- For connecting two mini slides DGSL - Sizing information refers to the y axis	–	548802	ZBV-M4-7	3
	12, 16			548803	ZBV-M5-7	
	20, 25			548804	ZBV-M6-9	
Shock absorber DYEF-...-Y1						
			Technical data → Internet: dyef			
	10	Flexible cushioning, without metal stop	P	1179834	DYEF-M8-Y1	1
	12			1179837	DYEF-M10-Y1	
	16			1179840	DYEF-M12-Y1	
	20			1179863	DYEF-M14-Y1	
	25			1179879	DYEF-M16-Y1	
Shock absorber DYEF-S-...-Y1						
			Technical data → Internet: dyef			
	10	Flexible cushioning, without metal stop, short design	E	1152536	DYEF-S-M8-Y1	1
	12			1152959	DYEF-S-M10-Y1	
	16			1153004	DYEF-S-M12-Y1	
	20			1153017	DYEF-S-M14-Y1	
	25			1153023	DYEF-S-M16-Y1	
Shock absorber DYEF-...-Y1F						
			Technical data → Internet: dyef			
	10	Flexible cushioning, with metal stop	P1	548373	DYEF-M8-Y1F	1
	12			548374	DYEF-M10-Y1F	
	16			548375	DYEF-M12-Y1F	
	20			548376	DYEF-M14-Y1F	
	25			548377	DYEF-M16-Y1F	
Shock absorber DYSW						
			Technical data → Internet: dysw			
	10	Progressive shock absorber, both ends	Y3	548071	DYSW-5-8-Y1F	1
	12			548072	DYSW-7-10-Y1F	
	16			548073	DYSW-8-14-Y1F	
	20			548074	DYSW-10-17-Y1F	
	25			548075	DYSW-12-20-Y1F	
Reducing sleeve DAYH						
	10	For DYSW-4-6	–	1165476	DAYH-4	1
	12	For DYSW-5-8		1165480	DAYH-5	
	16	For DYSW-7-10		1165484	DAYH-7	
	20	For DYSW-8-14		1165488	DAYH-8	
	25	For DYSW-10-17		1165491	DAYH-10	

1) Packaging unit

Mini slides DGSL-N, NPT

Accessories

FESTO

Ordering data					
	For size	Brief description	Part No.	Type	PU ¹⁾
One-way flow control valve GRLA			Technical data → Internet: grla		
	10, 12, 16	- For regulating speed - Only one GRLA-M3-QS-3 can be mounted on the front face with size 4	165008	GRLA-10-32-UNF-QS-5/32-U	1
	20, 25		165010	GRLA-1/8-NPT-QS-1/4-U	
Push-in fitting QB			Technical data → Internet: quick star		
	10, 12, 16	For connecting compressed air tubing with standard O.D.	533267	QB-10-32-UNF-5/32-U	10
	20, 25		533273	QB-1/8-1/4-U	

1) Packaging unit

Ordering data – Proximity sensors for C-slot, magneto-resistive Technical data → Internet: smt					
	Type of mounting	Switching output	Electrical connection, connection direction	Cable length [m]	Part No. Type
N/O contact					
	Insertable in the slot from above, flush with the cylinder profile	PNP	Cable, 3-wire, in-line	2.5	525915 SMT-10F-PS-24V-K2,5L-OE
			Plug M8x1, 3-pin, in-line	0.3	525916 SMT-10F-PS-24V-K0,3L-M8D
			Plug M8x1, 3-pin, angled	0.3	526675 SMT-10F-PS-24V-K0,3Q-M8D
	Insertable in the slot lengthwise	PNP	Plug M8x1, 3-pin, in-line	0.3	173220 SMT-10-PS-SL-LED-24
			Cable, 3-wire, in-line	2.5	173218 SMT-10-PS-KL-LED-24

Ordering data – Proximity sensors for C-slot, magnetic reed Technical data → Internet: sme					
	Type of mounting	Switching output	Electrical connection, connection direction	Cable length [m]	Part No. Type
N/O contact					
	Insertable in the slot from above, flush with the cylinder profile	Contacting	Plug M8x1, 3-pin, in-line	0.3	525914 SME-10F-DS-24V-K0,3L-M8D
			Cable, 3-wire, in-line	2.5	525913 SME-10F-DS-24V-K2,5L-OE
			Cable, 2-wire, in-line	2.5	526672 SME-10F-ZS-24V-K2,5L-OE
	Insertable in the slot lengthwise	Contacting	Plug M8x1, 3-pin, in-line	0.3	173212 SME-10-SL-LED-24
			Cable, 3-wire, in-line	2.5	173210 SME-10-KL-LED-24

Ordering data – Connecting cables Technical data → Internet: nebu					
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3