



#### Key features

#### Description

Thanks to a grid dimension of 9 mm and a valve with 8 outputs, the VTOI can be easily connected in series, precisely matched to the microwell plate. A 96-channel dispense head can now be realised with only 12 valves.

With just a few other components, you can have a complete dispensing system with a pressure-over-liquid setup.

As only high-performance materials such as PEI (ULTEM), PPS, FKM, ETFE and high-alloy stainless steel come into contact with the media, it can also be used to dispense and aspirate aggressive media.

[1] Dispense head VTOI

Clamping component Dosing needle VAVN

Fitting

[2]

[3]

[4]

#### Advantages:

- Extremely precise
- 9 mm grid dimension ideal for microwell plates
- Simple design with side-by-side mounting for increased throughput
- Complete system using just a few components

• Dispensing and aspirating gaseous

• 1 valve for 8 channels

Typical areas of application:

• Filling microwell plates • Dispensing gaseous and liquid

and liquid media

media

2 С 1 Ą 4

Electrical installation



Fluid installation



- [1] Electrical connection

Connect wire ends [1]. Polarity as desired.

- [1] Fitting with clamping component
- [2] Tubing [3] Port

Mount the clamping component [1] on the tubing [2]. Then tighten the clamping component [1] in the port [3].

Design of VTOI

## NEW

## Key features

### Description

Mounting



[1] Dispense head VTOI

- [2] Mounting surface
- [3] Screws

Position dispense head [1] on the mounting surface [2] and fasten using screws [3].

Mounting on drive with adapter plate



- [1] Dispense head VTOI
- [2] Adapter plate
- [3] Screws

# Product range overview

Function	Description	Nominal size Dosing needle	Operating voltage		
Dispense head	C C C C C C C C C C C C C C C C C C C	2/2-way valve, normally closed, single solenoid	2x individual wire, open end, 2-wire	0.3 mm	24 V DC

# NEW

# Type codes

001	Series
VTOI	Distributor
002	Dosing function
	Dispensing
Α	Dispensing and aspirating
003	Valve positions
	1 valve position
004	Distributor
V8	8 outputs per valve position
005	Output connection
30D3	With metering nozzle, length 30 mm, tapered, nominal width 0.3 mm

006	Input connection	
U14	Thread 1/4-28 UNF	
007	Nominal width	
08	0.8 mm	
008	Diaphragm and sealing material	
V	FPM	
009	Valve control	
S015	Individual connection, electric, with flying leads 0.15 m	
010	Nominal operating voltage	
1	24 V DC	

#### Datasheet

- **L** - Voltage 24 V DC



General technical data								
Туре			VTOI-A-V8	VT0I-V8				
Valve function			2/2-way valve, closed, single soleno	id				
Reset method			Mechanical spring					
Nominal size		[mm]	0.8					
Nominal width of dosing	needle	[mm]	0.3	0.3				
Internal volume		[µl]	167					
Min. dosing volume		[µl]	1					
Typical dosing precision			<= 5% tip-to-tip CV, <= 3% intra-run	CV				
Switching times	On	[ms]	-	7				
	Off	[ms]	-	2				
Operating pressure		[MPa]	-0.02 0.065	00.1				
		[bar]	-0.2 0.65	01				
		[psi]	-2.9 9.425	014.5				
Grid dimension		[mm]	9					
Fluid connection			Female thread 1/4-28 UNF-2B					
Note on fluid connection			Fitting for tubing with 3 mm outside diameter enclosed					
Actuation type			Electrical					
Type of control			Direct					
Sealing principle			Soft					
Type of mounting			With through-hole for M3 screw					
Mounting position			Vertical					
Product weight		[g]	55	52				
Suitable for vacuum			Yes	No				
Electrical connection			2x individual wire, open end, 2-wire					
Cable length		[m]	0.15					
Wire ends			Stripped					
Safety data								
			VTOI-A-V8	VTOI-V8				
Shock resistance			Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27					
Vibration resistance			Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6					
Electrical data								
			VTOI-A-V8	VTOI-V8				
Max. switching frequency	/	[Hz]	-	4				
Nominal operating voltag		[V DC]	24					
Permissible voltage fluctu		[%]	+/- 10					
Max. electrical power con		[W]	2	1.8				
	1		+					

100

IP30 (when mounted)

[%]

Duty cycle

Degree of protection

#### Datasheet

#### Operating and environmental conditions

Operating medium		Gaseous media			
		Liquid media			
LABS (PWIS) conformity	·	MA24364-B2-L			
Note on the operating/pilot medium		lote resistance of materials in contact with the media			
		Maximum particle size 20 µm			
Storage temperature	[°C]	5 40			
Ambient temperature	[°C]	5 40			
Temperature of medium	[°C]	5 50			
Corrosion resistance class CRC <sup>1)</sup>		0			

1) Corrosion resistance class CRC 0 to Festo standard FN 940070

No corrosion stress. Applies to small, visually unimportant standards-based parts such as threaded pins, circlips and clamping sleeves that are usually only available on the market in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.

#### Materials

Dosing needle material	ligh-alloy stainless steel		
Material number for dosing needle	1.4404		
Note on materials	RoHS-compliant		
Materials in contact with the media	ETFE, FPM, PEI, PPS, high-alloy stainless steel		

#### Datasheet



Туре	B1	B2	D1 Ø	D2 Ø	D3 Ø	D4 Ø	H1	H2	H3	H4	H5	H6
VTOI	9	6.4	7.5	1.6	1.3	3.2	55.3	42.8	23	8.2	29.8	21.2
Туре	L	1	L	2	L	3	L	.4	L	5	L	6
VTOI	8	8	4	4	12	2.5	6	.5	12	2.5	9	9

# NEW

# NEW

## Accessories

Ordering data							
					Part no.	Туре	
Dienonco hood			[MPa]	[Dar]			
Dispense head	2/2-way valve, normally closed	2x individual wire, open end, 2-wire	-0.02 0.065	-0.2 0.65	8114038	VTOI-A-V8-30D3-U14-08-V-S015-1	
I			0 0.1	01	8114037	VTOI-V8-30D3-U14-08-V-S015-1	
		Pressure regulation [MPa]	range [bar]	Part no.	Туре		
Proportional pressure regulator					1	-	
$\frown$	Current type, 4 2	0 mA	0.005 0.1	0.05 1	8046304	VEAB-L-26-D7-Q4-A4-1R1	
			0.0001 0.02	0.001 0.2	8046302	VEAB-L-26-D12-Q4-A4-1R1	
	Voltage type, 0 1	0 V	0.0005 0.1	0.005 1	8046303	VEAB-L-26-D7-Q4-V1-1R1	
			0.0001 0.02	0.001 0.2	8046301	VEAB-L-26-D12-Q4-V1-1R1	
Valve control module	•						
Precision pressure regulator	For up to 8 solenoid	valves			8088772	VAEM-V-S8EPRS2	
	For regulating the o	nerating pressure	_	0.05 0.7	159500	LRP-1/4-0.7	
Pressure sensor							
	For monitoring com	pressed air and non-	corrosive gases		8035542	SPAN-B2R-Q4-PNLK-PNVBA-L1	
Plastic tubing							
	<ul> <li>Colour: blue</li> <li>Material: TPE-U (I</li> <li>Ambient temperative</li> </ul>				197382	PUN-H-3X0.5-BL	
	<ul> <li>Colour: neutral</li> <li>Material: TPE-U (I</li> <li>Ambient temperative</li> </ul>				197375	PUN-H-3X0.5-NT	
	<ul> <li>Colour: neutral</li> <li>Material: PFA</li> <li>Ambient temperation</li> </ul>	ture: −20 150°C			8061167	PFAN-3X0.5-NT	

## Accessories

Ordering data			
	Description	Part no.	Туре
Adapter plate			
	For mounting the dispense and control front module VTOE on the electric slides EGSK-20, EGSK-26, EGSC-25 and EGSC-32	8140775	EHAM-MA-E19-25-C14